






HONEYWELL
PART NUMBER
1EN605-6
FAA - PMA 

REV	DOCUMENT	CHANGED BY	CHECK
6	0010577	KSR 19JAN05	AK



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
 - 3 - CIRCUIT DIAGRAM, FAA-PMA, DATE CODE, FED.MFG. CODE AND CAT. LISTING ARE SHOWN ON NAMEPLATE
 - 4 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
 - 5 - BASIC SWITCHES HAVE SOLID GOLD CONTACT MATERIAL
 - 6 - FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 1EN605 - 6 FOR FAA-PMA

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	TSK	26FEB85	Honeywell					
							CHECK	CEC	27FEB85						
OPERATING FORCE----- 6-12 LB		CONTACT ARRANGEMENT S P D T			NO PLACE X ± 0.040		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		TITLE SWITCH - ENCLOSED						
FULL OVERTRAVEL FORCE-----30 LB MAX		28 VDC			ONE PLACE .X ± 0.030										
RELEASE FORCE----- 4 LB MIN		LOAD	SEA LEVEL		TWO PLACE .XX ± 0.015		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		SIZE B	TYPE I	DRAWING NAME 1EN605 - 6		REV 6		
PRETRAVEL ----- 040 MAX			50,000 FT.		THREE PLACE .XXX ± 0.005										
DIFFERENTIAL TRAVEL-----020 MAX		RES	1	1	FOUR PLACE .XXXX ± 0.0005										
OVERTRAVEL -----.500 MIN		IND	.5	.5	ANGLES ± 2										
		MOTOR			THIRD ANGLE PROJECTION 										
		LAMP													
								RASTER		SCALE 1 : 1		WEIGHT 8.0 OZ MAX		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN605-6](#)