





Wiha Box Wrenches



475 Box Wrenches Metric DIN 838 / ISO 10104



Satin chromed sure grip body. Made from 31CRV3 high performance forged tool steel. Precision formed for an exact fit. 12 point drive.

Item			OAL	OAL	H ¹	H ²	D ¹	D ²		
No.	mm	mm	mm	Inch	mm	mm	mm	mm	lbs.	pkg.
475 01	5.5 x	7.0	165	6.5	5.8	6.3	10.6	12.2	.09	10
475 02	6.0 x	7.0	165	6.5	5.8	6.3	10.6	12.2	.09	10
475 41	7.0 x	8.0	170	6.7	6.0	6.7	12.2	13.5	.12	10
475 03	8.0 x	9.0	180	7.1	6.7	7.3	13.7	15.1	.13	10
475 04	10.0 x	11.0	195	7.6	7.5	8.1	16.4	17.9	.19	10
475 05	12.0 x	13.0	216	8.5	8.4	9.0	19.7	20.9	.26	10
475 06	14.0 x	15.0	238	9.3	9.6	10.1	22.4	25.0	.33	10
475 07	16.0 x	17.0	262	10.3	10.2	10.4	25.4	27.0	.44	10
475 08	18.0 x	19.0	290	11.4	10.8	11.0	27.8	29.7	.55	1
475 09	20.0 x	22.0	320	12.5	11.5	12.2	31.8	34.0	.75	1
475 10	21.0 x	23.0	326	12.8	11.8	12.5	32.4	35.3	.77	1
475 11	24.0 x	26.0	337	13.2	12.8	13.9	37.0	41.0	.92	1
475 12	25.0 x	28.0	346	13.6	13.0	14.2	29.2	43.0	1.1	1
475 13	27.0 x	29.0	346	13.6	13.9	14.6	40.5	45.3	1.1	1
475 14	30.0 x	32.0	360	14.1	13.9	15.5	45.5	49.0	1.3	1
475 15	30.0 x	34.0	380	14.9	14.8	16.5	45.5	51.8	1.3	1
475 16	36.0 x	41.0	440	17.3	18.0	19.5	53.5	60.5	2.5	1
475 17	46.0 x	50.0	500	19.6	21.4	22.4	67.0	73.0	3.6	1

475 Box Wrenches Inch DIN 838 / ISO 10104

Satin chromed sure grip body. Made from 31CRV3 high performance forged tool steel. Precision formed for an exact fit. 12 point drive.

Decision formed for an order for 12 point driver										
Item			OAL	OAL	H ¹	H ²	D ¹	D ²		
No.	Inch	Inch	mm	Inch	mm	mm	mm	mm	lbs.	pkg.
475 18	1/4x5/16		170	6.7	6.0	6.7	12.2	13.5	.12	10
475 19	5/16x3/8		180	7.1	6.7	7.5	13.7	16.4	.14	10
475 20	3/8x7/16		195	7.6	7.5	8.1	16.4	17.9	.19	10
475 21	7/16x1/2		216	8.5	8.4	9.0	18.3	20.9	.24	10
475 22	1/2x9/16		239	9.4	9.0	9.3	20.9	22.3	.32	10
475 23	9/16x5/8		239	9.4	9.3	9.7	22.3	25.0	.32	10
475 24	5/8x11/16		262	10.3	10.2	10.4	25.4	27.0	.42	10
475 25	5/8x3/4		290	11.4	10.2	11.0	25.4	29.7	.51	10
475 26	11/16x3/4		290	11.4	10.8	11.0	27.8	29.7	.58	1
475 27	3/4x25/32		290	11.4	11.0	11.4	29.7	31.8	.57	1
475 28	3/4x7/8		320	12.5	11.0	12.2	29.7	34.0	.67	1
475 29	13/16x7/8		320	12.5	11.5	12.2	31.8	34.0	.69	1
475 30	7/8x15/16		326	12.8	12.2	12.8	34.0	37.0	.77	1
475 31	15/16x1		337	13.2	12.8	13.9	37.0	41.0	.98	1
475 32	1x1-1/8		346	13.6	13.0	14.2	39.2	43.0	1.1	1
475 33	1-1/16x1-1/4		358	14.0	13.9	15.5	42.0	49.0	1.3	1
475 34	1-1/8x1-5/16		360	14.1	14.6	15.5	45.5	50.0	1.2	1
475 35	1-3/16x1-5/16		360	14.1	14.6	15.5	45.5	50.0	1.3	1
475 36	1-1/4x1-3/8		412	16.2	17.0	18.2	48.2	53.5	1.8	1
475 37	1-5/16x1-1/2		412	16.2	17.0	18.2	48.2	53.5	1.8	1
475 38	1-7/16x1-5/8		440	17.3	18.0	19.5	53.5	60.5	2.3	1
475 39	1-11/16x1-7/8		476	18.7	19.7	21.4	63.0	70.0	2.8	1
475 40	1-13/16x2		500	19.6	21.4	22.4	67.0	73.0	3.4	1



475 90 Set 10 Piece Metric Box Wrenches

Item No.	mm x mm	OAL mm	mm x mm	OAL mm
475 90	475 01 5.5 x 7.0	165	475 06 14.0 x 15.0	238
475 02	6.0 x 7.0	165	475 07 16.0 x 17.0	262
475 03	8.0 x 9.0	180	475 08 18.0 x 19.0	290
475 04	10.0 x 11.0	195	475 09 20.0 x 22.0	320
475 05	12.0 x 13.0	216	475 10 21.0 x 23.0	326

475 91 Set 8 Piece Inch Box Wrenches

Item No.	Inch x Inch	OAL mm	mm x mm	OAL mm
475 91	475 18 1/4 x 5/16	170	475 25 5/8 x 3/4	290
475 20	3/8 x 7/16	195	475 26 11/16 x 3/4	290
475 21	7/16 x 1/2	216	475 29 13/16 x 7/8	320
475 22	1/2 x 9/16	239		
475 23	9/16 x 5/8	239		