



General ordering data

Order No.	1609981044
Part designation	TM-I 15 BLANK RT
Version	Conductor markers, L x W: 15 x 4 mm, Polyamide 66, white
EAN	4008190914783
Qty.	400 pc(s).

Markings

Cadmium	no
Can be labelled with thermal transfer printers	No
Can be printed with plotter	Yes
Can be written with dot-matrix printer	No
Can be written with laser printer	No
Conductor O.D., max.	40 mm
Conductor O.D., min.	1 mm
Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	0.22 mm ²
Function	Conductor and cable markers
Halogen	no
Height	2 mm
Insulation cross-section, max.	40 mm
Length	15 mm
Material	Polyamide 66
Material colour	white
Material colour according to resistance code	9
Max. temperature, continuous	100 °C
Min. temperature, continuous	-40 °C
Pin can be written (STI)	Yes
PrintJet	Yes
Printed characters	without
Silicone	no
Speed marking laser	Yes
Type of printing	Neutral
UL 94 flammability class	V2

Markings

Width 4 mm

Approvals

Approvals institutes n.a.

Classifications

eClass 4.1	24-19-02-19
eClass 5.0	27-14-91-03
eClass 5.1	27-14-91-03

Similar products

Order No.	Part designation	Version
1609981693	TM-I 15 NEUTRAL	Conductor markers, L x W: 15 x 4 mm, Polyamide 66, Blue
1609981687	TM-I 15 BLANK BL	Conductor markers, L x W: 15 x 4 mm, Polyamide 66, yellow
1609981688	TM-I 15 BLANK GE	Conductor markers, L x W: 15 x 4 mm, Polyamide 66, green
1609981686	TM-I 15 BLANK GN	Conductor markers, L x W: 15 x 4 mm, Polyamide 66, red