

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [30700-1060](#)
Status: **Active**
Overview: H-DAC 64™ Dual-Row High Density Automotive Connectors
Description: 2.54mm Pitch, 0.64mm Width H-DAC 64™ High Density Automotive Connectors, Dual Row, Female Harness Assembly, 6 Circuits, Polarization Option 1, Gray

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-30700-0001 \(PDF\)](#)
[Product Specification PS-30968-0001 \(PDF\)](#)
[Application Specification AS-30700-000 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Crimp Housings
Series 30700
Application Power, Wire-to-Wire
Comments Polarization Option 1
Overview H-DAC 64™ Dual-Row High Density Automotive Connectors
Product Name H-DAC 64™
UPC 800754879613

Physical
Circuits (maximum) 6
Color - Resin Gray
Gender Female
Glow-Wire Compliant No
Lock to Mating Part Yes
Material - Resin Modified Polystyrene
Net Weight 2.733/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical
Current - Maximum per Contact 7A

Material Info

Reference - Drawing Numbers
Application Specification AS-30700-000
Product Specification PS-30700-0001, PS-30968-0001
Sales Drawing SD-30700-120



EU RoHS
ELV and RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
30700Series

Mates With
30700 Header, 30968 Crimp Housing

Use With
34230 Terminal