




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.





L17D TZK 09K XX T



Cable strain relief




L17D TZK 09K XX T




1

Thumb screw



Full metal

Screw thread



2

Screw

| Part Number       | A                | B                | Part Number    |
|-------------------|------------------|------------------|----------------|
| L17D TZK 09K FM T | 31<br>(1.220")   | 38.3<br>(1.508") | L17D TZK 09K T |
| L17D TZK 15K FM T | 39.5<br>(1.555") | 40.5<br>(1.594") | L17D TZK 15K T |
| L17D TZK 25K FM T | 53.4<br>(2.102") | 48.2<br>(1.897") | L17D TZK 25K T |
| L17D TZK 37K FM T | 70<br>(2.755")   | 52.2<br>(2.055") | L17D TZK 37K T |

Customer drawing

## REVISIONS

| SYM | ECN | DESCRIPTION | DATE     | APPROVED |
|-----|-----|-------------|----------|----------|
| 1   |     |             | 06/06/08 |          |

## D-SUB TECHNICAL DATA

Material and finish:

Shell: die-cast, nickel plated

Thumb screws: with metal knob, nickel plated

Screws: Steel, blue chromate plating, Philips head

Cable strain relief: Plastic UL94 V-0

Temperature range: -40°C to 120°C

Cable diameter: 4.0-13.0mm

Attenuation factor: >40 dB between 30 MHz and 1 GHz

## PRODUCT CODE

L 17DTZK XX K XX T

RoHS Compliance

Series 17DTZK:180°

Position: 9,15,25,37

Bulk Package

T: with threaded backshell, not self-tapering type

FM: Full steel metal screwlock  
Blank: plastic knob on screwlock


| UNLESS OTHERWISE SPECIFIED TOLERANCES |        | APPROVAL            | DATE     |
|---------------------------------------|--------|---------------------|----------|
| U.S.                                  | METRIC | DRAWN Sunny Li      | 06/06/08 |
| .X +/-                                | 0.50   | CHECKED Hk.wang     | 06/06/08 |
| .XX +/-                               | 0.30   | CHECKED             |          |
| .XXX +/-                              | 0.20   |                     |          |
| FRACTIONS +/-                         | 2'     |                     |          |
| ANGLES +/-                            |        |                     |          |
| FOR MATERIALS AND FINISHES SEE NOTES  |        | DRAWING FILE :      |          |
| REMOVE SHARP EDGES                    |        | ANGLE OF PROJECTION |          |
| DIMENSIONS                            |        | U.S. INCHES         |          |
| METRIC MM                             |        | NONE                |          |

Amphenol®




TITLE  
Metal Hood DTZK series

| SIZE  | DRAWING NO.         | REV.         |
|-------|---------------------|--------------|
| A4    | C L17D TZK XXX XX T | 1            |
| SCALE | NONE                | SHEET 1 OF 4 |


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.




L17D TZK 15K XX T




L17D TZK 15K XX T




Cable strain relief



Thumb screw



Screw thread



Screw

| Part Number       | A                | B                | Part Number    |
|-------------------|------------------|------------------|----------------|
| L17D TZK 09K FM T | 31<br>(1.220")   | 38.3<br>(1.508") | L17D TZK 09K T |
| L17D TZK 15K FM T | 39.5<br>(1.555") | 40.5<br>(1.594") | L17D TZK 15K T |
| L17D TZK 25K FM T | 53.4<br>(2.102") | 48.2<br>(1.897") | L17D TZK 25K T |
| L17D TZK 37K FM T | 70<br>(2.755")   | 52.2<br>(2.055") | L17D TZK 37K T |

Customer drawing

| REVISIONS |     |             |          |          |
|-----------|-----|-------------|----------|----------|
| SYM       | ECN | DESCRIPTION | DATE     | APPROVED |
| 1         |     |             | 06/06/08 |          |

D-SUB TECHNICAL DATA

Material and finish:  
Shell: die-cast, nickel plated  
Thumb screws: with metal knob, nickel plated  
Screws: Steel, blue chromate plating, Philips head  
Cable strain relief: Plastic UL94 V-0  
Temperature range: -40°C to 120°C  
Cable diameter: 4.0-13.0mm  
Attenuation factor: >40 dB between 30 MHz and 1 GHz

PRODUCT CODE

L 17DTZK XX K XX T

RoHS Compliance

Series 17DTZK:180°

Position:9,15,25,37

Bulk Package

T: with threaded backshell, not self-tapering type

FM: Full steel metal screwlock  
Blank: plastic knob on screwlock


| UNLESS OTHERWISE SPECIFIED TOLERANCES |        | APPROVAL            |         | DATE     |
|---------------------------------------|--------|---------------------|---------|----------|
| U.S.                                  | METRIC | DRAWN               | Checked | 06/06/08 |
| .X +/-                                | 0.50   | Sunny Li            | Wk.wang | 06/06/08 |
| .XX +/-                               | 0.30   | CHECKED             | CHECKED |          |
| .XXX +/-                              | 0.20   |                     |         |          |
| FRACTIONS +/-                         | 2'     |                     |         |          |
| ANGLES +/-                            |        |                     |         |          |
| FOR MATERIALS AND FINISHES SEE NOTES  |        | DRAWING FILE :      |         |          |
| REMOVE SHARP EDGES                    |        | ANGLE OF PROJECTION |         |          |
| DIMENSIONS                            |        |                     |         |          |
| U.S.                                  | INCHES |                     |         |          |
| METRIC                                | MM     |                     |         |          |

Amphenol®




TITLE  
Metal Hood DTZK series

| SIZE  | DRAWING NO.         | REV. |
|-------|---------------------|------|
| A4    | C L17D TZK XXX XX T | 1    |
| SCALE | SHEET 2 OF 4        |      |
| NONE  |                     |      |


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



L17D TZK 25K XX T



L17D TZK 25K XX T



Thumb screw

Screw

Customer drawing

| Part Number       | A                | B                | Part Number    |
|-------------------|------------------|------------------|----------------|
| L17D TZK 09K FM T | 31<br>(1.220")   | 38.3<br>(1.508") | L17D TZK 09K T |
| L17D TZK 15K FM T | 39.5<br>(1.555") | 40.5<br>(1.594") | L17D TZK 15K T |
| L17D TZK 25K FM T | 53.4<br>(2.102") | 48.2<br>(1.897") | L17D TZK 25K T |
| L17D TZK 37K FM T | 70<br>(2.755")   | 52.2<br>(2.055") | L17D TZK 37K T |

| REVISIONS |     |             |          |          |
|-----------|-----|-------------|----------|----------|
| SYM       | ECN | DESCRIPTION | DATE     | APPROVED |
| 1         |     |             | 06/06/08 |          |

D-SUB TECHNICAL DATA

Material and finish:  
Shell: die-cast, nickel plated  
Thumb screws: with metal knob, nickel plated  
Screws: Steel, blue chromate plating, Philips head  
Cable strain relief: Plastic UL94 V-0  
Temperature range: -40°C to 120°C  
Cable diameter: 4.0-13.0mm  
Attenuation factor: >40 dB between 30 MHz and 1 GHz

PRODUCT CODE

L 17DTZK XX K XX T

RoHS Compliance

Series 17DTZK:180°

Position: 9,15,25,37

Bulk Package

T: with threaded backshell, not self-tapering type

FM: Full steel metal screwlock  
Blank: plastic knob on screwlock

| UNLESS OTHERWISE SPECIFIED TOLERANCES |        | APPROVAL            |          | DATE |
|---------------------------------------|--------|---------------------|----------|------|
| U.S.                                  | METRIC | DRAWN               | Checked  |      |
| .X +/-                                | 0.50   | Sunny Li            | 06/06/08 |      |
| .XX +/-                               | 0.30   | Wk.wang             | 06/06/08 |      |
| .XXX +/-                              | 0.20   |                     |          |      |
| FRACTIONS +/-                         |        |                     |          |      |
| ANGLES +/-                            | 2°     |                     |          |      |
| FOR MATERIALS AND FINISHES SEE NOTES  |        | DRAWING FILE :      |          |      |
| REMOVE SHARP EDGES                    |        | ANGLE OF PROJECTION |          |      |
| DIMENSIONS                            |        |                     |          |      |
| U.S.                                  | INCHES |                     |          |      |
| METRIC                                | MM     |                     |          |      |

Amphenol®

TITLE  
Metal Hood DTZK series

SIZE  
A4


DRAWING NO.  
C L17D TZK XXX XX T

REV.  
1


SCALE  
NONE

SHEET 3 OF 4


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.




L17D TZK 37K XX T



Cable strain relief




Threaded hole




Threaded hole

L17D TZK 37K XX T




Plastic knob

1



Full metal

Screw thread



2

Screw

Customer drawing

| Part Number       | A                | B                | Part Number    |
|-------------------|------------------|------------------|----------------|
| L17D TZK 09K FM T | 31<br>(1.220")   | 38.3<br>(1.508") | L17D TZK 09K T |
| L17D TZK 15K FM T | 39.5<br>(1.555") | 40.5<br>(1.594") | L17D TZK 15K T |
| L17D TZK 25K FM T | 53.4<br>(2.102") | 48.2<br>(1.897") | L17D TZK 25K T |
| L17D TZK 37K FM T | 70<br>(2.755")   | 52.2<br>(2.055") | L17D TZK 37K T |

## REVISIONS

| SYM | ECN | DESCRIPTION | DATE     | APPROVED |
|-----|-----|-------------|----------|----------|
| 1   |     |             | 06/06/08 |          |

## D-SUB TECHNICAL DATA

Material and finish:

Shell: die-cast, nickel plated

Thumb screws: with metal knob, nickel plated

Screws: Steel, blue chromate plating, Philips head

Cable strain relief: Plastic UL94 V-0

Temperature range: -40°C to 120°C

Cable diameter: 4.0-13.0mm

Attenuation factor: >40 dB between 30 MHz and 1 GHz

## PRODUCT CODE

L 17DTZK XX K XX T

RoHS Compliance

Series 17DTZK:180°

Position:9,15,25,37

Bulk Package

T: with threaded backshell, not self-tapering type

FM: Full steel metal screwlock  
Blank: plastic knob on screwlock

| UNLESS OTHERWISE SPECIFIED TOLERANCES |        | APPROVAL            | DATE     |
|---------------------------------------|--------|---------------------|----------|
| U.S.                                  | METRIC | DRAWN Sunny Li      | 06/06/08 |
| .X +/-                                | 0.50   | CHECKED Hk.wang     | 06/06/08 |
| .XX +/-                               | 0.30   | CHECKED             |          |
| .XXX +/-                              | 0.20   |                     |          |
| FRACTIONS +/-                         |        |                     |          |
| ANGLES +/-                            | 2°     |                     |          |
| FOR MATERIALS AND FINISHES SEE NOTES  |        | DRAWING FILE :      |          |
| REMOVE SHARP EDGES                    |        | ANGLE OF PROJECTION |          |
| DIMENSIONS                            |        |                     |          |
| U.S.                                  | INCHES |                     |          |
| METRIC                                | MM     |                     |          |

Amphenol®

TITLE  
Metal Hood DTZK series

| SIZE  | DRAWING NO.         | REV.         |
|-------|---------------------|--------------|
| A4    | C L17D TZK XXK XX T | 1            |
| SCALE | NONE                | SHEET 4 OF 4 |