

Series AM1S-Z

1 Watt | DC-DC Converter



FEATURES:

- RoHS compliant
- 4 Pin SIP Package
- Low ripple and noise
- High efficiency up to 83%
- Operating temperature -40°C to + 85°C
- Input / Output isolation 1000 and 3000VDC
- Pin compatible with multiple manufacturers

Models Single output



Model	Input Voltage (V)	Output Voltage (V)	Output Current max (mA)	Isolation (VDC)	Max Capacitive Load (μF)	Input Current Full Load No Load (mA)		Efficiency (%)
AM1S-0303SZ	2.97-3.63	3.3	303	1000	220	421	25	72
AM1S-0305SZ	2.97-3.63	5	200	1000	220	394	25	77
AM1S-0307SZ	2.97-3.63	7.2	138.9	1000	220	384	25	79
AM1S-0309SZ	2.97-3.63	9	111.1	1000	220	404	30	75
AM1S-0312SZ	2.97-3.63	12	100	1000	220	473	45	77
AM1S-0315SZ	2.97-3.63	15	66.6	1000	220	384	35	79
AM1S-0318SZ	2.97-3.63	18	55.5	1000	220	399	35	76
AM1S-0324SZ	2.97-3.63	24	50	1000	220	461	53	79
AM1S-0503SZ	4.5-5.5	3.3	303	1000	220	257	20	78
AM1S-0505SZ	4.5-5.5	5	200	1000	220	247	25	81
AM1S-0507SZ	4.5-5.5	7.2	138.9	1000	220	241	16	83
AM1S-0509SZ	4.5-5.5	9	111.1	1000	220	250	26	80
AM1S-0512SZ	4.5-5.5	12	100	1000	220	300	25	80
AM1S-0515SZ	4.5-5.5	15	66.6	1000	220	244	35	82
AM1S-0518SZ	4.5-5.5	18	55.5	1000	220	247	25	81
AM1S-0524SZ	4.5-5.5	24	50	1000	220	289	35	83
AM1S-1203SZ	10.8-13.2	3.3	303	1000	220	107	15	78
AM1S-1205SZ	10.8-13.2	5	200	1000	220	105	16	79
AM1S-1207SZ	10.8-13.2	7.2	138.9	1000	220	100	16	83
AM1S-1209SZ	10.8-13.2	9	111.1	1000	220	107	15	78
AM1S-1212SZ	10.8-13.2	12	100	1000	220	125	20	80
AM1S-1215SZ	10.8-13.2	15	66.6	1000	220	105	15	79
AM1S-1218SZ	10.8-13.2	18	55.5	1000	220	104	20	80
AM1S-1224SZ	10.8-13.2	24	50	1000	220	123	25	71
AM1S-2403SZ	21.6-26.4	3.3	303	1000	220	54	8	77
AM1S-2405SZ	21.6-26.4	5	200	1000	220	52	8	80
AM1S-2407SZ	21.6-26.4	7.2	138.9	1000	220	54	10	77
AM1S-2409SZ	21.6-26.4	9	111.1	1000	220	54	7	77
AM1S-2412SZ	21.6-26.4	12	100	1000	220	62	8	80
AM1S-2415SZ	21.6-26.4	15	66.6	1000	220	51	8	81
AM1S-2418SZ	21.6-26.4	18	55.5	1000	220	52	8	80
AM1S-2424SZ	21.6-26.4	24	50	1000	220	60	9	83
AM1S-0303SH30Z	2.97-3.63	3.3	303	3000	220	421	25	72
AM1S-0305SH30Z	2.97-3.63	5	200	3000	220	394	25	77
AM1S-0307SH30Z	2.97-3.63	7.2	138.9	3000	220	384	25	79
AM1S-0309SH30Z	2.97-3.63	9	111.1	3000	220	404	30	75
AM1S-0312SH30Z	2.97-3.63	12	100	3000	220	473	45	77
AM1S-0315SH30Z	2.97-3.63	15	66.6	3000	220	384	35	79
AM1S-0318SH30Z	2.97-3.63	18	55.5	3000	220	399	35	76
AM1S-0324SH30Z	2.97-3.63	24	50	3000	220	461	53	79
AM1S-0503SH30Z	4.5-5.5	3.3	303	3000	220	257	20	78
AM1S-0505SH30Z	4.5-5.5	5	200	3000	220	247	25	81
AM1S-0507SH30Z	4.5-5.5	7.2	138.9	3000	220	241	16	83
AM1S-0509SH30Z	4.5-5.5	9	111.1	3000	220	250	26	80
AM1S-0512SH30Z	4.5-5.5	12	100	3000	220	300	25	80
AM1S-0515SH30Z	4.5-5.5	15	66.6	3000	220	244	35	82
AM1S-0518SH30Z	4.5-5.5	18	55.5	3000	220	247	25	81
AM1S-0524SH30Z	4.5-5.5	24	50	3000	220	289	35	83
AM1S-1203SH30Z	10.8-13.2	3.3	303	3000	220	107	15	78
AM1S-1205SH30Z	10.8-13.2	5	200	3000	220	105	16	79

AM1S-1207SH30Z	10.8-13.2	7.2	138.9	3000	220	100	16	83
AM1S-1209SH30Z	10.8-13.2	9	111.1	3000	220	107	15	78
AM1S-1212SH30Z	10.8-13.2	12	100	3000	220	125	20	80
AM1S-1215SH30Z	10.8-13.2	15	66.6	3000	220	105	15	79
AM1S-1218SH30Z	10.8-13.2	18	55.5	3000	220	104	20	80
AM1S-1224SH30Z	10.8-13.2	24	50	3000	220	123	25	71
AM1S-2403SH30Z	21.6-26.4	3.3	303	3000	220	54	8	77
AM1S-2405SH30Z	21.6-26.4	5	200	3000	220	52	8	80
AM1S-2407SH30Z	21.6-26.4	7.2	138.9	3000	220	54	10	77
AM1S-2409SH30Z	21.6-26.4	9	111.1	3000	220	54	7	77
AM1S-2412SH30Z	21.6-26.4	12	100	3000	220	62	8	80
AM1S-2415SH30Z	21.6-26.4	15	66.6	3000	220	51	8	81
AM1S-2418SH30Z	21.6-26.4	18	55.5	3000	220	52	8	80
AM1S-2424SH30Z	21.6-26.4	24	50	3000	220	60	9	83

Input Specifications

Parameters	Nominal	Typical	Maximum	Units
Voltage range	3.3 5 12 24	2.97-3.63 4.5-5.5 10.8-13.2 21.6-26.4		VDC
Filter	Capacitor			
Absolute Maximum Rating	3.3 Vin 5 Vin 12 Vin 24 Vin	0-6 0-7 0-15 0-28		VDC
Peak Input Voltage time		100		ms
Input reflected ripple current *		20		mA p-p

* Measured with a 12μH source inductor and a 47μF (ESR<1Ω at 100KHz) source capacitor.

Isolation Specifications

Parameters	Conditions	Typical	Rated	Units
Tested I/O voltage	60sec		1000, 3000	VDC
Resistance		> 1000		MOhm
Capacitance		60		pF

Output Specifications

Parameters	Conditions	Typical	Maximum	Units
Voltage accuracy			±3	%
Line voltage regulation	For 1% change of Vin		±1.2	% of Vin
Load voltage regulation	Load 20 – 100%		±10	%
	3.3V output models, Load 20 – 100%		±20	%
Temperature coefficient		±0.02		%/°C
Ripple & Noise	At 20MHz Bandwidth		100	mV p-p
Capacitive load			220	μF

General Specifications

Parameters	Conditions	Typical	Maximum	Units
Switching frequency	100% load , Variable	80		KHz
Operating temperature	Full Load without Derating	-40 to +85		°C
Storage temperature		-40 to +125		°C
Max Case temperature			100	°C
Cooling	Free air convection			
Humidity			95	%
Case material	Non-conductive black plastic UL94-VO			
Weight		1.5		g
Dimensions (L x W x H)	0.46 x 0.24 x 0.40 inches 11.68 x 6.00 x 10.15 mm			
MTBF	>1 121 000 hrs(MIL-HDBK -217F, Ground Benign, t=+25°C)			

NOTE: All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.


Safety Specifications

Standards	
Agency approvals	CE
Safety	EN55032 (Radiated Emissions) class B
	IEC61000-4-2(ESD) Criteria A
	IEC61000-4-3(Radiated immunity) Criteria A
	IEC61000-4-4(EFT) Criteria A, with the recommended EFT/Surge external circuit
	IEC61000-4-5(Surge) Criteria A, with the recommended EFT/Surge external circuit
	IEC61000-4-6(CS) Criteria A
	IEC61000-4-8(PFMF) Criteria A


Pin Out Specifications

Pin	Single
1	- V Input
2	+V Input
3	- V Output
4	+V Output

Dimensions




Input Reflected Ripple Test Circuit



* Tested at full load, and nominal input

EMI Filtering


To meet conducted emissions, the following circuit is recommended with the external components as noted in the table below.





Model	C1	L1	C2	C3
5Vin	2.2 μ F / 100V	18 μ H		
12 Vin	2.2 μ F / 100V	18 μ H		
24 Vin	2.2 μ F / 100V	18 μ H	2.2 μ F / 100V	470pF / 2KV


Additionally, in order to meet IEC 61000-4-4 and 61000-4-5 and external capacitor is recommended (ex. Nippon KY series of size 470 μ F / 100V).

EFT/Surge Application circuit



Typical Efficiency Chart Examples





NOTE: **1.** Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. **2.** Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. **3.** Mechanical drawings and specifications are for reference only. **4.** All specifications are measured at an ambient temperature of 25°C, humidity < 75%, nominal input voltage and at rated output load unless otherwise specified. **5.** Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. **6.** This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other than the ones listed in this datasheet. **7.** Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.