



Heyco® Snap-In Universal Strain Relief Bushings

Fit 1/2" Electrical Knock-out Hole

- **USR 400 fits the widest range of cable sizes.**
- **USR 401 fits the widest range of Romex® and other flat cable sizes.**
- **Captive screw forces the locking flap against the cable.**
- **Captive screw meets typical European requirements wherein the Strain Relief device must remain attached to the panel during cable removal or replacement.**
- **Nylon USR 400 & 401 comply with:**
 - IEC Publication #335
 - CEE #10 and # 11
- **Easy installation: fingertip pressure locks bushing into .875" (22,2 mm) diameter holes with panel thickness up to .125" (3,2 mm).**
- **Reinforcing ribs for extra strength.**
- **Bell mouth contour, radiused at 1.5x the exit hole diameter, eliminates the need for a separate cord guard.**
- **Protect cables against forces of pull, push, twist, and flex.**
- **For Heyco-Tite Liquid Tight Romex® Connectors, see page 4-35.**

Cross Section	WILL FIT THESE CABLES		PANEL DIMENSIONS						PART NO.	DESCRIPTION	SCREW TYPE
	Approximate Size		A	Mounting Hole Dia.	B	To Prevent Rotation	Panel Thickness				
	in.	mm.	in.	mm.	in.	mm.	in.	mm.			
Round or Flat	up to .360	up to 9,1	.875	22,2	.770	19,6	.062	1,6	1724	USR-400	nylon
							.125	3,2	1730	USR-40	steel

Standard color black. Consult Heyco for white and other colors.


Heyco® Snap-In Romex® Strain Relief Bushing*

Fit 1/2" Electrical Knock-out Hole

Romex Type	WILL FIT THESE CABLES		PANEL DIMENSIONS						PART NO.	DESCRIPTION	SCREW TYPE	
	AWG/Conds	Approximate Size	A	Mounting Hole Dia.	B	To Prevent Rotation	Panel Thickness					
			in.	mm.	in.	mm.	in.	mm.				
NM-B	14/2, 14/3, 12/2, 12/3, 10/2	up to .250 x .400	up to 6,4 x 10,2	.875	22,2	.770	19,6	.062	1,6	1726	USR-401	nylon

Standard color black. Consult Heyco for white and other colors.

*For Romex® and other flat cables.



1726

Quick Specs

Material
Certifications

Nylon 6/6

Recognized File E15331 for round and flat SPT type cables

Listed under Underwriters' Laboratories File E103540

Certified by the Canadian Standards Association File 81067

Flammability Rating
Temperature Range

94V-2

-04°F (-18°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

1726 1724 1730