



NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER PER QQ-C-533. GOLD PLATED PER MIL-G-45204 B TYPE 1 0.00001" [0.000254] THICK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.

2. PERFORMANCE:
MAXIMUM CURRENT: 5.9 AMPS WITH A 77° TEMPERATURE RISE.
MAXIMUM VOLTAGE: 5.4 KV
MAXIMUM TEMPERATURE: 200°F (93°C)
3. FEATURES:
HOOK FITS COMPONENTS UP TO 0.040" [1.01].
FIELD SERVICEABLE.



ACTUAL SIZE

		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		E-Z-HOOK[®] DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A. DESCRIPTION E-Z-MINI-HOOK TEST CONNECTOR			
			APPROVALS	DATE				
			DRAWN	R.L. 6/09				
			APPROVED BY					
		FINISH		SIZE	CODE IDENT NO.	DRAWING NO.	REV.	
		SEE NOTE.						
NEXT ASSY	USED ON				B	08505	X100W	
APPLICATION		DO NOT SCALE DRAWING			SCALE	2:1		SHEET 1 OF 1