



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SR2POSTAA

TAA Compliant 45U 2-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment



Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 45U 2-post open frame rack
- Black aluminum with round threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Description

SmartRack 2 post open frame racks are ideal for space constrained or cost conscious 19-inch rack mount applications. Multiple units can be bolted together side by side.

Features

- Supports 800lbs of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

PHYSICAL	
Shipping Dimensions (HWD/in)	7 X 3 X 85
Shipping Dimensions (HWD/cm)	17.78 x 7.62 x 215.9
Shipping weight (lbs)	29
Shipping weight (kg)	13.15
Unit Dimensions (in.)	84 x 20.3 x 4.75 (14" total depth with support base)
Unit Dimensions (cm)	213.36 x 51.56 x 12.07
Style	2-Post

WARRANTY**Product Warranty Period
(Worldwide)**

5-year limited warranty

Related Items**Optional Products**

Related Model	Description	Qty.
B019-000	KVM Switch Accessories - 2-Post Rackmount Bracket for B020,B021, B040, and B070 Consoles and KVM Consoles	1
B020-U08-19-IP	Console KVM Switch - 8-Port NetDirector 1U Rackmount Console IP KVM Switch w/17" LCD	1
B021-000-17	Rackmount Console - 1U Rackmount Console with 17" LCD	1
B021-000-19	Rackmount Console - 1U Rackmount Console with 19" LCD	1
B021-000-19-SH	Rackmount Console - 1U Short-Depth Rackmount Console with 19" LCD	1
B040-008-19	NetController 19" VGA Console KVM Switch - 8 Port	1
B040-016-19	NetController 19" VGA Console KVM Switch - 16 Port	1
N252-012	12-Port Cat6 Patch Panel 568B	1
N252-024	24-Port Cat6 Patch Panel 568B	1
N252-048	48-Port Cat6 Patch Panel 568B	1
SRBOLTDOWN	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	1
SRCABLEDUCTVRT	6-ft. (1.8 m) Vertical Cable Manager (Double finger duct with cover; toolless mounting.)	1
SRCABLEDUCT1U	1U Horizontal Cable Manager (Finger duct with cover.)	1
SRCABLELADDER	10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder (Includes 2 sections; requires SRCABLETRAY.)	1
SRCABLERINGVRT	6-ft. (1.8 m) Vertical Cable Manager (Flexible ring type; toolless mounting.)	1
SRCABLERING1U	1U Horizontal Cable Manager (Flexible ring type.)	1
SRCABLERING2U	2U Horizontal Cable Manager (Flexible ring type.)	1
SRFAN3U	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	1
SRSCREWS	Threaded hole hardware kit - 50 each #12-24 screws	1
SRSHELF2P	2U Cantilever Fixed Shelf (60 lb / 27 kg capacity; 18-in. / 457 mm depth.)	1
SRXFAN3U	3U Fan Panel, 230V (3 high-performance fans; 210 CFM; C14 inlet.)	1
UPSHDEARKIT	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb / 29 kg from front vertical rails in 4-post or 2-post racks and enclosures.)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4412.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.