

PLCC Sockets — Low Profile, Surface Mount (Continued)

Rectangular Socket —
32 Positions

Materials and Finish

Housing — Polyphenylene sulfide,
40% glass filled, UL 94V-0 rated

Contacts — Phosphor bronze with
.000200 [0.00508] 93/7 tin-lead per
MIL T 10727 Type I over .000050
[0.00127] nickel per
QQ-N-290



Packaging Quantities

28 Pcs./Tube*, 70 Tubes/Box

Total = 1960 Pcs./Box

Tape Mounted = 400/Reel*

*Minimum order quantity

Extraction Tool
Part No. 821980-1All Purpose Tool
Part No. 822154-1

Recommended Chip Carrier

No. of Pos.	Dimension E	Description	Low Insertion Force		
			Without Locating Posts	With Locating Posts	Tape Mounted Without Locating Posts
32	.564 14.44	Long Side (9 Contacts)	822273-1	822274-1	3-822273-1
	.464 11.79	Short Side (7 Contacts)			

No. of Pos.	Dimension E	Description	Ultra Low Profile Socket		
			Without Locating Posts	With Locating Posts	Tape Mounted Without Locating Posts
32	.565 14.35	Long Side (9 Contacts)	822403-1	822406-1	3-822403-1
	.465 11.81	Short Side (7 Contacts)			