



Super Bond™ Film Tape

396

Technical Data

September, 2012

Product Description	3M™ Super Bond™ Film Tape 396 is a polyester film tape for adhering to polyesters, polyethylenes and many other difficult-to-adhere-to surfaces.				
----------------------------	--	--	--	--	--

Product Construction	Backing	Adhesive	Color	Standard Roll Length	Standard Widths
	Polyester	Rubber-resin	Transparent	36 yds. (33 m)	3/4 in. (19 mm) 1 in. (25 mm) 2 in. (50 mm) 3 in. (75 mm) 4 in. (100 mm)

Typical Physical Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.	ASTM Test Method
Adhesion to Steel:	170 oz./in. width (190 N/100 mm)	D-3330
Tensile Strength at Break:	25 lbs./in. width (440 N/100 mm)	D-3759
Elongation at Break:	18%	D-3759
Backing Thickness:	1.7 mils (0.04 mm)	D-3652
Total Tape Thickness:	4.1 mils (0.10 mm)	D-3652

Features	<ul style="list-style-type: none">Polyester backing for abrasion, chemical and thermal resistance.Aggressive adhesion that adheres to many difficult-to-stick-to surfaces.Immediate adhesion for easy application.Adhesive thickness allows adhesion to many irregular surfaces.
-----------------	---

Application Ideas	<ul style="list-style-type: none">Splicing, sealing, repairing, holding and reinforcing a variety of difficult-to-hold materials.Splicing, reinforcing and repairing material.End-tabling material.Splicing manila board during die-cutting.Repairing and reinforcing high-wear areas of rip-stop nylon.Holding polyethylene barrel liners in place.Splicing large photographic acetate transparencies.Splicing polyester conveyor belts
--------------------------	---

3M™ Super Bond™ Film Tape

396

Storage Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 50% R.H. in the original carton.

Shelf Life To obtain best performance, use this product within 18 months from date of manufacture.

Technical Information The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06

St. Paul, MN 55144-1000

800-362-3550 • 877-369-2923 (Fax)

www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.

Printed in U.S.A.

©3M 2012 70070325942 (9/12)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M](#):

[396-3/4"x36yd](#) [396-1"x36yd](#) [396-2"x36yd](#)