



Sample photo

Order symbol: AL 165609
Product nbr: 7011330
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004215
El. number:
Finland: 3423629
Denmark: 8212004760
Italy: 7321080
Sweden: 2536331

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

Dimensions:			Length	Width	Height	Rating:
mm:	560	160	90			Ingress Protection (EN 60529): IP 66/67
inch:	22.0	6.3	3.5			Impact Resistance (EN 62262): IK 08
Materials:						NEMA Class: NEMA 1, 4, 4X, 12, 13
Material:	Aluminium					Certificates: Underwriters Laboratories Fimko UL Canada Gost R
Base colour:	RAL 7001					
Cover colour:	RAL 7001					
Cover screws material:	Stainless steel					
Gasket material:	Neoprene					
Temperatures:						
Short term:	-50 ... 140 °C					
Continuous:	-50 ... 80 °C					
Short term:	-60 ... 285 °F					
Continuous:	-60 ... 175 °F					
Accessories:						
AM 1656	Mounting plate					
ARH 1656	DIN-35 Mounting rail					
MRS 28541	Wall fastening lug (2 pcs)					
PH A & AH A/B	Hinge set					

FIBOX Aluminium AL 165609

