



Saws - Jigsaws

DW331K



DW331K Features

- Powerful 701 Watt motor with variable speed delivers fast cutting action up to 3100 strokes per minute
- Quick and easy patented keyless blade change system accepts T- shank blades
- Patented anti-vibration counterbalance mechanism and rubber grip provide smooth operation
- 4-position pendulum action controls the aggressiveness or smoothness of cuts
- Tool free adjustable shoe with anti scratch cover bevels to 45 degrees in both directions
- Full wave electronic speed control with feedback ensures that blade speed is maintained under any load for a consistent finish across all materials
- Soft start ensures accuracy at cut start
- Tapered saw blade roller to control blade deflection at maximum depth of cut
- Switchable dust blower keeps line of cut clear of chips
- Modular component design for trouble free servicing
- Compatible with DeWALT flush cutting blade DT2074, for cutting flush to an edge

DW331K Specifications

Power Input	701 Watts
Power Output	445 Watts
No Load Stroke Rate	0-3100 spm
Stroke Length	26 mm
Bevel Capacity	45 °
Max. Cutting Capacity [Wood]	135 mm
Max. Cutting Capacity [Steel]	12 mm
Max. Cutting Capacity [Non Ferrous Metal]	30 mm
Weight	2.8 kg
Length	250 mm
Height	210 mm

DW331K Standard

- 4 high performance jigsaw blades
- Anti-scratch cover
- Anti-splinter insert
- Dust extraction adapter
- Heavy duty carrying case