



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'DNF14250-X'

Your search criteria matched only one product, shown below

DNF14-250-X



- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
 - Barrel insulated design provides protection from electrical shorts
 - Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
 - Internal barrel serrations assure good wire contact and maximum tensile strength
 - Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
 - UL Flammability UL 94V -2/HB, maximum insulation temperature 194°F (90°C)
- ‡UL and CSA approved tooling/product combinations.

	Part Number	DNF14250-X
	RoHS Compliancy Status	Compliant
	Part Description	Female Disconnect, nylon barrel insulated, funnel entry, 16- 14 AWG, .250 X .032 tab size.
	Product Type	Disconnects
	CSA Certified	Yes
	UL Listed	Yes
	Height (In.)	.12
	Height (mm)	3.0
	Length (In.)	.83
	Length (mm)	21.1
	Width (In.)	.29
	Width (mm)	7.4
	CE Compliant	No
	CE Marking	No
	Max. Ins.	.162
	Panduit Color Code	Blue
	Pricing Description	Female Disconnect, nylon barrel insulated, 16- 14 AWG, .250 x .032 tab size, funnel entry
	Tab Size (In.)	.250 x .032
	Tab Size (mm)	6.3 x .8
	Tool	CT-600-A‡, CT-1550, CT-1551, CT-2500
	Wire Range	16 – 14 AWG
	Wire Range (mm ²)	1.5 – 2.5
	Min. Order UOM	PC
	Min. Order Qty.	100
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.