

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.			
		A $\pm .02$	W $\pm .01$	C $\pm .015$	M $\pm .02$
P14-6LF	#6	.70 (17.78)	.25 (6.35)	.22 (5.59)	.48 (12.19)
P14-6LFW	#6	.70 (17.78)	.29 (7.37)	.22 (5.59)	.48 (12.19)
P14-8LF	#8	.77 (19.56)	.29 (7.37)	.27 (6.86)	.53 (13.46)
P14-10LF	#10	.77 (19.56)	.33 (8.38)	.27 (6.86)	.53 (13.46)
P14-10LFN	#10	.77 (19.56)	.29 (7.37)	.27 (6.86)	.53 (13.46)

NOTES:


- UL LISTED AND CSA CERTIFIED FOR:
 - 18-14 AWG SOLID OR STRANDED COPPER WIRE
 - 302° F (150° C) MAX. TEMP. RATING
- MATERIAL:
 - STAMPING - .03" (.76) THK COPPER, TIN PLATED
- PACKAGE QTY: STD. PKG.-C=100
BULK PKG.-M=1000
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS:
 - UL LISTED AND CSA CERTIFIED: CT-100, CT-200, CT-270, CT-1570
 - PANDUIT APPROVED: CT-160, CT-260
- WIRE STRIP LENGTH: 9/32 ^{+1/32} ₀ (7.1 ^{+0.8} ₀)



LISTED
587H
E52164



CERTIFIED
LR31212



A41054_07

07	1/01	SAB		FILESPEC. WAS N41054AA_PCD_06				PANDUIT CORP. TINLEY PARK, ILLINOIS			
06		JKD		ADDED CT-1570 TOOL	07632						
--	----	--	RLS	REDRAWN ON CAD	03338	LCA	KS	#16-14 BARREL NON-INSULATED LOCKING FORK			
05	6/95	MS		UPDATED NOTES AND DIMENSIONS							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								MS	RLS	N/A	A41054