








STP CAT5 PLUG ZWP-8P8C-SRS

NOTES:

1. ALL DIMENSIONS ARE "MM".
2. ELECTRICAL:
UL APPLICATIONS: 250 VOLTS AC MAX., AT 2-AMPS.
DIELECTRIC WITHSTANDING VOLTAGE: 500 VOLTS AC.
INSULATION RESISTANCE: 500 MEGOHMS.
TERMINATION RESISTANCE: 35 MILLIOHMS MAX AFTER ENVIRONMENTAL TESTING.
3. MECHANICAL:
CABLE-TO-PLUG TENSILE STRENGTH: 20 lbs (89N) MIN.
DURABILITY: 200 MATING CYCLES.
4. MATERIAL & FINISH:
HOUSING: POLYCARBONATE, UL94-2. COLOR: NATURAL.
CONTACT: HIGH STRENGTH COPPER ALLOY.
GOLD PLATING OVER 100 MICRO INCH NICKEL.
CONDUCTOR: STRANDED. 24, 26, 28 AWG.
5. SHIELDING MATERIAL: BARSS. FINISH: NICKEL PLATED.

NOTE TOL: $\pm 0.1\text{mm}$

 UNIT mm/m SCALE 4/1 DWG NO:	DSGN	SUNNY	ITEM NO:
	CHK		MP-ES88-5011
	APPR		
	FULL ENTERPRISE CORPORATION.		