

StealthLite Rech. 2450

www.pelicanproducts.us



Submersible



StealthLite™ Rechargeable 2450 Flashlight

The rechargeable version of the [StealthLite 2400 Flashlight](#). The 2450 provides a consistently bright Xenon beam after every charge. It is submersible and corrosion proof. The charger base unit can be installed at home or work using the 110V transformer. Or in a vehicle through direct wiring or 12V plug-in. It comes with a long-life rechargeable NiMH battery pack, but 4 AA alkaline cells can also be used.

Minimum Pack 1 ea.

Packaged Weight: 1.4 lbs.

StealthLite™ Rechargeable 2450 Flashlight Specifications

	High	
LIGHT SOURCE	Xenon	
BATTERIES	4 AA NiMH (Included)	
CHARGE TIME	NiMH Battery Pack 2-3 hrs.	
VOLTAGE	6	
LENGTH	6.5" (16.5 cm)	
WEIGHT w/ BATTERIES	7.8 oz. (0.22 kg)	
WEIGHT w/o BATTERIES	4.4 oz. (0.12 kg)	

	FL1 STANDARD	High	
LIGHT OUTPUT		35 LUMENS	
RUNTIME (hours/min)		3h 30m	
BEAM DISTANCE (meters)		122m	
PEAK BEAM INTENSITY (candela)		3735cd	
WATERPROOF & SUBMERSIBLE		1m	

StealthLite™ Rechargeable 2450 Flashlight Configurations

Cat. #	Description
2450	StealthLite™ Rechargeable 2450 Flashlight (Carded)
2451B	StealthLite™ Rech. 2450 Flashlight w/battery only

StealthLite™ Rechargeable 2450 Flashlight Accessories

Cat. #	Description
700	Helmet Light Holder
710	Helmet Light Holder
711	Helmet Light Holder
712	Helmet Light Holder
750	Helmet Light Holder
760	Helmet Light Holder
770	Universal Helmet Light Holder
2404	StealthLite™ 2450 Xenon Lamp Module
2407	Cordura® Holster
2469	NiMH Replacement Battery Pack
2450FBC	Fast Bank Charger (5 receptacles)
2455N	12 V Plug-in for Charger
2467F	110V Transformer for Fast Charger
2470F	Desk/Dash Smart Charger Base Unit
6061F	Direct Wiring Rig for Fast Charger

StealthLite™ Rechargeable 2450 Flashlight Approvals



Class I, Div. 2; Gp ABCD; Class II; Div. 2; Gp G. T3C.



Class I, Div. 2; Gp. ABCD, T3.