



product details

HQL-T 400W/N/SI E40 FS1

Product description: HQL-T 400W/N/SI E40 FS1
EAN/ Product: 4050300376431
Quantity: Folding carton box (FS) contains 1 Piece (PCE)

You can find this product in the eCatalog:
http://catalog.myosram.com?~language=EN&~country=COM&it_p=4050300376431

Applications				
Burning position	any			
General Description				
ILCOS	MT-400/37/2B-H 133/S-E40-57.2/248			
SEG no.	8333098			
Sstl-Number	4834718			
Base (standard designation)	E40			
Technical - Electrical Data				
PFC capacitor at 50 Hz	45 µF ¹⁾			
Construction wattage	400 W			
Nominal wattage (packaging)	400 W			
Technical - Geometries				
Light centre length (LCL)	160 mm			
Length	248 mm			
Diameter	57 mm			
Technical - Life				
Lifespan	12000 h ²⁾			
Technical - Light Technical Data				
Colour temperature	3700 K			
Colour rendering group	2B			
Colour rendering index Ra	60 ... 69			
Luminous efficacy	78 lm/W			
Luminous flux	31000 lm			
Packaging units				
EAN	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4050300376431	Folding carton box contains 1 Piece	0,000 mm x 0,000 mm x 0,000 mm	0,000 g (247,000 g)	0,000 Cubic dec.
4050300376448	Shipping carton box contains 10 Piece	175,000 mm x 303,000 mm x 362,000 mm	3,050 kg (2,470 kg)	19,195 Cubic dec.

¹⁾ at rated voltage and $\cos \varphi \geq 0.9$

²⁾ Average lifespan