



Cable Protection Systems

Nyitóoldal | Termékek | Cable Protection Systems | HelaGuard Non-Metallic Conduits and Fittings

Termékek

Rólunk	
Termékek	
Újdonságok	
Cable Ties and Fixings	(1637)
Insulation Products	(2250)
Cable Protection Systems	(1667)
HelaGuard Non-Metallic Conduits and Fittings	(522)
HelaGuard Steel Conduits and Fittings	(95)
HelaGuard Steel Conduits with Plastic Coating and Fittings	(134)
HelaGuard Steel Conduits with Liquid-Tight Cover and Fittings	(82)
HelaGuard Steel Conduits with Plastic Coating and Steel Overbraid	(62)
HelaGuard Steel Conduits with Steel Overbraid and Fittings	(41)
HelaGuard PSR and PSRSC Spiral-Reinforced PVC Conduits and Fittings	(63)
HelaGuard Accessories	(210)
FlexiGuard Flexible Conduits and Fittings	(32)
Conduits for extreme conditions	(10)
Cable Management Systems	(46)
Spiral Binding	(94)
Wiring Ducts and Accessories	(8)
Wiring Ducts and Accessories 2	(8)
Braided Sleeving and Fabric Tubing	(165)
Edge Protection	(28)
Grommets	(67)
Installation Devices	(168)
Identification Systems	(2203)
Application Tooling	(129)
Connectivity	(0)
Kompetenciák	
Hírek & Események	
Letöltések	

Non-Metallic Conduits HG-HW13




When high mechanical protection is needed: HelaGuard PA6 Heavy.

HG-HW PA6 Heavy Weight, Cikkszám: 166-11302

- Heavy weight
- High mechanical strength
- Very abrasion resistant
- High impact strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus
- Low smoke and low toxicity
- Self-extinguishing according to UL94 V2
- Colour: black (UV resistant)

Heavy-duty machine building, plant construction, and public buildings, wherever high mechanical strength is required.



Catalogue page (April 2011)



All catalogue pages



Nyomtatás

▼ Base Data	
Colour	Black (BK)
Conduit Model	Plastic corrugated
Features and Benefits 2	Heavy weight corrugated flexible conduit for high mechanical demands.
Pitch Type	fine
Product Family	HG-HW PA6 Heavy Weight
Product Group	Non-Metallic Conduits
Type	HG-HW13-PA6-BK-50M

▼ Product Dimensions	
Bending Radius	35 mm
Inside Ø	9 mm
Length (L)	50 m
NW Ø	10 mm
Nominal Ø	13 mm
Outside Ø (OD)	13 mm
Weight (g/m)	37
Ø D	9 mm

▼ Logisitic and Packaging	
EAN code	4031026302492
Pack Cont.	50 m
Quantity of Europallet	0 pcs.
Quantity per	Reel
Reel Length	50 m
Weight (Kg)	3.7 kg

▼ Material and Specifications	
EN61386 Classification	24244066-210
Flammability	UL94 V2
Halogenfree	YES
IP-Rating	IP66 (in conjunction with HG fittings)
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Operating Temperature	-40 °C to +120 °C
Specification	IEC 61386

▼ Matching products



HGL13-90-M16
166-22800
Fittings with fixed external thread



HGL13-90-PG9
166-22808
Fittings with fixed external thread



HG13-SF-M16
166-21400
Fittings with swivel internal thread



HG13-SF-PG9
166-21408
Fittings with swivel internal thread

▼ Similar products



HG-HW16
166-11303
Non-Metallic Conduits



HG-HW21
166-11304
Non-Metallic Conduits



HG-HW28
166-11305
Non-Metallic Conduits



HG-HW34
166-11306
Non-Metallic Conduits