



SPECIFICATIONS:

Mat:

- Construction: Dual layer rubber material
- Static Dissipative top layer
 - Conductive rubber bottom layer

Material Thickness: .060" ($\pm 10\%$)

Color: Dark Blue

Texture: Smooth

Dissipative Color Side:

- RTT: 10E6 - 10E8 ohms per ANSI/ESD S4.1
- RTG: 10E6 - 10E8 ohms per ANSI/ESD S4.1

"Slows charge removal; meets minimum recommended work surface requirements of ANSI/ESD S20.20 and recommendations of STM 4.1"

Wrist Strap:

Construction: Soft elastic band with silver impregnated polypropylene on the inside for reliable removal of static charge

Snap: 4mm male stud snap

Cord Length: 6'

Cord Terminations: 4mm socket snap, molded banana plug

Ground Cord:

Length: 15'

Terminations: 10mm male stud snap, ring terminal

Resistor: 1 megohm

Universal Snap Kit:

Size: 10mm

Kit Includes: 10mm stud snap, 10mm socket snap, threaded backing washer, long screw, short screw, & groundable point label



PACKAGING:

Product to be packaged with Duratool label



MADE IN AMERICA

Special manufactured items are not returnable for credit



Packaging Label

Tolerances:

Width: ± 0.250 "

Length: ± 0.250 " every 1 linear foot of running material

CUSTOMER APPROVAL

DATE

BENCH TOP MAT, 2 LAYER RUBBER, 24" x 48", WRIST STRAP, ADJ ELASTIC, 6' COIL CORD, GROUNDING CORD, UNIVERSAL SNAP KIT, PACK WITH DURATOOL LABEL, MC35759

CMG

3651 WALNUT AVE., CHINO, CA 91710
PHONE (909) 627-9634 FAX (909) 363-7322
WEBSITE: www.CMG-Sales.com

**DRAWING
NUMBER**
CMG-10746

DATE
July
2010