

Hakko FX-301B Digital Solder Pot



Click Picture to Enlarge



Visit the Theatre



Print this Page

LIVE HELP

 Leave a message

Available weekdays
7:30am - 4:30pm PT

- Request a Catalog by mail
- Comments/Suggestions
- Report Trouble
- AHPDirect

Item No. / Description	MSLP	Stock Status
FX301B-03	US	☒ In Stock
POT,SDRG,TINNING,DIGITAL,FX-301B		 Buy Now

Features & Benefits	Specifications	Similar Products	Accessories	Replacement Parts	Technical Documents	FAQ
---------------------	----------------	------------------	-------------	-------------------	---------------------	-----

FX-301B SOLDER POT

Model Name	FX-301B
Power Consumption	290W (120V)
Temperature Accuracy	±10°C (±18°F)
Temperature Stability	±5°C (±9°F)
Weight (w/o solder and cord)	1.7 kg (3.74 lb.)
Outer dimensions	143(W) x 100(H) x 220(D) mm (5.6 x 4.0 x 6.7 in.)

EXTENDED LIFE CRUCIBLES

	50 x 50 mm Square	75 x 75 mm Square
Temperature range	200-450°C (400-840°F)	200-380°C (400-720°F)
Solder pot dimensions	50(W)x50(D)x43.5(H) mm 2.0(W)x2.0(D)x1.7(H) in.	75(W)x75(D)x52.5(H) mm 3.0(W)x3.0(D)x2.1(H) in.
Molten solder capacity	0.85 kg (1.87 lb.)	1.2 kg (2.64 lb.)

CONTENTS

Part Number	
FX301B-03	Unit (50 x 50 mm Extended Life Crucible included)
B2932	Spatula
B2919	J-shaped waste collector
B1417	Hexagon wrench

APPROVED



NOTE:
50 x 50 mm square Extended Life Crucible is included with the unit
75 x 75 mm square Extended Life Crucible is an optional part

Specifications and design subject to change without notice.

Temperature accuracy and stability specifications are established at idle with a full 50 x 50mm crucible.