





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	*MSCP ±25%	*LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7683EBP	5.0	.060	.050	0.63	100,000	C-2R
7715EBP	5.0	.115	.150	1.89	40,000	C-2R
8097EBP	12.0	.060	.150	1.89	16,000	C-2F
8099EBP	18.0	.026	.150	1.89	16,000	C-2F
7839EBP	28.0	.024	.150	1.89	16,000	CC-2F

*LAMP RATED ONLY (NOT IN BASE)

METRIC  THIRD ANGLE PROJECTION			DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION					
DRAWN BY L. WENGSTROM			APPV'D BY DATE BW 3/17/00		TITLE T-1 EUROPEAN BI-PIN BASED LAMPS					
RELEASED - CANCEL SM-EURBP-T1			3/17/00		SIZE A		FSCM NO. 55335		DRAWING NO. BI-PIN T-1 EUROPEAN	
REV. NO.			DESCRIPTION/ECO NUMBER		APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	
REV. NO.			DESCRIPTION/ECO NUMBER		APPV'D DATE		RELEASED DATE 3/17/00		REVISION DATE	
REV. NO.			DESCRIPTION/ECO NUMBER		APPV'D DATE		REV. NO.		SHEET 1 OF 1	