


ARRANGEMENT OF CONTACTS										SPECIFICATIONS	
PARTS	B9005-3P	B9005-4P	B9005-5P	B9005-5A	B9005-5B	B9005-6P	B9005-7P	B9005-8P	B9005-8A	Dielectric strength	1,000V AC/1 Minute
ANGLE	180°	216°	180°	240°	360°	240°	270°	270°	262°	Contact resistance	20MΩMax.
										Insulation resistance	100MΩMin. at 500V DC
										Rating	100V AC 2A
POSITION OF VIEWS											



7	SCREW	1	2AAR1050 [A4510]	NICKEL	3-5U"
6	PLASTIC TRAIL	1	PVC	BLACK	UL
5	LOCK COVER	1	DIECAST	NICKEL	3-5U"
4	MAIN BODY	1	DIECAST	NICKEL	3-5U"
3	CLIP PLATE	1	SPC SB (0.95t)	NICKEL	3-5U"
2	CONTACT TERMINAL	3	BSR-H (1.5D) [R-35]	SILVER PLATED	3-5U"
1	PLASTIC CORE	1	NYLON [101]	BLACK	UL94V2
P/N	PART NAME	Q'TY	MATERIAL	PLATING	REMARKS

DRAWN	KIDD	APP'D		UNIT	MM	TOLERANCE			
CHK'D				SCALE	1:1	.x ±0.20 .xx ±0.10 .xxx ±0.05 .xxxx ±0.03 ANGULA ±1°			
				TITLE B9007-3P METAL DIN CIRCULAR PLUG					SHEET
						PART NO. B9007-3P		DWG NO. METAL DIN PLUG	VERSION A