


## TECHNICAL SPECIFICATIONS SN-Series

|                               |                                |
|-------------------------------|--------------------------------|
| <b>Material:</b>              | UL Recognised Plastic Material |
| <b>Operating Temperature:</b> | -55°C to +110°C                |
| <b>Cable Entry:</b>           | Top                            |
| <b>Thumbscrews:</b>           | UNC 4-40                       |
| <b>Cable O.D:</b>             | Up to 11,5mm                   |
| <b>Colour:</b>                | Black or Light Grey            |



| Size   | A    | B    | C    |
|--------|------|------|------|
| 9-way  | 30,5 | 15,5 | 39,2 |
| 15-way | 40,1 | 15,5 | 39,6 |
| 25-way | 53,6 | 16,0 | 43,0 |

## Ordering information:

| Size:  | P/N - Kitted: | Product Code BLACK: |
|--------|---------------|---------------------|
| 9-way  | 2360-0101-01  | MHCCOV 9-SN-BK      |
| 15-way | 2360-0101-02  | MHCCOV15-SN-BK      |
| 25-way | 2360-0101-03  | MHCCOV25-SN-BK      |

| Size:  | P/N - Kitted: | Product Code LIGHT GREY |
|--------|---------------|-------------------------|
| 9-way  | 2360-0101-11  | MHCCOV 9-SN-LG          |
| 15-way | 2360-0101-12  | MHCCOV15-SN-LG          |
| 25-way | 2360-0101-13  | MHCCOV25-SN-LG          |