

Thread-cutting set 3 + 4 in steel case

1.6

Description	Article no.	Price / set €
37-piece thread-cutting set, HSS, ground, one three-piece set each of hand taps M DIN 352 HSS, ground, M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 die, M DIN EN 22568 HSS, ground, in each of the sizes M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 5 die stock DIN 225 in each of the sizes 20 x 5 mm - 20 x 7 mm - 25 x 9 mm - 30 x 11 mm - 38 x 14 mm + 2 tap wrench, size 1 and size 2 DIN 1814 + 1 screwdriver + 1 screw-pitch gauge	245 020	
37-piece thread-cutting set, HSS, ground, one three-piece set each of hand taps M DIN 352 HSS, ground, with taper tap 7-thread chamfer, second tap 5-thread chamfer and final tap 3-thread chamfer M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 die, M DIN EN 22568 HSS, ground, in each of the sizes M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 5 die stock DIN 225 in each of the sizes 20 x 5 mm - 20 x 7 mm - 25 x 9 mm - 30 x 11 mm - 38 x 14 mm + 2 tap wrench, size 1 and size 2 DIN 1814 + 1 screwdriver + 1 screw-pitch gauge	245 020 SK	



No. 245 020



No. 245 020 SK

NEW

Thread-cutting set 5 + 6 in steel case

Description	Article no.	Price / set €
44-piece thread-cutting set, HSS, ground, one three-piece set each of hand taps M DIN 352 HSS, ground, M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 twist drills DIN 338 type N HSS, ground Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm + 7 die, M DIN EN 22568 HSS, ground, in each of the sizes M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 5 die stock DIN 225 in each of the sizes 20 x 5 mm - 20 x 7 mm - 25 x 9 mm - 30 x 11 mm - 38 x 14 mm + 2 tap wrench, size 1 and size 2 DIN 1814 + 1 screwdriver + 1 screw-pitch gauge	245 030	
44-piece thread-cutting set, HSS, ground, one three-piece set each of hand taps M DIN 352 HSS, ground, with taper tap 7-thread chamfer, second tap 5-thread chamfer and final tap 3-thread chamfer M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 twist drills DIN 338 type N HSS, ground Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm + 7 die, M DIN EN 22568 HSS, ground, in each of the sizes M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 5 die stock DIN 225 in each of the sizes 20 x 5 mm - 20 x 7 mm - 25 x 9 mm - 30 x 11 mm - 38 x 14 mm + 2 tap wrench, size 1 and size 2 DIN 1814 + 1 screwdriver + 1 screw-pitch gauge	245 030 SK	



No. 245 030



No. 245 030 SK

NEW