



THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE = $\pm 5^\circ$
0.5-5 = ± 0.2
5-30 = ± 0.4
UNIT: MM 30-120 = ± 0.6
120-315 = ± 1.0



INNER CONDUCTOR ○ — ○ ALLIGATOR CLIP / RED
BRAID ○ — ○ ALLIGATOR CLIP / BLACK

FREQUENCY	400 MHZ
ATTENUATION	1 dB/M MIN.
CAPACITANCE	101 pF/M
MAX. VOLTAGE	1.5 KVRMS MIN.

NOTE:
1. BNC male – punch $\varnothing 8.3$

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN JDHNNY	DATE 04-24-13
	APPROVED	DATE



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR ROHS COMPLIANCY.



MH CONNECTORS LTD.

SCALE	SHEET OF	REV.:
	1 DF 1	1.0
DRAWING No	GEX373-1M	