

SPECIFICATION SHEET**JFW MODEL 57Z-2G SF/BF-P2****IMPEDANCE MATCHING PAD**

JFW Industries, Inc.
Phone: 317-887-1340
sales@jfwindustries.com
www.jfwindustries.com

Frequency Range	9-2000 MHz
Impedance	50 Ohm SMA female 75 Ohm BNC female
Return Loss	20 dB minimum (75 Ohm side) 11 dB nominal (50 Ohm side)
Insertion Loss	2.0 dB $\pm$ 0.5 dB @ 300 MHz
Insertion Loss Flatness	$\pm$ 2 dB
RF Input Power	1 Watt average
DC Blocking Voltage	100 Volts maximum
RF Connector	SMA female to BNC female panel mount
Connector Tightness	25 In-Lbs
Operating Temperature Range	0°C to +60°C
Physical Size	See outline drawing 092-2384

ECR/ECN #	DATE	REV	APPR / DATE	ECR/ECN #	DATE	REV	APPR / DATE
	08/30/1996			9999	08/28/2003	C	SL 10/06/2003
624	11/11/1996	A					
659	01/16/1997	B					