

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0845927100](#)
Status: **Obsolete**
Overview: [nanoc_pcb_mount_receptacles](#)
Description: Nano-Change® Male Straight 3-Circuit Bulkhead Receptacle, 24 AWG, 0.30m (11.81") Length

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	84592
Connector to Connector	Nano-C Panel-Mount Receptacle
Overview	nanoc_pcb_mount_receptacles
Product Name	Nano-C

Physical

Cable Length	0.30m (11.81")
Circuits (Loaded)	3
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Packaging Type	Bag
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	0.762µm (30µ")
Single Ended	Yes
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Insulation Diameter	N/A
Wire Size AWG	24
Wire/Cable Type	PVC


Electrical

Current - Maximum per Contact	4A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-84592-7100
---------------	---------------



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[84592Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION