


Model 2BA & 2BC Double Banana Plug Both Ends Cable Assembly



MATERIALS:

Banana Plugs:

Plug Bodies: Brass, Nickel Plated

Springs: Beryllium Copper, Nickel Plated

Insulation: Polypropylene Molded to the Plug Bodies and Cable. Color Matches Color of Cable

Marking: POMONA ELECTRONICS CO. INC. POMONA CALIFORNIA

Cable: 2BA: 2 Cond. Tw. 18 AWG 65 x 36 .250 (6,4) O.D., Color: Gray, Marking: 2BA-XX

2BC: RG58C/U, .195 (5,0) O.D., Color: Black, Marking: 2BC-XX

RATINGS:

Operating Temperature: +55°C Max.

Operating Voltage: 2BA – 300 VRMS, 2BB – 1900 VRMS, 2BC – 1400 VRMS

ORDERING INFORMATION: Model 2B*-XX

XX = Cable Length, Standard Lengths: 18" (457,2cm), 24" (60,96cm), 36" (91,44cm), 48" (121,92cm) & 60" (152,4cm). Additional lengths can be quoted upon request.

* = Cable

Ordering Example: 2BA-18 Cable Assembly is 18" (457,2cm), Cable is 2 Cond. Twisted Pair, 18 AWG, Color is Gray.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[2BA-48](#) [2BA-60](#) [2BC-60](#) [2BC-48](#) [2BC-24](#) [2BC-36](#) [2BA-24](#) [2BA-18](#) [2BA-36](#)