



3 - M4 X 4.9 mm
TERMINAL SCREW AND
INTERNAL TOOTHED
LOCK WASHER




CHARACTERISTICS

ELECTRICAL RATING	15A 125VAC OR 250VAC UL APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	350 GMS
RELEASE FORCE MIN.	114 GMS
PRETRAVEL MAX.	.016 [0.4 mm]
OVERTRAVEL MIN.	.216 [5.5 mm]
MOVE. DIFF. MAX.	.002 [0.05 mm]
OPERATING POSITION	.826 TO .890 [21.0 TO 22.6 mm]

DWN: JED
APVD: SB

DATE: 25-May-04

THIRD ANGLE PROJECTION



THE CONFIDENTIAL AND PROPRIETARY
INFORMATION CONTAINED IN THIS DOCUMENT
IS OWNED BY CHERRY ELECTRICAL PRODUCTS,
A DIVISION OF THE CHERRY CORPORATION WHO
MUST GIVE WRITTEN PERMISSION BEFORE THE
DOCUMENT OR INFORMATION CAN BE COPIED,
DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED

X.XX	X.XXX	ANGLES
± 0.02	± 0.015	± 5°

PROJECT / ESR

CHERRY
ELECTRICAL PRODUCTS

3600 SUNSET AVENUE
WAUKEGAN, IL 60087

SWITCH

B ITEM NO. GPTCNH01

SCALE: 2:1 SH 1 OF 1

REV	ECN NO.	DATE	PREP	APVD
B	11388	02-Jun-04	JED	SB