

SERIES 39 SPST, 150 mA

FEATURES


- 1/4" Diameter
- Up to 1,000,000 Cycles of Operation
- PC Mount



DIMENSIONS in inches (and millimeters)

SPST-Normally Open, without Nut


39-405*



Rating at 28 Vdc Resistive	Operations at Rated Load	*Complete Part Number	Button Color
150 mA	1,000,000	39-405 RED 39-405 BLK	Red Black
Action	Total Travel	Actuating Force (oz.)	
Momentary	.035 ± .015 (0,89 ± 0,38)	4 + 4 - 2	

SPST-Normally Open, with Nut


39-401*



Rating at 28 Vdc Resistive	Operations at Rated Load	*Complete Part Number	Button Color
150 mA	1,000,000	39-401 RED 39-401 BLK	Red Black
Action	Total Travel	Actuating Force (oz.)	
Momentary	.035 ± .015 (0,89 ± 0,38)	4 + 4 - 2	

SPST-Normally Open, with Overtravel

39-424*



Rating at 28 Vdc Resistive	Operations at Rated Load	*Complete Part Number	Button Color
150 mA	100,000	39-424 RED 39-424 BLK	Red Black
Action	Total Travel	Over Travel	Actuating Force (oz.)
Momentary	.130 ± .025 (3,30 ± 0,64)	.015 (0,38) Min.	5 ± 3

