



## Belt-Ty™ In-Line Cable Ties – Nylon and Weather Resistant Nylon 6.6


- Natural nylon material for indoor use
- Weather resistant material has greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- Parallel-entry cable tie that threads like a belt (180° entry)
- Low profile head avoids snags and reduces overall bundle size
- 35% lower head height than conventional 90° ties
- Parallel-entry limits exposure to sharp edges and protects workers' arms/hands
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation
- Nylon 6.6 cable ties are UL Listed for use in plenum or air handling spaces per NEC



ILT2S-C



ILT2S-C0



| Part Number | Length |    | Width |    | Thickness |    | Max. Bundle Dia. |    | Min. Loop Tensile Str. |   | Recommended Installation Tool | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|--------|----|-------|----|-----------|----|------------------|----|------------------------|---|-------------------------------|----------------|----------------|
|             | In.    | mm | In.   | mm | In.       | mm | In.              | mm | Lbs.                   | N |                               |                |                |

### Nylon 6.6

#### Standard Cross Section – Plenum-Rated

|         |      |     |      |     |      |     |      |     |    |     |                                                        |     |      |
|---------|------|-----|------|-----|------|-----|------|-----|----|-----|--------------------------------------------------------|-----|------|
| ILT2S-C | 8.3  | 211 | .190 | 4.8 | .052 | 1.3 | 1.88 | 48  | 50 | 222 | GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2 | 100 | 1000 |
| ILT3S-C | 11.5 | 292 | .190 | 4.8 | .052 | 1.3 | 3.00 | 76  | 50 | 222 |                                                        | 100 | 1000 |
| ILT4S-C | 14.7 | 373 | .190 | 4.8 | .052 | 1.3 | 4.00 | 102 | 50 | 222 |                                                        | 100 | 1000 |

#### Light-Heavy Cross Section – Plenum-Rated

|           |      |     |      |     |      |     |      |     |     |     |                                    |     |      |
|-----------|------|-----|------|-----|------|-----|------|-----|-----|-----|------------------------------------|-----|------|
| ILT4LH-TL | 14.8 | 376 | .300 | 7.6 | .075 | 1.9 | 4.00 | 102 | 120 | 534 | GTH, GS4H, GS4EH, PTH, STH2, ST3EH | 250 | 2500 |
| ILT6LH-C  | 21.2 | 538 | .300 | 7.6 | .075 | 1.9 | 6.00 | 152 | 120 | 534 |                                    | 100 | 2000 |

### Weather Resistant Nylon 6.6

#### Standard Cross Section

|          |      |     |      |     |      |     |      |     |    |     |                                                        |     |      |
|----------|------|-----|------|-----|------|-----|------|-----|----|-----|--------------------------------------------------------|-----|------|
| ILT2S-C0 | 8.3  | 211 | .190 | 4.8 | .052 | 1.3 | 1.88 | 48  | 50 | 222 | GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2 | 100 | 1000 |
| ILT3S-C0 | 11.5 | 292 | .190 | 4.8 | .052 | 1.3 | 3.00 | 76  | 50 | 222 |                                                        | 100 | 1000 |
| ILT4S-C0 | 14.7 | 373 | .190 | 4.8 | .052 | 1.3 | 4.00 | 102 | 50 | 222 |                                                        | 100 | 1000 |

#### Light-Heavy Cross Section

|            |      |     |      |     |      |     |      |     |     |     |                                    |     |      |
|------------|------|-----|------|-----|------|-----|------|-----|-----|-----|------------------------------------|-----|------|
| ILT4LH-TL0 | 14.8 | 376 | .300 | 7.6 | .075 | 1.9 | 4.00 | 102 | 120 | 534 | GTH, GS4H, GS4EH, PTH, STH2, ST3EH | 250 | 2500 |
| ILT6LH-C0  | 21.2 | 538 | .300 | 7.6 | .075 | 1.9 | 6.00 | 152 | 120 | 534 |                                    | 100 | 2000 |

Weather resistant nylon 6.6 cable ties are UL Recognized, UL Listed, and CSA Certified, except ILT4LH/6LH.

A.  
System  
Overview

B1.  
Cable  
Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ILT2S-C](#) [ILT2S-C0](#) [ILT3S-C](#) [ILT3S-C0](#) [ILT4LH-TL](#) [ILT4LH-TL0](#) [ILT4S-C](#) [ILT4S-C0](#) [ILT6LH-C](#) [ILT6LH-C0](#)