



OUTLINE REF.	MOUNTING ** TYPE	DIMENSIONS IN INCHES (mm in parentheses)						
		A	B	C	D	E	F	G
LA50P900 TO 1200	4, 4T†	6.97 (177)	3.00 (76.2)	3.22 (81.8)	4.97 (126)	0.63 (16.0)	2.38 (60.5)	0.44 (11.1)

*MOUNTING TYPE: 4 - BOLT-IN BLADES



RATINGS

AC: 900-1200A 500VAC, 100kA I.R.
DC: 900-1000A 450VDC, 79kA I.R.
L/R = 10 ms

CATALOG NUMBER	FUSE AMPERE RATING	INDICATOR	UPC CODE
LA50P9004	900	NO	079458 15145
LA50P10004	1000	NO	079458 15146
LA50P10004TI	1000	YES	079458 15148
LA50P12004	1200	NO	079458 15147
LA50P12004TI	1200	YES	079458 15149

●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS - MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

[illegible]