



LISTA GENERAL STORAGE CATALOG



LISTA
making workspace work®

Lista offers a comprehensive array of innovative storage systems and accessories, all of which are described in this catalog. Within the following pages, you'll find:

- Easy-Order offerings of a broad array of Lista products
- A wide selection of accessories that allow you to create your own custom solutions
- Other specialized workspace solutions such as overhead cabinets and computer cabinets
- And much more!

You can use this catalog to order the workspace and storage systems that exactly suit your individual needs.

To help you navigate the catalog, our sections are color coded:

Full Depth Cabinets

Shallow Depth Cabinets

Storage Wall Systems

Tool Storage

Unique Workspace Solutions

Drawer Accessories

Information about ordering custom configured products is indicated in **yellow**, and Easy-Order combinations are indicated in **green**.

For in-depth index, see page 123.

Lista – Making Workspace Work® 4

Drawer Storage Cabinets 6

Cabinet Features 10

Drawer Features 12

Lista Full Depth Cabinets 13

Easy-Order Full Depth Cabinets 13

Easy-Order NW Narrow Width Cabinets 14

Easy-Order MP Width Cabinets 18

Easy-Order SC Standard Width Cabinets 22

Easy-Order MW Mid-Width Cabinets 28

Easy-Order DW Double Width Cabinets 32

Custom Configured Full Depth Cabinets 36



Lista Shallow Depth Cabinets 42

Easy-Order Shallow Depth Cabinets 43

Easy-Order CL Width Cabinets 44

Easy-Order ST Width Cabinets 48

Easy-Order HS Width Cabinets 52

Custom Configured Shallow Depth Cabinets 56



Lista Cabinet Options 62

Lock Options 62

Combination Cabinets 63

Mobile Cabinets 64

Cabinet Tops 67

Shelf Cabinets 68





Lista Storage Wall® Systems 70

- Features 74
- How to Order Storage Wall Systems 77
- Full Depth Systems 78
- Shallow Depth Systems 80
- Locking Systems and Accessories 82
- Storage Wall Doors 84



Lista Tool Storage 86

- Tool Storage Components 90
- Tool Transporters 92
- CNC and Machine Tool Cabinets 96
- Tool Crib Cabinets 100



Lista Unique Workspace Solutions 102

- Overhead Cabinets 104
- Counter Tops 107
- Computer Cabinets 108
- Sink Cabinets 111
- File Cabinets 111
- Control Stations 112
- Mezzanines and Stacked Cabinets 114



Lista Drawer Accessories 116

- How to Order Drawer Partitions and Dividers 118
- Accessories 119



Index 123

At Lista, we provide more than efficient storage space; we also create productive working environments that:

- Are secure, built-to-last solutions
- Offer the greatest possible density, organization and access
- Are ergonomically designed with the user in mind
- Are constructed from the highest quality materials
- Provide a durable, high-quality, attractive powder coat finish

OUR OPENING ATTRACTION

Lista drawers are the centerpiece of our modular building block system because they:

- Provide complete organization of tools, components or instrumentation, right at the point of use
- Feature an advanced drawer suspension system that provides smoother, quieter performance and impressive cycle life (see page 12 for details)
- Maximize use of cubic capacity for improved space utilization
- Are available in a wide variety of sizes and shapes
- Can be subdivided to create custom compartments



THE ALTERNATIVE TO SHELVING

When you replace shelving with Lista cabinets, you maximize space, enhance inventory control and protect your tools and parts from dust, dirt and shrinkage. When deciding where to invest your business dollars, consider the savings you get from Lista cabinets in:

- Space
- Time
- Money



The installation of Lista cabinets provides for organized storage, maximized density and easy inventory control. This previously disorganized working environment (left) is now clean, professional and aesthetically pleasing (right).

BUILT TO LAST

The result of high-quality, all-steel construction and innovative engineering and design, Lista products are built to provide decades of functionality and ease of use in the most rugged working environments. An investment in a Lista modular workspace system will still be paying dividends years from now with safe, convenient storage and problem-free operation.



Thirty-year-old Lista cabinets stand the test of time. Installed at the General Electric Steam Turbine Division, Lista cabinets were still in use three decades later. The cabinets store a variety of heavy machine tooling equipment, such as turbine casing tools, end mills and cutting tools. GE's program manager of computer aided manufacturing says, "Lista cabinets don't wear out, and there's no real maintenance to speak of."



Design services

Lista's engineering and design team is ready to provide you with a detailed plan for your individual workspace and storage needs, free of charge. We offer solutions that are designed for maximum efficiency and future flexibility, optimizing space and profitability.

- **Floorspace utilization analysis.** We can prepare plan and elevation CAD drawings for a grouping of products, or entire room-sized solutions.
- **Customized surveys and layouts.** Lista experts will survey your current and future storage and workspace needs, and propose solutions that provide the highest density and greatest productivity.
- **Integration with architectural and construction planning.** Rely on our experience with coordinating with architectural and construction professionals at any stage of a project's development.



- **Price quotes.** We are happy to provide free estimates and price quotes for any project, regardless of size.

Custom applications

When you work with Lista, you're certain to get the workspace you need. Together, our engineering and manufacturing teams will work closely with you to analyze your needs and modify our standard products to meet your special requirements.

Unmatched customer support

Lista has knowledgeable, helpful resellers throughout North America. No matter where you are, their guidance, products and support are always close at hand.



Lista Drawer Storage Cabinets

Lista cabinets can be configured in a variety of ways, using high-density drawers, convenient roll-out trays, and shelf cabinets for bulk storage. At Corporate Jet Support in Moonachie, NJ, rows of stacked HS shallow depth drawer and shelf cabinets provide high-density storage for aircraft parts in a wide range of sizes and shapes.



Lista Drawer Storage Cabinets

Cabinet Features 10

Drawer Features 12

Full Depth Cabinets 13

NW Width Easy-Order Combinations 14

MP Width Easy-Order Combinations 18

Standard Width Easy-Order Combinations 22

Mid-Width Easy-Order Combinations 28

Double Width Easy-Order Combinations 32

How to Order Full Depth Cabinets 36

Shallow Depth Cabinets 42

CL Width Easy-Order Combinations 44

ST Width Easy-Order Combinations 48

HS Width Easy-Order Combinations 52

How to Order Shallow Depth Cabinets 56

Cabinet Lock Options 62

Combination Cabinets 63

Mobile Cabinets and Accessories 64

Cabinet Tops 67

Shelf Cabinets 68



Lista Cabinets Make Any Workspace Work

Lista's versatile and flexible storage cabinets are an ideal fit for a wide range of workspace and storage needs – from manufacturing to warehousing to research and development.



Clusters of mobile repair stations show off their versatility by allowing for grouped arrangements. Singly, these workcenters can be easily moved to the point of repair for convenience and increased productivity.



This major microchip manufacturer equipped the mobile aisles in its warehouse with stacked Lista drawer and shelf cabinets. The cabinets perfectly fit the mobile aisle housings, and their one-drawer-at-a-time Preventip® feature fits the company's safety needs.



By topping a row of Lista cabinets with a butcher block counter top, Mary Hitchcock Hospital's maintenance area created an efficient issue counter with plenty of convenient under-counter storage.



Rusty Wallace, Inc. outfitted its shop with a variety of Lista storage cabinet solutions, including drawer cabinets and double-hinged door cabinets with shelves and roll-out trays. This configuration enables the race team to store everything from small parts to large supplies and equipment in the same work bay.

Lista's full height sidewalls, partitions and dividers allow the complete use of the cubic storage capacity of the drawer.



The wide variety of Lista storage options allows this maintenance area to accommodate items in a variety of sizes and shapes, stored in a convenient and logical manner.



Stacked Lista cabinets at this government agency's repair facility feature a variety of door styles to protect contents in drawers, on shelves and on roll-out trays.



A row of Lista cabinets with stainless steel cabinet covers provides a combination of clean, organized storage space with convenient counter space. Overhead cabinets supported by stationary riser shelves allow storage of a wide variety of books, manuals and instruments in close proximity to the work area.

Lista Cabinets Have More of What You Need

We pack every Lista storage solution with more of the features you need to create the most productive work environments.

With their all-steel construction and heavy-duty welds, these storage solutions are built for the long haul.

Lista has modular drawer storage cabinets that perfectly suit the widest range of applications. Our cabinets:

- Provide the highest density storage
- Provide maximum weight-bearing capacity, organization and access
- Feature all the benefits of our unique, infinitely customizable drawer
- Offer the flexibility to adapt to your future requirements



Innovative handle covers, supplied with all cabinets, protect drawer labels from handling, tears, spills, grease, grime, etc. The clear plastic hinged cover resists yellowing while clearly displaying the information on labels. Bar codes protected by the hinged label covers are easily read by bar code readers.



Feature: Variety of locking systems

Security options to suit the widest variety of applications. Removable/replaceable lock core for field repairs. See pages 62-63 for details.

Benefit: Reduces shrinkage, limits access, improves safety, easily retrofitted and updated

Feature: 100% full extension on drawers and roll-out trays

Continuous smooth extension even with a full 440 lb. load

Benefit: Easy access and full use of the furthest corner of storage

Feature: Drawer dividers with ability to add labeling

Angled tops allow easy identification of contents, and can accommodate most text and bar code labels. Dividers can be fastened to drawer bottom for mobile applications.

Benefit: Fast, accurate identification of compartment contents and easier inventory control

Feature: Housing supports slotted at 1" increments

Drawers, shelves and roll-out trays can be assembled in any sequence

Benefit: Easily reconfigured for maximum versatility

Feature: Customizable drawer compartments

Drawers have partitioning slots on all four sides and can be subdivided with a wide variety of drawer accessories for maximum partitioning flexibility. See pages 119-122 for details.

Benefit: Better organization, faster retrieval

Feature: Ergonomic handles

When drawers are closed, handles are flush with housing so nothing protrudes. Drawer handles are full width, and are located at top of drawer.

Benefit: Improved safety, appearance and ergonomics

Feature: Hinged drawer handle covers/label holders

Unique handle cover has hinged plastic cover that easily opens and closes to allow labels to be added and changed, while protecting labels from handling, tears and dirt. Drawers and contents can be labeled with free, downloadable Lista Script software.

Benefit: Faster retrieval and easier inventory control

Feature: PrevenTip® interlock system

Unique, patented drawer locking system ensures that when one drawer is extended, all other drawers are locked closed to prevent accidental tip-over

Benefit: Added safety and security

Feature: Variety of bases

Different bases allow for easy stacking or moving with a fork or pallet truck, even when fully loaded. Mobile bases can be added to most cabinets. See pages 39 and 59 for details.

Benefit: Flexibility and ease of relocation or rearrangement



A variety of locking options offer the exact security enhancements your application demands. For more information, see page 62.



Casters can be added to most *Lista* cabinets to transform them into mobile workstations on wheels. For more information, see pages 64-66.

CHOOSE FROM EIGHT CABINET FOOTPRINTS

FULL DEPTH – 28 1/2" (725mm) DEEP



NW WIDTH
16 7/8" wide



MP WIDTH
22 3/16" wide



SC WIDTH
28 1/4" wide



MW WIDTH
47" wide



DW WIDTH
56 1/2" wide



CL WIDTH
22 3/16" wide



ST WIDTH
28 1/4" wide



HS WIDTH
40 1/4" wide

SHALLOW DEPTH – 22 1/2" (572mm) DEEP

Lista's Unique Drawer Construction – Unequaled Performance

Lista drawers set the standard in quality modular storage worldwide. In fact, our drawers have measured up to the RAL standards, a rigorous set of independent benchmarks for drawer performance (see below).

Unique drawer construction

Lista's drawers are constructed like no other competitive drawer. Their superior engineering and construction give them outstanding capacity and durability.

All our drawers and roll-out trays extend 100% from the cabinet housing, allowing easy, ergonomic access to the entire contents, even in the farthest corners. All four sides of the drawer are fully reinforced for maximum integrity.

We offer two drawer weight capacities – 440 lbs. (200kg) and 165 lbs. (75kg). See the chart below for which capacities are available for each of our housing footprints.

DRAWER WEIGHT CAPACITIES

NW Width	165 lbs.
MP Width	165 lbs.
	440 lbs.
SC Width	440 lbs.
MW Width	440 lbs.
DW Width	440 lbs.
CL Width	165 lbs.
ST Width	165 lbs.
	440 lbs.
HS Width	440 lbs.

ONE-PIECE DRAWER FACE AND HANDLE

Lista's drawer front has an integral handle and is welded to the bottom of the drawer for added stability (shown to the right without handle end cap). No hardware is used to attach the drawer front or handle, resulting in superior durability and ergonomic safety.



SUSPENSION SYSTEM

Our exclusive suspension system incorporates a guide track, which wraps under the drawer body for additional stability and strength. This unique system features quiet Polyoxymethylene (POM) bearings, combining strength, hardness, dimensional stability, fatigue resistance, low wear and low friction, to give Lista drawers remarkably smooth, quiet operation.



FULL HEIGHT SIDEWALLS



Pack our drawers to the top.

Our six full-height sidewalls allow for optimal use of the system's cubic storage capacity. Items stored in the drawer won't fall out either the sides or the back of the drawer. Additionally, we offer six matching partition and divider heights to allow maximum use of the cube in each and every drawer compartment.

DRAWER PERFORMANCE

When we say our drawers provide unequaled performance, we have the results to back that claim up.

To test our drawers, we chose the RAL-RG 614 standard from the German Institute of Quality Assurance and Marking, a globally respected standard. This test required our drawers to pass a series of difficult test criteria.

In these demanding tests, Lista excelled. Both suspensions were tested and exceeded the required number of cycles without diminished performance.



Lista *Easy-Order* Full Depth Cabinets – 28 1/2" deep



Ordering an Easy-Order Lista cabinet or mobile cabinet takes just a few simple steps, and enables you to have a customized cabinet (down to the base, lock and paint color) without having to break a sweat.

TO ORDER AN EASY-ORDER COMBINATION:

(housing with preconfigured drawers and option of drawer interior sets)

	CABINETS	MOBILE CABINETS	DRAWER INTERIOR SETS
NW	pages 14-15	page 16	page 17
MP	pages 18-19	page 20	page 21
SC	pages 22-24	page 25	pages 26-27
MW	pages 28-29	page 30	page 31
DW	pages 32-33	page 34	page 35

FULL DEPTH CABINET FOOTPRINTS



NW WIDTH
16 7/8" wide



MP WIDTH
22 3/16" wide



SC WIDTH
28 1/4" wide



MW WIDTH
47" wide




DW WIDTH
56 1/2" wide

STEPS TO ORDER AN EASY-ORDER FULL DEPTH CABINET

1 Select cabinet footprint and height

Select the particular cabinet size that best suits your needs. When choosing your housing height, keep in mind the cabinet top's potential use as a work surface. See chart above for pages showing the different housing footprints.



DRAWER HT. DRAWER INT.

2" (75F)	420
2" (75F)	420
3" (100F)	420
3" (100F)	420
5" (150F)	316
7" (200F)	209
7" (200F)	209

2

Select preferred drawer configuration

The column to the immediate right of each cabinet illustration indicates drawer heights.

3

Select drawer interior sets (optional)

Decide whether you want your cabinet to be pre-configured with drawer interior sets. The second column to the right of the illustration shows the numerical portion of the part number for the drawer interior sets which are included if you choose this configuration (designated by an "A" or "B" at the end of the part number – i.e., SC0750-0703FA or MW0900-0504FB). The chart below the illustration indicates the number of drawer compartments created by the interior sets (which are shown on the page following each footprint's Easy-Order models).

PART NO.

SC0900-0703F-

DRWS.

7

COMPARTS.

-

SC0900-0703FA-

7

114

4

Select base type


5

Select lock type

6

Select paint color

NW Narrow Width Easy-Order Cabinet Combinations



*inside usable drawer dimensions

NW Narrow Width Cabinets

- 100% extension drawers with 165 lb. load capacity

The slim footprint of these cabinets enables them to be used in a variety of tight spaces. They make especially versatile mobile cabinets.

How to order a Narrow Width Easy-Order Cabinet

1. Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by an "A" at the end of the part number – i.e., NW0600-0601NA). Drawer interior sets are shown on page 17.

2. Select base type.

NB = none
2FB = 2" frame base
4FB = 4" frame base
6FB = 6" frame base

For additional bases, see page 39; for Easy-Order mobile combinations, see page 16.

3. Select lock type.

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

4. Select paint color. For color chart, see the back cover or below.

EXAMPLE: to order an NW0600-0402N cabinet with a 6" frame base, an individual lock and Bright Blue paint, the part number would be **NW0600-0402N-F6RBBB**.

NW600 Cabinets

27 1/2" high

DRAWER HT.	DRAWER INTERIOR
2" (75N)	212
2" (75N)	212
2" (75N)	107
3" (100N)	107
3" (100N)	107
3" (100N)	107

PART NO.	DRWS.	COMPTS.
NW0600-0701N-	7	-
NW0600-0701NA-	7	59

DRAWER HT.	DRAWER INTERIOR
2" (75N)	105
2" (75N)	212
3" (100N)	107
3" (100N)	107
3" (100N)	107
5" (150N)	104

PART NO.	DRWS.	COMPTS.
NW0600-0601N-	6	-
NW0600-0601NA-	6	42

DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
2" (75N)	212
3" (100N)	212
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0600-0501N-	5	-
NW0600-0501NA-	5	50

DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
3" (100N)	212
4" (125N)	104
11" (300N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW0600-0401N-	4	-
NW0600-0401NA-	4	34

DRAWER HT.	DRAWER INTERIOR
3" (100N)	212
5" (150N)	104
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0600-0402N-	4	-
NW0600-0402NA-	4	24

DRAWER HT.	DRAWER INTERIOR
5" (150N)	104
5" (150N)	104
11" (300N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW0600-0301N-	3	-
NW0600-0301NA-	3	8

DRAWER HT.	DRAWER INTERIOR
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW0600-0201N-	2	-

DRAWER HT.	DRAWER INTERIOR
5" (150N)	104
450 DOOR	
BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
NW0600-0202N-	1	-
NW0600-0202NA-	1	4

NW750 Cabinets

33 1/2" high

DRAWER HT.	DRAWER INTERIOR
2" (75N)	212
2" (75N)	212
2" (75N)	107
3" (100N)	107
3" (100N)	107
3" (100N)	107
5" (150N)	104

PART NO.	DRWS.	COMPTS.
NW0750-0801N-	8	-
NW0750-0801NA-	8	60

DRAWER HT.	DRAWER INTERIOR
2" (75N)	212
2" (75N)	212
2" (75N)	107
3" (100N)	107
3" (100N)	107
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0750-0701N-	7	-
NW0750-0701NA-	7	53

DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
2" (75N)	018
3" (100N)	212
5" (150N)	104
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0750-0601N-	6	-
NW0750-0601NA-	6	60

DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
3" (100N)	212
4" (125N)	104
5" (150N)	104
11" (300N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW0750-0501N-	5	-
NW0750-0501NA-	5	38

NW900 Cabinets

39 3/8" high



DRAWER HT.	DRAWER INTERIOR
3" (100N)	212
3" (100N)	212
5" (150N)	104
5" (150N)	104
9" (250N)	-

PART NO.	DRWS.	COMPTS.
NW0750-0502N-  	5	-
NW0750-0502NA-  	5	32



DRAWER HT.	DRAWER INTERIOR
5" (150N)	107
5" (150N)	104
7" (200N)	107
9" (250N)	104

PART NO.	DRWS.	COMPTS.
NW0750-0401N-  	4	-
NW0750-0401NA-  	4	22



DRAWER HT.	DRAWER INTERIOR
5" (150N)	104
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW0750-0301N-  	3	-
NW0750-0301NA-  	3	4



DRAWER HT.	DRAWER INTERIOR
5" (150N)	104
600 DOOR	
ADJUSTABLE SHELF	
BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
NW0750-0302N-  	1	-
NW0750-0302NA-  	1	4



DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
2" (75N)	018
2" (75N)	212
2" (75N)	212
3" (100N)	107
3" (100N)	107
3" (100N)	107
5" (150N)	104
5" (150N)	104

PART NO.	DRWS.	COMPTS.
NW0900-0901N-  	9	-
NW0900-0901NA-  	9	89



DRAWER HT.	DRAWER INTERIOR
2" (75N)	212
2" (75N)	212
3" (100N)	107
3" (100N)	107
3" (100N)	107
3" (100N)	107
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0900-0801N-  	8	-
NW0900-0801NA-  	8	60



DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
2" (75N)	212
3" (100N)	212
5" (150N)	104
5" (150N)	104
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0900-0701N-  	7	-
NW0900-0701NA-  	7	58



DRAWER HT.	DRAWER INTERIOR
3" (100N)	212
3" (100N)	212
5" (150N)	104
5" (150N)	104
5" (150N)	104
9" (250N)	-

PART NO.	DRWS.	COMPTS.
NW0900-0601N-  	6	-
NW0900-0601NA-  	6	36



DRAWER HT.	DRAWER INTERIOR
5" (150N)	107
5" (150N)	107
5" (150N)	104
7" (200N)	104
9" (250N)	104

PART NO.	DRWS.	COMPTS.
NW0900-0501N-  	5	-
NW0900-0501NA-  	5	26



DRAWER HT.	DRAWER INTERIOR
7" (200N)	104
7" (200N)	107
9" (250N)	104
9" (250N)	108

PART NO.	DRWS.	COMPTS.
NW0900-0401N-  	4	-
NW0900-0401NA-  	4	23



DRAWER HT.	DRAWER INTERIOR
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW0900-0301N-  	3	-



DRAWER HT.	DRAWER INTERIOR
5" (150N)	104
750 DOOR	
ADJUSTABLE SHELF	
BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
NW0900-0302N-  	1	-
NW0900-0302NA-  	1	4

NW1225 Cabinets

52 3/16" high



DRAWER HT.	DRAWER INTERIOR
5" (150N)	107
6" (175N)	104
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW1225-0501N-  	5	-
NW1225-0501NA-  	5	11



DRAWER HT.	DRAWER INTERIOR
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER
11" (300N-FFH)	FILE DRAWER
12" (325N-FFH)	FILE DRAWER

PART NO.	DRWS.	COMPTS.
NW1225-0401N-  	4	-

NW Narrow Width **Easy-Order** Mobile Cabinet Combinations



Each mobile cabinet comes with:

- 2 fixed and 2 swivel casters with wheel locks
- Handles
- Individual drawer latches
- 100% extension drawers with 165 lb. load capacity

How to read the charts on this page

The 2 columns to the right of each cabinet illustration indicate:

- Drawer heights
- Drawer interior sets (shown on page 17)

The chart below the illustration indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (shown on page 17)

How to order a Narrow Width Easy-Order Mobile Cabinet

1. **Select Easy-Order Cabinet Combination** either without or with drawer interior sets (designated by an "A" near the end of the part number – i.e., NW0600-0601NA-M).

2. **Select lock type.**

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

3. **Select paint color.** For color chart, see back cover.

EXAMPLE: to order an NW0600-0501NA-M cabinet with an individual lock and Red paint, the part number would be **NW0600-0501NA-M-RGNR** (shown in photo at top of page).

NW600 Mobile Cabinets 33 1/8" high x 16 7/8" wide

DRAWER HT.	DRAWER INTERIOR
2" (75N)	105
2" (75N)	212
3" (100N)	107
3" (100N)	107
3" (100N)	107
5" (150N)	104

PART NO.	DRWS.	COMPTS.
NW0600-0601N-M-	6	-
NW0600-0601NA-M-	6	42

includes 4" x 1 1/4" casters

DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
2" (75N)	212
3" (100N)	212
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0600-0501N-M-	5	-
NW0600-0501NA-M-	5	50

includes 4" x 1 1/4" casters

DRAWER HT.	DRAWER INTERIOR
3" (100N)	212
5" (150N)	104
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0600-0402N-M-	4	-
NW0600-0402NA-M-	4	24

includes 4" x 1 1/4" casters

NW750 Mobile Cabinets 39 1/8" high x 16 7/8" wide

DRAWER HT.	DRAWER INTERIOR
2" (75N)	018
2" (75N)	018
3" (100N)	212
5" (150N)	104
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0750-0601N-M-	6	-
NW0750-0601NA-M-	6	60

includes 4" x 1 1/4" casters

DRAWER HT.	DRAWER INTERIOR
2" (75N)	212
2" (75N)	212
3" (100N)	212
3" (100N)	107
5" (150N)	107
9" (250N)	104

PART NO.	DRWS.	COMPTS.
NW0750-0602N-M-	6	-
NW0750-0602NA-M-	6	54

includes 4" x 1 1/4" casters

DRAWER HT.	DRAWER INTERIOR
3" (100N)	212
5" (150N)	107
5" (150N)	107
5" (150N)	104
7" (200N)	104

PART NO.	DRWS.	COMPTS.
NW0750-0503N-M-	5	-
NW0750-0503NA-M-	5	34

includes 4" x 1 1/4" casters

NW600 Mobile Work Centers 33 3/4" high x 33 3/4" wide

DRAW. HT.	INT.	INCL.	INT.
2" (75N)	212	5" (150N)	104
2" (75N)	107		
3" (100N)	107		
5" (150N)	104		
7" (200N)	104		

PART NO.	DRWS.	COMPTS.
MNW0600-0701-	6	-
MNW0600-0701A-	6	38

includes 4" x 2" casters

DRAW. HT.	INT.	INCLUDES
3" (100N)	212	600 DOOR
3" (100N)	212	ADJ. SHELF
5" (150N)	107	
9" (250N)	104	BOTTOM SHELF

PART NO.	DRWS.	COMPTS.
MNW0600-0601-	4	-
MNW0600-0601A-	4	35

includes 4" x 2" casters

INCL.	INT.	INCL.	INT.
5" (150N)	104	5" (150N)	104
450 DOOR		450 DOOR	
BOTTOM SHELF		BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
MNW0600-0401-	2	-
MNW0600-0401A-	2	8

includes 4" x 2" casters

Mobile Cabinet Options



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 28 1/2" deep.

PART NO.	MOUNTS TO
FS-36DX15-L	left side
FS-36DX15-R	right side

NW Mobile Cabinet Tops

For top descriptions, see page 67.

PART NO.	DESCRIPTION	HT.
NW-RT	retainer top with ribbed mat	3/4"
2NW-RT*	retainer top with ribbed mat	3/4"
NW1BCT	butcher block	1 3/4"
NW2BCT*	butcher block	1 3/4"
NW1PCT	plastic laminate	1 9/16"
NW2PCT*	plastic laminate	1 9/16"

*use with mobile work centers

Mesh Drawer Liner

Non-slip polyester mesh liner protects items in drawers without drawer interior sets from shifting or sliding. Protects drawer bottom from scratches and dents. Liner is non-toxic, washable and treated to inhibit mold and mildew.

PART NO.
NWMDL



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
NWDR104-■	2	5 1/2"
	2	6 1/4"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
NWDR105-■	3	4 1/8"
	2	7 1/2"



For drawer heights 75 through 300

PART NO.	COMPTS.	CMPT. WIDTH
NWDR106-■	3	6 1/4"
	3	5 1/2"

How to order a Narrow Width Easy-Order Drawer Interior Set

To order the drawer interior sets shown on this page, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order an NWDR106 drawer interior set for a 100 height (3") drawer, the part ordering number would be **NWDR106-100**.



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
NWDR107-■	4	4 1/8"
	3	7 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
NWDR108-■	4	5 1/2"
	4	6 1/4"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
NWDR209-■	6	3 1/2"
	3	4 1/8"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
NWDR212-■	4	4 1/8"
	8	3 1/2"



For drawer heights 75 through 100

PART NO.	COMPTS.	CMPT. SIZE
NWDR008-■	8	6" x 6"



For drawer heights 75 through 100

PART NO.	COMPTS.	CMPT. SIZE
NWDR012-■	8	3" x 6"
	4	6" x 6"



For drawer heights 75 through 100

PART NO.	COMPTS.	CMPT. SIZE
NWDR016-■	16	3" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
NWDR018-■	2	6" x 6"
	8	3" x 6"
	8	3" x 3"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
NWDR024-■	16	3" x 3"
	8	3" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
NWDR082-■	16	3" x 3"
	24	3" x 2"



For drawer height 75


PART NO.	COMPTS.	CMPT. SIZE
NWDR083-■	32	2" x 3"
	24	2" x 2"



Sliding accessory tray

For drawer heights 100 through 250		
PART NO.	COMPTS.	CMPT. WID.
NWDR-AT06-■	5	3"

MP Width Easy-Order Cabinet Combinations



*inside usable drawer dimensions

MP Width Cabinets

- 100% extension drawers

MP cabinets are the perfect storage solution when space is at a premium, and make perfect mobile cabinets and toolboxes.

How to order an MP Width Easy-Order Cabinet

1. Select Easy-Order Cabinet Combination

either without or with drawer interior sets (designated by an "A" at the end of the part number – i.e., MP0750-0302NA). Drawer interior sets are shown on page 21.

2. Select drawer weight-bearing capacity.

N = 165 lb. (75kg)
F = 440 lb. (200kg)

3. Select base type.

NB = none
FT = fork truck
2FB = 2" frame base
4FB = 4" frame base
6FB = 6" frame base

For additional bases, see page 39; for Easy-Order mobile combinations, see page 20.

4. Select lock type.

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

5. Select paint color. For color chart, see the back cover or below.

EXAMPLE: to order an MP0750-0302A cabinet with 440 lb. capacity drawers, a fork truck base, an individual lock and Light Gray paint, the part number would be **MP0750-0302FA-FTRGLG**.

MP300 Cabinets 15 3/4" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	2" (75)	316
	2" (75)	209
	2" (75)	209

PART NO.	DRWS.	COMPTS.
MP0300-0401	4	-
MP0300-0401A	4	50

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	3" (100)	209
	4" (125)	209

PART NO.	DRWS.	COMPTS.
MP0300-0301	3	-
MP0300-0301A	3	34

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	209
	7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0300-0201	2	-
MP0300-0201A	2	13

	DRAWER HT.	DRAWER INTERIOR
	5" (150)	209
	5" (150)	104

PART NO.	DRWS.	COMPTS.
MP0300-0202	2	-
MP0300-0202A	2	13

MP600 Cabinets 27 1/2" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	2" (75)	316
	2" (75)	209
	2" (75)	209
	3" (100)	209
	3" (100)	209
	3" (100)	209

PART NO.	DRWS.	COMPTS.
MP0600-0701	7	-
MP0600-0701A	7	77

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	028
	2" (75)	316
	3" (100)	316
	3" (100)	209
	3" (100)	209
	5" (150)	104

PART NO.	DRWS.	COMPTS.
MP0600-0601	6	-
MP0600-0601A	6	82

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	2" (75)	316
	3" (100)	209
	5" (150)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0600-0501	5	-
MP0600-0501A	5	49

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	209
	3" (100)	209
	5" (150)	104
	5" (150)	104

PART NO.	DRWS.	COMPTS.
MP0600-0502	5	-
MP0600-0502A	5	42

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	3" (100)	209
	4" (125)	104
	11" (300)	-

PART NO.	DRWS.	COMPTS.
MP0600-0401	4	-
MP0600-0401A	4	29

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	5" (150)	209
	5" (150)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0600-0402	4	-
MP0600-0402A	4	33

	DRAWER HT.	DRAWER INTERIOR
	5" (150)	209
	7" (200)	104
	9" (250)	104

PART NO.	DRWS.	COMPTS.
MP0600-0302	3	-
MP0600-0302A	3	17

	DRAWER HT.	DRAWER INTERIOR
	5" (150)	104
	450 DOOR	
	BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
MP0600-0202	1	-
MP0600-0202A	1	4

MP750 Cabinets

33 1/2" high

DRAWER HT.	DRAWER INTERIOR
2" (75)	510
2" (75)	510
2" (75)	316
2" (75)	316
3" (100)	209
3" (100)	209
9" (250)	104

PART NO.	DRWS.	COMPTS.
MP0750-0702	7	-
MP0750-0702	7	74

DRAWER HT.	DRAWER INTERIOR
3" (100)	316
3" (100)	209
5" (150)	209
5" (150)	104
9" (250)	104

PART NO.	DRWS.	COMPTS.
MP0750-0502	5	-
MP0750-0502	5	42

DRAWER HT.	DRAWER INTERIOR
2" (75)	028
2" (75)	316
3" (100)	316
3" (100)	209
3" (100)	209
5" (150)	209
5" (150)	104

PART NO.	DRWS.	COMPTS.
MP0750-0703	7	-
MP0750-0703	7	91

DRAWER HT.	DRAWER INTERIOR
5" (150)	209
5" (150)	104
7" (200)	104
9" (250)	104

PART NO.	DRWS.	COMPTS.
MP0750-0401	4	-
MP0750-0401	4	21

DRAWER HT.	DRAWER INTERIOR
2" (75)	028
2" (75)	316
3" (100)	209
5" (150)	209
5" (150)	104
7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0750-0601	6	-
MP0750-0601	6	70

DRAWER HT.	DRAWER INTERIOR
3" (100)	316
5" (150)	209
7" (200)	104
11" (300)	-

PART NO.	DRWS.	COMPTS.
MP0750-0402	4	-
MP0750-0402	4	29

DRAWER HT.	DRAWER INTERIOR
2" (75)	316
2" (75)	316
3" (100)	209
3" (100)	209
5" (150)	104
9" (250)	104

PART NO.	DRWS.	COMPTS.
MP0750-0602	6	-
MP0750-0602	6	58

DRAWER HT.	DRAWER INTERIOR
5" (150)	104
600 DOOR	
ADJUSTABLE SHELF	
BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
MP0750-0302	1	-
MP0750-0302	1	4

MP900 Cabinets

39 3/8" high

DRAWER HT.	DRAWER INTERIOR
2" (75)	510
2" (75)	510
2" (75)	316
2" (75)	316
3" (100)	209
3" (100)	209
3" (100)	209
5" (150)	104
5" (150)	104

PART NO.	DRWS.	COMPTS.
MP0900-0901	9	-
MP0900-0901	9	87

DRAWER HT.	DRAWER INTERIOR
5" (150)	209
5" (150)	104
5" (150)	104
7" (200)	104
9" (250)	104

PART NO.	DRWS.	COMPTS.
MP0900-0501	5	-
MP0900-0501	5	25

DRAWER HT.	DRAWER INTERIOR
2" (75)	316
2" (75)	316
3" (100)	316
3" (100)	316
3" (100)	209
3" (100)	209
5" (150)	104
7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0900-0801	8	-
MP0900-0801	8	90

DRAWER HT.	DRAWER INTERIOR
3" (100)	316
5" (150)	209
5" (150)	209
7" (200)	104
11" (300)	-

PART NO.	DRWS.	COMPTS.
MP0900-0502	5	-
MP0900-0502	5	38

DRAWER HT.	DRAWER INTERIOR
2" (75)	028
2" (75)	316
3" (100)	316
5" (150)	209
5" (150)	209
5" (150)	104
7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0900-0701	7	-
MP0900-0701	7	86

DRAWER HT.	DRAWER INTERIOR
3" (100)	209
7" (200)	104
600 DOOR	
ADJUSTABLE SHELF	
BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
MP0900-0402	2	-
MP0900-0402	2	13

DRAWER HT.	DRAWER INTERIOR
3" (100)	316
3" (100)	209
5" (150)	209
5" (150)	104
5" (150)	104
9" (250)	104

PART NO.	DRWS.	COMPTS.
MP0900-0601	6	-
MP0900-0601	6	46

DRAWER HT.	DRAWER INTERIOR
5" (150)	104
750 DOOR	
ADJUSTABLE SHELF	
BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
MP0900-0302	1	-
MP0900-0302	1	4

MP Width Easy-Order Mobile Cabinet Combinations



Each mobile cabinet comes with:

- 2 fixed and 2 swivel casters with wheel locks
- Tubular steel handles
- Individual drawer latches
- 100% extension drawers

How to read the charts on this page

The 2 columns to the right of each cabinet illustration indicate:

- Drawer heights
- Drawer interior sets (shown on page 21)

The chart below the illustration indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (shown on page 21)

How to order an MP Width Easy-Order Mobile Cabinet

1. **Select Easy-Order Cabinet Combination** either without or with drawer interior sets (designated by an "A" near the end of the part number – i.e., MP0600-0402NA-M).

2. **Select drawer weight-bearing capacity.**

N = 165 lb. (75kg)

F = 440 lb. (200kg)

3. **Select lock type.**

NL = none

RG = individual

KA = keyed-alike

MA = master


For additional lock options, see page 62.

4. **Select paint color.** For color chart, see back cover.

EXAMPLE: to order an MP0600-0501A-M cabinet with 165 lb. capacity drawers, an individual lock, Bright Blue paint and a retainer top, the part number would be **MP0600-0501NA-M-RGBB**, with an MP-RT top (shown in photo at top of page).

MP300 Mobile Carts

32 1/2" high x 22 3/16" wide



PART NO.	DRWS.	COMPTS.
MSC-□	-	-

includes 4" x 1 1/4" casters

includes 4-sided retainer top with ribbed mat

DRAWER HT.	DRAWER INTERIOR
2" (75)	316
3" (100)	209
4" (125)	209

PART NO.	DRWS.	COMPTS.
MCMP0300-0301-□-□	3	-
MCMP0300-0301-□-□	3	34

includes 4" x 1 1/4" casters

includes 4-sided retainer top with ribbed mat

DRAWER HT.	DRAWER INTERIOR
3" (100)	209
7" (200)	104

PART NO.	DRWS.	COMPTS.
MCMP0300-0201-□-□	2	-
MCMP0300-0201-□-□	2	13

includes 4" x 1 1/4" casters

includes 4-sided retainer top with ribbed mat

MP600 Mobile Cabinets

35 1/2" high x 22 3/16" wide



DRAWER HT.	DRAWER INTERIOR
2" (75)	028
2" (75)	316
3" (100)	316
3" (100)	209
3" (100)	209
5" (150)	104

PART NO.	DRWS.	COMPTS.
MP0600-0601-□-M-□	6	-
MP0600-0601-□-A-M-□	6	82

includes 6" x 2" casters

DRAWER HT.	DRAWER INTERIOR
2" (75)	316
2" (75)	316
3" (100)	209
5" (150)	104
7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0600-0501-□-M-□	5	-
MP0600-0501-□-A-M-□	5	49

includes 6" x 2" casters

DRAWER HT.	DRAWER INTERIOR
3" (100)	316
5" (150)	209
5" (150)	104
7" (200)	104

PART NO.	DRWS.	COMPTS.
MP0600-0402-□-M-□	4	-
MP0600-0402-□-A-M-□	4	33

includes 6" x 2" casters

MP600 Mobile Work Centers

35 1/2" high



DRAW.HT. IN.	INCLUDES
2" (75) 316	600 DOOR
2" (75) 316	ADJ. SHELF
3" (100) 209	
5" (150) 104	
7" (200) 104	BOTTOM SHELF

PART NO.	DRWS.	COMPTS.
MMP0600-0702-□-□	5	-
MMP0600-0702A-□-□	5	49

includes 6" x 2" casters

44 3/8" wide



DRAW.HT. IN.	DRAW.HT. IN.
5" (150) 104	5" (150) 104
450 DOOR	450 DOOR
BOTTOM SHELF	BOTTOM SHELF

PART NO.	DRWS.	COMPTS.
MMP0600-0402-□-□	2	-
MMP0600-0402A-□-□	2	8

includes 6" x 2" casters

44 3/8" wide



DRAW.HT. IN.	INCLUDES
2" (75) 510	600 DOOR
2" (75) 018	
3" (100) 316	ADJ. SHELF
5" (150) 209	
7" (200) 104	BOTTOM SHELF

PART NO.	DRWS.	COMPTS.
MMPNW0600-0703-□-□	5	-
MMPNW0600-0703A-□-□	5	57

includes 6" x 2" casters

39" wide (MP width drawers, NW width door)

Mobile Cabinet Options



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 28 1/2" deep. Not for use with mobile carts. When used with MP600 mobile cabinets shown above, cabinets will have black plastic handles.

PART NO.	MOUNTS TO
FS-36DX15-L	left side
FS-36DX15-R	right side

MP Mobile Cabinet Tops

For top descriptions, see page 67.

PART NO.	DESCRIPTION	HT.
MP-RT	retainer top with ribbed mat	3/4"
2MP-RT*	retainer top with ribbed mat	3/4"
MP1BCT	butcher block	1 3/4"
MP2BCT*	butcher block	1 3/4"
MP1PCT	plastic laminate	1 9/16"
MP2PCT*	plastic laminate	1 9/16"

*use with 2 MP housings

Mesh Drawer Liner

Non-slip polyester mesh liner protects items in drawers without drawer interior sets from shifting or sliding. Protects drawer bottom from scratches and dents. Liner is non-toxic, washable and treated to inhibit mold and mildew.

PART NO.
MPMDL



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
MPDR104-■	2	7 1/2"
	2	9 1/4"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
MPDR206-■	6	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
MPDR209-■	9	5 1/2"

How to order an MP Width Easy-Order Drawer Interior Set

To order the drawer interior sets shown on this page, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order an MPDR206 drawer interior set for a 100 height (3") drawer, the part ordering number would be **MPDR206-100**.



For drawer heights 75 through 150

PART NO.	COMPTS.	CMPT. WIDTH
MPDR312-■	3	3 1/2"
	9	4 1/8"



For drawer heights 75 through 150

PART NO.	COMPTS.	CMPT. WIDTH
MPDR316-■	4	3 1/2"
	12	4 1/8"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. WIDTH
MPDR430-■	18	2 5/8"
	12	3 1/2"



For drawer heights 75 through 150

PART NO.	COMPTS.	CMPT. DEPTH
MPDR510-■	6	3 1/2"
	4	15 5/8"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. WIDTH
MPDR524-■	12	2 1/8"
	12	2 5/8"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. SIZE
MPDR012-■	12	6" x 6"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. SIZE
MPDR018-■	12	3" x 6"
	6	6" x 6"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
MPDR024-■	24	3" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
MPDR028-■	16	3" x 3"
	8	3" x 6"
	4	6" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. WIDTH
MPDR480-■	24	1 1/4"
	16	1 3/4"



For drawer height 75


PART NO.	COMPTS.	CMPT. WIDTH
MPDR482-■	23	1 3/4"
	14	2 3/4"



Sliding accessory tray

For drawer heights 100 through 300		
PART NO.	COMPTS.	CMPT. WIDTH
MPDR-AT10-■	1	6"
	8	3"

SC Standard Width Easy-Order Cabinet Combinations



*inside usable drawer dimensions

SC Standard Width Cabinets

- 100% extension drawers with 440 lb. load capacity

Our most popular footprint, the SC cabinet is available with a large variety of drawer heights and drawer interior sets.

How to order a Standard Width Easy-Order Cabinet

1. Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by an "A" at the end of the part number – i.e., SC0750-0703FA). Drawer interior sets are shown on pages 26-27.

2. Select base type.

- NB = none
- FT = fork truck
- PT = pallet truck
- 2FB = 2" frame base
- 4FB = 4" frame base
- 6FB = 6" frame base

For additional bases, see page 39; for Easy-Order mobile combinations, see page 25.

3. Select lock type.

- NL* = none
- RG = individual
- KA = keyed-alike
- MA = master

*not available for double hinged door cabinets

For additional lock options, see page 62.

4. Select paint color. For color chart, see back cover or below.

EXAMPLE: to order an SC0900-1101FA cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **SC0900-1101FA-FTRGBB**.

SC750 Cabinets 33 1/2" high

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	524
	2" (75F)	524
	2" (75F)	420
	2" (75F)	420
	3" (100F)	312
	3" (100F)	312
	3" (100F)	209

PART NO.	DRWS.	COMPARTS.
SC0750-0901F-	9	-
SC0750-0901FA-	9	193

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	524
	3" (100F)	420
	3" (100F)	420
	3" (100F)	312
	5" (150F)	312
	5" (150F)	209

PART NO.	DRWS.	COMPARTS.
SC0750-0703F-	7	-
SC0750-0703FA-	7	133

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	3" (100F)	420
	3" (100F)	312
	3" (100F)	312
	3" (100F)	209
	3" (100F)	209
	5" (150F)	209

PART NO.	DRWS.	COMPARTS.
SC0750-0704F-	7	-
SC0750-0704FA-	7	91

	DRAWER HT.	DRAWER INT.
	5" (150F)	312
	7" (200F)	209
	7" (200F)	104
	7" (200F)	104

PART NO.	DRWS.	COMPARTS.
SC0750-0404F-	4	-
SC0750-0404FA-	4	29

SC900 Cabinets 39 3/8" high

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	524
	2" (75F)	524
	2" (75F)	524
	2" (75F)	524
	2" (75F)	420
	2" (75F)	420
	3" (100F)	312
	3" (100F)	312
	3" (100F)	312

PART NO.	DRWS.	COMPARTS.
SC0900-1101F-	11	-
SC0900-1101FA-	11	244

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	036
	2" (75F)	524
	2" (75F)	524
	2" (75F)	524
	3" (100F)	420
	3" (100F)	420
	4" (125F)	316
	4" (125F)	316

PART NO.	DRWS.	COMPARTS.
SC0900-1001F-	10	-
SC0900-1001FA-	10	252

	DRAWER HT.	DRAWER INT.
	2" (75F)	524
	2" (75F)	524
	2" (75F)	420
	2" (75F)	420
	3" (100F)	316
	3" (100F)	316
	3" (100F)	316
	5" (150F)	209
	5" (150F)	209

PART NO.	DRWS.	COMPARTS.
SC0900-0901F-	9	-
SC0900-0901FA-	9	154

	DRAWER HT.	DRAWER INT.
	3" (100F)	524
	3" (100F)	524
	3" (100F)	524
	3" (100F)	420
	3" (100F)	420
	3" (100F)	420
	3" (100F)	316
	3" (100F)	316
	3" (100F)	316

PART NO.	DRWS.	COMPARTS.
SC0900-0904F-	9	-
SC0900-0904FA-	9	180

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	3" (100F)	420
	3" (100F)	420
	3" (100F)	312
	3" (100F)	312
	3" (100F)	312
	5" (150F)	209
	5" (150F)	209

PART NO.	DRWS.	COMPARTS.
SC0900-0804F-	8	-
SC0900-0804FA-	8	114

	DRAWER HT.	DRAWER INT.
	2" (75F)	420
	2" (75F)	420
	3" (100F)	420
	3" (100F)	420
	5" (150F)	316
	7" (200F)	209
	7" (200F)	209

PART NO.	DRWS.	COMPARTS.
SC0900-0703F-	7	-
SC0900-0703FA-	7	114

	DRAWER HT.	DRAWER INT.
	2" (75F)	524
	2" (75F)	524
	3" (100F)	420
	3" (100F)	420
	5" (150F)	312
	5" (150F)	209
	9" (250F)	104

PART NO.	DRWS.	COMPARTS.
SC0900-0704F-	7	-
SC0900-0704FA-	7	113

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	3" (100F)	420
	3" (100F)	316
	5" (150F)	316
	7" (200F)	209
	9" (250F)	104

PART NO.	DRWS.	COMPARTS.
SC0900-0602F-	6	-
SC0900-0602FA-	6	85

SC1050 Cabinets 45 1/4" high

	DRAWER HT.	DRAWER INT.
	5" (150F)	316
	5" (150F)	316
	5" (150F)	209
	5" (150F)	209
	5" (150F)	104
	5" (150F)	104


PART NO.	DRWS.	COMPARTS.
SC0900-0605F- 	6	-
SC0900-0605FA- 	6	58

	DRAWER HT.	DRAWER INT.
	5" (150F)	316
	5" (150F)	316
	5" (150F)	316
	7" (200F)	209
	9" (250F)	104

PART NO.	DRWS.	COMPARTS.
SC0900-0501F- 	5	-
SC0900-0501FA- 	5	61

	DRAWER HT.	DRAWER INT.
	5" (150F)	316
	5" (150F)	316
	7" (200F)	209
	7" (200F)	209
	7" (200F)	104

PART NO.	DRWS.	COMPARTS.
SC0900-0504F- 	5	-
SC0900-0504FA- 	5	54



PART NO.	TRAYS
SC0900-0304D- 	3

door cabinet is 29 1/2" deep

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	524
	2" (75F)	524
	3" (100F)	420
	3" (100F)	420
	3" (100F)	420
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312


PART NO.	DRWS.	COMPARTS.
SC1050-1001F- 	10	-
SC1050-1001FA- 	10	216

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	3" (100F)	420
	3" (100F)	312
	3" (100F)	312
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	5" (150F)	209
	7" (200F)	209

PART NO.	DRWS.	COMPARTS.
SC1050-0801F- 	8	-
SC1050-0801FA- 	8	106

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	5" (150F)	312
	5" (150F)	312
	7" (200F)	209
	7" (200F)	209
	9" (250F)	104

PART NO.	DRWS.	COMPARTS.
SC1050-0601F- 	6	-
SC1050-0601FA- 	6	66



PART NO.	TRAYS
SC1050-0301D- 	3

door cabinet is 29 1/2" deep

SC1225 Cabinets 52 3/16" high

	DRAWER HT.	DRAWER INT.
	2" (75F)	524
	2" (75F)	524
	2" (75F)	524
	2" (75F)	524
	3" (100F)	316
	3" (100F)	316
	3" (100F)	316
	3" (100F)	316
	3" (100F)	316
	3" (100F)	316
	5" (150F)	209

PART NO.	DRWS.	COMPARTS.
SC1225-1301F- 	13	-
SC1225-1301FA- 	13	241

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	524
	3" (100F)	524
	3" (100F)	420
	3" (100F)	420
	5" (150F)	312
	5" (150F)	312
	7" (200F)	209
	7" (200F)	209

PART NO.	DRWS.	COMPARTS.
SC1225-1001F- 	10	-
SC1225-1001FA- 	10	202

	DRAWER HT.	DRAWER INT.
	2" (75F)	524
	2" (75F)	524
	2" (75F)	524
	3" (100F)	316
	3" (100F)	316
	7" (200F)	209
	9" (250F)	104
	9" (250F)	104

PART NO.	DRWS.	COMPARTS.
SC1225-0901F- 	9	-
SC1225-0901FA- 	9	137

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	3" (100F)	420
	4" (125F)	420
	5" (150F)	316
	5" (150F)	316
	7" (200F)	209
	7" (200F)	209
	7" (200F)	104

PART NO.	DRWS.	COMPARTS.
SC1225-0801F- 	8	-
SC1225-0801FA- 	8	114

	DRAWER HT.	DRAWER INT.
	4" (125F)	420
	5" (150F)	316
	5" (150F)	316
	5" (150F)	316
	7" (200F)	209
	7" (200F)	209
	9" (250F)	104


PART NO.	DRWS.	COMPARTS.
SC1225-0701F- 	7	-
SC1225-0701FA- 	7	90

	DRAWER HT.	DRAWER INT.
	4" (125F)	420
	7" (200F)	316
	7" (200F)	209
	7" (200F)	209
	9" (250F)	104
	9" (250F)	104

PART NO.	DRWS.	COMPARTS.
SC1225-0601F- 	6	-
SC1225-0601FA- 	6	62

	DRAWER HT.	DRAWER INT.
	8" (225F)	209
	9" (250F)	206
	9" (250F)	206
	9" (250F)	104
	9" (250F)	104

PART NO.	DRWS.	COMPARTS.
SC1225-0502F- 	5	-
SC1225-0502FA- 	5	29



PART NO.	TRAYS
SC1225-0301D- 	3

door cabinet is 29 1/2" deep

SC Standard Width *Easy-Order* Cabinet Combinations

SC1350 Cabinets

57 1/8" high

DRAWER HT.	DRAWER INT.
2" (75F)	036
2" (75F)	036
2" (75F)	524
2" (75F)	524
2" (75F)	524
2" (75F)	524
2" (75F)	524
2" (75F)	524
2" (75F)	420
2" (75F)	420
3" (100F)	420
3" (100F)	312
3" (100F)	312
3" (100F)	312
3" (100F)	312

PART NO.	DRWS.	COMPTS.
SC1350-1601F- 	16	-
SC1350-1601FA- 	16	344

DRAWER HT.	DRAWER INT.
2" (75F)	524
2" (75F)	524
2" (75F)	524
2" (75F)	524
3" (100F)	316
3" (100F)	316
3" (100F)	316
3" (100F)	316
4" (125F)	316
6" (175F)	209
6" (175F)	209
6" (175F)	209

PART NO.	DRWS.	COMPTS.
SC1350-1204F- 	12	-
SC1350-1204FA- 	12	203

DRAWER HT.	DRAWER INT.
5" (150F)	316
5" (150F)	316
5" (150F)	316
5" (150F)	316
5" (150F)	212
5" (150F)	212
5" (150F)	212
5" (150F)	212
5" (150F)	212

PART NO.	DRWS.	COMPTS.
SC1350-0903F- 	9	-
SC1350-0903FA- 	9	124

DRAWER HT.	DRAWER INT.
5" (150F)	312
5" (150F)	312
5" (150F)	209
5" (150F)	209
7" (200F)	209
9" (250F)	104
11" (300F)	104

PART NO.	DRWS.	COMPTS.
SC1350-0703F- 	7	-
SC1350-0703FA- 	7	59

DRAWER HT.	DRAWER INT.
2" (75F)	320
2" (75F)	320
2" (75F)	320
2" (75F)	320
2" (75F)	320
2" (75F)	320
2" (75F)	320
2" (75F)	320
3" (100F)	320
3" (100F)	320
3" (100F)	320
3" (100F)	320
3" (100F)	320
3" (100F)	320
3" (100F)	320
4" (125F)	320

PART NO.	DRWS.	COMPTS.
SC1350-1502F- 	15	-
SC1350-1502FA- 	15	300

DRAWER HT.	DRAWER INT.
2" (75F)	320
2" (75F)	320
2" (75F)	320
2" (75F)	320
4" (125F)	316
4" (125F)	316
4" (125F)	316
4" (125F)	316
5" (150F)	312
5" (150F)	312
9" (250F)	104

PART NO.	DRWS.	COMPTS.
SC1350-1103F- 	11	-
SC1350-1103FA- 	11	172

DRAWER HT.	DRAWER INT.
5" (150F)	312
5" (150F)	312
5" (150F)	312
5" (150F)	209
5" (150F)	209
7" (200F)	209
7" (200F)	209
7" (200F)	209

PART NO.	DRWS.	COMPTS.
SC1350-0801F- 	8	-
SC1350-0801FA- 	8	81

DRAWER HT.	DRAWER INT.
7" (200F)	206
7" (200F)	206
7" (200F)	206
7" (200F)	206
9" (250F)	104
11" (300F)	104

PART NO.	DRWS.	COMPTS.
SC1350-0601F- 	6	-
SC1350-0601FA- 	6	32

DRAWER HT.	DRAWER INT.
2" (75F)	524
2" (75F)	524
3" (100F)	524
3" (100F)	524
3" (100F)	420
3" (100F)	420
3" (100F)	420
3" (100F)	420
3" (100F)	420
3" (100F)	420
3" (100F)	420
3" (100F)	420
3" (100F)	312
5" (150F)	312
5" (150F)	312

PART NO.	DRWS.	COMPTS.
SC1350-1302F- 	13	-
SC1350-1302FA- 	13	252

DRAWER HT.	DRAWER INT.
2" (75F)	524
2" (75F)	524
3" (100F)	420
3" (100F)	420
3" (100F)	420
5" (150F)	316
5" (150F)	316
5" (150F)	316
7" (200F)	209
9" (250F)	104

PART NO.	DRWS.	COMPTS.
SC1350-1002F- 	10	-
SC1350-1002FA- 	10	169

DRAWER HT.	DRAWER INT.
5" (150F)	312
5" (150F)	312
5" (150F)	312
5" (150F)	312
5" (150F)	312
5" (150F)	312
7" (200F)	206
9" (250F)	206

PART NO.	DRWS.	COMPTS.
SC1350-0803F- 	8	-
SC1350-0803FA- 	8	84

DRAWER HT.	DRAWER INT.
9" (250F)	104
9" (250F)	104
9" (250F)	104
9" (250F)	104
11" (300F)	104
11" (300F)	104

PART NO.	DRWS.	COMPTS.
SC1350-0501F- 	5	-
SC1350-0501FA- 	5	20

DRAWER HT.	DRAWER INT.
2" (75F)	524
2" (75F)	524
2" (75F)	524
2" (75F)	524
2" (75F)	420
2" (75F)	420
2" (75F)	420
2" (75F)	420
4" (125F)	316
6" (175F)	209
7" (200F)	209
9" (250F)	104


PART NO.	DRWS.	COMPTS.
SC1350-1202F- 	12	-
SC1350-1202FA- 	12	214

DRAWER HT.	DRAWER INT.
3" (100F)	420
3" (100F)	420
3" (100F)	420
3" (100F)	420
5" (150F)	316
5" (150F)	316
5" (150F)	316
5" (150F)	316
5" (150F)	316
7" (200F)	209

PART NO.	DRWS.	COMPTS.
SC1350-1004F- 	10	-
SC1350-1004FA- 	10	169

DRAWER HT.	DRAWER INT.
5" (150F)	312
7" (200F)	312
7" (200F)	312
7" (200F)	209
7" (200F)	209
7" (200F)	209
7" (200F)	104

PART NO.	DRWS.	COMPTS.
SC1350-0701F- 	7	-
SC1350-0701FA- 	7	67



PART NO.	TRAYS
SC1350-0401D- 	4

door cabinet is 29 1/2" deep

SC600 Mobile Cabinets 35 1/2" high x 28 1/4" wide

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	524
	2" (75F)	524
	3" (100F)	420
	3" (100F)	420
	3" (100F)	420

PART NO.	DRWS.	COMPTS.
SC0600-0701F-M-■□	7	-
SC0600-0701FA-M-■□	7	180

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	3" (100F)	420
	3" (100F)	316
	5" (150F)	316
	5" (150F)	209

PART NO.	DRWS.	COMPTS.
SC0600-0502F-M-■□	5	-
SC0600-0502FA-M-■□	5	81

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	5" (150F)	316
	5" (150F)	316
	7" (200F)	209

PART NO.	DRWS.	COMPTS.
SC0600-0402F-M-■□	4	-
SC0600-0402FA-M-■□	4	61

SC750 Mobile Cabinets 41 1/2" high x 28 1/4" wide

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	420
	2" (75F)	420
	3" (100F)	316
	3" (100F)	316
	3" (100F)	209
	5" (150F)	209

PART NO.	DRWS.	COMPTS.
SC0750-0801F-M-■□	8	-
SC0750-0801FA-M-■□	8	162

	DRAWER HT.	DRAWER INT.
	3" (100F)	316
	3" (100F)	316
	3" (100F)	316
	5" (150F)	209
	5" (150F)	209
	5" (150F)	209

PART NO.	DRWS.	COMPTS.
SC0750-0617F-M-■□	6	-
SC0750-0617FA-M-■□	6	75

	DRAWER HT.	DRAWER INT.
	5" (150F)	316
	5" (150F)	316
	7" (200F)	209
	9" (250F)	104

PART NO.	DRWS.	COMPTS.
SC0750-0401F-M-■□	4	-
SC0750-0401FA-M-■□	4	45

SC900 Mobile Cabinets 47 3/8" high x 28 1/4" wide

	DRAWER HT.	DRAWER INT.
	2" (75F)	036
	2" (75F)	036
	2" (75F)	524
	2" (75F)	524
	3" (100F)	420
	3" (100F)	420
	3" (100F)	316
	3" (100F)	316
	3" (100F)	209
	3" (100F)	209

PART NO.	DRWS.	COMPTS.
SC0900-1002F-M-■□	10	-
SC0900-1002FA-M-■□	10	210

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	3" (100F)	420
	3" (100F)	316
	3" (100F)	316
	4" (125F)	312
	4" (125F)	312
	4" (125F)	209
	4" (125F)	209

PART NO.	DRWS.	COMPTS.
SC0900-0805F-M-■□	8	-
SC0900-0805FA-M-■□	8	114

	DRAWER HT.	DRAWER INT.
	3" (100F)	420
	5" (150F)	420
	5" (150F)	316
	5" (150F)	316
	5" (150F)	209
	7" (200F)	209

PART NO.	DRWS.	COMPTS.
SC0900-0607F-M-■□	6	-
SC0900-0607FA-M-■□	6	90



Each mobile cabinet comes with:

- 2 fixed and 2 swivel 6" x 2" casters with wheel locks
- Tubular steel handles
- Individual drawer latches
- 100% extension drawers with 440 lb. load capacity

How to read the charts on this page

The 2 columns to the right of each cabinet illustration indicate:

- Drawer heights
- Drawer interior sets (see pages 26-27)

The chart below the illustration indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (see pages 26-27)

How to order a Standard Width Easy-Order Mobile Cabinet

1. Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by an "A" near the end of the part number – i.e., SC0600-0502FA-M).

2. ■ Select lock type.

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

3. □ Select paint color. For color chart, see back cover or below.

EXAMPLE: to order an SC0600-0502FA-M cabinet with an individual lock, Red paint and a retainer top, the part number would be **SC0600-0502FA-M-RGNR**, with an SC-RT top (shown in photo at top of page).

Mobile Cabinet Options

Hanging Shelf Cabinet

Optional shelf cabinet, painted to match mobile cabinet, is 28 1/4" wide x 15" deep x 29" high. It is attached to the side of mobile cabinet for easy maneuvering. Each cabinet has a bottom shelf and 1 adjustable 13 1/2" deep shelf. Individual lock (RG) and 2 keys are furnished. Can only be mounted on 750 height or higher mobile cabinets.



PART NO.	DESCRIPTION
OHC2829-CM	shelf cabinet
OHC1BCT/36	butcher block top (28 1/4" x 15" x 1 1/4")



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 28 1/2" deep. When used with mobile cabinets shown above, cabinets will have black plastic handles.

PART NO.	MOUNTS TO
FS-36DX15-L	left side
FS-36DX15-R	right side

Standard Width Mobile Cabinet Tops

For additional top choices, see page 67.

PART NO.	DESCRIPTION	HT.
SC-RT	retainer top w/ribbed mat	3/4"
SC1BCT	butcher block	1 3/4"
SC1PCT	plastic laminate	1 9/16"

Mesh Drawer Liner

Non-slip polyester mesh liner protects items in drawers without drawer interior sets from shifting or sliding. Liner is non-toxic, washable and treated to inhibit mold and mildew.

PART NO.
SCMDL

GG (Green paint) LG (Light Gray paint) NR (Red paint) SN (Sand paint) FW (White paint)

SC Standard Width *Easy-Order* Drawer Interior Sets

How to order a Standard Width Easy-Order Drawer Interior Set

To order the drawer interior sets shown on these two pages, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order a DR312 drawer interior set for a 100 height (3") drawer, the part ordering number would be **DR312-100**.



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR104-■	4	11 1/2"



For drawer heights 75 through 300

PART NO.	COMPTS.	CMPT. WIDTH
DR106-■	6	11 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR206-■	6	7 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR209-■	9	7 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR211-■	11	7 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR212-■	12	7 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR3AD-■	4	5 1/2"
	3	7 1/2"
	2	9 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR312-■	12	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR316-■	16	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR319-■	19	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR320-■	20	5 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR4AD-■	15	3 1/2"
	11	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
DR406-■	2	5 1/2"
	4	5 1/2" x 18"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR420-■	16	4 1/8"
	4	4 7/8"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR425-■	20	4 1/8"
	5	4 7/8"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR518-■	18	3 1/2"




For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR524-■	24	3 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR530-■	30	3 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR548-■	48	3 1/2"




For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
DR635-■	30	2 5/8"
	5	3 1/2"



For drawer heights 75 through 150

PART NO.	COMPTS.	CMPT. WIDTH
DR712-■	6	3 1/2"
	6	3 1/2" x 16"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. WIDTH
DR740-■	20	2 1/8"
	20	2 5/8"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. WIDTH
DR818-■	18	2 1/8"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
DR016-■	16	6" x 6"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
DR024-■	16	3" x 6"
	8	6" x 6"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
DR032-■	32	3" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
DR036-■	16	3" x 3"
	16	3" x 6"
	4	6" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
DR064-■	64	3" x 3"



For drawer height 75

PART NO.	COMPTS.	CMPT. WIDTH
DR162-■	38	2 3/4"



For drawer height 75


PART NO.	COMPTS.	CMPT. WIDTH
DR163-■	51	1 3/4"



For drawer height 75

PART NO.	COMPTS.	CMPT. WIDTH
DR164-■	64	1 1/4"

MW Mid-Width Easy-Order Cabinet Combinations



*inside usable drawer dimensions

MW Mid-Width Cabinets

- 100% extension drawers with 440 lb. load capacity

These cabinets are ideal for storing tools and parts that are 24" in length or longer, while allowing for the combined storage of short and long items in the same cabinet.

How to order a Mid-Width Easy-Order Cabinet

- Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by a "B" at the end of the part number – i.e., MW0750-0803FB). Drawer interior sets are shown on page 31.

2. ■ Select base type.

NB = none
FT = fork truck
PT = pallet truck

For additional bases, see page 39; for Easy-Order mobile combinations, see page 30.

3. ■ Select lock type.

NL* = none
RG = individual
KA = keyed-alike
MA = master

*not available for double hinged door cabinets

For additional lock options, see page 62.

- Select paint color. For color chart, see back cover or below.

EXAMPLE: to order an MW0900-0304D cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **MW0900-0304D-FTRGBB**.

MW750 Cabinets 33 1/2" high

	DR. HT.	DR. INT.
2" (75F)	836	
2" (75F)	836	
2" (75F)	836	
2" (75F)	836	
3" (100F)	732	
3" (100F)	732	
4" (125F)	628	
4" (125F)	628	

PART NO.	DRWS.	COMPTS.
MW0750-0802F-■ ■ ■	8	-
MW0750-0802FB-■ ■ ■	8	264

	DR. HT.	DR. INT.
2" (75F)	836	
2" (75F)	836	
3" (100F)	635	
3" (100F)	635	
3" (100F)	635	
3" (100F)	628	
3" (100F)	628	
3" (100F)	628	

PART NO.	DRWS.	COMPTS.
MW0750-0803F-■ ■ ■	8	-
MW0750-0803FB-■ ■ ■	8	261

	DR. HT.	DR. INT.
2" (75F)	836	
3" (100F)	732	
3" (100F)	732	
4" (125F)	628	
5" (150F)	524	
7" (200F)	420	

PART NO.	DRWS.	COMPTS.
MW0750-0604F-■ ■ ■	6	-
MW0750-0604FB-■ ■ ■	6	172

	DR. HT.	DR. INT.
3" (100F)	635	
3" (100F)	635	
3" (100F)	635	
3" (100F)	635	
5" (150F)	524	
7" (200F)	420	

PART NO.	DRWS.	COMPTS.
MW0750-0605F-■ ■ ■	6	-
MW0750-0605FB-■ ■ ■	6	184

	DR. HT.	DR. INT.
2" (75F)	836	
3" (100F)	732	
4" (125F)	628	
5" (150F)	524	
11" (300F)	312	

PART NO.	DRWS.	COMPTS.
MW0750-0501F-■ ■ ■	5	-
MW0750-0501FB-■ ■ ■	5	132

	DR. HT.	DR. INT.
3" (100F)	635	
7" (200F)	524	
7" (200F)	524	
9" (250F)	420	

PART NO.	DRWS.	COMPTS.
MW0750-0403F-■ ■ ■	4	-
MW0750-0403FB-■ ■ ■	4	103

	DR. HT.	DR. INT.
5" (150F)	628	
7" (200F)	420	
7" (200F)	420	
7" (200F)	420	

PART NO.	DRWS.	COMPTS.
MW0750-0404F-■ ■ ■	4	-
MW0750-0404FB-■ ■ ■	4	88

	INCLUDES
	ROLL-OUT TRAY
	ROLL-OUT TRAY

PART NO.	TRAYS
MW0750-0201D-■ ■ ■	2

door cabinet is 29 1/2" deep

MW900 Cabinets 39 3/8" high

	DR. HT.	DR. INT.
2" (75F)	732	
2" (75F)	732	
2" (75F)	732	
3" (100F)	628	
3" (100F)	628	
3" (100F)	628	
5" (150F)	420	

PART NO.	DRWS.	COMPTS.
MW0900-0901F-■ ■ ■	9	-
MW0900-0901FB-■ ■ ■	9	252

	DR. HT.	DR. INT.
3" (100F)	635	
3" (100F)	635	
3" (100F)	635	
3" (100F)	524	
3" (100F)	524	
3" (100F)	524	
3" (100F)	420	
3" (100F)	420	

PART NO.	DRWS.	COMPTS.
MW0900-0904F-■ ■ ■	9	-
MW0900-0904FB-■ ■ ■	9	237

	DR. HT.	DR. INT.
3" (100F)	732	
3" (100F)	732	
3" (100F)	732	
3" (100F)	732	
5" (150F)	628	
5" (150F)	628	
7" (200F)	420	

PART NO.	DRWS.	COMPTS.
MW0900-0702F-■ ■ ■	7	-
MW0900-0702FB-■ ■ ■	7	204

	DR. HT.	DR. INT.
2" (75F)	836	
3" (100F)	732	
4" (125F)	628	
4" (125F)	628	
4" (125F)	628	
5" (150F)	524	
7" (200F)	420	

PART NO.	DRWS.	COMPTS.
MW0900-0705F-■ ■ ■	7	-
MW0900-0705FB-■ ■ ■	7	196



DR. HT.	DR. INT.
3" (100F)	635
4" (125F)	628
4" (125F)	628
5" (150F)	524
7" (200F)	420
7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW0900-0606F-	6	-
MW0900-0606FB-	6	155



DR. HT.	DR. INT.
3" (100F)	635
5" (150F)	524
7" (200F)	420
7" (200F)	420
9" (250F)	312

PART NO.	DRWS.	COMPTS.
MW0900-0503F-	5	-
MW0900-0503FB-	5	111



DR. HT.	DR. INT.
5" (150F)	524
5" (150F)	524
7" (200F)	420
7" (200F)	420
7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW0900-0504F-	5	-
MW0900-0504FB-	5	108



INCLUDES
ROLL-OUT TRAY
ROLL-OUT TRAY
ROLL-OUT TRAY

PART NO.	TRAYS
MW0900-0304D-	3

door cabinet is 29 1/2" deep

MW1225 Cabinets 52 3/16" high



DR. HT.	DR. INT.
2" (75F)	732
2" (75F)	732
2" (75F)	732
3" (100F)	628
3" (100F)	628
3" (100F)	628
5" (150F)	524
7" (200F)	420
7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW1225-1001F-	10	-
MW1225-1001FB-	10	268




DR. HT.	DR. INT.
3" (100F)	732
3" (100F)	732
4" (125F)	628
5" (150F)	524
5" (150F)	524
7" (200F)	420
7" (200F)	420
7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW1225-0801F-	8	-
MW1225-0801FB-	8	200



DR. HT.	DR. INT.
4" (125F)	628
7" (200F)	420
7" (200F)	420
7" (200F)	420
9" (250F)	312
9" (250F)	312

PART NO.	DRWS.	COMPTS.
MW1225-0601F-	6	-
MW1225-0601FB-	6	112




INCLUDES
ROLL-OUT TRAY
ROLL-OUT TRAY
ROLL-OUT TRAY
ROLL-OUT TRAY

PART NO.	TRAYS
MW1225-0301D-	3


door cabinet is 29 1/2" deep

MW1350 Cabinets 57 1/8" high



DR. HT.	DR. INT.
2" (75F)	836
2" (75F)	836
2" (75F)	836
2" (75F)	836
3" (100F)	635
3" (100F)	635
3" (100F)	635
3" (100F)	635
3" (100F)	628
3" (100F)	628
3" (100F)	628
4" (125F)	524
4" (125F)	524

PART NO.	DRWS.	COMPTS.
MW1350-1401F-	14	-
MW1350-1401FB-	14	444



DR. HT.	DR. INT.
2" (75F)	836
2" (75F)	836
2" (75F)	836
2" (75F)	836
3" (100F)	628
3" (100F)	628
3" (100F)	628
3" (100F)	628
5" (150F)	524
5" (150F)	524
7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW1350-1201F-	12	-
MW1350-1201FB-	12	348



DR. HT.	DR. INT.
2" (75F)	836
2" (75F)	836
2" (75F)	836
3" (100F)	635
3" (100F)	635
4" (125F)	524
4" (125F)	524
4" (125F)	524
7" (200F)	420
9" (250F)	312

PART NO.	DRWS.	COMPTS.
MW1350-1102F-	11	-
MW1350-1102FB-	11	317



DR. HT.	DR. INT.
3" (100F)	635
3" (100F)	635
3" (100F)	635
5" (150F)	524
5" (150F)	524
7" (200F)	420
7" (200F)	420
7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW1350-0902F-	9	-
MW1350-0902FB-	9	237



DR. HT.	DR. INT.
3" (100F)	635
3" (100F)	635
5" (150F)	524
5" (150F)	524
7" (200F)	420
7" (200F)	420
7" (200F)	420
9" (250F)	312

PART NO.	DRWS.	COMPTS.
MW1350-0802F-	8	-
MW1350-0802FB-	8	190




DR. HT.	DR. INT.
5" (150F)	628
5" (150F)	628
5" (150F)	628
7" (200F)	420
7" (200F)	420
9" (250F)	312
9" (250F)	312

PART NO.	DRWS.	COMPTS.
MW1350-0702F-	7	-
MW1350-0702FB-	7	148



DR. HT.	DR. INT.
9" (250F)	420
9" (250F)	420
9" (250F)	420
11" (300F)	203
11" (300F)	203

PART NO.	DRWS.	COMPTS.
MW1350-0501F-	5	-
MW1350-0501FB-	5	66



INCLUDES
ROLL-OUT TRAY
ROLL-OUT TRAY
ROLL-OUT TRAY
ROLL-OUT TRAY

PART NO.	TRAYS
MW1350-0401D-	4

door cabinet is 29 1/2" deep

MW Mid-Width *Easy-Order* Mobile Cabinet Combinations



Each mobile cabinet comes with:

- 2 fixed and 2 swivel 6" x 2" casters with wheel locks
- Tubular steel handles
- Individual drawer latches
- 100% extension drawers with 440 lb. load capacity

How to read the charts on this page

The 2 columns to the right of each cabinet illustration indicate:

- Drawer heights
- Drawer interior sets (shown on page 31)

The chart below the illustration indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (shown on page 31)

How to order a Mid-Width Easy-Order Mobile Cabinet

1. **Select Easy-Order Cabinet Combination** either without or with drawer interior sets (designated by a "B" near the end of the part number – i.e., MW0750-0605FB-M).

2. **Select lock type.**

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

3. **Select paint color.** For color chart, see back cover.

EXAMPLE: to order an MW0750-0605FB-M cabinet with an individual lock, Red paint and a retainer top, the part number would be **MW0750-0605FB-M-RG NR**, with an MW-RT top (shown in photo at top of page).

MW750 Mobile Cabinets 41 1/2" high x 47" wide

	DR. HT.	DR. INT.
	2" (75F)	836
	2" (75F)	836
	3" (100F)	635
	3" (100F)	635
	3" (100F)	635
	3" (100F)	628
	3" (100F)	628
	3" (100F)	628

PART NO.	DRWS.	COMPTS.
MW0750-0803F-M- ☐	8	-
MW0750-0803FB-M- ☐	8	261

	DR. HT.	DR. INT.
	3" (100F)	635
	3" (100F)	635
	3" (100F)	635
	3" (100F)	635
	5" (150F)	524
	7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW0750-0605F-M- ☐	6	-
MW0750-0605FB-M- ☐	6	184

	DR. HT.	DR. INT.
	5" (150F)	628
	7" (200F)	420
	7" (200F)	420
	7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW0750-0404F-M- ☐	4	-
MW0750-0404FB-M- ☐	4	88

MW900 Mobile Cabinets 47 3/8" high x 47" wide

	DR. HT.	DR. INT.
	3" (100F)	635
	3" (100F)	635
	3" (100F)	635
	3" (100F)	524
	3" (100F)	524
	3" (100F)	524
	3" (100F)	420
	3" (100F)	420
	3" (100F)	420

PART NO.	DRWS.	COMPTS.
MW0900-0904F-M- ☐	9	-
MW0900-0904FB-M- ☐	9	237

	DR. HT.	DR. INT.
	2" (75F)	836
	3" (100F)	732
	4" (125F)	628
	4" (125F)	628
	4" (125F)	628
	5" (150F)	524
	7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW0900-0705F-M- ☐	7	-
MW0900-0705FB-M- ☐	7	196

	DR. HT.	DR. INT.
	5" (150F)	524
	5" (150F)	524
	7" (200F)	420
	7" (200F)	420
	7" (200F)	420

PART NO.	DRWS.	COMPTS.
MW0900-0504F-M- ☐	5	-
MW0900-0504FB-M- ☐	5	108

Mobile Cabinet Options

Hanging Shelf Cabinet

Optional shelf cabinet, painted to match mobile cabinet, is 28 1/4" wide x 15" deep x 29" high. It is attached to the side of mobile cabinet for easy maneuvering. Each cabinet has a bottom shelf and 1 adjustable 13 1/2" deep shelf. Individual lock (RG) and 2 keys are furnished. Can only be mounted on 750 height or higher mobile cabinets.

PART NO.	DESCRIPTION
OHC2829-CM	shelf cabinet
OHC1BCT/36	butcher block top (28 1/4" x 15" x 1 1/4")



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 28 1/2" deep.

PART NO.	MOUNTS TO
FS-36DX15-L	left side
FS-36DX15-R	right side

Mid-Width Mobile Cabinet Tops

For additional top choices, see page 67.

PART NO.	DESCRIPTION	HT.
MW-RT	retainer top w/ribbed mat	3/4"
MW1BCT	butcher block	1 3/4"
MW1PCT	plastic laminate	1 9/16"

Mesh Drawer Liner

Non-slip polyester mesh liner protects items in drawers without drawer interior sets from shifting or sliding. Liner is non-toxic, washable and treated to inhibit mold and mildew.

PART NO.
MWMDL



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR203-■	3	14"



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR-LR209-■	9	7 1/2"

How to order a Mid-Width Drawer Easy-Order Interior Set

To order the drawer interior sets shown on this page, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order an MWDR203 drawer interior set for a 100 height (3") drawer, the part ordering number would be **MWDR203-100**.



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR312-■	3	6 1/4"
	9	11 1/2"



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR-LR312-■	12	5 1/2"



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR420-■	4	6 1/4"
	8	7 1/2"
	8	9 1/2"



For drawer heights 75 through 150

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR-LR518-■	18	3 1/2"



For drawer heights 75 through 300

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR524-■	16	6 1/4"
	8	7 1/2"




For drawer heights 75 through 300

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR628-■	24	5 1/2"
	4	6 1/4"




For drawer heights 75 through 300

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR635-■	30	5 1/2"
	5	6 1/4"



For drawer heights 75 through 200


PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR732-■	32	4 7/8"



For drawer heights 75 through 200

PART NO.	COMPARTMENTS	COMPART. WIDTH
MWDR836-■	32	4 1/8"
	4	4 7/8"

DW Double Width *Easy-Order* Cabinet Combinations



*inside usable drawer dimensions

DW Double Width Cabinets

- 100% extension drawers with 440 lb. load capacity

DW cabinets are perfect for stacking above pairs of SC Standard Width cabinets, and allow for storage of items up to 52" in length. Their huge capacity can hold up to 8 cubic feet.

How to order a Double Width Easy-Order Cabinet

1. Select Easy-Order Cabinet

Combination either without or with drawer interior sets (designated by a "B" at the end of the part number – i.e., DW0750-0601FB). Drawer interior sets are shown on page 35.

2. ■ Select base type.

NB = none
FT = fork truck
PT = pallet truck

For additional bases, see page 39;
for Easy-Order mobile combinations,
see page 34.

3. ■ Select lock type.

NL* = none
RG = individual
KA = keyed-alike
MA = master

*not available for double hinged door cabinets

For additional lock options, see page 62.

4. □ Select paint color. For color chart, see back cover or below.

EXAMPLE: to order a DW0900-0704FB cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **DW0900-0704FB-FTRGBB**.

DW750 Cabinets 33 1/2" high

DRAWER HT.	DRAWER INTERIOR
2" (75F)	940
2" (75F)	940
2" (75F)	836
2" (75F)	836
3" (100F)	732
3" (100F)	732
3" (100F)	732
5" (150F)	621


PART NO.	DRAWERS	COMPARTMENTS
DW0750-0801F-■□□	8	-
DW0750-0801FB-■□□	8	269

DRAWER HT.	DRAWER INTERIOR
2" (75F)	836
2" (75F)	836
3" (100F)	732
5" (150F)	621
5" (150F)	621
7" (200F)	415

PART NO.	DRAWERS	COMPARTMENTS
DW0750-0601F-■□□	6	-
DW0750-0601FB-■□□	6	161

DRAWER HT.	DRAWER INTERIOR
5" (150F)	621
5" (150F)	621
7" (200F)	524
9" (250F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW0750-0401F-■□□	4	-
DW0750-0401FB-■□□	4	76



PART NO.	TRAYS
DW0750-0201D-■□□	2

door cabinet is 29 1/2" deep

DW900 Cabinets 39 3/8" high

DRAWER HT.	DRAWER INTERIOR
2" (75F)	836
2" (75F)	836
2" (75F)	836
2" (75F)	836
3" (100F)	621
3" (100F)	621
3" (100F)	621
5" (150F)	524
5" (150F)	524


PART NO.	DRAWERS	COMPARTMENTS
DW0900-0901F-■□□	9	-
DW0900-0901FB-■□□	9	255

DRAWER HT.	DRAWER INTERIOR
2" (75F)	732
2" (75F)	732
3" (100F)	621
3" (100F)	621
5" (150F)	524
5" (150F)	524
9" (250F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW0900-0704F-■□□	7	-
DW0900-0704FB-■□□	7	164

DRAWER HT.	DRAWER INTERIOR
3" (100F)	732
5" (150F)	524
7" (200F)	415
7" (200F)	415
9" (250F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW0900-0503F-■□□	5	-
DW0900-0503FB-■□□	5	96



PART NO.	TRAYS
DW0900-0304D-■□□	3

door cabinet is 29 1/2" deep

BE (Beige paint) BB (Bright Blue paint) BK (Black paint) CB (Classic Blue paint) GR (Dark Gray paint)

DW1225 Cabinets

52 3/16" high



DRAWER HT.	DRAWER INTERIOR
2" (75F)	836
2" (75F)	836
2" (75F)	836
3" (100F)	621
3" (100F)	621
3" (100F)	621
5" (150F)	524
7" (200F)	410
7" (200F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW1225-1001F-	10	-
DW1225-1001FB-	10	239



DRAWER HT.	DRAWER INTERIOR
3" (100F)	836
3" (100F)	836
4" (125F)	732
5" (150F)	524
5" (150F)	524
7" (200F)	410
7" (200F)	410
7" (200F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW1225-0801F-	8	-
DW1225-0801FB-	8	182



DRAWER HT.	DRAWER INTERIOR
4" (125F)	621
7" (200F)	415
7" (200F)	415
7" (200F)	415
9" (250F)	410
9" (250F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW1225-0601F-	6	-
DW1225-0601FB-	6	86



INCLUDES

ROLL-OUT TRAY

ROLL-OUT TRAY

ROLL-OUT TRAY

PART NO.	TRAYS
DW1225-0301D-	3

door cabinet is 29 1/2" deep

DW1350 Cabinets

57 1/8" high



DRAWER HT.	DRAWER INTERIOR
2" (75F)	940
2" (75F)	940
2" (75F)	940
2" (75F)	940
2" (75F)	836
2" (75F)	836
2" (75F)	836
3" (100F)	732
3" (100F)	732
3" (100F)	732
3" (100F)	732
4" (125F)	621
4" (125F)	621

PART NO.	DRAWERS	COMPARTMENTS
DW1350-1501F-	15	-
DW1350-1501FB-	15	506



DRAWER HT.	DRAWER INTERIOR
2" (75F)	940
2" (75F)	940
2" (75F)	940
3" (100F)	836
3" (100F)	836
3" (100F)	836
3" (100F)	836
5" (150F)	524
5" (150F)	524
5" (150F)	415
7" (200F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW1350-1201F-	12	-
DW1350-1201FB-	12	377



DRAWER HT.	DRAWER INTERIOR
3" (100F)	836
3" (100F)	836
4" (125F)	621
4" (125F)	621
5" (150F)	524
5" (150F)	524
5" (150F)	524
5" (150F)	410
5" (150F)	410
5" (150F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW1350-1001F-	10	-
DW1350-1001FB-	10	216



DRAWER HT.	DRAWER INTERIOR
3" (100F)	836
3" (100F)	732
3" (100F)	732
5" (150F)	524
5" (150F)	524
7" (200F)	410
7" (200F)	410
7" (200F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW1350-0902F-	9	-
DW1350-0902FB-	9	202



DRAWER HT.	DRAWER INTERIOR
5" (150F)	621
5" (150F)	621
5" (150F)	621
7" (200F)	524
7" (200F)	524
9" (250F)	415
9" (250F)	415

PART NO.	DRAWERS	COMPARTMENTS
DW1350-0702F-	7	-
DW1350-0702FB-	7	141



DRAWER HT.	DRAWER INTERIOR
7" (200F)	621
7" (200F)	621
7" (200F)	524
7" (200F)	524
9" (250F)	415
11" (300F)	203

PART NO.	DRAWERS	COMPARTMENTS
DW1350-0601F-	6	-
DW1350-0601FB-	6	108



DRAWER HT.	DRAWER INTERIOR
9" (250F)	410
9" (250F)	410
9" (250F)	410
11" (300F)	203
11" (300F)	203

PART NO.	DRAWERS	COMPARTMENTS
DW1350-0501F-	5	-
DW1350-0501FB-	5	36



INCLUDES

ROLL-OUT TRAY

ROLL-OUT TRAY

ROLL-OUT TRAY

ROLL-OUT TRAY

PART NO.	TRAYS
DW1350-0401D-	4

door cabinet is 29 1/2" deep

Double Width *Easy-Order* Mobile Cabinet Combinations



Each mobile cabinet comes with:

- 2 fixed and 2 swivel 6" x 2" casters with wheel locks
- Tubular steel handles
- Individual drawer latches
- 100% extension drawers with 440 lb. load capacity

How to read the charts on this page

The 2 columns to the right of each cabinet illustration indicate:

- Drawer heights
- Drawer interior sets (shown on page 35)

The chart below the illustration indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (shown on page 35)

How to order a Double Width Easy-Order Mobile Cabinet

1. Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by a "B" near the end of the part number – i.e., DW0750-0503FB-M).

2. ■ Select lock type.

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

3. ☐ Select paint color. For color chart, see back cover.

EXAMPLE: to order a DW0750-0703FB-M cabinet with an individual lock, Black paint and a retainer top, the part number would be **DW0750-0703FB-M-RGBK**, with a DW-RT top (shown in photo at top of page).

DW750 Mobile Cabinets

41 1/2" high x 56 1/2" wide

	DRAWER HT.	DRAWER INTERIOR
	2" (75F)	940
	2" (75F)	940
	3" (100F)	621
	3" (100F)	621
	3" (100F)	621
	5" (150F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW0750-0703F-M- ■ ☐	7	-
DW0750-0703FB-M- ■ ☐	7	163

	DRAWER HT.	DRAWER INTERIOR
	3" (100F)	836
	5" (150F)	621
	5" (150F)	621
	5" (150F)	621
	5" (150F)	621
	7" (200F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW0750-0503F-M- ■ ☐	5	-
DW0750-0503FB-M- ■ ☐	5	109

	DRAWER HT.	DRAWER INTERIOR
	5" (150F)	621
	5" (150F)	621
	7" (200F)	524
	9" (250F)	410
	9" (250F)	410

PART NO.	DRAWERS	COMPARTMENTS
DW0750-0401F-M- ■ ☐	4	-
DW0750-0401FB-M- ■ ☐	4	76

DW900 Mobile Cabinets

47 3/8" high x 56 1/2" wide

	DRAWER HT.	DRAWER INTERIOR
	3" (100F)	732
	3" (100F)	732
	3" (100F)	732
	3" (100F)	732
	3" (100F)	524
	3" (100F)	524
	3" (100F)	524
	3" (100F)	524
	3" (100F)	524

PART NO.	DRAWERS	COMPARTMENTS
DW0900-0904F-M- ■ ☐	9	-
DW0900-0904FB-M- ■ ☐	9	248

	DRAWER HT.	DRAWER INTERIOR
	3" (100F)	732
	3" (100F)	732
	5" (150F)	524
	5" (150F)	524
	5" (150F)	524
	5" (150F)	524
	9" (250F)	203

PART NO.	DRAWERS	COMPARTMENTS
DW0900-0601F-M- ■ ☐	6	-
DW0900-0601FB-M- ■ ☐	6	139

	DRAWER HT.	DRAWER INTERIOR
	5" (150F)	524
	5" (150F)	524
	7" (200F)	415
	7" (200F)	415
	7" (200F)	415

PART NO.	DRAWERS	COMPARTMENTS
DW0900-0504F-M- ■ ☐	5	-
DW0900-0504FB-M- ■ ☐	5	93

Mobile Cabinet Options

Hanging Shelf Cabinet

Optional shelf cabinet, painted to match mobile cabinet, is 28 1/4" wide x 15" deep x 29" high. It is attached to the side of mobile cabinet for easy maneuvering. Each cabinet has a bottom shelf and 1 adjustable 13 1/2" deep shelf. Individual lock (RG) and 2 keys are furnished. Can only be mounted on 750 height or higher mobile cabinets.



PART NO.	DESCRIPTION
OHC2829-CM	shelf cabinet
OHC1BCT/36	butcher block top (28 1/4" x 15" x 1 1/4")



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 28 1/2" deep.

PART NO.	MOUNTS TO
FS-36DX15-L	left side
FS-36DX15-R	right side

Double Width Mobile Cabinet Tops

For additional top choices, see page 67.

PART NO.	DESCRIPTION	HT.
DW-RT	retainer top w/ribbed mat	3/4"
SC2BCT	butcher block	1 3/4"
SC2PCT	plastic laminate	1 9/16"

Mesh Drawer Liner

Non-slip polyester mesh liner protects items in drawers without drawer interior sets from shifting or sliding. Liner is non-toxic, washable and treated to inhibit mold and mildew.

PART NO.
DWMDL



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR203-■	3	17 1/4"



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR-LR209-■	9	7 1/2"

How to order a Double Width Easy-Order Drawer Interior Set

To order the drawer interior sets shown on this page, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order a DWDR203 drawer interior set for a 100 height (3") drawer, the part ordering number would be **DWDR203-100**.



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR-LR312-■	12	5 1/2"



For drawer heights 75 through 300

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR410-■	8	9 1/2"
	2	11 1/2"



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR415-■	6	7 1/2"
	9	11 1/2"



For drawer heights 75 through 150

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR-LR518-■	18	3 1/2"



For all drawer heights

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR524-■	16	7 1/2"
	8	9 1/2"




For drawer heights 75 through 300

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR621-■	9	6 1/4"
	12	7 1/2"



For drawer heights 75 through 300

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR732-■	24	5 1/2"
	8	7 1/2"



For drawer heights 75 through 200

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR836-■	12	5 1/4"
	24	5 1/2"



For drawer heights 75 through 200

PART NO.	COMPARTMENTS	COMPART. WIDTH
DWDR940-■	8	4 1/8"
	32	4 7/8"

How to Order Custom Full Depth Cabinets (28 1/2" deep)

There are tens of thousands of ways to configure a Lista cabinet. Our modular building block system means that your cabinets can be configured to exactly suit your requirements.

By walking through the steps summarized on the facing page and shown on the following four pages, you can create cabinets that will exactly fit your own specific needs.



Row of SC cabinets with plastic laminate counter top.



Mobile MP cabinets make perfect toolboxes.



MW cabinets with stainless steel counter top.




DW drawer/door cabinets stacked above pairs of SC cabinets.

TO ORDER AN EASY-ORDER COMBINATION:

(housing with preconfigured drawers and option of drawer interior sets)

	CABINETS	MOBILE CABINETS	DRAWER INTERIOR SETS
NW	pages 14-15	page 16	page 17
MP	pages 18-19	page 20	page 21
SC	pages 22-24	page 25	pages 26-27
MW	pages 28-29	page 30	page 31
DW	pages 32-33	page 34	page 35

STEPS TO ORDER A CUSTOM CONFIGURED FULL DEPTH CABINET




- 1 Select cabinet housing**
Select the particular cabinet housing that best suits your needs. When choosing your housing height, keep in mind the cabinet top's potential use as a worksurface. **See page 38.**
- 2 Select a lock**
Choose from a wide array of locking options. **See page 39.**
- 3 Select a cabinet base (optional)**
A number of optional bases to suit a wide variety of uses. **See page 39.**
- 4 Select a cabinet top or counter top (optional)**
Top descriptions can be found on **page 67**; information about counter tops to span rows of cabinets is on **page 107**.
- 5 Select drawers, shelves, roll-out trays and doors**
Drawers, shelves and roll-out trays can be used in any sequence or combination you wish. **See pages 40-41.**
- 6 Select drawer partitions and dividers (optional)**
Choose from the Easy-Order drawer interior sets shown in each cabinet's Easy-Order section, or order custom drawer partitions and dividers (**page 118**). Choose from many accessories (**pages 119-122**).
- 7 Select colors**
Select color from the chart on **page 41**. Housing and drawer fronts can be different colors but drawer interiors are always gray.

The total drawer and/or door model numbers must add up to the model number of the housing.


EXAMPLES:

Model 900 Housing

(2) 100 drawers	=	200
(2) 150 drawers	=	300
(2) 200 drawers	=	400
		900



(2) 150 drawers	=	300
(1) 600 door	=	600
		900



Sample Cabinet Order

QUANTITY	PART NO.	DESCRIPTION	1
1	SC900	housing	
1	KA	keyed alike lock	
1	SC-FTB	fork truck base	
1	SC1BCT	butcher block top	
2	SC100F	drawers	
2	SC150F	drawers	
2	SC200F	drawers	
2	DR316-100	drawer interiors	
2	DR206-150	drawer interiors	
2	DR104-200	drawer interiors	
	Housing: BB	Bright Blue	
	Drawers: LG	Light Gray	

How to Order **Custom Full Depth Cabinets (28 1/2" deep)**

1 Select cabinet housing

Cabinet housing can be configured with any sequence of drawers, shelves and roll-out trays (see page 40). See the graphic on page 37 for information on configuring the correct height(s) of drawers and doors to fit the housing you have selected. Housing includes an individual lock and 2 keys.

FOOTPRINTS



NW WIDTH
16 7/8" wide



MP WIDTH
22 3/16" wide



SC WIDTH
28 1/4" wide



MW WIDTH
47" wide



DW WIDTH
56 1/2" wide

HEIGHTS



MODEL 300
15 3/4" overall height



MODEL 450
21 5/8" overall height



MODEL 600
27 1/2" overall height



MODEL 750
33 1/2" overall height



MODEL 900
39 3/8" overall height



MODEL 1050
45 1/4" overall height



MODEL 1225
52 3/16" overall height



MODEL 1350
57 1/8" overall height



MODEL 1525
64" overall height

AVAIL. HT. (points)	OVERALL HEIGHT (inches/mm)	NW	MP	SC	MW	DW
300	15 3/4" (400mm)	NW300	MP300	SC300	MW300	DW300
450	21 5/8" (550mm)	NW450	MP450	SC450	MW450	DW450
600	27 1/2" (700mm)	NW600	MP600	SC600	MW600	DW600
750	33 1/2" (850mm)	NW750	MP750	SC750	MW750	DW750
900	39 3/8" (1000mm)	NW900	MP900	SC900	MW900	DW900
1050	45 1/4" (1150mm)	-	MP1050	SC1050	MW1050	DW1050
1225	52 3/16" (1325mm)	NW1225	MP1225	SC1225	MW1225	DW1225
1350	57 1/8" (1450mm)	NW1350	MP1350	SC1350	MW1350	DW1350
1525	64" (1625mm)	-	-	SC1525	-	-

OR select cabinet housing with double hinged doors (housing depth is 29 1/2")

Double hinged door housing includes a pair of hinged doors and an individual lock and 2 keys. It can be configured with any sequence of drawers, shelves and roll-out trays (see page 40). For tops for double hinged door cabinets, contact your Lista representative.



AVAIL. HT. (points)	OVERALL HEIGHT (inches/mm)	NW	MP	SC	MW	DW
600	27 1/2" (700mm)	-	MPDHD600	SCDHD600	MWDHD600	DWDHD600
750	33 1/2" (850mm)	-	MPDHD750	SCDHD750	MWDHD750	DWDHD750
900	39 3/8" (1000mm)	-	MPDHD900	SCDHD900	MWDHD900	DWDHD900
1050	45 1/4" (1150mm)	-	-	SCDHD1050	MWDHD1050	-
1225	52 3/16" (1325mm)	-	MPDHD1225	SCDHD1225	MWDHD1225	DWDHD1225
1350	57 1/8" (1450mm)	-	MPDHD1350	SCDHD1350	MWDHD1350	DWDHD1350
1525	64" (1625mm)	-	-	SCDHD1525	-	-

2 Select lock and keying options (choose from additional selections on page 62)


If you have locking and security needs other than the individual lock (lock and 2 keys) that comes with all cabinets, select from the options below or see page 62.

Individual Lock (RG)

Cabinets come with an individual lock and 2 keys. Each cabinet lock is keyed differently.

No Lock (NL)


Specify if no cylinder lock is desired for cabinet housing. Cabinet will still include PreventTip® one-drawer-at-a-time safety feature. Not available for double hinged door cabinets.



Keyed Alike Lock (KA)

All cabinets have identical locks, each with 2 keys; the same key opens all cabinets. Each cabinet in the keyed alike group must have keyed alike (KA) specified on the order. Cabinets containing drawers and doors will only be keyed alike if specified.

PART NO.	LOCK TYPE
KA	keyed alike lock



Master Keyed Lock (MA)

Each cabinet has a different lock with 2 keys. Each cabinet in the master key group must have master keyed lock (MA) specified on the order. Master key (MK) that opens all locks must be ordered separately.

PART NO.	LOCK TYPE
MA	master lock
MK	group master key
GMK	grand master key

3 Select optional cabinet base

Fork Truck Base

Steel fork truck base permits moving of fully loaded cabinets. Base has snap-on front and rear covers, and is recessed 1 1/8" (30mm) from the front of the housing. Bases are pre-punched to allow stacking. Color: to match housing.



Pallet Truck Base

Steel pallet truck base permits moving of fully loaded cabinets with a hand pallet truck. Base has snap-on front and rear covers, and is recessed 1 1/8" (30mm) each from the front and back of the housing. Color: to match housing.



Frame Base

Steel base is used to bring cabinets up to desired work height. Base is recessed 1 1/8" (30mm) from the front of the housing. Color: to match housing.



Mobile Caster Base

A set of 2 fixed and 2 swivel casters. Each swivel caster has an individual wheel lock. Casters are factory mounted to the base. (See page 66 for other mobile accessories.)



Wet Clean Base

Allows for easy cleaning below housing in areas where floors are often washed (such as labs and hospitals), or where wet floors are an issue. Raises cabinet housing 4 9/16" above floor. Individual leg height is further adjustable to allow for leveling (up to 1 3/4" additional height), even on extremely uneven surfaces. Cabinet can be lifted and moved with a hand pallet truck.



TYPE	OVERALL HEIGHT	CASTER DIMEN.	WEIGHT CAPACITY	NW	MP	SC	MW	DW
Fork truck base	2 3/8" (60mm)			-	MP-FTB	SC-FTB	MW-FTB	DW-FTB
Pallet truck base	4" (100mm)		-		MP-PTB	SC-PTB	MW-PTB	DW-PTB
Frame base	2" (50mm)			NW-2	MP-2	SC-2FB	MW-2FB	DW-2FB
Frame base	4" (100mm)			NW-4	MP-4	SC-4FB	MW-4FB	DW-4FB
Frame base	6" (150mm)			NW-6	MP-6	SC-6FB	MW-6FB	DW-6FB
Mobile base*	4 3/4"	3 1/2" x 1 1/4"	900 lb.	TMMB-19/3.5	-	-	-	-
Mobile base*	5 5/8"	4" x 1 1/4"	1000 lb.	CB-NW4X1	CB-MP4X1	CB-SC4X1	-	-
Mobile base*	6 1/4"	4" x 2"	1400 lb.	CB-NW4B	CB-MP4B	CB-SC4B	-	-
Mobile base*	6 1/4"	4" x 2"	2400 lb.	-	CB-MP4ML	CB-SC4ML	CB-MW4ML	CB-DW4ML
Mobile base*	8"	6" x 2"	2400 lb.	-	CB-MP6B	CB-SC6B	-	-
Mobile base*	8"	6" x 2"	3600 lb.	-	CB-MP6ML	CB-SC6ML	CB-MW6ML	CB-DW6ML
Wet clean base	4 9/16"			WCB-NW	WCB-MP	WCB-SC	WCB-MW	WCB-DW

*mobile bases not recommended for use with 1225 height or higher cabinets

How to Order **Custom Full Depth Cabinets (28 1/2" deep)**

4 Select optional cabinet top (individual cabinet tops page 67; counter tops for multiple cabinets page 107)

5 Select drawers, shelves and/or roll-out trays

Drawers, shelves and roll-out trays can be arranged and re-arranged in a cabinet housing in any sequence. **See the graphic on page 37 for information on configuring the correct height(s) of drawers and doors to fit the housing you have selected.**

Drawers

Drawers are 100% full extension, allowing complete use of the furthest corners and easy access to all contents. Each drawer has a maximum load capacity of either 440 lb. (200kg) or 165 lb. (75kg).



Shelves

Fixed bottom shelves and adjustable upper shelves can be moved up or down in 1" increments. Vertical dividers are available to sub-divide shelves. Shelf cabinets are often stacked above drawer cabinets for maximum space savings. Maximum load capacity of 440 lbs. (200kg) evenly distributed.



Roll-Out Trays

Roll-out trays allow easy access to stored items, even in the farthest corner. 100% full extension, 440 lb. (200 kg) or 165 lb. (75kg) maximum load capacity.



DRAWER FOOTPRINTS (usable inside widths shown below – all full depth drawers are 24" / 610mm / 36 units deep)



NW WIDTH
12 1/2" wide
(318mm / 19 units)



MP WIDTH
18" wide
(459mm / 27 units)



SC WIDTH
24" wide
(610mm / 36 units)



MW WIDTH
42 13/16" wide
(1088mm / 64 units)



DW WIDTH
52 3/16" wide
(1325mm / 78 units)

DRAWERS

HEIGHT (points)	USEABLE HEIGHT	SIDEWALL HEIGHT	NW 165 lb. capacity	MP 165 lb. capacity	MP 440 lb. capacity	SC 440 lb. capacity	MW 440 lb. capacity	DW 440 lb. capacity
75	2 1/8" (55mm)	2" (50mm)	NW75N	MP75N	MP75F	SC75F	MW75F	DW75F
100	3 1/8" (80mm)	3" (77mm)	NW100N	MP100N	MP100F	SC100F	MW100F	DW100F
125	4 1/8" (105mm)	3" (77mm)	NW125N	MP125N	MP125F	SC125F	MW125F	DW125F
150	5 1/8" (130mm)	5" (127mm)	NW150N	MP150N	MP150F	SC150F	MW150F	DW150F
175	6 1/8" (155mm)	5" (127mm)	NW175N	MP175N	MP175F	SC175F	MW175F	DW175F
200	7 1/16" (180mm)	7" (177mm)	NW200N	MP200N	MP200F	SC200F	MW200F	DW200F
225	8 1/16" (205mm)	7" (177mm)	NW225N	MP225N	MP225F	SC225F	MW225F	DW225F
250	9" (230mm)	8 15/16" (227mm)	NW250N	MP250N	MP250F	SC250F	MW250F	DW250F
275	10" (255mm)	8 15/16" (227mm)	NW275N	MP275N	MP275F	SC275F	MW275F	DW275F
300	11" (280mm)	10 15/16" (277mm)	NW300N	MP300N	MP300F	SC300F	MW300F	DW300F
300-FFH	11" (280mm)	10" (254mm)	NW300N-FFH*	-	-	-	-	-
325	12" (305mm)	10 15/16" (277mm)	NW325N	MP325N	MP325F	SC325F	MW325F	DW325F
325-FFH	12" (305mm)	10" (254mm)	NW325N-FFH*	-	-	-	-	-
350	13" (330mm)	10 15/16" (277mm)	-	-	MP350F	SC350F	MW350F	DW350F

*file drawer

SHELVES AND TRAYS

D = depth; UW = usable width

TYPE	NW 440 lb. capacity	MP 165 lb. capacity	MP 440 lb. capacity	SC 440 lb. capacity	MW 440 lb. capacity	DW 440 lb. capacity
Adjustable shelf 24 1/4" (616mm) D	NW-AS 14 3/8" (366mm) UW		MP-AS 19 3/4" (502mm) UW	SC-AS 25 13/16" (655mm) UW	MW-AS 44 1/2" (1131mm) UW	DW-AS 53 29/32" (1369mm) UW
Bottom shelf 23 3/4" (604mm) D	NW-BS 14 7/16" (367mm) UW		MP-BS 19 13/16" (503mm) UW	SC-BS 25 7/8" (656mm) UW	MW-BS 44 9/16" (1132mm) UW	DW-BS 53 15/16" (1370mm) UW
Roll-out tray 24" (609mm) D	-	MP-TCN 17 1/8" (435mm) UW	MP-TCF 18" (459mm) UW	SC-TCF 24" (610mm) UW	MW-TCF 42 13/16" (1088mm) UW	DW-TCF 52 3/16" (1326mm) UW

5 Select cabinet doors

Flush Hinged Door

Single door protects cabinet contents. Door is provided with integrated handle (reversible in field to allow door to open in opposite direction), individual lock (RG) and 2 keys. **Only bottom and adjustable shelves may be installed behind flush doors – no drawers or roll-out trays, except for MP-TCN roll-out trays in MP width cabinets.**



Retractable Door

Door slides out and back, stored out of the way when not in use. Door is provided with handles, individual lock (RG) and 2 keys. **Only bottom and adjustable shelves may be installed behind retractable doors – no drawers or roll-out trays.**



Double Hinged Door Cabinets

To order double hinged door cabinets, see the ordering information on page 38.



Sliding and Hinged Door Shelf Cabinets

For ordering information on sliding and hinged door shelf cabinets, see pages 68-69.



FLUSH HINGED DOORS

HEIGHT (points)	HEIGHT	NW*	MP*	SC*	MW	DW
300	11 13/16" (300mm)	FD300-19 ■ **	FD300-27 ■ **	-	-	-
450	17 11/16" (450mm)	FD450-19 ■ **	FD450-27 ■ **	FD450-36 ■ **	-	-
600	23 5/8" (600mm)	FD600-19 ■ ***	FD600-27 ■ ***	FD600-36 ■ ***	-	-
750	29 9/16" (750mm)	FD750-19 ■	FD750-27 ■	FD750-36 ■	-	-
900	35 7/16" (900mm)	FD900-19 ■	FD900-27 ■	FD900-36 ■	-	-

* to order, door opening orientation ("R" for right or "L" for left) must be written in place of the red box (■) in the part number.

** limit: 1 adjustable shelf or 1 bottom shelf

***limit: 2 shelves (adjustable shelf and/or bottom shelf)

RETRACTABLE DOORS


TYPE	HT. (points)	USEABLE HT.	NW	MP	SC	MW	DW
Solid steel door	300	8 5/16"	-	RD300/MP	RD300/SC	RD300/MW	RD300/DW
Solid steel door	450	14 1/4"	-	RD450/MP	RD450/SC	RD450/MW	RD450/DW
Solid steel door	600	20 1/8"	-	RD600/MP	RD600/SC	RD600/MW	RD600/DW
Solid steel door with plexiglas window	450	14 1/4"	-	RD450/MP-P	RD450/SC-P	RD450/MW-P	RD450/DW-P
Solid steel door with plexiglas window	600	20 1/8"	-	RD600/MP-P	RD600/SC-P	RD600/MW-P	RD600/DW-P

6 Select drawer partitions and dividers

Drawer interior sets are located in corresponding Easy-Order footprint section (see chart on page 36). Additional drawer accessories are on pages 119-122.

7 Select colors

Housings and drawer fronts can be different colors but drawer interiors are always gray. Color differences exist between color samples and actual finishes. Please contact your Lista representative for accurate color matching. Custom colors are available and will be quoted on request.

COLOR CODE										
	Beige BE	Bright Blue BB*	Black BK*	Classic Blue CB	Dark Gray GR	Green GG	Light Gray LG*	Red NR	Sand SN	White FW

*Available with ESD properties. To specify ESD paint, add prefix "ESD" to paint part number. For ESD paint specifications, see Lista's Workbench and Workspace Furniture Catalog.

Lista Shallow Depth Cabinets Make Workspace Work

Lista's shallow depth cabinets (CL, ST and HS Width) provide the ultimate in space savings and ergonomic design. With their high density storage and shallow footprint, these cabinets are ideal for replacing shelves and maximizing floor space in narrow aisles, inside small trucks and vans, or under 24" deep counters.

Our shallow depth drawer is the centerpiece of these remarkably efficient cabinets. Each drawer, while just 18" deep, provides storage for items of up to 18" (CL), 24" (ST) or 36" (HS) in length.

At Lista, we recognize the importance of ergonomic design. With 18" deep drawers, all items are within easy reach. In addition, drawer handles are located at the top of each drawer, reducing reach and strain.



Aisle width

Lista's shallow depth cabinets save floorspace. They are 22 1/2" deep and only require a 36" aisle.

Drawer partitioning


The perforated drawer bottom allows for greater partitioning possibilities. This creates custom compartments for items up to 36" long (HS Width cabinet) and almost any shape.

18" deep drawer


The 100% full extension drawer stores all items in a comfortable radius of any worker's reach, making movements easy and natural.

Recessed handles

Full width handles close flush with the face of the housing, preventing possible injury or the snagging of clothing.



This overhead view shows two rows of Lista shallow depth cabinets on either side of a comfortable 36" wide access aisle. The aisle leaves enough room for a fully extended drawer and the person accessing it. The cabinets and aisle occupy a total depth of 6' 9".



This overhead view shows two rows of industry standard cabinets on either side of a 42" wide access aisle. This width aisle is required to accommodate a fully extended standard drawer and the person accessing it. The cabinets and aisle occupy a total depth of 8' 2".

Lista *Easy-Order* Shallow Depth Cabinets (22 1/2" deep)



Ordering an Easy-Order Lista cabinet or mobile cabinet takes just a few simple steps, and enables you to have a customized cabinet (down to the base, lock and paint color) without having to break a sweat.

TO ORDER AN EASY-ORDER COMBINATION:

(housing with preconfigured drawers and option of drawer interior sets)

	CABINETS	MOBILE CABINETS	DRAWER INTERIOR SETS
CL	pages 44-45	page 46	page 47
ST	pages 48-49	page 50	page 51
HS	pages 52-53	page 54	page 55

SHALLOW DEPTH CABINET FOOTPRINTS



CL WIDTH
22 3/16" wide



ST WIDTH
28 1/4" wide



HS WIDTH
40 1/4" wide

STEPS TO ORDER AN EASY-ORDER SHALLOW DEPTH CABINET

1 **Select cabinet footprint and height**

Select the particular cabinet size that best suits your needs. When choosing your housing height, keep in mind the cabinet top's potential use as a worksurface. See chart above for pages showing the different housing footprints.

2 **Select preferred drawer configuration**

The column to the immediate right of each cabinet illustration indicates drawer heights.

3 **Select drawer interior sets (optional)**

Decide whether you want your cabinet to be pre-configured with drawer interior sets. The second column to the right of the illustration shows the numerical portion of the part number for the drawer interior sets which are included if you choose this configuration (designated by an "A" or "B" at the end of the part number – i.e., SC0750-0703FA or MW0900-0504FB). The chart below the illustration indicates the number of drawer compartments created by the interior sets (which are shown on the page following each footprint's Easy-Order models).

4 **Select base type**


5 **Select lock type**

6 **Select paint color**

DRAWER HT.	DRAWER INTERIOR
3" (100F)	316
3" (100F)	316
3" (100F)	316
5" (150F)	209
7" (200F)	209
9" (250F)	104

PART NO.	DRWS.	COMPTS.
ST0900-0602F- ■ ■ □	6	-
ST0900-0602FA- ■ ■ □	6	70

CL Width Easy-Order Cabinet Combinations



*inside usable drawer dimensions

CL Width Cabinets

- 100% extension drawers with 165 lb. load capacity

Our most compact footprint, these cabinets are perfect for small, tight spaces. They also make easy-to-maneuver mobile cabinets.

How to order a CL Width Easy-Order Cabinet

1. Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by an "A" at the end of the part number – i.e., CL0600-0302NA). Drawer interior sets are shown on page 47.

2. Select base type.

NB = none
2FB = 2" frame base
4FB = 4" frame base
6FB = 6" frame base

For additional bases, see page 59; for Easy-Order mobile combinations, see page 46.

3. Select lock type.

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

4. Select paint color. For color chart, see back cover or below.

EXAMPLE: to order a CL0900-0603NA cabinet with no base, an individual lock, and Red paint for the housing with Light Gray drawers, the part number would be **CL0900-0603NA-NBRG**NR/LG.

CL600 Cabinets 27 1/2" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209

PART NO.	DRWS.	COMPTS.
CL0600-0701N- ■ ■ ■	7	-
CL0600-0701NA- ■ ■ ■	7	75

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206

PART NO.	DRWS.	COMPTS.
CL0600-0601N- ■ ■ ■	6	-
CL0600-0601NA- ■ ■ ■	6	57

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	3" (100N)	209
	4" (125N)	209
	4" (125N)	209

PART NO.	DRWS.	COMPTS.
CL0600-0604N- ■ ■ ■	6	-
CL0600-0604NA- ■ ■ ■	6	60

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	5" (150N)	206
	7" (200N)	104

PART NO.	DRWS.	COMPTS.
CL0600-0501N- ■ ■ ■	5	-
CL0600-0501NA- ■ ■ ■	5	43

	DRAWER HT.	DRAWER INTERIOR
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206

PART NO.	DRWS.	COMPTS.
CL0600-0502N- ■ ■ ■	5	-
CL0600-0502NA- ■ ■ ■	5	39

	DRAWER HT.	DRAWER INTERIOR
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206
	7" (200N)	104

PART NO.	DRWS.	COMPTS.
CL0600-0402N- ■ ■ ■	4	-
CL0600-0402NA- ■ ■ ■	4	25

	DRAWER HT.	DRAWER INTERIOR
	5" (150N)	206
	7" (200N)	104
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0600-0302N- ■ ■ ■	3	-
CL0600-0302NA- ■ ■ ■	3	14

	DRAWER HT.	DRAWER INTERIOR
	5" (150N)	206
	450 DOOR	
	BOTTOM SHELF	

PART NO.	DRWS.	COMPTS.
CL0600-0202N- ■ ■ ■	1	-
CL0600-0202NA- ■ ■ ■	1	6

CL750 Cabinets 33 1/2" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	5" (150N)	206
	7" (200N)	104

PART NO.	DRWS.	COMPTS.
CL0750-0701N- ■ ■ ■	7	-
CL0750-0701NA- ■ ■ ■	7	67

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206

PART NO.	DRWS.	COMPTS.
CL0750-0703N- ■ ■ ■	7	-
CL0750-0703NA- ■ ■ ■	7	63

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206
	7" (200N)	104

PART NO.	DRWS.	COMPTS.
CL0750-0601N- ■ ■ ■	6	-
CL0750-0601NA- ■ ■ ■	6	49

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0750-0602N- ■ ■ ■	6	-
CL0750-0602NA- ■ ■ ■	6	52

CL900 Cabinets

39 3/8" high

	DRAWER HT.	DRAWER INTERIOR
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206
	5" (150N)	206
	7" (200N)	104

PART NO.	DRWS.	COMPTS.
CL0750-0503N-■ ■ ■	5	-
CL0750-0503NA-■ ■ ■	5	31

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	3" (100N)	209
	4" (125N)	209
	7" (200N)	104
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0750-0505N-■ ■ ■	5	-
CL0750-0505NA-■ ■ ■	5	38

	DRAWER HT.	DRAWER INTERIOR
	5" (150N)	206
	5" (150N)	206
	7" (200N)	104
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0750-0401N-■ ■ ■	4	-
CL0750-0401NA-■ ■ ■	4	20

	DRAWER HT.	DRAWER INTERIOR
	5" (150N)	206
600 DOOR		
ADJUSTABLE SHELF		
BOTTOM SHELF		

PART NO.	DRWS.	COMPTS.
CL0750-0302N-■ ■ ■	1	-
CL0750-0302NA-■ ■ ■	1	6

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206

PART NO.	DRWS.	COMPTS.
CL0900-0802N-■ ■ ■	8	-
CL0900-0802NA-■ ■ ■	8	69

	DRAWER HT.	DRAWER INTERIOR
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206
	7" (200N)	104

PART NO.	DRWS.	COMPTS.
CL0900-0702N-■ ■ ■	7	-
CL0900-0702NA-■ ■ ■	7	52

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	2" (75N)	312
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0900-0704N-■ ■ ■	7	-
CL0900-0704NA-■ ■ ■	7	58

	DRAWER HT.	DRAWER INTERIOR
	3" (100N)	209
	3" (100N)	209
	5" (150N)	206
	5" (150N)	206
	5" (150N)	206
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0900-0601N-■ ■ ■	6	-
CL0900-0601NA-■ ■ ■	6	40

	DRAWER HT.	DRAWER INTERIOR
	2" (75N)	312
	3" (100N)	209
	4" (125N)	209
	5" (150N)	206
	7" (200N)	104
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0900-0603N-■ ■ ■	6	-
CL0900-0603NA-■ ■ ■	6	44

	DRAWER HT.	DRAWER INTERIOR
	3" (100N)	209
	5" (150N)	206
	7" (200N)	104
	7" (200N)	104
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0900-0503N-■ ■ ■	5	-
CL0900-0503NA-■ ■ ■	5	27

	DRAWER HT.	DRAWER INTERIOR
	7" (200N)	104
	7" (200N)	104
	9" (250N)	104
	9" (250N)	104

PART NO.	DRWS.	COMPTS.
CL0900-0401N-■ ■ ■	2	-
CL0900-0401NA-■ ■ ■	2	16

	DRAWER HT.	DRAWER INTERIOR
	5" (150N)	206
750 DOOR		
ADJUSTABLE SHELF		
BOTTOM SHELF		

PART NO.	DRWS.	COMPTS.
CL0900-0302N-■ ■ ■	1	-
CL0900-0302NA-■ ■ ■	1	6

CL Width Easy-Order Mobile Cabinet Combinations



Each mobile cabinet comes with:

- 2 fixed and 2 swivel casters with wheel locks
- Handles
- Individual drawer latches
- 100% full extension drawers with 165 lb. load capacity

How to read the charts on this page

The column to the right of each cabinet illustration indicates drawer heights.

The chart below the illustration indicates:

- Part numbers
- Number of drawers

How to order a CL Width Easy-Order Mobile Cabinet

1. **Select Easy-Order Cabinet Combination** either without or with mesh drawer liners (designated by an "A" near the end of the part number – i.e., CL0750-0601NA-M).

2. **Select lock type.**

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

3. **Select paint color.** For color chart, see back cover.

EXAMPLE: to order a CL0600-0504N-M cabinet with an individual lock, Dark Gray paint for the housing with Light Gray drawers, the part number would be **CL0600-0504N-M-RGGR/LG** (shown in photo at top of page).

CL600 Mobile Cabinets 33 1/8" high x 22 3/16" wide

DRAWER HEIGHT	
2" (75N)	
2" (75N)	
3" (100N)	
3" (100N)	
5" (150N)	

PART NO.	DRWS. INCL.
CL0600-0601N-M	6 -
CL0600-0601NA-M	6 mesh liners

includes 4" x 1 1/4" casters

DRAWER HEIGHT	
2" (75N)	
2" (75N)	
3" (100N)	
5" (150N)	
7" (200N)	

PART NO.	DRWS. INCL.
CL0600-0501N-M	5 -
CL0600-0501NA-M	5 mesh liners

includes 4" x 1 1/4" casters

DRAWER HEIGHT	
2" (75N)	
3" (100N)	
4" (125N)	
5" (150N)	
5" (150N)	

PART NO.	DRWS. INCL.
CL0600-0504N-M	5 -
CL0600-0504NA-M	5 mesh liners

includes 4" x 1 1/4" casters

CL750 Mobile Cabinets 39 1/8" high x 22 3/16" wide

DRAWER HEIGHT	
2" (75N)	
2" (75N)	
3" (100N)	
4" (125N)	
5" (150N)	
5" (150N)	

PART NO.	DRWS. INCL.
CL0750-0708N-M	7 -
CL0750-0708NA-M	7 mesh liners

includes 4" x 1 1/4" casters

DRAWER HEIGHT	
2" (75N)	
2" (75N)	
3" (100N)	
5" (150N)	
5" (150N)	
7" (200N)	

PART NO.	DRWS. INCL.
CL0750-0601N-M	6 -
CL0750-0601NA-M	6 mesh liners

includes 4" x 1 1/4" casters

DRAWER HEIGHT	
2" (75N)	
3" (100N)	
4" (125N)	
7" (200N)	
9" (250N)	

PART NO.	DRWS. INCL.
CL0750-0505N-M	5 -
CL0750-0505NA-M	5 mesh liners

includes 4" x 1 1/4" casters

CL600 Mobile Work Centers 33 3/4" high x 44 3/8" wide

DRAW. HEIGHT		DRAW. HEIGHT	
2" (75N)		5" (150N)	
2" (75N)		7" (200N)	
3" (100N)		9" (250N)	
5" (150N)			
7" (200N)			

PART NO.	DRWS. INCL.
MCL0600-0801N	8 -
MCL0600-0801NA	8 mesh liners

includes 4" x 2" casters

DRAW. HEIGHT		DRAW. HEIGHT	
2" (75N)		5" (150N)	
2" (75N)		450 DOOR	
3" (100N)		BOTTOM SHELF	
5" (150N)			
7" (200N)			

PART NO.	DRWS. INCL.
MCL0600-0601N	6 -
MCL0600-0601NA	6 mesh liners

includes 4" x 2" casters

DRAW. HEIGHT		INCLUDES	
2" (75N)		600 DOOR	
2" (75N)		ADJUSTABLE SHELF	
3" (100N)		BOTTOM SHELF	
5" (150N)			
7" (200N)			

PART NO.	DRWS. INCL.
MCL0600-0501N	5 -
MCL0600-0501NA	5 mesh liners

includes 4" x 2" casters

Mobile Cabinet Options

Hanging Shelf Cabinet

Optional shelf cabinet, painted to match mobile cabinet, is 22 3/16" wide x 15" deep x 29" high. It is attached to the side of mobile cabinet for easy maneuvering. Each cabinet has a bottom shelf and 1 adjustable 13 1/2" deep shelf. Individual lock (RG) and 2 keys are furnished. Can only be mounted on 750 height or higher mobile cabinets.

PART NO.	DESCRIPTION
OHC2329-CM	shelf cabinet
OHC1BCT/27	butcher block top (22 3/16" x 15" x 1 1/4")



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 22 1/2" deep.

PART NO.	MOUNTS TO
FS-27DX15-L	left side
FS-27DX15-R	right side

CL Width Mobile Cabinet Tops

For additional top choices, see page 67.

PART NO.	DESCRIPTION	HT.
CL-RT	retainer top w/ribbed mat	3/4"
CL1BCT	butcher block	1 3/4"
CL2BCT*	butcher block	1 3/4"
CL1PCT	plastic laminate	1 9/16"
CL2PCT*	plastic laminate	1 9/16"

*use with mobile work centers



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
CLDR104-■	2	7 1/2"
	2	9 1/4"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
CLDR206-■	6	5 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
CLDR209-■	9	5 1/2"

How to order a CL Width Easy-Order Drawer Interior Set

To order the drawer interior sets shown on this page, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order a CLDR420 drawer interior set for a 100 height (3") drawer, the part ordering number would be **CLDR420-100**.



For drawer heights 75 through 150

PART NO.	COMPTS.	CMPT. WIDTH
CLDR312-■	3	3 1/2"
	9	4 1/8"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
CLDR316-■	4	3 1/2"
	12	4 1/8"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. WIDTH
CLDR415-■	9	2 5/8"
	6	3 1/2"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. WIDTH
CLDR420-■	12	2 5/8"
	8	3 1/2"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. SIZE
CLDR009-■	9	6" x 6"



For drawer heights 75 through 125

PART NO.	COMPTS.	CMPT. SIZE
CLDR012-■	6	6" x 6"
	6	3" x 6"



For drawer heights 75 through 125


PART NO.	COMPTS.	CMPT. SIZE
CLDR018-■	18	3" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
CLDR021-■	3	6" x 6"
	6	3" x 6"
	12	3" x 3"

ST Width Easy-Order Cabinet Combinations



*inside usable drawer dimensions

ST Width Cabinets

- 100% extension drawers

This versatile footprint combines high density with easy ergonomic accessibility. It makes an ideal replacement for existing shelving, and is a popular size for mobile cabinets.

How to order an ST Width Easy-Order Cabinet

- Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by an "A" at the end of the part number – i.e., ST0900-0901FA). Drawer interior sets are shown on page 51.

- Select drawer weight-bearing capacity.

N = 165 lb. (75kg)
F = 440 lb. (200kg)

- Select base type.

NB = none
FT = fork truck
PT = pallet truck

For additional bases, see page 59; for Easy-Order mobile combinations, see page 50.

- Select lock type.

NL* = none
RG = individual
KA = keyed-alike
MA = master

*not available for double hinged door cabinets

For additional lock options, see page 62.

- Select paint color. For color chart, see back cover or below.

EXAMPLE: to order an ST0900-0702A cabinet with 440 lb. capacity drawers, a fork truck base, an individual lock, and Classic Blue paint for the housing with Sand drawers, the part number would be **ST0900-0702FA-FTRGCB/SN**.

ST750 Cabinets 33 1/2" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	3" (100)	316
	3" (100)	316
	3" (100)	209
	5" (150)	206
	5" (150)	104


PART NO.	DRWS.	COMPTS.
ST0750-0703	7	-
ST0750-0703A	7	91

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	3" (100)	316
	4" (125)	209
	4" (125)	209
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0750-0603	6	-
ST0750-0603A	6	78

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	5" (150)	209
	7" (200)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST0750-0504	5	-
ST0750-0504A	5	49



PART NO.	TRAYS
ST0750-0201D	2

door cabinet is 23 1/2" deep

ST900 Cabinets 39 3/8" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	2" (75)	316
	2" (75)	316
	3" (100)	316
	3" (100)	209
	3" (100)	206
	5" (150)	206
	5" (150)	104

PART NO.	DRWS.	COMPTS.
ST0900-0901	9	-
ST0900-0901A	9	113

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	3" (100)	316
	3" (100)	316
	3" (100)	316
	5" (150)	209
	5" (150)	209
	5" (150)	209

PART NO.	DRWS.	COMPTS.
ST0900-0802	8	-
ST0900-0802A	8	115

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	3" (100)	209
	3" (100)	209
	5" (150)	206
	5" (150)	206
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST0900-0702	7	-
ST0900-0702A	7	66

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	2" (75)	316
	3" (100)	209
	3" (100)	209
	5" (150)	209
	7" (200)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST0900-0703	7	-
ST0900-0703A	7	67

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	3" (100)	316
	5" (150)	209
	7" (200)	209
	9" (250)	104


PART NO.	DRWS.	COMPTS.
ST0900-0602	6	-
ST0900-0602A	6	70

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	5" (150)	209
	7" (200)	206
	7" (200)	104
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0900-0503	5	-
ST0900-0503A	5	39

	DRAWER HT.	DRAWER INTERIOR
	7" (200)	209
	7" (200)	209
	9" (250)	104
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0900-0401	4	-
ST0900-0401A	4	26



PART NO.	TRAYS
ST0900-0304D	3

door cabinet is 23 1/2" deep

ST1225 Cabinets

52 3/16" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	2" (75)	316
	2" (75)	316
	2" (75)	316
	2" (75)	316
	3" (100)	316
	3" (100)	316
	3" (100)	316
	3" (100)	209
	3" (100)	209
	4" (125)	209
	5" (150)	209
	5" (150)	209

PART NO.	DRWS.	COMPTS.
ST1225-1201	12	-
ST1225-1201	12	157

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	2" (75)	316
	2" (75)	316
	2" (75)	316
	3" (100)	316
	3" (100)	316
	3" (100)	316
	5" (150)	209
	5" (150)	209
	7" (200)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST1225-1001	10	-
ST1225-1001	10	122

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	316
	2" (75)	316
	2" (75)	316
	2" (75)	316
	3" (100)	209
	3" (100)	209
	3" (100)	209
	7" (200)	209
	9" (250)	104
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST1225-0901	9	-
ST1225-0901	9	92

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	4" (125)	316
	5" (150)	209
	5" (150)	209
	7" (200)	104
	7" (200)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST1225-0801	8	-
ST1225-0801	8	78

ST1350 Cabinets

57 1/8" high

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	2" (75)	420
	2" (75)	420
	2" (75)	420
	2" (75)	316
	2" (75)	316
	2" (75)	316
	3" (100)	316
	3" (100)	316
	3" (100)	316
	3" (100)	209
	3" (100)	209
	3" (100)	209

PART NO.	DRWS.	COMPTS.
ST1350-1601	16	-
ST1350-1601	16	255

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	2" (75)	420
	2" (75)	420
	3" (100)	316
	3" (100)	316
	3" (100)	316
	3" (100)	316
	3" (100)	209
	3" (100)	209
	3" (100)	209
	3" (100)	209
	4" (125)	209

PART NO.	DRWS.	COMPTS.
ST1350-1401	14	-
ST1350-1401	14	198

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	2" (75)	316
	2" (75)	316
	3" (100)	316
	3" (100)	316
	3" (100)	209
	3" (100)	209
	3" (100)	209
	5" (150)	206
	5" (150)	206
	5" (150)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST1350-1201	12	-
ST1350-1201	12	142

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	3" (100)	316
	3" (100)	316
	3" (100)	316
	5" (150)	209
	5" (150)	209
	5" (150)	209
	5" (150)	104
	5" (150)	104

PART NO.	DRWS.	COMPTS.
ST1350-1101	11	-
ST1350-1101	11	131

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	4" (125)	316
	4" (125)	316
	5" (150)	209
	5" (150)	209
	5" (150)	209
	5" (150)	104
	5" (150)	104
	5" (150)	104

PART NO.	DRWS.	COMPTS.
ST1350-1001	10	-
ST1350-1001	10	103

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	420
	2" (75)	420
	3" (100)	316
	3" (100)	316
	3" (100)	316
	5" (150)	209
	5" (150)	209
	5" (150)	209
	7" (200)	209
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST1350-1002	10	-
ST1350-1002	10	128

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	3" (100)	316
	3" (100)	316
	5" (150)	209
	5" (150)	209
	7" (200)	209
	7" (200)	209
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST1350-0901	9	-
ST1350-0901	9	104

	DRAWER HT.	DRAWER INTERIOR
	3" (100)	316
	3" (100)	316
	3" (100)	316
	5" (150)	209
	5" (150)	209
	5" (150)	206
	7" (200)	206
	7" (200)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST1350-0902	9	-
ST1350-0902	9	86

	DRAWER HT.	DRAWER INTERIOR
	5" (150)	316
	5" (150)	316
	5" (150)	209
	5" (150)	209
	5" (150)	209
	7" (200)	209
	7" (200)	209
	7" (200)	104


PART NO.	DRWS.	COMPTS.
ST1350-0801	8	-
ST1350-0801	8	81

	DRAWER HT.	DRAWER INTERIOR
	5" (150)	209
	7" (200)	209
	7" (200)	209
	7" (200)	209
	7" (200)	104
	7" (200)	104
	7" (200)	104

PART NO.	DRWS.	COMPTS.
ST1350-0701	7	-
ST1350-0701	7	48

	DRAWER HT.	DRAWER INTERIOR
	5" (150)	316
	5" (150)	209
	5" (150)	209
	7" (200)	206
	7" (200)	104
	9" (250)	104
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST1350-0702	7	-
ST1350-0702	7	52



PART NO.	TRAYS
ST1350-0401D	4

door cabinet is 23 1/2" deep

ST Width Easy-Order Mobile Cabinet Combinations



Each mobile cabinet comes with:

- 2 fixed and 2 swivel 6" x 2" casters with wheel locks
- Tubular steel handles
- Individual drawer latches
- 100% full extension drawers

How to read the charts on this page

The 2 columns to the right of each cabinet illustration indicate:

- Drawer heights
- Drawer interior sets (shown on page 51)

The chart below the illustration indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (shown on page 51)

How to order an ST Width Easy-Order Mobile Cabinet

1. **Select Easy-Order Cabinet Combination** either without or with drawer interior sets (designated by an "A" near the end of the part number – i.e., ST0600-0501A-M).

2. **Select drawer weight-bearing capacity.**

N = 165 lb. (75kg)

F = 440 lb. (200kg)

3. **Select lock type.**

NL = none

RG = individual

KA = keyed-alike

MA = master

For additional lock options, see page 62.

4. **Select paint color.** For color chart, see back cover.

EXAMPLE: to order an ST0750-0701A-M cabinet with 165 lb. capacity drawers, an individual lock, Light Gray paint for the housing with Red drawers, and a retainer top, the part number would be **ST0750-0701NA-M-RGLG/NR**, with an ST-RT top (shown in photo at top of page).

ST600 Mobile Cabinets 35 1/2" high x 28 1/4" wide

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	2" (75)	308
	3" (100)	308
	5" (150)	206
	7" (200)	206

PART NO.	DRWS.	COMPTS.
ST0600-0501 -M- ☐	5	-
ST0600-0501 -A-M- ☐	5	46

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	2" (75)	518
	3" (100)	308
	3" (100)	308
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0600-0503 -M- ☐	5	-
ST0600-0503 -A-M- ☐	5	56

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	3" (100)	308
	4" (125)	206
	5" (150)	104
	5" (150)	104

PART NO.	DRWS.	COMPTS.
ST0600-0504 -M- ☐	5	-
ST0600-0504 -A-M- ☐	5	40

ST750 Mobile Cabinets 41 1/2" high x 28 1/4" wide

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	2" (75)	518
	2" (75)	308
	2" (75)	308
	3" (100)	308
	5" (150)	206
	7" (200)	206

PART NO.	DRWS.	COMPTS.
ST0750-0701 -M- ☐	7	-
ST0750-0701 -A-M- ☐	7	72

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	2" (75)	518
	3" (100)	308
	3" (100)	308
	5" (150)	206
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0750-0602 -M- ☐	6	-
ST0750-0602 -A-M- ☐	6	62

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	3" (100)	308
	4" (125)	308
	7" (200)	206
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0750-0505 -M- ☐	5	-
ST0750-0505 -A-M- ☐	5	44

ST900 Mobile Cabinets 47 3/8" high x 28 1/4" wide

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	2" (75)	518
	2" (75)	308
	2" (75)	308
	3" (100)	308
	3" (100)	308
	5" (150)	206
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0900-0803 -M- ☐	8	-
ST0900-0803 -A-M- ☐	8	78

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	2" (75)	518
	3" (100)	308
	3" (100)	308
	5" (150)	206
	5" (150)	206
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0900-0704 -M- ☐	7	-
ST0900-0704 -A-M- ☐	7	68

	DRAWER HT.	DRAWER INTERIOR
	2" (75)	518
	3" (100)	308
	4" (125)	308
	5" (150)	206
	7" (200)	206
	9" (250)	104

PART NO.	DRWS.	COMPTS.
ST0900-0603 -M- ☐	6	-
ST0900-0603 -A-M- ☐	6	50

Mobile Cabinet Options

Hanging Shelf Cabinet

Optional shelf cabinet, painted to match mobile cabinet, is 22 3/16" wide x 15" deep x 29" high. It is attached to the side of mobile cabinet for easy maneuvering. Each cabinet has a bottom shelf and 1 adjustable 13 1/2" deep shelf. Individual lock (RG) and 2 keys are furnished. Can only be mounted on 750 height or higher mobile cabinets.

PART NO.	DESCRIPTION
OHC2329-CM	shelf cabinet
OHC1BCT/27	butcher block top (22 3/16" x 15" x 1 1/4")



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 22 1/2" deep.

PART NO.	MOUNTS TO
FS-27DX15-L	left side
FS-27DX15-R	right side

ST Width Mobile Cabinet Tops

For additional top choices, see page 67.

PART NO.	DESCRIPTION	HT.
ST-RT	retainer top w/ribbed mat	3/4"
ST1BCT	butcher block	1 3/4"
ST1PCT	plastic laminate	1 9/16"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
SDR104-	4	11 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
SDR106-	6	11 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
SDR206-	6	7 1/2"

How to order an ST Width Easy-Order Drawer Interior Set

To order the drawer interior sets shown on this page, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order an SDR308 drawer interior set for a 100 height (3") drawer, the part ordering number would be **SDR308-100**.




For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
SDR209-	9	7 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
SDR308-	8	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
SDR312-	12	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
SDR316-	16	5 1/2"




For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
SDR420-	16	4 1/8"
	4	4 7/8"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
SDR518-	18	3 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
SDR530-	30	3 1/2"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
SDR012-	12	6" x 6"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
SDR020-	4	6" x 6"
	16	3" x 6"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
SDR024-	24	3" x 6"



For drawer height 75


PART NO.	COMPTS.	CMPT. SIZE
SDR032-	16	3" x 6"
	16	3" x 3"



For drawer height 75

PART NO.	COMPTS.	CMPT. WIDTH
SDR160-	24	2 1/4"
	36	1 3/4"

HS Width **Easy-Order** Cabinet Combinations



*inside usable drawer dimensions

HS Width Cabinets

- 100% extension drawers with 440 lb. load capacity

Ideal for storing items up to 36" in length, these cabinets are designed for the utmost ergonomic efficiency.

How to order an HS Width Easy-Order Cabinet

1. **Select Easy-Order Cabinet Combination** either without or with drawer interior sets (designated by an "A" at the end of the part number – i.e., HS0900-0902FA). Drawer interior sets are shown on page 55.

2. **Select base type.**

NB = none
FT = fork truck
PT = pallet truck

For additional bases, see page 59; for Easy-Order mobile combinations, see page 54.

3. **Select lock type.**

NL* = none
RG = individual
KA = keyed-alike
MA = master

*not available for double hinged door cabinets

For additional lock options, see page 62.

4. **Select paint color.** For color chart, see back cover or below.

EXAMPLE: to order an HS0900-0503FA cabinet with a fork truck base, an individual lock and Red paint, the part number would be **HS0900-0503FA-FTRGNR**.

HS750 Cabinets 33 1/2" high



DRAWER HT.	DR. INT.
2" (75F)	621
2" (75F)	621
2" (75F)	518
2" (75F)	518
3" (100F)	415
3" (100F)	415
3" (100F)	415
5" (150F)	206

PART NO.	DRWS.	COMPTS.
HS0750-0801F-   	8	-
HS0750-0801FA-   	8	129



DRAWER HT.	DR. INT.
2" (75F)	518
2" (75F)	518
3" (100F)	415
3" (100F)	415
3" (100F)	415
5" (150F)	312
5" (150F)	312

PART NO.	DRWS.	COMPTS.
HS0750-0703F-   	7	-
HS0750-0703FA-   	7	105



DRAWER HT.	DR. INT.
3" (100F)	415
3" (100F)	415
5" (150F)	312
7" (200F)	206
7" (200F)	206

PART NO.	DRWS.	COMPTS.
HS0750-0504F-   	5	-
HS0750-0504FA-   	5	54



INCLUDES
ROLL-OUT TRAY
ROLL-OUT TRAY

PART NO.	TRAYS
HS0750-0201D-   	2

door cabinet is 23 1/2" deep

HS900 Cabinets 39 3/8" high



DRAWER HT.	DR. INT.
2" (75F)	518
2" (75F)	518
2" (75F)	415
2" (75F)	415
3" (100F)	415
3" (100F)	312
3" (100F)	312
5" (150F)	206
5" (150F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0901F-   	9	-
HS0900-0901FA-   	9	117



DRAWER HT.	DR. INT.
2" (75F)	518
2" (75F)	518
3" (100F)	518
3" (100F)	518
3" (100F)	415
3" (100F)	415
3" (100F)	415
5" (150F)	312
5" (150F)	312

PART NO.	DRWS.	COMPTS.
HS0900-0902F-   	9	-
HS0900-0902FA-   	9	147



DRAWER HT.	DR. INT.
2" (75F)	518
2" (75F)	518
3" (100F)	518
3" (100F)	518
3" (100F)	415
3" (100F)	415
3" (100F)	312
7" (200F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0801F-   	8	-
HS0900-0801FA-   	8	120



DRAWER HT.	DR. INT.
3" (100F)	518
3" (100F)	518
3" (100F)	415
3" (100F)	415
5" (150F)	312
5" (150F)	312
7" (200F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0702F-   	7	-
HS0900-0702FA-   	7	96



DRAWER HT.	DR. INT.
2" (75F)	518
3" (100F)	518
4" (125F)	415
5" (150F)	415
7" (200F)	312
9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0603F-   	6	-
HS0900-0603FA-   	6	84



DRAWER HT.	DR. INT.
3" (100F)	415
3" (100F)	415
5" (150F)	312
5" (150F)	312
7" (200F)	206
7" (200F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0604F-   	6	-
HS0900-0604FA-   	6	66



DRAWER HT.	DR. INT.
3" (100F)	415
5" (150F)	312
7" (200F)	312
7" (200F)	206
9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0503F-   	5	-
HS0900-0503FA-   	5	51



INCLUDES
ROLL-OUT TRAY
ROLL-OUT TRAY
ROLL-OUT TRAY

PART NO.	TRAYS
HS0900-0304D-   	3

door cabinet is 23 1/2" deep

HS1225 Cabinets

52 3/16" high

	DRAWER HT.	DR. INT.
	2" (75F)	621
	2" (75F)	621
	2" (75F)	621
	2" (75F)	518
	2" (75F)	518
	3" (100F)	415
	3" (100F)	415
	3" (100F)	415
	3" (100F)	415
	5" (150F)	312
	5" (150F)	312

PART NO.	DRWS.	COMPTS.
HS1225-1202F-  	12	-
HS1225-1202FA-  	12	195

	DRAWER HT.	DR. INT.
	2" (75F)	621
	2" (75F)	621
	2" (75F)	621
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	5" (150F)	415
	5" (150F)	415
	7" (200F)	312
	7" (200F)	312

PART NO.	DRWS.	COMPTS.
HS1225-1001F-  	10	-
HS1225-1001FA-  	10	171

	DRAWER HT.	DR. INT.
	3" (100F)	518
	3" (100F)	518
	4" (125F)	415
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	5" (150F)	206
	5" (150F)	206
	5" (150F)	206

PART NO.	DRWS.	COMPTS.
HS1225-0902F-  	9	-
HS1225-0902FA-  	9	105

	DRAWER HT.	DR. INT.
	4" (125F)	415
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	7" (200F)	206
	7" (200F)	206
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS1225-0701F-  	7	-
HS1225-0701FA-  	7	69

HS1350 Cabinets

57 1/8" high

	DRAWER HT.	DR. INT.
	2" (75F)	621
	2" (75F)	621
	2" (75F)	621
	2" (75F)	621
	2" (75F)	518
	2" (75F)	518
	2" (75F)	518
	3" (100F)	415
	3" (100F)	415
	3" (100F)	415
	3" (100F)	415
	4" (125F)	312
	4" (125F)	312

PART NO.	DRWS.	COMPTS.
HS1350-1501F-  	15	-
HS1350-1501FA-  	15	255

	DRAWER HT.	DR. INT.
	2" (75F)	621
	2" (75F)	621
	2" (75F)	621
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	3" (100F)	415
	3" (100F)	415
	3" (100F)	415
	4" (125F)	312
	4" (125F)	312
	7" (200F)	206

PART NO.	DRWS.	COMPTS.
HS1350-1301F-  	13	-
HS1350-1301FA-  	13	213

	DRAWER HT.	DR. INT.
	2" (75F)	415
	2" (75F)	415
	2" (75F)	312
	2" (75F)	312
	3" (100F)	312
	3" (100F)	312
	3" (100F)	LR209
	3" (100F)	LR209
	5" (150F)	206
	5" (150F)	206
	5" (150F)	LR106
	7" (200F)	LR106

PART NO.	DRWS.	COMPTS.
HS1350-1201F-  	12	-
HS1350-1201FA-  	12	120

	DRAWER HT.	DR. INT.
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	3" (100F)	415
	3" (100F)	415
	5" (150F)	312
	5" (150F)	312
	5" (150F)	206
	5" (150F)	206

PART NO.	DRWS.	COMPTS.
HS1350-1101F-  	11	-
HS1350-1101FA-  	11	150

	DRAWER HT.	DR. INT.
	2" (75F)	621
	2" (75F)	621
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	5" (150F)	415
	5" (150F)	415
	7" (200F)	312
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS1350-1002F-  	10	-
HS1350-1002FA-  	10	159

	DRAWER HT.	DR. INT.
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	4" (125F)	415
	4" (125F)	415
	7" (200F)	312
	7" (200F)	312

PART NO.	DRWS.	COMPTS.
HS1350-1003F-  	10	-
HS1350-1003FA-  	10	156

	DRAWER HT.	DR. INT.
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	3" (100F)	518
	5" (150F)	415
	5" (150F)	415
	7" (200F)	312
	7" (200F)	312
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS1350-0901F-  	9	-
HS1350-0901FA-  	9	132

	DRAWER HT.	DR. INT.
	3" (100F)	415
	3" (100F)	415
	3" (100F)	415
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	7" (200F)	206
	7" (200F)	206

PART NO.	DRWS.	COMPTS.
HS1350-0902F-  	9	-
HS1350-0902FA-  	9	105

	DRAWER HT.	DR. INT.
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	7" (200F)	206
	7" (200F)	206
	7" (200F)	206

PART NO.	DRWS.	COMPTS.
HS1350-0801F-  	8	-
HS1350-0801FA-  	8	78

	DRAWER HT.	DR. INT.
	3" (100F)	518
	3" (100F)	518
	5" (150F)	415
	5" (150F)	415
	7" (200F)	312
	7" (200F)	312
	7" (200F)	312
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS1350-0802F-  	8	-
HS1350-0802FA-  	8	108

	DRAWER HT.	DR. INT.
	5" (150F)	312
	5" (150F)	312
	5" (150F)	312
	7" (200F)	312
	7" (200F)	206
	9" (250F)	206
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS1350-0702F-  	7	-
HS1350-0702FA-  	7	66

	INCLUDES
	ROLL-OUT TRAY
	ROLL-OUT TRAY
	ROLL-OUT TRAY
	ROLL-OUT TRAY

PART NO.	TRAYS
HS1350-0401D-  	4

door cabinet is 23 1/2" deep

HS Width *Easy-Order* Mobile Cabinet Combinations



Each mobile cabinet comes with:

- 2 fixed and 2 swivel 6" x 2" casters with wheel locks
- Tubular steel handles
- Individual drawer latches
- 100% full extension drawers with 440 lb. load capacity

How to read the charts on this page

The 2 columns to the right of each cabinet illustration indicate:

- Drawer heights
- Drawer interior sets (shown on page 55)

The chart below the illustration indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (shown on page 55)

How to order an HS Width Easy-Order Mobile Cabinet

1. Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by an "A" near the end of the part number – i.e., HS0600-0501FA-M).

2. ☒ Select lock type.

NL = none

RG = individual

KA = keyed-alike

MA = master

For additional lock options, see page 62.

3. ☐ Select paint color. For color chart, see back cover.

EXAMPLE: to order an HS0900-0803FA-M cabinet with an individual lock, Light Gray paint for the housing with Black drawers, and a retainer top, the part number would be **HS0900-0803FA-M-RGLG/BK**, with an HS-RT retainer top (shown in photo at top of page).

HS600 Mobile Cabinets 35 1/2" high x 40 1/4" wide

	DRAWER HT.	DR. INT.
	2" (75F)	518
	2" (75F)	LR312
	3" (100F)	312
	3" (100F)	312
	3" (100F)	LR312
	5" (150F)	206

PART NO.	DRWS.	COMPTS.
HS0600-0601F-M- ☐	6	-
HS0600-0601FA-M- ☐	6	72

	DRAWER HT.	DR. INT.
	2" (75F)	617
	2" (75F)	LR312
	2" (75F)	518
	3" (100F)	312
	5" (150F)	LR106

PART NO.	DRWS.	COMPTS.
HS0600-0501F-M- ☐	5	-
HS0600-0501FA-M- ☐	5	65

	DRAWER HT.	DR. INT.
	3" (100F)	LR312
	3" (100F)	518
	5" (150F)	312
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS0600-0403F-M- ☐	4	-
HS0600-0403FA-M- ☐	4	48

HS750 Mobile Cabinets 41 1/2" high x 40 1/4" wide

	DRAWER HT.	DR. INT.
	2" (75F)	617
	2" (75F)	617
	2" (75F)	LR312
	2" (75F)	LR312
	3" (100F)	518
	5" (150F)	312
	7" (200F)	LR106

PART NO.	DRWS.	COMPTS.
HS0750-0701F-M- ☐	7	-
HS0750-0701FA-M- ☐	7	94

	DRAWER HT.	DR. INT.
	2" (75F)	617
	2" (75F)	LR312
	3" (100F)	518
	3" (100F)	LR209
	5" (150F)	312
	9" (250F)	LR106

PART NO.	DRWS.	COMPTS.
HS0750-0602F-M- ☐	6	-
HS0750-0602FA-M- ☐	6	74

	DRAWER HT.	DR. INT.
	2" (75F)	518
	3" (100F)	LR312
	4" (125F)	312
	7" (200F)	206
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS0750-0505F-M- ☐	5	-
HS0750-0505FA-M- ☐	5	54

HS900 Mobile Cabinets 47 3/8" high x 40 1/4" wide

	DRAWER HT.	DR. INT.
	2" (75F)	518
	2" (75F)	518
	2" (75F)	LR312
	3" (100F)	312
	3" (100F)	312
	4" (125F)	312
	4" (125F)	312
	5" (150F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0903F-M- ☐	9	-
HS0900-0903FA-M- ☐	9	114

	DRAWER HT.	DR. INT.
	2" (75F)	617
	2" (75F)	617
	2" (75F)	LR312
	3" (100F)	518
	3" (100F)	518
	5" (150F)	312
	9" (250F)	LR106

PART NO.	DRWS.	COMPTS.
HS0900-0803F-M- ☐	8	-
HS0900-0803FA-M- ☐	8	112

	DRAWER HT.	DR. INT.
	2" (75F)	518
	2" (75F)	LR312
	3" (100F)	312
	3" (100F)	LR312
	5" (150F)	206
	5" (150F)	206
	9" (250F)	206

PART NO.	DRWS.	COMPTS.
HS0900-0704F-M- ☐	7	-
HS0900-0704FA-M- ☐	7	72

Mobile Cabinet Options

Hanging Shelf Cabinet

Optional shelf cabinet, painted to match mobile cabinet, is 22 3/16" wide x 15" deep x 29" high. It is attached to the side of mobile cabinet for easy maneuvering. Each cabinet has a bottom shelf and 1 adjustable 13 1/2" deep shelf. Individual lock (RG) and 2 keys are furnished. Can only be mounted on 750 height or higher mobile cabinets.

PART NO.	DESCRIPTION
OHC2329-CM	shelf cabinet
OHC1BCT/27	butcher block top
	(22 3/16" x 15" x 1 1/4")



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 22 1/2" deep.

PART NO.	MOUNTS TO
FS-27DX15-L	left side
FS-27DX15-R	right side

HS Mobile Cabinet Tops

For additional top choices, see page 67.

PART NO.	DESCRIPTION	HT.
HS-RT	retainer top w/ribbed mat	3/4"
HS1BCT	butcher block	1 3/4"
HS1PCT	plastic laminate	1 9/16"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
HDR-LR106-■	3	7 1/2"
	3	9 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
HDR206-■	6	11 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
HDR-LR207-■	3	3 3/4"
	2	5 3/4"
	2	7 3/4"

How to order an HS Width Easy-Order Drawer Interior Set

To order the drawer interior sets shown on this page, use the part number in the chart and add the drawer height in place of the green box.

EXAMPLE: to order an HDR312 drawer interior set for a 100 height (3") drawer, the part ordering number would be **HDR312-100**.



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
HDR-LR209-■	9	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
HDR312-■	6	7 1/2"
	6	9 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
HDR-LR312-■	10	3 1/2"
	2	5 1/2"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
HDR415-■	6	5 1/2"
	9	7 3/4"



For all drawer heights

PART NO.	COMPTS.	CMPT. WIDTH
HDR518-■	18	5 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
HDR617-■	10	3 1/2"
	5	5 1/2"
	2	7 1/2"



For drawer heights 75 through 200

PART NO.	COMPTS.	CMPT. WIDTH
HDR621-■	15	5 1/4"
	6	4 1/2"




For drawer heights 75 through 100

PART NO.	COMPTS.	CMPT. WIDTH
HDR836-■	36	3 1/2"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
HDR024-■	12	6" x 6"
	12	3" x 6"



For drawer heights 75 and 100

PART NO.	COMPTS.	CMPT. SIZE
HDR036-■	36	3" x 6"



For drawer height 75

PART NO.	COMPTS.	CMPT. SIZE
HDR040-■	6	6" x 6"
	14	3" x 6"
	20	3" x 3"



For drawer height 75

PART NO.	COMPTS.	CMPT. WIDTH
HDR-SG432-■	6	2 3/4"
	10	1 3/4"
	15	1 1/4"

How to Order Custom Shallow Depth Cabinets (22 1/2" deep)

There are tens of thousands of ways to configure a Lista cabinet. Our modular building block system means that your cabinets can be configured to exactly suit your requirements.

By walking through the steps summarized on the facing page and shown on the following four pages, you can create shallow depth cabinets that will exactly fit your own specific needs.



HS cabinets with stainless steel counter top.



High-density HS drawers.

Mobile HS (left) and ST (right) cabinets are versatile toolboxes.




Stacked HS shelf and drawer cabinets allow narrow aisles.

TO ORDER AN EASY-ORDER COMBINATION:

(housing with preconfigured drawers and option of drawer interior sets)

	CABINETS	MOBILE CABINETS	DRAWER INTERIOR SETS
CL	pages 44-45	page 46	page 47
ST	pages 48-49	page 50	page 51
HS	pages 52-53	page 54	page 55

STEPS TO ORDER A CUSTOM CONFIGURED SHALLOW DEPTH CABINET



1 Select cabinet housing
Select the particular cabinet housing that best suits your needs. When choosing your housing height, keep in mind the cabinet top's potential use as a worksurface. **See page 58.**

2 Select a lock
Choose from a wide array of locking options. **See page 59.**

3 Select a cabinet base (optional)
A number of optional bases to suit a wide variety of uses. **See page 59.**

4 Select a cabinet top or counter top (optional)
Top descriptions can be found on **page 67**; information about counter tops to span rows of cabinets is on **page 107**.

5 Select drawers, shelves, roll-out trays and doors
Drawers, shelves and roll-out trays can be used in any sequence or combination you wish. **See pages 60-61.**

6 Select drawer partitions and dividers (optional)
Choose from the Easy-Order drawer interior sets shown in each cabinet's Easy-Order section, or order custom drawer partitions and dividers (**page 118**). Choose from many accessories (**pages 119-122**).


7 Select colors
Select color from the chart on **page 61**. Housing and drawer fronts can be different colors but drawer interiors are always gray.

The total drawer and/or door model numbers must add up to the model number of the housing.


EXAMPLES:

Model 900 Housing

(2) 100 drawers	=	200
(2) 150 drawers	=	300
(2) 200 drawers	=	400
		900



(2) 150 drawers	=	300
(1) 600 door	=	600
		900



Sample Cabinet Order

QUANTITY	PART NO.	DESCRIPTION	
1	ST900	housing	1
1	KA	keyed alike lock	2
1	ST-FTB	fork truck base	3
1	ST1BCT	butcher block top	4
2	ST100F	drawers	5
2	ST150F	drawers	5
2	ST200F	drawers	5
2	SDR420-100	drawer interiors	6
2	SDR308-150	drawer interiors	6
2	SDR104-200	drawer interiors	6
	Housing: BB	Bright Blue	7
	Drawers: LG	Light Gray	7

How to Order **Custom Shallow Depth Cabinets (22 1/2" deep)**

1 Select cabinet housing

Cabinet housing can be configured with any sequence of drawers, shelves and roll-out trays (see page 60). See the graphic on page 57 for information on configuring the correct height(s) of drawers and doors to fit the housing you have selected. Housing includes an individual lock and 2 keys.

FOOTPRINTS



CL WIDTH
22 3/16" wide



ST WIDTH
28 1/4" wide



HS WIDTH
40 1/4" wide

HEIGHTS




MODEL 300
15 3/4" overall height



MODEL 450
21 5/8" overall height



MODEL 600
27 1/2" overall height



MODEL 750
33 1/2" overall height



MODEL 900
39 3/8" overall height



MODEL 1050
45 1/4" overall height



MODEL 1225
52 3/16" overall height



MODEL 1350
57 1/8" overall height

AVAIL. HT. (points)	OVERALL HEIGHT (inches/mm)	CL	ST	HS
300	15 3/4" (400mm)	CL300	ST300	HS300
450	21 5/8" (550mm)	CL450	ST450	HS450
600	27 1/2" (700mm)	CL600	ST600	HS600
750	33 1/2" (850mm)	CL750	ST750	HS750
900	39 3/8" (1000mm)	CL900	ST900	HS900
1050	45 1/4" (1150mm)	CL1050	ST1050	HS1050
1225	52 3/16" (1325mm)	CL1225	ST1225	HS1225
1350	57 1/8" (1450mm)	CL1350	ST1350	HS1350

OR select cabinet housing with double hinged doors (housing depth is 23 1/2")

Double hinged door housing includes a pair of hinged doors and an individual lock and 2 keys. It can be configured with any sequence of drawers, shelves and roll-out trays (see page 60). For tops for double hinged door cabinets, contact your Lista representative.



AVAIL. HT. (points)	OVERALL HEIGHT (inches/mm)	CL	ST	HS
600	27 1/2" (700mm)	-	STDHD600	HSDHD600
750	33 1/2" (850mm)	-	STDHD750	HSDHD750
900	39 3/8" (1000mm)	-	STDHD900	HSDHD900
1225	52 3/16" (1325mm)	-	STDHD1225	HSDHD1225
1350	57 1/8" (1450mm)	-	STDHD1350	HSDHD1350

2 Select lock and keying options (choose from additional selections on page 62)


If you have locking and security needs other than the individual lock (lock and 2 keys) that comes with all cabinets, select from the options below or see page 62.

Individual Lock (RG)

Cabinets come with an individual lock and 2 keys. Each cabinet lock is keyed differently.

No Lock (NL)


Specify if no cylinder lock is desired for cabinet housing. Cabinet will still include Preventip® one-drawer-at-a-time safety feature. Not available for double hinged door cabinets.



Keyed Alike Lock (KA)

All cabinets have identical locks, each with 2 keys; the same key opens all cabinets. Each cabinet in the keyed alike group must have keyed alike (KA) specified on the order. Cabinets containing drawers and doors will only be keyed alike if specified.

PART NO.	LOCK TYPE
KA	keyed alike lock



Master Keyed Lock (MA)

Each cabinet has a different lock with 2 keys. Each cabinet in the master key group must have master keyed lock (MA) specified on the order. Master key (MK) that opens all locks must be ordered separately.

PART NO.	LOCK TYPE
MA	master lock
MK	group master key
GMK	grand master key

3 Select optional cabinet base

Fork Truck Base

Steel fork truck base permits moving of fully loaded cabinets. Base has snap-on front and rear covers, and is recessed 1 1/8" (30mm) from the front of the housing. Bases are pre-punched to allow stacking. Color: to match housing.



Pallet Truck Base

Steel pallet truck base permits moving of fully loaded cabinets with a hand pallet truck. Base has snap-on front and rear covers, and is recessed 1 1/8" (30mm) each from the front and back of the housing. Color: to match housing.



Frame Base

Steel base is used to bring cabinets up to desired work height. Base is recessed 1 1/8" (30mm) from the front of the housing. Color: to match housing.



Mobile Caster Base

A set of 2 fixed and 2 swivel casters. Each swivel caster has an individual wheel lock. Casters are factory mounted to the base. (See page 66 for other mobile accessories.)



Wet Clean Base

Allows for easy cleaning below housing in areas where floors are often washed (such as labs and hospitals), or where wet floors are an issue. Raises cabinet housing 4 9/16" above floor. Individual leg height is further adjustable to allow for leveling (up to 1 3/4" additional height), even on extremely uneven surfaces. Cabinet can be lifted and moved with a hand pallet truck.



TYPE	OVERALL HEIGHT	CASTER DIMEN.	WEIGHT CAPACITY	CL	ST	HS
Fork truck base	2 3/8" (60mm)			CL-FTB	ST-FTB	HS-FTB
Pallet truck base	4" (100mm)		-	CL-PTB	ST-PTB	HS-PTB
Frame base	2" (50mm)			CL-2FB	ST-2FB	HS-2FB
Frame base	4" (100mm)			CL-4FB	ST-4FB	HS-4FB
Frame base	6" (150mm)			CL-6FB	ST-6FB	HS-6FB
Mobile base*	5 5/8"	4" x 1 1/4"	1000 lb.	CB-CL3.5X1	-	-
Mobile base*	6 1/4"	4" x 2"	1400 lb.	CB-CL4B	CB-ST4B	CB-HS4B
Mobile base*	8"	6" x 2"	2400 lb.	CB-CL6B	CB-ST6B	CB-HS6B
Mobile base*	8"	6" x 2"	3600 lb.	-	CB-ST6ML	CB-HS6ML
Wet clean base	4 9/16"			WCB-CL	WCB-ST	WCB-HS

*mobile bases not recommended for use with 1225 height or higher cabinets

How to Order **Custom Shallow Depth Cabinets (22 1/2" deep)**

4 Select optional cabinet top (individual cabinet tops page 67; counter tops for multiple cabinets page 107)

5 Select drawers, shelves and/or roll-out trays

Drawers, shelves and roll-out trays can be arranged and re-arranged in a cabinet housing in any sequence. **See the graphic on page 57 for information on configuring the correct height(s) of drawers and doors to fit the housing you have selected.**

Drawers

Drawers are 100% full extension, allowing complete use of the furthest corners and easy access to all contents. Each drawer has a maximum load capacity of either 440 lb. (200kg) or 165 lb. (75kg).



Shelves

Fixed bottom shelves and adjustable upper shelves can be moved up or down in 1" increments. Vertical dividers are available to sub-divide shelves. Shelf cabinets are often stacked above drawer cabinets for maximum space savings. Maximum load capacity of 440 lbs. (200kg) evenly distributed.



Roll-Out Trays

Roll-out trays allow easy access to stored items, even in the farthest corner. 100% full extension, 440 lb. (200 kg) or 165 lb. (75kg) maximum load capacity.



DRAWER FOOTPRINTS (usable inside widths shown below – all shallow depth drawers are 18" / 459mm / 27 units deep)



CL WIDTH
18" wide
(459mm / 27 units)



ST WIDTH
24" wide
(610mm / 36 units)



HS WIDTH
36 1/8" wide
(918mm / 54 units)

DRAWERS

HEIGHT (points)	USEABLE HEIGHT	SIDEWALL HEIGHT	CL 165 lb. capacity	ST 165 lb. capacity	ST 440 lb. capacity	HS 440 lb. capacity
75	2 1/8" (55mm)	2" (50mm)	CL75N	ST75N	ST75F	HS75F
100	3 1/8" (80mm)	3" (77mm)	CL100N	ST100N	ST100F	HS100F
125	4 1/8" (105mm)	3" (77mm)	CL125N	ST125N	ST125F	HS125F
150	5 1/8" (130mm)	5" (127mm)	CL150N	ST150N	ST150F	HS150F
175	6 1/8" (155mm)	5" (127mm)	CL175N	ST175N	ST175F	HS175F
200	7 1/16" (180mm)	7" (177mm)	CL200N	ST200N	ST200F	HS200F
225	8 1/16" (205mm)	7" (177mm)	CL225N	ST225N	ST225F	HS225F
250	9" (230mm)	8 15/16" (227mm)	CL250N	ST250N	ST250F	HS250F
275	10" (255mm)	8 15/16" (227mm)	CL275N	ST275N	ST275F	HS275F
300	11" (280mm)	10 15/16" (277mm)	CL300N	ST300N	ST300F	HS300F
325	12" (305mm)	10 15/16" (277mm)	CL325N	ST325N	ST325F	-
350	13" (330mm)	10 15/16" (277mm)	CL350N	ST350N	ST350F	HS350F

SHELVES AND TRAYS

D = depth; UW = usable width

TYPE	CL 165 lb. capacity	CL 440 lb. capacity	ST 165 lb. capacity	ST 440 lb. capacity	HS 440 lb. capacity
Adjustable shelf 18 1/4" (463mm) D		CL-AS 19 3/4" (502mm) UW		ST-AS 25 13/16" (655mm) UW	HS-AS 37 13/16" (961mm) UW
Bottom shelf 17 3/4" (451mm) D		CL-BS 19 13/16" (503mm) UW		ST-BS 25 7/8" (656mm) UW	HS-BS 37 7/8" (962mm) UW
Roll-out tray 17 1/8" (435mm) D	CL-TCN 18 1/8" (460mm) UW		ST-TCN 24" (610mm) UW	ST-TCF* 24" (610mm) UW	HS-TCF* 36 1/8" (918mm) UW

*depth is 18" (459mm)

5 Select cabinet doors

Flush Hinged Door

Single door protects cabinet contents. Door is provided with integrated handle (reversible in field to allow door to open in opposite direction), individual lock (RG) and 2 keys. **Only bottom and adjustable shelves may be installed behind flush doors – no drawers or roll-out trays.**



Retractable Door

Door slides out and back, stored out of the way when not in use. Door is provided with handles, individual lock (RG) and 2 keys. **Only bottom and adjustable shelves may be installed behind retractable doors – no drawers or roll-out trays.**



Double Hinged Door Cabinets

To order double hinged door cabinets, see the ordering information on page 58.



Sliding and Hinged Door Shelf Cabinets

For ordering information on sliding and hinged door shelf cabinets, see pages 68-69.



FLUSH HINGED DOORS

HEIGHT (points)	HEIGHT	CL*	ST*	HS
300	11 13/16" (300mm)	FD300-27 ■ **	-	-
450	17 11/16" (450mm)	FD450-27 ■ **	FD450-36 ■ **	-
600	23 5/8" (600mm)	FD600-27 ■ ***	FD600-36 ■ ***	-
750	29 9/16" (750mm)	FD750-27 ■	FD750-36 ■	-
900	35 7/16" (900mm)	FD900-27 ■	FD900-36 ■	-

* to order, door opening orientation ("R" for right or "L" for left) must be written in place of the red box (■) in the part number.

** limit: 1 adjustable shelf or 1 bottom shelf

***limit: 2 shelves (adjustable shelf and/or bottom shelf)

RETRACTABLE DOORS

TYPE	HEIGHT (points)	USEABLE HEIGHT	CL	ST	HS
Solid steel door	300	8 5/16"	-	RD300/ST	RD300/HS
Solid steel door	450	14 1/4"	-	RD450/ST	RD450/HS
Solid steel door with plexiglas window	450	14 1/4"	-	RD450/ST-P	RD450/HS-P

6 Select drawer partitions and dividers

Drawer interior sets are located in corresponding Easy-Order footprint section (see chart on page 56). Additional drawer accessories are on pages 119-122.

7 Select colors

Housings and drawer fronts can be different colors but drawer interiors are always gray. Color differences exist between color samples and actual finishes. Please contact your Lista representative for accurate color matching. Custom colors are available and will be quoted on request.



COLOR
CODE

Beige
BE

Bright Blue
BB*

Black
BK*

Classic Blue
CB

Dark Gray
GR

Green
GG

Light Gray
LG*

Red
NR

Sand
SN

White
FW

*Available with ESD properties. To specify ESD paint, add prefix "ESD" to paint part number. For ESD paint specifications, see Lista's Workbench and Workspace Furniture Catalog.

Cabinet Lock Options

Lista offers a number of different keying and locking options to meet the unique needs of almost any application.

Lock Options

Core Lock

Lista's cylinder lock comes standard with all drawer cabinets. It features a removable core that can be easily removed from the cylinder housing using a release tool (must be ordered separately, see below). Each lock is provided with 2 keys.

Replacement Lock Assemblies

Used to replace locks installed before March, 2005.



PART NO.	LOCK TYPE
IC-CYL-RG	individual cylinder lock
IC-CYL-KA	keyed alike cylinder lock
IC-CYL-MA	master cylinder lock
IC-MDR-RG	individual flush door lock
IC-MDR-KA	keyed alike flush door lock
IC-MDR-MA	master flush door lock

Replacement Lock Cores

For field replacement of lock cores. Available for drawer housing and flush door locks shipped after March 2005.



PART NO.	LOCK TYPE
IC-CORE-RG	individual
IC-CORE-KA	keyed alike
IC-CORE-MA	master

Lock Core Release Tool

For extracting interchangeable cylinder core. Works only in conjunction with the original Lista key supplied with the core.



PART NO.	DESCRIPTION
IC-REL-TOOL	lock release tool

Hasp Lock

Rotates 90° clockwise to disengage latch. For use with hinged and double hinged doors (cannot be used with single hinged flush doors or retractable doors). Secured with padlock (not included). Maximum padlock latch diameter is 3/8". For ordering information, please contact your Lista representative.



Hinged Locking Bars

Particularly suitable for mobile applications or wherever additional security is desired. Hinged locking bar mounts to the left or right of any drawer cabinet on the vertical housing support. Indicate side for mounting by writing an "L" for left or "R" for right in place of the red box (■) in the part number. A padlock (not included) secures the bar. Maximum padlock latch diameter is 5/16". To retrofit to existing cabinet, please contact your Lista representative.



PART NO.	FOR CABINET HEIGHT
HLB300-■	300
HLB450-■	450
HLB600-■	600
HLB750-■	750
HLB900-■	900
HLB1050-■	1050
HLB1225-■	1225
HLB1350-■	1350
HLB1525-■	1525



Security Panel

Individual locks for each drawer, with a central lock for the cabinet as a whole. Each drawer has a steel security panel between it and the drawer above, so contents are secure even when individual drawers have been removed. Available only for NW, MP, SC and ST Width cabinets and drawer sizes 125, 175, 225, 275, 325 and 350. For ordering information, please contact your Lista representative.



Keyless Keypad System

Provides controlled, easy keyless access to items stored in Lista cabinets. Access codes can be changed as needed without having to collect and reissue keys. LEDs provide visual confirmation that keypad has been hit. Easily retrofitted to field units. Lock kit comes complete with four AA batteries.

The keypad can be programmed with up to five different user codes at a time, which can be changed as often as needed. The attractive keypad fits snugly against the cabinet housing for a clean profile.

The keypad lock can be ordered for any new Lista drawer storage cabinet and most new mobile drawer cabinets, or can be retrofit to any Lista drawer cabinet or most mobile drawer cabinets sold since 1995. **The keypad lock can not be used with any NW, MP, SC or CL mobile cabinet using front-mounted handles (MTBH or MHAN).**

PART NO.	DESCRIPTION
KPLOCK/HSG	keypad lock for cabinet
KPLOCK/HSG-RF	keypad lock retrofit kit

Drawer/Retaining Options



Individual Drawer Latch (IDL)

Individual drawer latches lock drawers and roll-out trays closed for safety when moving. Particularly applicable for cabinets in vehicles, mobile cabinets, and where seismic activity is a consideration. Finger pull latch is recessed under the drawer handle. Comes standard with all mobile cabinets. IDL can be added at any time.

PART NO.	DESCRIPTION
IDL	for right location
IDL-L	for left location

Lock-In-Lock-Out (LILO)

LILO safety device locks drawer in fully opened or fully closed position. Latch



is mounted on the lower right face of the drawer. Particularly suitable for vehicles, shipboard and other mobile applications. Factory installed. Only available for 440 lb. (200kg) suspension drawers.

PART NO.
LILO



Security Shelf Battens

Batten secures to front of housing to keep boxes and other loose items from falling off shelf. Suitable for mobile vehicles, service vans, military containers and aircraft. Usable behind hinged doors, double hinged doors or flush doors (450 height or higher). Made from galvanized steel, unpainted.

PART NO.	FOR USE WITH
SB-27U	CL, MP cab. or 27U Storage Wall
SB-36U	SC, ST cab. or 36U Storage Wall
SB-54U	HS cab. or 54U Storage Wall
SB-64U	MW cab. or 64U Storage Wall
SB-78U	DW cab. or 78U Storage Wall

Combination Cabinets

These cabinets feature full-width top drawer(s), which can store unusually long items safely and securely. The cabinets (either full or shallow depth) can be configured with a variety of drawer sizes, with the option of shelf or roll-out tray storage for bulky items, and with a variety of bases including a mobile base.



Part numbers are for housings only. Units include individual locking system with PreventTip® locking system. Drawers, shelves, roll-out trays, doors, base and top must be configured separately, and are not included (see pages 39-41 and 59-61 to order).

DW/SC Combination Cabinet Housing

56 1/2" wide x 28 1/2" deep –
DW top drawer(s) usable width 52 3/16" (see page 40 to order),
SC bottom drawers usable width 24" (see page 40 to order)
Housing accepts DW tops and bases (see pages 39 and 67 to order)



	CABINET HOUSING	TOP DRAWER(S)	BOTTOM DRAWER(S)
PART NO.	OVERALL HEIGHT	AVAILABLE HEIGHT	AVAIL. HT./SIDE
DW750-C600/SCSC	750 (33 1/2")	150 points	600 points
DW900-C750/SCSC	900 (39 3/8")	150 points	750 points
DW1050-C900/SCSC	1050 (45 1/4")	150 points	900 points
DW1225-C1050/SCSC	1225 (52 3/16")	175 points	1050 points
DW1350-C1050/SCSC	1350 (57 1/8")	300 points	1050 points

MW/MP Combination Cabinet Housing

47" wide x 28 1/2" deep –
MW top drawer(s) usable width 42 13/16" (see page 40 to order),
MP bottom drawers usable width 18" (see page 40 to order)
Housing accepts MW tops and bases (see pages 39 and 67 to order)



	CABINET HOUSING	TOP DRAWER(S)	BOTTOM DRAWER(S)
PART NO.	OVERALL HEIGHT	AVAILABLE HEIGHT	AVAIL. HT./SIDE
MW750-C600/MPMP	750 (33 1/2")	150 points	600 points
MW900-C750/MPMP	900 (39 3/8")	150 points	750 points
MW1050-C900/MPMP	1050 (45 1/4")	150 points	900 points
MW1225-C900/MPMP	1225 (52 3/16")	175 points	1050 points

HT/ST Combination Cabinet Housing

56 1/2" wide x 22 1/2" deep –
HT top drawer(s) usable width 52 3/16" (see chart below to order),
ST bottom drawers usable width 24" (see page 60 to order)



	CABINET HOUSING	TOP DRAWER(S)	BOTTOM DRAWER(S)
PART NO.	OVERALL HEIGHT	AVAILABLE HEIGHT	AVAIL. HT./SIDE
HT750-C600/STST	750 (33 1/2")	150 points	600 points
HT900-C750/STST	900 (39 3/8")	150 points	750 points
HT1050-C900/STST	1050 (45 1/4")	150 points	900 points
HT1225-C1050/STST	1225 (52 3/16")	175 points	1050 points
HT1350-C1050/STST	1350 (57 1/8")	300 points	1050 points

HT Cabinet Components

PART NO.	DESCRIPTION	USABLE HEIGHT	USABLE WIDTH	USABLE DEPTH
HT150F-C/STST	wide top drawer	5 1/16"	52 3/16"	18"
HT175F-C/STST	wide top drawer	6 1/16"	52 3/16"	18"
HTMDL	mesh drawer liner		52 3/16"	18"

Mobile Cabinets, Work Centers and Toolboxes

When you need storage plus mobility, Lista mobile storage cabinets, work centers and toolboxes provide safe and secure storage and transport for parts and tools. Almost any Lista cabinet can be mounted on a mobile base to allow for maximum flexibility and versatility. Each mobile workstation can be designed to exactly suit your specific needs.

By combining a pair of housings in one mobile work center, your storage options multiply even further.

For specific mobile accessories, see page 66.



Combination Cabinets

For mobile combination cabinets featuring full-width top drawer(s), see page 63.

EASY-ORDER MOBILE CABINET COMBINATIONS

We offer a number of pre-configured Easy-Order mobile cabinets.

NW Width	page 16
MP Width	page 20
SC Width	page 25
MW Width	page 30
DW Width	page 34
CL Width	page 46
ST Width	page 50
HS Width	page 54

Lista mobile cabinets provide a diverse array of storage options:

- Can be combined in side-by-side configurations
- A wide variety of modular components and accessories
- A variety of worksurfaces
- Available with Lista's Nexus Accessory System (see Lista's Workbench and Workspace Furniture Catalog for details)

Each mobile cabinet comes with:

- 4 heavy-duty casters (2 fixed and 2 swivel with wheel locks)
- Handle(s)
- Cylinder lock and 2 keys
- Individual drawer latches (IDL)
- The patented Preventip® safety system (prevents cabinets from tipping by ensuring that when one drawer is open, all others are secured closed)





Mobile cabinets bring tooling to work areas in manufacturing settings.



Mobile cabinets can be easily stored under worksurfaces.



Drawer and door cabinets form a mobile work center that serves as a quality station.



The Nexus Accessory System can be mounted above a mobile cabinet for convenient access to parts.



A mobile workstation with a stainless steel top is ideal for working in clean environments.



Combination cabinets with wide top drawer(s) enable versatile storage of items of highly diverse sizes, especially when configured with a door compartment. To order, see page 63.



Heavy equipment can be stored and easily moved atop a mobile cabinet.



A variety of tops are available to form a convenient worksurface.

Choose from a variety of accessories for your mobile cabinets and work centers.



Black Plastic Handles

Handles mounted on front of cabinet. Cabinets are pre-drilled and handles are mounted in the field. Hardware included.

PART NO.	FOR USE WITH
MHAN	NW, MP and CL cabinets



Tubular Steel Handles

Handles mount on the front of single MP and SC Width mobile cabinets, and on the side of all other cabinet sizes. Cabinets are pre-drilled and handles are mounted in the field. Hardware included.

PART NO.	FOR USE WITH
MTBH	all cabinets except NW



Push Handles

Single tubular steel handle attaches to side of mobile cabinet to push tall, large and/or heavily loaded cabinets. Cabinets are pre-drilled and handles are mounted in the field. Hardware included.

PART NO.	FOR USE WITH
HSG-HNDL/27	CL, ST and HS cabinets, shallow depth workcenters
HSG-HNDL/36	SC, MW and DW cabinets, full depth workcenters



Folding Shelves

Shelf can be mounted on either the left or right side of any mobile or stationary cabinet. 50 lb. maximum capacity. Shelf is 15" wide and is available for full and shallow depth cabinets. Can not be used with cabinets that have front-mounted tubular steel handles (MTBH). Only compatible with front-mounted black plastic handles (MHAN) or side-mounted tubular steel handles (MTBH).

PART NO.	DEPTH	MOUNTS TO
Full depth		
FS-36DX15-L	28 1/2"	left side
FS-36DX15-R	28 1/2"	right side
Shallow depth		
FS-27DX15-L	22 1/2"	left side
FS-27DX15-R	22 1/2"	right side

Hanging Shelf Cabinets

Optional shelf cabinet, painted to match mobile cabinet, is 15" deep x 29" high. It is attached to the side of mobile cabinet for easy maneuvering. Each cabinet has a bottom shelf and 1 adjustable 13 1/2" deep shelf. Individual lock (RG) and 2 keys are furnished. Can only be mounted on 750 height or higher mobile cabinets.



PART NO.	DESCRIPTION
Full depth	
OHC2829-CM	full depth shelf cabinet
OHC1BCT/36	butcher block top for OHC2829
Shallow depth	
OHC2329-CM	shallow depth shelf cabinet
OHC1BCT/27	butcher block top for OHC2329

Individual Casters

Individual replacement casters (not mounted to a mobile base) are available to suit the weight-bearing needs of your application. Capacity shown is per caster.



250 Lb. Capacity

PART NO.	DESCRIPTION
CAST4X1.25	4" x 1 1/4" set (2 fixed, 2 swivel)
CAST4X1.25R	4" x 1 1/4" fixed (1)
CAST4X1.25S	4" x 1 1/4" swivel (1)



350 Lb. Capacity

PART NO.	DESCRIPTION
CAST4X2	4" x 2" set (2 fixed, 2 swivel)
CAST4X2R	4" x 2" fixed (1)
CAST4X2S	4" x 2" swivel (1)



600 Lb. Capacity

PART NO.	DESCRIPTION
CAST6X2	6" x 2" set (2 fixed, 2 swivel)
CAST6X2R	6" x 2" fixed (1)
CAST6X2S	6" x 2" swivel (1)



900 Lb. Capacity

PART NO.	DESCRIPTION
CAST6X2ML	6" x 2" set (2 fixed, 2 swivel)
CAST6X2RML	6" x 2" fixed (1)
CAST6X2SML	6" x 2" swivel (1)

Lista offers a variety of worksurfaces that turn the tops of cabinets into practical work areas. For tops that form a continuous counter top across multiple cabinets, see page 107.



Retainer Tops with Mat

Retainer top, painted to match housing with raised edges on back and sides, provides a practical non-skid work surface. Height is 3/4". Ribbed mat is included.



Butcher Block Cabinet Tops

Tops are satin finish 1 3/4" thick hardwood and are flush to the cabinet side-to-side and front-to-back.



Plastic Laminate Cabinet Tops

Tops are 1 9/16" thick plastic laminate over particle board core and are flush to the cabinet side-to-side and front-to-back. Dove gray is standard but other colors are available on request.



Stainless Steel Cabinet Covers

Cover is constructed of durable, heavy gauge stainless steel. Fits over top and sides of cabinet, and provides easy access to locking system. Adds 1/16" to overall cabinet height and 1/8" to overall width and depth.



Phenolic Resin Cabinet Tops

Top is a high-pressure laminate designed for laboratory worksurfaces and mounts flush to the cabinet side-to-side and front-to-back. Resistant to chemicals, stains or discoloration. Top is 1" thick phenolic resin, available in black.

FULL DEPTH CABINETS

TOP TYPE	# OF CABS. SPANNED	NW	MP	SC	MW	DW
Retainer top with mat	1	NW-RT	MP-RT	SC-RT	MW-RT	DW-RT
Retainer top with mat	2	2NW-RT	2MP-RT	-	-	-
Butcher block	1	NW1BCT	MP1BCT	SC1BCT	MW1BCT	SC2BCT
Butcher block	2	NW2BCT	MP2BCT	SC2BCT	-	SC4BCT
Plastic laminate	1	NW1PCT	MP1PCT	SC1PCT	MW1PCT	SC2PCT
Plastic laminate	2	NW2PCT	MP2PCT	SC2PCT	-	SC4PCT
Stainless steel cover	1	NW1SSC	MP1SSC	SC1SSC	MW1SSC	DW1SSC
Stainless steel cover	2	NW2SSC	MP2SSC	SC2SSC	MW2SSC	-
Phenolic resin	1	NW1RCT	MP1RCT	SC1RCT	MW1RCT	SC2RCT
Phenolic resin	2	NW2RCT	MP2RCT	SC2RCT	-	-

SHALLOW DEPTH CABINETS

TOP TYPE	# OF CABS. SPANNED	CL	ST	HS
Retainer top with mat	1	CL-RT	ST-RT	HS-RT
Butcher block	1	CL1BCT	ST1BCT	HS1BCT
Butcher block	2	CL2BCT	ST2BCT	HS2BCT
Plastic laminate	1	CL1PCT	ST1PCT	HS1PCT
Plastic laminate	2	CL2PCT	ST2PCT	HS2PCT
Stainless steel cover	1	CL1SSC	ST1SSC	HS1SSC
Stainless steel cover	2	CL2SSC	ST2SSC	HS2SSC
Phenolic resin	1	CL1RCT	ST1RCT	HS1RCT
Phenolic resin	2	-	ST2RCT	HS2RCT

Shelf Cabinets

Shelf cabinets are an efficient means for storing bulky items that don't lend themselves to drawer storage. Shelf cabinets are built with the same all-steel construction as all Lista cabinets.

Sliding door shelf cabinets are often stacked on complementary sized drawer cabinets, so smaller drawer contents and bulky items can be stored and locked together. The sliding door lock can be positioned at the door bottom to facilitate stacking.



Lista rides to the rescue at Harley Davidson's Vehicle Maintenance and Repair Department. Lista sliding door shelf cabinets, housing large items such as motor oil, greasing and cleaning agents, sit atop drawer cabinets, which store small parts such as nuts, bolts and o-rings.



At the Production Control Center of San Diego's Naval Air Depot, double hinged door cabinets safely and securely store a wide variety of electronic test equipment and supplies used for the precision modification and repair of tactical air navigation transmission boxes.



Stacked sliding door cabinets at Marine Spill, a marine emergency response company, maximize use of available floor space, while providing inventory control and fast retrieval.



Sliding and Hinged Door Shelf Cabinets

Shelves have a maximum load capacity of 440 lbs. (200kg) evenly distributed and can be moved up or down in 1" increments for the greatest flexibility in arrangement. All units have a stationary bottom shelf and are equipped with the number of adjustable shelves shown in the charts to the right. Optional vertical dividers are also available. All models are shipped fully assembled as described.

Sliding Door Shelf Cabinets

Sliding doors roll smoothly to give access to 50% of cabinet interior at a time.

MW Mid-Width Sliding Door Cabinets

47" wide x 28 1/2" deep

PART NO.	HEIGHT (without base)	# ADJ. SHLV.
MWSD750- ■ ■ □	33 1/2" (850mm)	2
MWSD900- ■ ■ □	39 3/8" (1000mm)	2
MWSD1225- ■ ■ □	52 3/16" (1325mm)	3
MWSD1350- ■ ■ □	57 1/8" (1450mm)	3

DW Double Width Sliding Door Cabinets

56 1/2" wide x 28 1/2" deep

PART NO.	HEIGHT (without base)	# ADJ. SHLV.
DWSD750- ■ ■ □	33 1/2" (850mm)	2
DWSD900- ■ ■ □	39 3/8" (1000mm)	2
DWSD1225- ■ ■ □	52 3/16" (1325mm)	3
DWSD1350- ■ ■ □	57 1/8" (1450mm)	3

HS Width Sliding Door Cabinets

40 1/4" wide x 22 1/2" deep

PART NO.	HEIGHT (without base)	# ADJ. SHLV.
HSSD750- ■ ■ □	33 1/2" (850mm)	2
HSSD900- ■ ■ □	39 3/8" (1000mm)	2
HSSD1225- ■ ■ □	52 3/16" (1325mm)	3
HSSD1350- ■ ■ □	57 1/8" (1450mm)	3



Self-Adhesive Label Holders

Plastic hinged label holder adheres to face of shelf to allow identification of shelf contents. 1 3/16" high. Does not include label paper. For Lista Script, use 18.932 labels.

PART NO.	LENGTH
18.926	4 1/8" (105mm)
18.927	8 1/4" (210mm)
18.929	39 3/8" (1000mm)

Hinged Door Shelf Cabinets

Double hinged doors open to give complete access to cabinet interior.

MW Mid-Width Hinged Door Cabinets

47" wide x 28 1/2" deep

PART NO.	HEIGHT (without base)	# ADJ. SHLV.
MWHD750- ■ ■ □	33 1/2" (850mm)	2
MWHD900- ■ ■ □	39 3/8" (1000mm)	2
MWHD1225- ■ ■ □	52 3/16" (1325mm)	3
MWHD1350- ■ ■ □	57 1/8" (1450mm)	3

DW Double Width Hinged Door Cabinets

56 1/2" wide x 28 1/2" deep

PART NO.	HEIGHT (without base)	# ADJ. SHLV.
DWHD750- ■ ■ □	33 1/2" (850mm)	2
DWHD900- ■ ■ □	39 3/8" (1000mm)	2
DWHD1225- ■ ■ □	52 3/16" (1325mm)	3
DWHD1350- ■ ■ □	57 1/8" (1450mm)	3

HS Width Hinged Door Cabinets

40 1/4" wide x 22 1/2" deep

PART NO.	HEIGHT (without base)	# ADJ. SHLV.
HSHD750- ■ ■ □	33 1/2" (850mm)	2
HSHD900- ■ ■ □	39 3/8" (1000mm)	2
HSHD1225- ■ ■ □	52 3/16" (1325mm)	3
HSHD1350- ■ ■ □	57 1/8" (1450mm)	3

Additional Adjustable Shelves and Shelf Dividers

Made of steel sheet with reinforcing ribs welded on, each shelf has a load capacity of 440 lbs. Support brackets included. Color: gray.

PART NO.	DESCRIPTION	HT.
MW-AS	MW adj. shelf	1" (25mm)
DW-AS	DW adj. shelf	1" (25mm)
VSD100/36	4" shelf divider	4" (102mm)
VSD150/36	6" shelf divider	6" (152mm)
Shallow depth shelf and dividers		
HS-AS	HS adj. shelf	1" (25mm)
VSD100/27	4" shelf divider	4" (102mm)
VSD150/27	6" shelf divider	6" (152mm)

Tops

For top choices, see page 67; for counter tops, see page 107.

How to order an Easy-Order shelf cabinet

1. Select cabinet from charts.

2. ■ Select base type.

NB = none

FT = fork truck

PT = pallet truck

For additional bases for MW and DW width cabinets, see page 39.

For additional bases for HS width cabinets, see page 59.

3. ■ Select lock type.

RG = individual

KA = keyed-alike

MA = master

Lock is required. For additional lock options, see page 62. To have lock installed at bottom of sliding or hinged door, add "/LB" to the end of the part number.

4. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order a DWSD900 cabinet with no base, an individual lock installed at the bottom of the door and Bright Blue paint, the part number would be **DWSD900-NBRGBB/LB** (shown in photo at top left of page).

Lista Storage Wall® Systems



At Panoz Motor Sports, Lista's shallow depth Storage Wall Systems allow maximum storage capacity and full access, together with space-saving narrow aisles.

Lista Storage Wall® Systems

Features	74
Building a Storage Wall System	76
How to Order a Storage Wall System	77
Full Depth System Components	78
Vertical Side Frames	78
End, Universal, Rear Panels	78
Sway Braces	78
Roll-Out Trays	79
Shelves and Accessories	79
Shallow Depth System Components	80
Vertical Side Frames	80
End, Universal, Rear Panels	80
Sway Braces	80
Roll-Out Trays	81
Shelves and Accessories	81
Locking Systems	82
Bookcases, Counter Tops and Ladders	83
Doors	84



Lista Storage Wall® Systems Make Any Workspace Work

For the optimum use of space, Lista Storage Wall Systems have it all:

- Drawers to store small parts and components
- Roll-out trays for easy access to large, heavy items
- Shelves to handle larger items
- Doors for additional security and finished appearance

A cost-effective solution

The combination of these modular components means you can store small and large parts together and have easy access to both.

It also means your Lista Storage Wall System can easily accommodate changes and additions and never be outdated – a cost-effective solution for now and in the future.

Custom designed and arranged for your individual needs, no other single storage system can match it.

Capacity

In addition to full use of available ceiling height, the Lista Storage Wall System gives you maximum weight and cubic volume capacity. The all-steel construction makes it ideal for supporting a mezzanine.

Full and shallow depth

Lista offers two different Storage Wall Systems, as shown in the footprints to the right.

The full depth Storage Wall System is the ideal solution for easily accessible storage of a variety of large and small items.

The shallow depth Storage Wall System excels where aisle and floor space is critical and vertical space can be utilized.

Storage Wall Footprints

Full Depth (page 78)
27 3/4" (705mm) deep



Standard Width Section
28 1/8" (714mm) wide*



Mid-Width Section
46 7/8" (1190mm) wide*



Double Width Section
56 1/4" (1428mm) wide*

Shallow Depth (page 80)
21 3/4" (552mm) deep



ST Width Section
28 1/8" (714mm) wide*



HS Width Section
40 5/32" (1020mm) wide*

**Widths shown are center-to-center of vertical side frame. To calculate your total system width (length), see charts on pages 78 and 80.*



Viti Mercedes uses a Storage Wall® System with roll-out trays to house heavy brake rotors in its parts department. The trays have a 440 lb. capacity; heavy-duty roll-out trays featuring a 770 lb. capacity are also available.



Storage Wall sections featuring different combinations of shelves, drawers and roll-out trays allow the maintenance department at this biotech manufacturer to make the most of every inch of their available space.



The Storage Wall System enables the New York Daily News to store oversized items such as motors, gears and drive shafts on shelves, while keeping smaller items such as drill bits and hand tools in highly organized, adjacent modular drawers. Lockable sliding doors keep contents safe and secure.



The shallow depth Storage Wall System at Jensen Aircraft Leasing is a perfect match for the narrow mezzanine aisle on the second level of this aircraft hangar. Despite the limited space available, the Storage Wall System allows for the full use of the drawers' storage, with plenty of easily accessible storage space on the Storage Wall's shelves for large, bulky items.

Lista Storage Wall® Features

The Lista Storage Wall System is packed wall-to-wall with unequalled features and benefits. This unique System's extraordinary flexibility means you get the exact solution that your storage needs demand.

Feature: Six stackable heights

Storage Wall Systems come in six standard sizes up to 118 1/8" high. They can be arranged as multi-story installations with mezzanines.

Benefit: Maximum use of storage space by using available height

Feature: Track-guided safety ladder

Ladder folds flat when not in use so aisle is never blocked

Benefit: Easy and safe access to upper levels

Feature: Adjustable drawers, shelves and roll-out trays

For your current or changing needs, drawers, shelves and roll-out trays can be combined in any sequence in any section and easily rearranged

Benefit: Total flexibility

Feature: Roll-out trays

Full extension roll-out trays roll smoothly with their full 440 lb. or 770 lb. load capacities

Benefit: Heavy items are easily accessible

Feature: Variety of locking systems

Individual sections can be locked for added, specific security

Benefit: Your security requirements can be totally satisfied

Feature: 100% full extension drawers

Drawers ride smoothly on a unique precision suspension system

Benefit: Full use of all drawer space and easy access to farthest corner

Feature: Six different full sidewall height drawers

Sidewall and partition height are equal to usable drawer height

Benefit: Full use of cubic volume with no wasted space

Feature: Hinged drawer handle covers/label holders

Unique handle cover has hinged plastic cover that easily opens and closes to allow labels to be added and changed, while protecting labels from handling, tears and dirt. Drawers and contents can be labeled with free, downloadable Lista Script software.

Benefit: Faster retrieval and easier inventory control

Feature: Custom compartments

All drawers have partitioning slots on all four sides, and Lista offers a wide variety of partitioning accessories

Benefit: Maximum organization and faster retrieval

SHALLOW DEPTH STORAGE WALL SYSTEM
21 3/4" DEEP



FULL DEPTH STORAGE WALL SYSTEM
27 3/4" DEEP



Building a Storage Wall® System

All Storage Wall Systems come in build-as-you-go units. Each starter section consists of a pair of matched height vertical side frames joined with appropriate width top and bottom universal panels. For lateral stability, rear panels or diagonal sway braces are fastened to the side frames. Rear and end panels can be used to enclose the sec-

tions. To add a section, just order an additional vertical side frame and the appropriate universal panels for the section width you are adding. Sections can be added at any time in the future.


All components for both full and shallow depth Storage Wall Systems can be ordered separately from the charts on the following pages.

Design assistance


Our experienced technical support and design team is pleased to review your needs and assist you in solving any storage problem, free of charge.

Assembly

Lista Storage Wall Systems are shipped knocked down and come with a complete set of easy-to-follow assembly instructions. No special tools or equipment are necessary. Your Lista representative is always available for assistance or for additional technical support.



How to Order a Storage Wall® System



Sample Full Depth Storage Wall Order

QUANTITY	PART NO.	DESCRIPTION
3	VSF2200	vertical side frames
4	UP/36U	universal panels
1	SWLP3636/1	lock panel
1	SWLP3636/2	lock panel
1	SWLK900-RG	lock system
2	SB36U	sway braces (pairs)
2	SC75F	drawers
6	SC100F	drawers
4	SC150F	drawers
1	SC-TCF	roll-out tray
2	AS-P/36U	adjustable shelves
	BB	bright blue paint

Select vertical side frames

Select the vertical side frames. Keep in mind the depth and height of the system you are designing. See page 78 for full depth systems and page 80 for shallow depth systems.

Select universal panels and optional lock system panels

Select panel, which determines the width of the section. See page 82 for locking system choices.

Select rear and end panels

Select rear panel or sway braces and optional end panels. See page 78 for full depth systems and page 80 for shallow depth systems.

Select drawers, shelves and roll-out trays

Select the correct-sized drawers, shelves and roll-out trays for the system you are designing. See page 79 for full depth system components and page 81 for shallow depth system components.

Select system options

Select doors, bookcases and/or ladders from the options shown on pages 83-85.

Select paint colors

Select color(s) from the color chart on the back cover. System frame and panels can be a different color from drawer fronts, but drawer interiors are always gray.

Full Depth Storage Wall® System (27 3/4" deep) – Frames and Panels

Full depth Storage Wall sections (27 3/4" deep) come in three different widths. Panel/section widths correspond to Lista Standard, Mid- and Double Width components.

At any time, additional sections can be added, and drawers, roll-out trays, and shelves can be easily reconfigured to accommodate growth and changing needs.

Ordering

All basic components are ordered separately from the charts on these two pages. Be sure to match the width of the drawers, shelves, etc. to the section width you are building. For step-by-step directions for ordering, see page 77.

Please note that the final digits in the part numbers for universal panels, sway braces and rear panels indicate width in units:

- 36U for Standard Width
- 64U for Mid-Width
- 78U for Double Width

Vertical Side Frames

Heavy duty one-piece vertical uprights with welded horizontal struts. Vertical uprights are slotted at 1" increments for placement of drawers, roll-out trays or shelves. Color: to match unit.



PART NO.	OVERALL HT.	USABLE HT.
VSF1000	39 3/8"	35 7/16" (900mm)
VSF1450	57 1/8"	53 1/8" (1350mm)
VSF2000	78 3/4"	74 3/4" (1900mm)
VSF2200	86 5/8"	80 3/4" (2050mm)
VSF2500	98 7/16"	92 1/2" (2350mm)
VSF3000	118 1/8"	112 1/4" (2850mm)

Length of Storage Wall Systems

To determine actual Storage Wall length, add together the sections you are assembling and add an additional 2". If end panels are used, add 29/32" for each.

SECTION WIDTH	LENGTH BETWEEN SIDE FRAME CTRS.
standard (36 units)	28 1/8" (714mm)
mid-width (64 units)	46 7/8" (1190mm)
double width (78 units)	56 1/4" (1428mm)

End Panels

These optional steel sheet panels enclose the ends of the completed units. Hardware included. Color: to match unit.

PART NO.	HEIGHT
EP1000	39 3/8" (1000mm)
EP1450	57 1/8" (1450mm)
EP2000	78 3/4" (2000mm)
EP2200	86 5/8" (2200mm)
EP2500	98 7/16" (2500mm)
EP3000	118 1/8" (3000mm)



Universal Panels

Steel sheet universal panels measure 2" (50mm) in height and are fastened to the top and bottom of the vertical side frames to complete each section. Sections with vertical side frames 2200 or greater must have a third intermediate universal panel. Fasteners are included. Color: to match unit. For panels that accept the lock system, see page 82.

Universal Panels

PART NO.	WIDTH	LOAD CAP.
UP/36U	26" (661mm)	550 lbs. (250kg)
UP/64U	44 3/4" (1137mm)	550 lbs. (250kg)
UP/78U	54 1/8" (1375mm)	550 lbs. (250kg)

Universal Panels with Mounting Holes

For use with counter tops, tambour doors (top panel only) and double hinged doors (top and bottom panel).

PART NO.	WIDTH	LOAD CAP.
UP/36U-UM	26" (661mm)	550 lbs. (250kg)
UP/64U-UM	44 3/4" (1137mm)	550 lbs. (250kg)
UP/78U-UM	54 1/8" (1375mm)	550 lbs. (250kg)

Rear Panels

Panels are bolted to the vertical side frames to enclose the rear of each section and provide lateral stability. Rear panels must be fitted at least every fourth section. Fasteners included. Color: to match unit. Sway braces can be substituted.

PART NO.	HEIGHT
Standard width 28 1/8" (714mm) – 36 units	
RP1000/36U	39 3/8" (1000mm)
RP1450/36U	57 1/8" (1450mm)
RP2000/36U	78 3/4" (2000mm)
RP2200/36U	86 5/8" (2200mm)
RP2500/36U	98 7/16" (2500mm)
RP3000/36U	118 1/8" (3000mm)
Mid-width 46 7/8" (1190mm) – 64 units	
RP1000/64U	39 3/8" (1000mm)
RP1450/64U	57 1/8" (1450mm)
RP2000/64U	78 3/4" (2000mm)
RP2200/64U	86 5/8" (2200mm)
RP2500/64U	98 7/16" (2500mm)
RP3000/64U	118 1/8" (3000mm)
Double width 56 1/4" (1428mm) – 78 units	
RP1000/78U	39 3/8" (1000mm)
RP1450/78U	57 1/8" (1450mm)
RP2000/78U	78 3/4" (2000mm)
RP2200/78U	86 5/8" (2200mm)
RP2500/78U	98 7/16" (2500mm)
RP3000/78U	118 1/8" (3000mm)

Sway Braces

Used for units without rear panels to provide the necessary lateral stability. Diagonal braces must be fitted at least every fourth section. Color: to match unit. Supplied in pairs with fasteners included.

PART NO.	WIDTH
SB36U	28 1/8" (714mm)
SB64U	46 7/8" (1190mm)
SB78U	56 1/4" (1428mm)

Optional Drawers

To order drawers for full depth Storage Walls sections, please see page 40.

Full Depth Storage Wall® Roll-Out Trays, Shelves and Accessories



Roll-Out Trays

Roll-out trays can be mounted in any sequence or combination with drawers and shelves. Each tray uses the equivalent height of a 100 drawer (100mm high). Trays have full length handles, galvanized insert panels, and 1 3/4" rear and side retaining walls. Be sure to order trays to match the particular section width you are outfitting.

- Usable depth of tray is 24".
- Weight capacity is 440 lbs. for evenly distributed loads.

PART NO.	SECTION	USABLE WIDTH
SC-TCF	36U (standard)	24" (610mm)
MW-TCF	64U (mid-width)	42 13/16" (1088mm)
DW-TCF	78U (double wid.)	52 3/16" (1326mm)



Heavy Duty Roll-Out Tray

Trays have full length handles and galvanized insert panels. Each tray uses the equivalent height of a 225 drawer (225mm high). Available for standard width sections only. Use of individual drawer latch and retainer strip is required (see page 82).

- Usable depth of tray is 24".
- Weight capacity is 770 lbs. for evenly distributed loads.

PART NO.	SECTION	USABLE WIDTH
HDTCF/SC	36U (standard)	23" (584mm)



Adjustable Shelves

Steel shelves can easily be moved at any time and used in any combination or sequence with drawers and roll-out trays. Shelves are 1" (25mm) high. Shelf support clips are included. Color: to match unit. Be sure to order shelves to match the particular section width you are outfitting.

- Usable depth of shelf is 27 1/2".
- Shelves have a 440 lb. maximum load capacity for evenly-distributed loads.

PART NO.	SECTION	USABLE WIDTH
AS-P/36U	36U (standard)	26" (661mm)
AS-P/64U	64U (mid-width)	44 3/4" (1137mm)
AS-P/78U	78U (double wid.)	54 1/8" (1375mm)



Shelf Dividers

Steel sheet dividers fit over lip of shelf. Color: to match shelves.

PART NO.	HEIGHT
SWSD100/36	4" (100mm)
SWSD150/36	6" (150mm)
SWSD200/36	8" (200mm)



Self-Adhesive Label Holders

Plastic hinged label holder adheres to face of shelf to allow identification of shelf contents. 1 3/16" high. Does not include label paper. For Lista Script, use 18.932 labels.

PART NO.	LENGTH
18.926	4 1/8" (105mm)
18.927	8 1/4" (210mm)
18.929	39 3/8" (1000mm)



Shelf End Panels

Steel sheet panel, 26" long, provides side wall for shelves. Color: to match unit. Inserted without additional hardware.

PART NO.	HEIGHT	MIN. SHELF SPACING
X684/3	5 15/16" (150mm)	7 7/8" (200mm)
X684/5	7 7/8" (200mm)	9 7/8" (250mm)
X684/7	9 7/8" (250mm)	11 3/4" (300mm)



Frame Top Fill-In Strip

Steel sheet strip, covers top of vertical side frames to create a smooth continuous surface. Not for use with sliding doors or vertical tambour doors. Color: to match unit.

PART NO.
X699



Intermediate Fill-In Strip

Steel sheet strip fills the space created by vertical side frames between shelves or universal panels to create a smooth continuous shelf surface. Must be used between 2 shelves or 2 universal panels. Color: to match unit. Retainer clip included.

PART NO.
X700

Shallow Depth Storage Wall® System (21 3/4" deep) – Frames, Panels

Shallow depth Storage Wall sections (21 3/4" deep) come in two different widths. Panel/section widths correspond to Lista ST and HS Width components.

At any time, additional sections can be added, and drawers, roll-out trays, and shelves can be easily reconfigured to accommodate growth and changing needs.

Ordering

All basic components are ordered separately from the charts on these two pages. Be sure to match the width of the drawers, etc. to the section width you are building. For step-by-step directions for ordering, see page 77.

Please note that the final digits in the part numbers for universal panels, sway braces and rear panels indicate width in units:

- 36U for ST Width
- 54U for HS Width

Vertical Side Frames

Heavy duty one-piece vertical uprights with welded horizontal struts. Vertical uprights are slotted at 1" increments for placement of drawers, roll-out trays or shelves. Color: to match unit.



PART NO.	OVERALL	
	HEIGHT	USABLE HEIGHT
VSF1000/B255	39 3/8"	35 7/16" (900mm)
VSF1450/B255	57 1/8"	53 1/8" (1350mm)
VSF2000/B255	78 3/4"	74 3/4" (1900mm)
VSF2200/B255	86 5/8"	80 3/4" (2050mm)
VSF2500/B255	98 7/16"	92 1/2" (2350mm)
VSF3000/B255	118 1/8"	112 1/4" (2850mm)

Length of Storage Wall Systems

To determine actual Storage Wall length, add together the sections you are assembling and add an additional 2". If end panels are used, add 29/32" for each.

SECTION WIDTH	LENGTH BETWEEN	
	SIDE FRAME CTRS.	
ST (36 units)	28 1/8" (714mm)	
HS (54 units)	40 5/32" (1020mm)	

End Panels

These optional panels enclose the ends of the completed units. Hardware included. Color: to match unit.

PART NO.	HEIGHT
EP1000/B255	39 3/8" (1000mm)
EP1450/B255	57 1/8" (1450mm)
EP2000/B255	78 3/4" (2000mm)
EP2200/B255	86 5/8" (2200mm)
EP2500/B255	98 7/16" (2500mm)
EP3000/B255	118 1/8" (3000mm)



Universal Panels

Steel sheet universal panels measure 2" (50mm) in height and are fastened to the top and bottom of the vertical side frames to complete each section. Sections with vertical side frames 2200 or greater must have a third intermediate universal panel. Fasteners are included. Color: to match unit. For panels that accept the lock system, see page 82.

Universal Panels

PART NO.	WIDTH	LOAD CAPACITY
UP/3627U	26" (661mm)	550 lbs. (250kg)
UP/54U	38" (967mm)	550 lbs. (250kg)

Universal Panels with Mounting Holes

For use with counter tops, tambour doors (top panel only) and double hinged doors (top and bottom panel).

PART NO.	WIDTH	LOAD CAPACITY
UP/3627U-UM	26" (661mm)	550 lbs. (250kg)
UP/54U-UM	38" (967mm)	550 lbs. (250kg)

Rear Panels

Panels are bolted to the vertical side frames to enclose the rear of each section and provide lateral stability. Rear panels must be fitted at least every fourth section. Fasteners included. Color: to match unit. Sway braces can be substituted.

PART NO.	HEIGHT
ST width 28 1/8" (714mm) – 36 units	
RP1000/36U	39 3/8" (1000mm)
RP1450/36U	57 1/8" (1450mm)
RP2000/36U	78 3/4" (2000mm)
RP2200/36U	86 5/8" (2200mm)
RP2500/36U	98 7/16" (2500mm)
RP3000/36U	118 1/8" (3000mm)
HS width 40 1/8" (1020mm) – 54 units	
RP1000/54U	39 3/8" (1000mm)
RP1450/54U	57 1/8" (1450mm)
RP2000/54U	78 3/4" (2000mm)
RP2200/54U	86 5/8" (2200mm)
RP2500/54U	98 7/16" (2500mm)
RP3000/54U	118 1/8" (3000mm)

Sway Braces

Used for units without rear panels to provide the necessary lateral stability. Diagonal braces must be fitted at least every fourth section. Color: to match unit. Supplied in pairs with fasteners included.

PART NO.	WIDTH
SB36U	28 1/8" (714mm)
SB54U	40 1/8" (1020mm)

Optional Drawers

To order drawers for shallow depth Storage Walls sections, please see page 60.



Roll-Out Trays

Roll-out trays can be mounted in any sequence or combination with drawers and shelves. Each tray uses the equivalent height of a 100 drawer (100mm high). Trays have full length handles, galvanized insert panels, and 1 3/4" rear and side retaining walls. Be sure to order trays to match the particular section width you are outfitting.

- Usable depth of tray is 18".
- Weight capacity is 440 lbs. for evenly distributed loads.

PART NO.	SECTION	USABLE WIDTH
ST-TCF	36U (ST)	24" (610mm)
HS-TCF	54U (HS)	36 1/8" (918mm)



Heavy Duty Roll-Out Tray

Trays have full length handles and galvanized insert panels. Each tray uses the equivalent height of a 225 drawer (225mm high). Available for HS width sections only. Use of individual drawer latch and retainer strip is required (see page 82).

- Usable depth of tray is 18".
- Weight capacity is 770 lbs. for evenly distributed loads.

PART NO.	SECTION	USABLE WIDTH
HDTCTF/HS	54U (HS)	35 1/8" (892mm)



Adjustable Shelves

Steel shelves can easily be moved at any time and used in any combination or sequence with drawers and roll-out trays. Shelves are 1" (25mm) high. Shelf support clips are included. Color: to match unit. Be sure to order shelves to match the particular section width you are outfitting.

- Usable depth of shelf is 21 3/4".
- Weight capacity is 440 lbs. for evenly distributed loads.

PART NO.	SECTION	USABLE WIDTH
AS-P/3627U	36U (ST)	26" (661mm)
AS-P/54U	54U (HS)	38" (967mm)



Shelf Dividers

Steel sheet dividers fit over lip of shelf. Color: to match shelves.

PART NO.	HEIGHT
SWSD100/27	4" (100mm)
SWSD150/27	6" (150mm)
SWSD200/27	8" (200mm)



Self-Adhesive Label Holders

Plastic hinged label holder adheres to face of shelf to allow identification of shelf contents. 1 3/16" high. Does not include label paper. For Lista Script, use 18.932 labels.

PART NO.	LENGTH
18.926	4 1/8" (105mm)
18.927	8 1/4" (210mm)
18.929	39 3/8" (1000mm)



Shelf End Panels

Steel sheet panel provides side wall for shelves. Color: to match unit. Inserted without additional hardware.

PART NO.	HEIGHT	MIN. SHELF SPACING
X612/03	5 15/16" (150mm)	7 7/8" (200mm)
X612/05	7 7/8" (200mm)	9 7/8" (250mm)
X612/07	9 7/8" (250mm)	11 3/4" (300mm)



Frame Top Fill-In Strip

Steel sheet strip, covers top of vertical side frames to create a smooth continuous surface. Not for use with sliding doors or vertical tambour doors. Color: to match unit.

PART NO.
X611



Intermediate Fill-In Strip

Steel sheet strip fills the space created by vertical side frames between shelves or universal panels to create a smooth continuous shelf surface. Must be used between 2 shelves or 2 universal panels. Color: to match unit. Retainer clip included.

PART NO.
X610



Storage Wall® Drawer Locking Systems

For a variety of security needs, Lista offers individual, keyed-alike or master key locking systems for drawer sections. If you wish to lock and secure sections made up of a combination of drawers, roll-out trays and/or shelves, choose from the doors shown on pages 84-85.

How to order a lock system

1. Select the appropriate size and type of panels needed to match the Storage Wall section you are building. See the illustrations to the right to find the panels needed for the configuration you have chosen (partial or full height section).
2. Select the appropriate lock system based on the configuration you have chosen (partial or full height section). See ordering example on page 77.
3. ■ Select lock type.
 - RG = individual
 - KA = keyed-alike
 - MA = master

EXAMPLE: to lock a 2200 height Standard Width (36 unit wide) Storage Wall section containing a 900 height group of drawers below the lock and a 1300 height group of drawers above the lock with an individual lock, you would need to order (1) **SWLP3636/1** panel at the bottom, (1) **SWLP3636/2** panel at the top and (1) **SWLP3636/3** panel at the center, and an **SWLK2200-RG** lock system.

Panels for Lock System

Same basic construction as universal panels but equipped for installation of lock system. Color: to match unit.

Full Depth Storage Wall System

PART NO.	USABLE WID.	LOAD CAP.
Standard width – 36 units		
SWLP3636/1	26" (661mm)	440 lbs. (200kg)
SWLP3636/2	26" (661mm)	440 lbs. (200kg)
SWLP3636/3	26" (661mm)	440 lbs. (200kg)
Mid-width – 64 units		
SWLP6436/1	44 3/4" (1137mm)	440 lbs. (200kg)
SWLP6436/2	44 3/4" (1137mm)	440 lbs. (200kg)
SWLP6436/3	44 3/4" (1137mm)	440 lbs. (200kg)
Double width – 78 units		
SWLP7836/1	54 1/8" (1375mm)	440 lbs. (200kg)
SWLP7836/2	54 1/8" (1375mm)	440 lbs. (200kg)
SWLP7836/3	54 1/8" (1375mm)	440 lbs. (200kg)


Shallow Depth Storage Wall System

PART NO.	USABLE WID.	LOAD CAP.
ST width – 36 units		
SWLP3627/1	26" (661mm)	440 lbs. (200kg)
SWLP3627/2	26" (661mm)	440 lbs. (200kg)
SWLP3627/3	26" (661mm)	440 lbs. (200kg)
HS width – 54 units		
SWLP5427/1	38" (967mm)	440 lbs. (200kg)
SWLP5427/2	38" (967mm)	440 lbs. (200kg)
SWLP5427/3	38" (967mm)	440 lbs. (200kg)



Lock Systems


For locking a partial height section of drawers. Locks all drawers located below the lock.



PART NO.	DRAWER SECTION HEIGHT
SWLK300-■	11 3/4" (300mm)
SWLK600-■	23 9/16" (600mm)
SWLK750-■	29 9/16" (750mm)
SWLK900-■	35 7/16" (900mm)
SWLK1050-■	41 5/16" (1050mm)
SWLK1225-■	48 1/4" (1225mm)
SWLK1350-■	53 3/16" (1350mm)
SWLK1525-■	60" (1525mm)

Lock Systems for Full Height Drawer Section

For Storage Wall section that contains only drawers top-to-bottom. Locks all drawers located above and below the lock. **Lower section must be 900 height.**



PART NO.	STORAGE WALL TOTAL HT.
SWLK2000-■	74 3/4" (1900mm)
SWLK2200-■	80 3/4" (2050mm)
SWLK2500-■	92 1/2" (2350mm)
SWLK3000-■	112 1/4" (2850mm)

Retainer strip



Individual Drawer Latch (IDL)

Individual drawer latches lock drawers and roll-out trays closed. Particularly suitable for mobile applications or where seismic activity is a consideration. Finger pull latches are recessed and mounted on the right side of the drawer handle. Can be added at any time. Requires retainer strip (ordered separately – see below).

PART NO.
IDL

Retainer Strips

Strips bolt to vertical side frame to secure individual drawer latches. **These strips are necessary for IDLs.**

PART NO.	HEIGHT
VP-IDL/1000	39 3/8" (1000mm)
VP-IDL/1450	57 1/8" (1450mm)
VP-IDL/2000	78 3/4" (2000mm)
VP-IDL/2200	86 5/8" (2200mm)
VP-IDL/2500	98 7/16" (2500mm)
VP-IDL/3000	118 1/8" (3000mm)



Lock-In-Lock-Out (LILO)

These safety devices lock drawers in fully opened or fully closed positions. LILO is primarily used in mobile applications or where seismic activity is a consideration. Part number is for individual LILO device only; drawers must be ordered separately. Only available for 440 lb. (200kg) suspension drawers.

PART NO.
LILO

Storage Wall® Bookcases, Counter Tops and Ladders



These offerings make your Storage Wall System even more versatile. The bookcase and counter top are available for both full depth and shallow depth Storage Wall Systems.

Bookcases

Overhead bookcase offers quick access to reference materials and manuals. Bookcase is 12 5/8" deep, with a useable depth of 11 7/8". Color: to match unit.

PART NO.	FOR USE WITH	USE. WIDTH
BC36U	full and shallow depth	25 7/8"
BC54U	shallow depth	37 7/8"
BC64U	full depth	44 1/2"
BC78U*	full and shallow depth	54"

*for (1) 78U or (2) 36U

Butcher Block Counter Tops

Counter style worktop is 1 3/4" thick butcher block hardwood. Mounts on top of universal panel with mounting holes (see pages 78 and 80).

PART NO.	FOR USE WITH
BCT/3627U	shallow depth
BCT/3636U	full depth
BCT/5427U	shallow depth
BCT/6436U	full depth
BCT/7836U	full depth

Track-Guided Folding Safety Ladders

Without sacrificing aisle space, safe, secure and easy access to upper levels is provided by our track-guided folding ladder. Ladder can pivot to right or left so any section is within easy reach. Broad wooden steps, a sturdy handrail, and a hand brake are features engineered for safety. Available in our bright yellow safety color only.

- minimum aisle width to accommodate ladder is 35 1/2"
- not recommended for use with Double Width drawers
- **tracks must be ordered separately (see below)**

PART NO.	MIN. ROOM HEIGHT
LADDER/2000	106 1/4" (2700mm)
LADDER/2200	106 1/4" (2700mm)
LADDER/2500	106 1/4" (2700mm)
LADDER/3000	126" (3200mm)
LADDER/EXT*	

*must be ordered when specifying a Storage Wall ladder in conjunction with sliding doors

Track Tops and Bottoms

Order 1 track length section to match each Storage Wall section (width) you are ordering. Tracks come in pairs, top and bottom. Color: to match unit.

PART NO.	TRACK LENGTH
TRACK/36U	28 1/8" (714mm)
TRACK/54U	40 1/8" (1020mm)
TRACK/64U	46 7/8" (1190mm)
TRACK/78U	56 1/4" (1428mm)



Safety ladder only extends 12 5/8" from Storage Wall when folded flat.



A variety of door options can enhance the safety and security of your stored items, while protecting items on shelves from dust and environmental grime.



How to order Storage Wall doors

1. Select door style.
2. ■ Select lock type.

RG = individual
KA = keyed-alike
MA = master

EXAMPLE: to order sliding doors for a Storage Wall section that has a 2500 height vertical side frame (100 5/8" high) and is 36 units wide with an individual lock, the part number for the starter door would be **SD2500/36U-S-RG**, and the part number for the adder door would be **SD2500/36U-A-RG**.

Hinged Door Sets

Protect inventory and equipment from dirt and theft with full-height hinged doors. Economical and easy to install on single or multiple Storage Wall sections. Door sets add 2" to the depth of the Storage Wall section. Requires top and bottom universal panels with mounting holes. Painted to match the unit. To specify lock, please see instructions to left.

Hinged Door Starters

PART NO.	HEIGHT
Standard and ST width – 36 units	
DHD2000/36SW-S-■	78 3/4" (2000mm)
DHD2200/36SW-S-■	86 5/8" (2200mm)
HS width – 54 units	
DHD2000/54SW-S-■	78 3/4" (2000mm)
DHD2200/54SW-S-■	86 5/8" (2200mm)
Mid-width – 64 units	
DHD2000/64SW-S-■	78 3/4" (2000mm)
DHD2200/64SW-S-■	86 5/8" (2200mm)
Double width – 78 units	
DHD2000/78SW-S-■	78 3/4" (2000mm)
DHD2200/78SW-S-■	86 5/8" (2200mm)

Hinged Door Adders

PART NO.	HEIGHT
Standard and ST width – 36 units	
DHD2000/36SW-A-■	78 3/4" (2000mm)
DHD2200/36SW-A-■	86 5/8" (2200mm)
HS width – 54 units	
DHD2000/54SW-A-■	78 3/4" (2000mm)
DHD2200/54SW-A-■	86 5/8" (2200mm)
Mid-width – 64 units	
DHD2000/64SW-A-■	78 3/4" (2000mm)
DHD2200/64SW-A-■	86 5/8" (2200mm)
Double width – 78 units	
DHD2000/78SW-A-■	78 3/4" (2000mm)
DHD2200/78SW-A-■	86 5/8" (2200mm)

Sliding Door Sets

Doors move smoothly on ball bearings. Doors and track add an additional 5" to the depth and 1/4" to the height of the section. Painted to match the unit. To specify lock, please see instructions to left. Doors come as pairs, to cover even number of same-sized sections. To order doors for odd numbers of sections, contact your Lista representative.

Sliding Door Starters

PART NO.	HEIGHT
Standard and ST width – 36 units	
SD2000/36U-S-■	80 15/16" (2055mm)
SD2200/36U-S-■	88 13/16" (2255mm)
SD2500/36U-S-■	100 5/8" (2555mm)
SD3000/36U-S-■	120 5/16" (3055mm)
HS width – 54 units	
SD2000/54U-S-■	80 15/16" (2055mm)
SD2200/54U-S-■	88 13/16" (2255mm)
SD2500/54U-S-■	100 5/8" (2555mm)
SD3000/54U-S-■	120 5/16" (3055mm)
Mid-width – 64 units	
SD2000/64U-S-■	80 15/16" (2055mm)
SD2200/64U-S-■	88 13/16" (2255mm)
SD2500/64U-S-■	100 5/8" (2555mm)
SD3000/64U-S-■	120 5/16" (3055mm)
Double width – 78 units	
SD2000/78U-S-■	80 15/16" (2055mm)
SD2200/78U-S-■	88 13/16" (2255mm)
SD2500/78U-S-■	100 5/8" (2555mm)
SD3000/78U-S-■	120 5/16" (3055mm)

Sliding Door Adders

PART NO.	HEIGHT
Standard and ST width – 36 units	
SD2000/36U-A-■	80 15/16" (2055mm)
SD2200/36U-A-■	88 13/16" (2255mm)
SD2500/36U-A-■	100 5/8" (2555mm)
SD3000/36U-A-■	120 5/16" (3055mm)
HS width – 54 units	
SD2000/54U-A-■	80 15/16" (2055mm)
SD2200/54U-A-■	88 13/16" (2255mm)
SD2500/54U-A-■	100 5/8" (2555mm)
SD3000/54U-A-■	120 5/16" (3055mm)
Mid-width – 64 units	
SD2000/64U-A-■	80 15/16" (2055mm)
SD2200/64U-A-■	88 13/16" (2255mm)
SD2500/64U-A-■	100 5/8" (2555mm)
SD3000/64U-A-■	120 5/16" (3055mm)
Double width – 78 units	
SD2000/78U-A-■	80 15/16" (2055mm)
SD2200/78U-A-■	88 13/16" (2255mm)
SD2500/78U-A-■	100 5/8" (2555mm)
SD3000/78U-A-■	120 5/16" (3055mm)



Full height end panel



Vertical Tambour Doors

Individual Storage Wall sections can be locked with vertical tambour door. Vertical door rides effortlessly on tracks mounted to the vertical side frames and retracts into a box mounted on the top of the section. The box adds 12 3/4" to the height of the unit. The additional framing for the slides and lock add 2 3/8" to the depth of the unit. Requires universal panel with mounting holes at top. Box and frame are painted to match the unit but door comes in dove gray only. To specify lock, please see instructions on page 84.

PART NO.	TOTAL HEIGHT
Standard and ST width – 36 units	
VD1450/36U-■	69 7/8" (1773mm)
VD2000/36U-■	91 1/2" (2323mm)
VD2200/36U-■	99 3/8" (2523mm)
VD2500/36U-■	111 1/8" (2823mm)
HS width – 54 units	
VD1450/54U-■	69 7/8" (1773mm)
VD2000/54U-■	91 1/2" (2323mm)
VD2200/54U-■	99 3/8" (2523mm)
VD2500/54U-■	111 1/8" (2823mm)
Mid-width – 64 units	
VD1450/64U-■	69 7/8" (1773mm)
VD2000/64U-■	91 1/2" (2323mm)
VD2200/64U-■	99 3/8" (2523mm)
VD2500/64U-■	111 1/8" (2823mm)
Double width – 78 units	
VD1450/78U-■	69 7/8" (1773mm)
VD2000/78U-■	91 1/2" (2323mm)
VD2200/78U-■	99 3/8" (2523mm)
VD2500/78U-■	111 1/8" (2823mm)

Tambour Door Full Height End Panels

Optional end panels extend up to the top of the tambour door box to enclose the ends of the completed unit for a finished appearance. Painted to match the unit.

PART NO.	HEIGHT	DEPTH
EP1450/VD	69 7/8"	full
EP2000/VD	91 1/2"	full
EP2200/VD	99 3/8"	full
EP2500/VD	111 1/8"	full
EP1450/VD/B255	69 7/8"	shallow
EP2000/VD/B255	91 1/2"	shallow
EP2200/VD/B255	99 3/8"	shallow
EP2500/VD/B255	111 1/8"	shallow



Full Height Inner Panels

Provides a clean, neat appearance, as well as added security for Storage Wall section enclosed with a door. Steel sheet panel fills entire inner area of a vertical side frame. Installs easily. Order to match height of vertical side frames. Painted to match the unit.

PART NO.	FOR USE WITH
Full depth – 36 units	
IP1450/36U-■	1450VSF
IP2000/36U-■	2000VSF
IP2200/36U-■	2200VSF
IP2500/36U-■	2500VSF
IP3000/36U-■	3000VSF
Shallow depth – 27 units	
IP1450/27U-■	1450VSF/B255
IP2000/27U-■	2000VSF/B255
IP2200/27U-■	2200VSF/B255
IP2500/27U-■	2500VSF/B255
IP3000/27U-■	3000VSF/B255



Lista Tool Storage



Lista stacked cabinets safely and efficiently house a broad array of machine and CNC tools in the tool crib at C&D Aerospace, an aircraft interior manufacturer.

Lista Tool Storage

Tool Storage, Transport and Use Cycle 88

Tool Holders 90

Tool Trays and Tool Holder Frames for Drawers 91

Tool Transporters 92

Tool Holder Frames for Tool Transporters 92

Tool Transporter Accessories 93

Shelves 93

Document Pocket 93

B220 Easy-Order Tool Transporters 94

B240 Easy-Order Tool Transporters 95

CNC and Machine Tool Cabinet Easy-Order Combinations 96-97

CNC Bench Stand 97

CNC Workbench Easy-Order Combinations 97

Machine Tool Cabinet Easy-Order Combinations 98-99

Tool Crib Cabinet Easy-Order Combinations 100-101




From the smallest shop to the largest machining operation, Lista can economically provide everything you need for safe and efficient storage of valuable tools.



CNC and machine tool storage, transport and use cycle

With our many different CNC tool storage products and accessories, Lista provides an efficient, organized and secure link among all the various stages of tool storage, transport and use.



Lista Tool Storage and Transport Systems Make Any Workspace Work

Sliding door machine tool cabinets with butcher block tops provide both complete protection for tooling and a highly functional worksurface at Galileo Electro Optic Corporation's machine shop (left) and F&S Tool (right).



Lista CNC tool transporters are used to safely deliver tools directly to the work area at Continental Machines, a leading machine tool and hydraulic component manufacturing company.



The Lista Storage Wall® System is used to store a variety of different-sized CNC tooling at Tremec, a manufacturer of manual transmissions. This vertical solution maximizes Tremec's floorspace while providing the company with safe, secure and completely organized CNC storage. For more information on the Lista Storage Wall System, see pages 72-85.

Safety and ease of use for storage and transport are the priorities in the design of the Lista system. Our tool holders are the basic components of an integrated solution to vertical storage of pre-set tools. Lista tool holders are ideal for all types of pre-set tool handling. Even if only small numbers of tools are involved, safe and accessible storage adjacent to machines is economical.



Molded Tool Holders

Tool holders are made from ABS high impact and oil resistant plastic that protects the heaviest tool shanks. Tool holders are designed to be held securely in place on either Lista tool trays or tool holder frames.

PART NO.	DESCRIPTION	MAX. QTY./ROW	
		36U	54U
12.880	30 taper	8	12
12.879	35 taper	8	12
12.062	40 taper	8	12
12.877	45 taper	5	9
12.875	50 taper	5	8
12.890	TR28	6	9
12.888	TR36	6	9
12.883	1 3/4" straight	6	9
12.882	2" straight	6	9
12.881	2 1/4" straight	5	8
15.314	HSK32	9	14
15.318	HSK40	9	14
15.319	HSK50	8	12
15.320	HSK63	6	9
15.330	HSK80	5	9
15.336	HSK100	4	7



Custom Tool Holders

Lista will modify blank inserts for any type, size or brand of tool holder (ABS, Capto, etc.). Each custom tool holder holds one tool. Provide your Lista representative with drawings and dimensions of the specific tools, and we will modify the blanks to your precise specifications.

PART NO.	TOOL SHANK	MAX. QTY./ROW	
		36U	54U
STH32KM	KM32	10	16
STH40KM	KM40	9	1
STH50KM	KM50	7	12
STH63KM	KM63	6	10
STH25HSK	HSK25	11	17
STH25ABS	ABS25	16	25
STH32ABS	ABS32	12	19
STH40ABS	ABS40	9	14
STH50ABS	ABS50	9	14
STH63ABS	ABS63	7	11
STH80ABS	ABS80	6	9
STH100ABS	ABS100	5	8
STH125ABS	ABS125	4	6



Tool Inserts

The tool blank fits a TT-1 tool tray, TF2736 tool frame or TF3636 tool frame. By boring or drilling (up to a maximum of 4" diameter), you can create custom tool holders to your precise specifications. The insert is made of 3/4" thick UHMW (ultra high molecular weight) polyethylene.

Tool Blank

PART NO.	LENGTH
TTB	21 1/16" (535mm)

21" Long Premachined Tool Inserts

PART NO.	TOOL SHANK	NO. OF POSITIONS
TTB-KM40/8	KM40	8
TTB-KM40/12	KM40	12
TTB-KM40/15	KM40	15
TTB-KM50/6	KM50	6
TTB-KM50/8	KM50	8
TTB-KM63/5	KM63	5
TTB-KM63/6	KM63	6
TTB-HSK32/15	HSK32	15
TTB-HSK40/8	HSK40	8
TTB-HSK50/6	HSK50	6
TTB-HSK63/6	HSK63	6
TTB-HSK63/7	HSK63	7
TTB-HSK80/5	HSK80	5
TTB-HSK100/4	HSK100	4
TTB-HSK110/6	HSK110	6
TTB-HSK125/3	HSK125	3
TTB-HSK125/4	HSK125	4
TTB-HSK160/3	HSK160	3
TTB-ABS32/10	ABS32	10
TTB-ABS50/8	ABS50	8
TTB-ABS63/8	ABS63	8



Tool Trays and Tool Holder Frames for Drawers



Tool Trays

Lista tool trays allow tools to be easily moved from drawer to transporter and back. They are designed to fit securely into drawers, tool transporters or in Bench Stands without the use of bolts. Made of heavy gauge welded steel, they are designed with a universal grid system that guarantees precise positioning of the tool holders. Handles fold down when not in use. Recommended for 150 height or higher drawers. Not compatible with TT-1 tool trays and TTBR brackets sold before May, 2003.

PART NO.	TRAYS PER DRAWER
TT-1	4 per SC side-to-side
	3 per ST side-to-side
	3 per MP front-to-back



Tool Tray Drawer Brackets, Pairs

These supports are bolted into the perforated bottom of the Lista drawer. Mounted in pairs, they hold the TT-1 tool tray firmly in place. Made of heavy gauge steel. Not compatible with TT-1 tool trays sold before May, 2003.

PART NO.	HEIGHT
TTBR-D	6"



Tool Holder Frames


Tool holder frames are mounted in drawers. They are bolted to pairs of brackets (see below), which in turn are bolted to the perforated drawer bottom. Recommended for 150 height or higher drawers. Color: gray.

PART NO.	USE	ROW WID.
TF3636	SC drawers	36U
TF2736	MP and ST drawers	36U
TF5427	HS drawers	54U

Frame Drawer Brackets, Pairs

Pairs of brackets are bolted to the perforated bottom of a Lista drawer and to the sides of the frame. Height indicated is from the top of the frame to the drawer bottom.

PART NO.	USE	HEIGHTS
X4065	TF3636	2 5/8" or 3 1/2"
X4066	TF3636	4 3/8" or 5 3/4"
X4065-27	TF2736 or TF5427	2 5/8" or 3 1/2"
X4066-27	TF2736 or TF5427	4 3/8" or 5 3/4"



SC drawer with TT-1 tool trays and various-sized molded tool holders.




SC drawer with TF3636 tool holder frame and molded tool holders.

Tool Transporters

Lista B220 and B240 transporter units serve as the mobile link between all other Lista tool storage system components.


All transporters have the following features:

- Rigid steel frame and tubular steel handle
- Steel sheet side panels slotted at 1" intervals for positioning trays, frames, shelves and other accessories
- 2 fixed and 2 swivel heavy duty 6" x 2" casters with wheel locks, for optimum traction and maneuverability even on irregular surfaces
- 600 lb. capacity per wheel (2400 lb. total)
- Can be safely and easily transported large distances with a fork truck



Transporter Unit B220

This is the smaller of the 2 Lista transporter units. It can be fitted with 3 tool trays in a row, or a frame. Fully equipped Easy-Order transporters are shown on page 94.



Transporter Unit B240

The larger of the transporter units has a greater capacity and can be fitted with 4 tool trays in a row or a frame. The B240 has an additional front rack for tool trays, adjustable shelves or horizontal supports for long tools. Fully equipped Easy-Order transporters are shown on page 95.



Tool Tray Mounting Brackets, Pairs

Two types of brackets are available: 1 for horizontal, the other for angled mounting of the TT-1 tool tray on transporters or in Bench Stands. Made of heavy gauge steel with locking pins included. **Color: to match transporter.** Not compatible with TT-1 tool trays sold before May, 2003.

PART NO.	USE
TTBR-T	straight
TTBR-TA	20° angle



Tool Holder Frame/Brackets

Brackets bolt securely on the perforated sides of the transporter unit in horizontal positions. Tool holder frames fit into vertical slots on the brackets (both required). Color: to match transporter.

Frame

PART NO.	USE
TF2736	B220 transporter
TF3636	B240 transporter

Transporter Bracket (pairs)

PART NO.	USE
TFBR27	B220 transporter
TFBR36	B240 transporter




Tool Transporter Accessories



Adjustable Shelf

The adjustable shelf can be mounted on either the B220 or B240 transporter unit. Suitable for measuring and other small tools, each includes a ribbed mat and 4 shelf clips. Color: to match transporter.

PART NO.	SIZE
NAS23	11 3/4" x 23 1/2"



B220 Stationary Shelf

Attached to the front end of the B220 transporter, this shelf, with its 1" (25mm) lip, is perfect for holding measuring and other small tools. Ribbed mat and fasteners included. Color: to match transporter.

PART NO.	SIZE
NSS22	12" x 19 3/8"



B240 Suspended Inserts

These suspended tool storage inserts can be fitted into the B240 transporter unit. Fasteners included. Color: gray.

PART NO.	USE	MAX. QTY. TOOLS
SI-50	50 taper	5
SI-40	40 taper	9



Document Pocket

A compact storage box for technical drawings, documents, etc. that can be fitted to the front or back of either the B220 or B240 transporter unit. Color: gray.

PART NO.	SIZE
DP-1	14 1/8" W x 1 3/4" D x 7" H

Lista's broad selection of accessories can convert your basic transporter into a customized tool trolley.



For sheer strength, easy maneuverability and adaptability, Lista's tool transporters set the standard. Lista tool holders and trays are safely and easily transferred from drawers to transporter.

Lista offers a total of six fully equipped standard combinations of transporter units: three B220 series and three B240 series.

For additional parts and accessories, see pages 92-93.

Ordering

Please specify the part number for the tool holder size you require. Choose paint color from the color chart on the back cover.

B220 Tool Transporters



B220-A Transporters

Comes with 1 stationary shelf with ribbed mat, 1 adjustable shelf with ribbed mat and shelf support clips, and 3 tool holder trays with 3 pairs of mounting brackets.

PART NO.	TOOL HOLDER	QTY.
B220-A-30	12.880	24
B220-A-35	12.879	24
B220-A-40	12.062	21
B220-A-45	12.877	15
B220-A-50	12.875	15
B220-A-04	12.888	18
B220-A-05	12.890	18
B220-A-HSK50	15.319	24
B220-A-HSK63	15.320	18
B220-A-HSK80	15.330	15
B220-A-HSK100	15.336	12



B220-B Transporters

Comes with 1 stationary shelf with ribbed mat, and 4 tool holder trays with 4 pairs of mounting brackets.

PART NO.	TOOL HOLDER	QTY.
B220-B-30	12.880	32
B220-B-35	12.879	32
B220-B-40	12.062	28
B220-B-45	12.877	20
B220-B-50	12.875	20
B220-B-04	12.888	24
B220-B-05	12.890	24
B220-B-HSK50	15.319	32
B220-B-HSK63	15.320	24
B220-B-HSK80	15.330	20
B220-B-HSK100	15.336	16



B220-C Transporters

Comes with 1 stationary shelf with ribbed mat, and 5 tool holder trays with 5 pairs of mounting brackets.

PART NO.	TOOL HOLDER	QTY.
B220-C-30	12.880	40
B220-C-35	12.879	40
B220-C-40	12.062	35
B220-C-45	12.877	25
B220-C-50	12.875	25
B220-C-04	12.888	30
B220-C-05	12.890	30
B220-C-HSK50	15.319	40
B220-C-HSK63	15.320	30
B220-C-HSK80	15.330	25
B220-C-HSK100	15.336	20



B240 Tool Transporters



B240-A Transporters

Comes with 2 adjustable shelves with ribbed mats and shelf support clips, 2 tool holder trays with 2 pairs of angled mounting brackets and 1 tool frame with 1 pair of transporter frame brackets.

PART NO.	TOOL HOLDER	QTY.
B240-A-30	12.880	48
B240-A-35	12.879	48
B240-A-40	12.062	42
B240-A-45	12.877	30
B240-A-50	12.875	30
B240-A-04	12.888	36
B240-A-05	12.890	36
B240-A-HSK50	15.319	48
B240-A-HSK63	15.320	36
B240-A-HSK80	15.330	30
B240-A-HSK100	15.336	24



B240-B Transporters

Comes with 1 adjustable shelf with ribbed mat and shelf support clips, 5 tool holder trays with 5 pairs of angled mounting brackets and 1 tool frame with 1 pair of transporter frame brackets.

PART NO.	TOOL HOLDER	QTY.
B240-B-30	12.880	72
B240-B-35	12.879	72
B240-B-40	12.062	63
B240-B-45	12.877	45
B240-B-50	12.875	45
B240-B-04	12.888	54
B240-B-05	12.890	54
B240-B-HSK50	15.319	72
B240-B-HSK63	15.320	54
B240-B-HSK80	15.330	45
B240-B-HSK100	15.336	36



B240-C Transporters

Comes with 2 tool holder trays, 2 pairs of angled mounting brackets, and 2 tool frames with 2 pairs of transporter frame brackets.

PART NO.	TOOL HOLDER	QTY.
B240-C-30	12.880	80
B240-C-35	12.879	80
B240-C-40	12.062	70
B240-C-45	12.877	50
B240-C-50	12.875	50
B240-C-04	12.888	60
B240-C-05	12.890	60
B240-C-HSK50	15.319	80
B240-C-HSK63	15.320	60
B240-C-HSK80	15.330	50
B240-C-HSK100	15.336	40



Lista's CNC and machine tool storage cabinets can be arranged and equipped to meet your specific needs. Flexible combinations of drawers and roll-out trays are closed behind lockable hinged or sliding doors which protect tools from the working environment. The addition of a butcher block top or retainer top with ribbed mat provides a highly functional worksurface. (To order a top for these cabinets, contact your Lista representative.)

Ordering

To order a custom CNC or machine tool cabinet, please contact your Lista representative.

The CNC and machine tool storage cabinets shown here come fully equipped with tool holder frames and tool holders for a variety of standard sizes of CNC tools.

Drawers are accessorized with partitions and dividers to hold measuring and cutting tools, collets, vises and other accessories. As in all Lista cabinets, their modular design means drawers and roll-out trays can be easily reconfigured for changing needs.

All drawers and roll-out trays are 100% full extension with a 440 lb. load capacity.

How to order an Easy-Order tool cabinet

Please note that the final digits in the ordering charts refer to the specific tool sizes (for example, MTC9150NC/40 stores 40 taper tools).

1. Select Easy-Order Cabinet Combination.

2. ■ Select base type.

NB = none
FT = fork truck

3. ■ Select lock type.

RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

4. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order an MTC900NC/30 cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **MTC900NC/30-FTRGBB**.



MTC9150 Machine Tool Cabinets

28 1/4" wide x 29 1/2" deep x 39 3/8" high

Lower hinged door compartment contains 3 drawers and a single roll-out tray for larger items. One drawer is fitted with a frame and tool holders. Separate 2-drawer upper level is partitioned for small tools. Upper and lower sections lock separately. Cabinet comes fully assembled with a retainer top with 3/4" raised edges on back and sides and a ribbed mat.

PART NO.	TOOL HOLD.	QTY.
Easy-Order combinations		
MTC9150NC/30-■□	12.880	32
MTC9150NC/35-■□	12.879	32
MTC9150NC/40-■□	12.062	28
Housing only		HEIGHT
MTC9150-■□	39 3/8"	



MTC900 Machine Tool Cabinets

28 1/4" wide x 29 1/2" deep x 39 3/8" high

This hinged door cabinet contains 5 drawers and a single roll-out tray. Lower drawer is fitted with a frame and tool holders, and upper drawers are partitioned for small tools and accessories. Cabinet comes fully assembled with a retainer top with 3/4" raised edges on back and sides and a ribbed mat.

PART NO.	TOOL HOLD.	QTY.
Easy-Order combinations		
MTC900NC/30-■□	12.880	32
MTC900NC/35-■□	12.879	32
MTC900NC/40-■□	12.062	32
MTC900NC/50-■□	12.875	20
Housing only		HEIGHT
SCDHD900-■□	39 3/8"	



1350NC Machine Tool Cabinets

28 1/4" wide x 29 1/2" deep x 59 1/2" high

This hinged door cabinet contains 4 drawers fully outfitted with frames and tool holders. **Includes fork truck base.**

PART NO.	TOOL HOLD.	QTY.
Easy-Order combinations		
1350NC/40-■□	12.062	112
1350NC/45-■□	12.877	80
1350NC/50-■□	12.875	80
1350NC/HSK50-■□	15.319	128
1350NC/HSK63-■□	15.320	96
1350NC/HSK80-■□	15.330	80
Housing only		HEIGHT
SCDHD1350-FT ■□	57 1/8"	

1525NC Machine Tool Cabinets

28 1/4" wide x 29 1/2" deep x 66 3/8" high

This hinged door cabinet contains 5 drawers fully outfitted with frames and tool holders. **Includes fork truck base.**

PART NO.	TOOL HOLD.	QTY.
Easy-Order combinations		
1525NC/40-■□	12.062	140
1525NC/45-■□	12.877	100
1525NC/50-■□	12.875	100
1525NC/HSK50-■□	15.319	160
1525NC/HSK63-■□	15.320	120
1525NC/HSK80-■□	15.330	100
Housing only		HEIGHT
SCDHD1525-FT ■□	64"	



SIDE A

SIDE B


MTC900-5

56 1/2" wide x 30 3/4" deep x 39 3/8" high

This is a Double Width sliding door cabinet. Side A contains 6 drawers with partitioning for tool holder accessories, and a roll-out tray for large items. Side B has 2 drawers outfitted with frames and tool holders. Retainer top with 3/4" raised edges on back and sides and a ribbed mat is included.

PART NO.	TOOL HOLD.	QTY.
Easy-Order combinations		
MTC9005NC/30- ■ ■ □	12.880	64
MTC9005NC/40- ■ ■ □	12.062	56
MTC9005NC/45- ■ ■ □	12.877	40
MTC9005NC/50- ■ ■ □	12.875	40
MTC9005NC/HSK50- ■ ■ □	15.319	64
MTC9005NC/HSK63- ■ ■ □	15.320	48
MTC9005NC/HSK80- ■ ■ □	15.330	40
Housing only		
MTC900-5 ■ ■ □ *	39 3/8"	
MTC750-5 ■ ■ □ *	33 1/2"	

*does not include retainer top or ribbed mat



CNC Bench Stand

Bench Stands are made of heavy gauge steel for maximum strength and stability, and trays can be inserted or removed without the use of bolts. Not compatible with TT-1 tool trays sold before May, 2003.

Bench Stand Combinations

23 5/8" wide x 19 13/16" deep x 12 7/16" high

Equipped as shown with 3 tool holder trays and tool holders. Specify the part number for the tool holder size you require. Specify paint color in place of the box (□) at the end of the part number (see color chart on back cover).

PART NO.	TOOL HOLD.	QTY.
Easy-Order combinations		
TS224-30- □	12.880	24
TS224-35- □	12.879	24
TS224-40- □	12.062	21
TS224-45- □	12.877	15
TS224-50- □	12.875	15
TS224-04- □	12.888	18
TS224-05- □	12.890	18
TS224-HSK50- □	15.319	24
TS224-HSK63- □	15.320	18
TS224-HSK80- □	15.330	15

Frame only

TS224

Rugged, durable Lista workbenches are ideal for setting and assembling CNC tools as well as for storing accessories adjacent to any machine. The models shown below are fully outfitted with drawer partitioning.

All cabinet housings and leg assemblies are constructed of welded heavy gauge steel. All drawers are 100% full extension with a 440 lb. load capacity.

Bench tops are 1 3/4" (45mm) thick butcher block.



MC750-A

60" wide x 30" deep x 35 1/4" high

This pre-set bench has 5 drawers, fully outfitted with drawer partitioning for storage of hand tools, collets, hardware and set-up equipment. The bottom drawer is outfitted with a frame and tool holders. Specify the part number for the tool holder size you require.

PART NO.	TOOL HOLD.	QTY.
MC750-A-30- ■ □	12.880	32
MC750-A-35- ■ □	12.879	32
MC750-A-40- ■ □	12.062	28
MC750-A-45- ■ □	12.877	20
MC750-A-50- ■ □	12.875	20
MC750-A-04- ■ □	12.888	24
MC750-A-05- ■ □	12.890	24
MC750-A-HSK50- ■ □	15.319	32
MC750-A-HSK63- ■ □	15.320	24
MC750-A-HSK80- ■ □	15.330	20

How to order an Easy-Order CNC workbench

Please note that the final digits in the ordering charts refer to the specific tool sizes (for example, MC750-A-40 stores 40 taper tools).

1. Select Easy-Order workbench.

2. ■ Select lock type.

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

3. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order an MC750-B-30 workbench with an individual lock and Bright Blue paint, the part number would be **MC750-B-30-RGBB**.



MC750-B

60" wide x 30" deep x 35 1/4" high

This pre-set bench has 3 drawers – 1 drawer outfitted with drawer partitioning for small tools, and 2 deep drawers outfitted with frames and tool holders. Specify the part number for the tool holder size you require.

PART NO.	TOOL HOLD.	QTY.
MC750-B-30- ■ □	12.880	64
MC750-B-35- ■ □	12.879	64
MC750-B-40- ■ □	12.062	56
MC750-B-45- ■ □	12.877	40
MC750-B-50- ■ □	12.875	40
MC750-B-04- ■ □	12.888	48
MC750-B-05- ■ □	12.890	48
MC750-B-HSK50- ■ □	15.319	64
MC750-B-HSK63- ■ □	15.320	48
MC750-B-HSK80- ■ □	15.330	40

Easy-Order Machine Tool Cabinet Combinations

The combinations shown on these two pages have proven themselves in hundreds of installations to be the most versatile and useful for a broad variety of machine tool needs.

Like all Lista systems, their modular design means the greatest flexibility for your present and future needs. All standard combinations have ¾" retainer tops with raised edges on back and sides and a ribbed mat for a practical non-skid worksurface.

All drawers and roll-out trays are full 100% extension and have a 440 lb. load capacity.

Ordering

To order a custom machine tool cabinet, please contact your Lista representative.

How to read the charts on pages 98 and 99

The 2 columns to the right of each cabinet photo indicate:

- Drawer heights/tray information
- Drawer interior sets

For SC drawer capacities and sizes, see page 40.

The chart below the photo indicates:

- Part numbers
- Number of drawers
- Number of drawer compartments created by the interior sets (shown on pages 26-27)

How to order an Easy-Order Machine Tool Cabinet

1. Select Easy-Order Cabinet Combination either without or with drawer interior sets (designated by an "A" at the end of the part number – i.e., MTC-900-2A).

2. ■ Select base type.

NB = none
FT = fork truck
PT = pallet truck

3. ■ Select lock type.

RG = individual
KA = keyed-alike
MA = master

4. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order an MTC-900-3A cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **MTC-900-3A-FTRGBB**.

Model 900 CNC Cabinets

28 ¼" wide x 29 ½" deep x 39 ¾" high

Outfitted as described. Drawers and roll-out trays are adjustable in 1" increments.



INCLUDES INT.
2" (75F) 524

2" (75F) 312

ROLL-OUT TRAY

ROLL-OUT TRAY

PART NO.	DRWRS.	COMPARTS.
MTC-900-1-■ ■ □	2	-
MTC-900-1A-■ ■ □	2	36



INCLUDES INT.
2" (75F) 524

2" (75F) 312

ROLL-OUT TRAY

ROLL-OUT TRAY

PART NO.	DRWRS.	COMPARTS.
MTC-900-2-■ ■ □	3	-
MTC-900-2A-■ ■ □	3	45



INCLUDES INT.

2" (75F) 524

2" (75F) 312

2" (75F) 312

2" (75F) 209

ROLL-OUT TRAY

PART NO.	DRWRS.	COMPARTS.
MTC-900-3-■ ■ □	4	-
MTC-900-3A-■ ■ □	4	57



Model 9150 Machine Tool Cabinets

28 1/4" wide x 29 1/2" deep x 39 3/8" high

These cabinets have drawer(s) on the top for personal operator tools, gauges etc. Upper and lower sections lock separately. Drawers and roll-out trays are adjustable in 1" increments.



INCLUDES	INT.
5" (150F)	209
2" (75F)	524
2" (75F)	312
ROLL-OUT TRAY	
ROLL-OUT TRAY	

PART NO.	DRWRS.	COMPARTS.
MTC-9150-1- ■ ■ □	3	-
MTC-9150-1A- ■ ■ □	3	45

Model 9005 Machine Tool Cabinets

56 1/2" wide x 30 3/4" deep x 39 3/8" high

These Double Width cabinets have a center support that allows drawers and roll-out trays to be used on either side. Outfitted as described, photos show 1 side with half of the drawers and trays. Drawers and roll-out trays are adjustable in 1" increments.



INCLUDES	INTERIOR	INCLUDES	INT.
2" (75F)	312	2" (75F)	312
ROLL-OUT TRAY		ROLL-OUT TRAY	
ROLL-OUT TRAY		ROLL-OUT TRAY	
ROLL-OUT TRAY		ROLL-OUT TRAY	

PART NO.	DRWRS.	COMPARTS.
MTC-9005-1- ■ ■ □	2	-
MTC-9005-1A- ■ ■ □	2	24



INCLUDES	INT.
2" (75F)	312
2" (75F)	209
2" (75F)	524
2" (75F)	312
2" (75F)	209
ROLL-OUT TRAY	

PART NO.	DRWRS.	COMPARTS.
MTC-9150-2- ■ ■ □	5	-
MTC-9150-2A- ■ ■ □	5	66



INCLUDES	INTERIOR	INCLUDES	INT.
2" (75F)	312	2" (75F)	312
2" (75F)	524	2" (75F)	524
ROLL-OUT TRAY		ROLL-OUT TRAY	
ROLL-OUT TRAY		ROLL-OUT TRAY	

PART NO.	DRWRS.	COMPARTS.
MTC-9005-2- ■ ■ □	4	-
MTC-9005-2A- ■ ■ □	4	72



INCLUDES	INTERIOR	INCLUDES	INT.
2" (75F)	524	2" (75F)	524
2" (75F)	312	2" (75F)	312
2" (75F)	209	2" (75F)	209
ROLL-OUT TRAY		ROLL-OUT TRAY	

PART NO.	DRWRS.	COMPARTS.
MTC-9005-3- ■ ■ □	6	-
MTC-9005-3A- ■ ■ □	6	90

Easy-Order Tool Crib Cabinet Combinations

Lista cabinets, with their modular drawer interiors, are ideal for tool crib storage.

The cabinets on these pages contain everything you need to properly and efficiently store all items shown in the charts. Lista has pre-assembled these specific combinations because they are the most frequently ordered combinations.

Chosen for the specific parts shown, drawers can easily be rearranged within the cabinet or within cabinet groupings.

Drawers are 100% full extension with a 440 lb. (200kg) weight capacity. They have usable inside dimensions of 24" (610mm) wide x 24" (610mm) deep.

How to order an Easy-Order Tool Crib Cabinet

1. Select Easy-Order Tool Crib Cabinet Combination.

2. ■ Select base type.

NB = none
FT = fork truck
PT = pallet truck

3. ■ Select lock type.

NL = none
RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

4. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order a TCC-4 cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **TCC-4-FTRGBB**.



Model 900 Cabinet Combinations

28 1/4" wide x 28 1/2" deep x 39 3/8" high

Model 900 cabinets are convenient for a counter height worksurface. All drawers are 100% full extension with a 440 lb. load capacity.

TCC-1- ■ ■ ■ Drills & Taps (11 Drawers)

QTY.	DRW.	STORE
1	SC75F	number drills 1 thru 80
1	SC75F	letter drills A thru Z center drills 00 thru 8
1	SC75F	fractional drills, jobbers 1/64" thru 1/2" x 1/64"
1	SC75F	fractional drills, specials 1/64" thru 1/2" x 1/64"
1	SC75F	standard tapers 0-80 thru 1/4" -28"
1	SC75F	5/16" -18" thru 7/8" -20"
1	SC100F	15/16" -16" thru 2" -16"
1	SC100F	pipe taps, sleeves, easy outs
2	SC75F	assigned cutting tools
1	SC100F	assigned cutting tools

TCC-2- ■ ■ ■ Taper Shank Drills (10 Drawers)

QTY.	DRW.	STORE
1	SC75F	taper shank drills 33/64" thru 25/32" x 1/64" (4 each)
1	SC75F	51/64" thru 1 1/32" x 1/64" (4 each)
1	SC100F	1 3/64" thru 1 11/64" x 1/64" (4 each)
1	SC100F	1 3/16" thru 1 5/16" x 1/64" (4 each)
1	SC100F	1 21/64" thru 1 27/64" x 1/64" (4 each)
1	SC100F	1 7/16" thru 1 1/2" x 1/64" (6 each)
1	SC75F	1 17/32" thru 1 11/16" x 1/32" (2 each)
1	SC75F	1 23/32" thru 1 7/8" x 1/32" (2 each)
1	SC100F	1 29/32" thru 2" x 1/32" (2 each)
1	SC100F	(2) expansion or 1/64" sizes
1	SC100F	drifts, sleeves, and reserve drills

TCC-3- ■ ■ ■ Milling (10 Drawers)

QTY.	DRW.	STORE
4	SC75F	milling cutters, slitting saws
1	SC75F	end mills 1/8" thru 1/2"
1	SC100F	17/32" thru 1"
1	SC100F	1 1/8" thru 1 1/2"
1	SC100F	hog, ball, and other
1	SC100F	key cutters
1	SC125F	slab & face mills

TCC-4- ■ ■ ■ Reamers & Supplies (10 Drawers)

QTY.	DRW.	STORE
1	SC75F	chucking reamers, st-sk 1/16" thru 17/32" x 1/64"
1	SC75F	9/16" thru 1" x 1/32"
1	SC75F	misc. over 1"
1	SC75F	counter bores and pilots
2	SC75F	assigned cutting tools
1	SC100F	emery sheets
1	SC100F	burrs, stones and mounted points
1	SC100F	allen keys and chuck key
1	SC150F	stamps, punches, mallets

TCC-5- ■ ■ ■ Turning (10 Drawers)

QTY.	DRW.	STORE
1	SC75F	tool holder repair parts, anvils, screws, clamps, shims
1	SC75F	carbide brazed & high speed tools
2	SC75F	s.s. boring bars
2	SC75F	insert tool holders
3	SC100F	carbide inserts
1	SC150F	turret tool holders

TCC-6- ■ ■ ■ Precision Tools (10 Drawers)

QTY.	DRW.	STORE
2	SC75F	micrometers
1	SC75F	plain plug gages
1	SC75F	thread plug gages
1	SC75F	plain and thread rings
1	SC75F	verniers, gages, indicators, etc.
2	SC100F	verniers, gages, indicators, etc.
2	SC125F	verniers, gages, indicators, etc.

TCC-7- ■ ■ ■ Hand Tools (7 Drawers)

QTY.	DRW.	STORE
2	SC75F	files
3	SC100F	hand tools
1	SC200F	power tools
1	SC250F	power tools

TCC-8- ■ ■ ■ Fasteners (10 Drawers)

QTY.	DRW.	STORE
4	SC75F	fasteners, all types
6	SC100F	fasteners, all types





Model 1350 Cabinet Combinations

28 1/4" wide x 28 1/2" deep x 57 1/8" high

Model 1350 cabinets are eye level height and provide more storage in the same footprint as the Model 900. All drawers are 100% full extension with a 440 lb. load capacity.

TCC-21-■■■ Drills & Taps (15 Drawers)

QTY.	DRW.	STORE
1	SC75F	number drills 1 thru 80
1	SC75F	letter drills A thru Z center drills 00 thru 8
1	SC75F	fractional drills, jobbers 1/64" thru 1/2" x 1/64"
1	SC75F	fractional drills, specials 1/64" thru 1/2" x 1/64"
1	SC75F	standard taps 0-80 thru 1/4" -28"
1	SC75F	5/16" -18" thru 7/8" -20"
1	SC100F	15/16" -16" thru 2" -16"
1	SC100F	pipe taps, sleeves, easy outs
2	SC75F	assigned cutting tools
3	SC100F	assigned cutting tools
1	SC125F	tap adapters, collets and extensions
1	SC125F	drill collets

TCC-22-■■■ Taper Shank Drills (16 Drawers)

QTY.	DRW.	STORE
1	SC75F	frac. T.S. drills 33/64" thru 23/32" x 1/64" (15 each)
1	SC75F	47/64" thru 7/8" x 1/64" (10 each)
1	SC75F	57/64" thru 1 1/32" x 1/64" (8 each)
1	SC75F	1 3/64" thru 1 7/64" x 1/64" (8 each)
1	SC75F	1 1/8" thru 1 3/16" x 1/64" (8 each)
1	SC75F	1 13/64" thru 1 17/64" x 1/64" (8 each)
1	SC100F	1 9/32" thru 1 11/32" x 1/64" (8 each)
1	SC100F	1 23/64" thru 1 27/64" x 1/64" (6 each)
1	SC100F	1 7/16" thru 1 1/2" x 1/64" (6 each)
1	SC75F	1 33/64" thru 1 37/64" x 1/64" (3 each)
1	SC75F	1 19/32" thru 1 21/32" x 1/64" (3 each)
1	SC75F	1 43/64" thru 1 47/64" x 1/64" (3 each)
1	SC75F	1 3/4" thru 1 7/8" x 1/32" (3 each)
1	SC75F	1 29/32" thru 2" x 1/32" (2 each)
1	SC125F	drill sleeves - drifts
1	SC100F	misc. reserve drills

TCC-23-■■■ Milling (14 Drawers)

QTY.	DRW.	STORE
4	SC75F	milling cutters slitting saws
1	SC75F	end mills 1/8" thru 1/2"
1	SC100F	17/32" thru 1"
1	SC100F	1 1/8" thru 1 1/2"
2	SC100F	hog, ball, and other
1	SC100F	key cutters
1	SC125F	slab & face mills
1	SC100F	insertable end mills
1	SC100F	broaches & sleeves
1	SC150F	misc. expansion

TCC-24-■■■ Reamers & Supplies (14 Drawers)

QTY.	DRW.	STORE
1	SC75F	chucking reamers, st-sk 1/16" thru 17/32" x 1/64"
1	SC75F	9/16" thru 1" x 1/32"
1	SC75F	misc. over 1"
1	SC75F	counter bores and pilots
1	SC75F	spot facers
2	SC75F	assigned cutting tools
1	SC100F	emery sheets
1	SC100F	burrs, stones and mounted points
1	SC100F	fixture components
1	SC100F	allen keys and chuck keys
1	SC125F	hole saws
2	SC150F	stamps, punches, mallets

TCC-25-■■■ Turning (15 Drawers)

QTY.	DRW.	STORE
2	SC75F	tool holder repair parts, anvils, screws, clamps, shims
2	SC75F	carbide brazed & high speed tools
2	SC75F	s.s. boring bars
2	SC75F	insert tool holders
5	SC100F	carbide inserts
1	SC100F	boring heads, cartridges
1	SC150F	turret tool holders

TCC-26-■■■ Precision Tools (12 Drawers)

QTY.	DRW.	STORE
2	SC75F	micrometers
1	SC75F	plain plug gages
1	SC75F	thread plug gages
1	SC75F	plain and thread rings
1	SC75F	verniers, gages, indicators, etc.
2	SC100F	verniers, gages, indicators, etc.
2	SC125F	verniers, gages, indicators, etc.
1	SC150F	"V" blocks, dial bore gages
1	SC300F	boxed tool sets

TCC-27-■■■ Hand Tools (10 Drawers)

QTY.	DRW.	STORE
2	SC75F	files
3	SC100F	hand tools
1	SC150F	grinding wheels to 7" dia.
2	SC150F	misc. supplies
1	SC200F	power tools
1	SC250F	power tools

TCC-28-■■■ Fasteners (14 Drawers)

QTY.	DRW.	STORE
6	SC75F	fasteners, all types
6	SC100F	fasteners, all types
2	SC150F	fasteners, all types



Lista Unique Workspace Solutions

Overhead cabinets featuring sliding doors with steel-framed plexiglas windows enable lab personnel at DCE Aprilis, Inc. to access delicate lab instruments and glassware. The row of cabinets below is topped by a phenolic resin counter top.



Lista Unique Workspace Solutions

Overhead Cabinets	104
Overhead Cabinets and Shelves	105
Overhead Cabinet Mounting Components	106
Counter Tops	107
Computer Cabinets	108
Computer Cabinet Features and Options	109
Computer Cabinet Easy-Order Combination	110
Computer Cabinet Accessories	110
Sink Cabinets	111
File Drawer Cabinets	111
Control Stations	112
Mezzanines and Stacked Cabinets	114



Overhead Cabinets

Ideal companions to Lista's modular drawer storage cabinets, overhead cabinets bring organization to the storage of binders, bulk storage or any items that require constant access, ample room and safe storage.

Overhead cabinets with steel-framed plexiglas doors hold an array of books, manuals and binders in a classroom at the Four Rivers Career Center.



Overhead cabinets bring organized, efficient storage of instruction manuals, binders and other reference books to this airline's repair shop.



An overhead cabinet with retractable door provides convenient bulk storage above a drawer cabinet in the machining area of an aircraft repair facility.



Open shelf overhead cabinets store jars of additives in the food testing labs at T. Marzetti, a manufacturer of salad dressings.

Overhead Cabinets and Shelves



16" High Overhead Cabinets

Cabinets come with bottom shelf, and are 15" deep with a usable shelf depth of 13 1/2". Useable height for cabinet without door is 14", and with retractable door is 13".

PART NO.	WIDTH	TO MATCH
OHC2316-   	22 3/16"	MP, CL
OHC2816-   	28 1/4"	SC, ST
OHC3016-   	30"	-
OHC3416-   	33 3/4"	2 NW
OHC3616-   	36"	-
OHC4016-   	40 1/4"	HS
OHC4216-   	42"	-
OHC4716-   	47"	MW
OHC4816-   	48"	-
OHC5616-   	56 1/2"	DW
OHC6016-   	60"	-



Retractable Doors for 16" High Overhead Cabinets

Retractable doors (RD) are available in solid steel.



29" High Overhead Cabinets

Cabinets come with a flush bottom shelf and 1 adjustable shelf, and are 15" deep with a usable shelf depth of 13 1/2". They have vertical supports slotted at 1 1/2" increments for shelves. Additional shelves may be ordered from the chart to the right.

PART NO.	WIDTH	TO MATCH
OHC2329-   	22 3/16"	MP, CL
OHC2829-   	28 1/4"	SC, ST
OHC3029-   	30"	-
OHC3429-   	33 3/4"	2 NW
OHC3629-   	36"	-
OHC4029-   	40 1/4"	HS
OHC4229-   	42"	-
OHC4729-   	47"	MW
OHC4829-   	48"	-
OHC5629-   	56 1/2"	DW



Hinged Doors for 29" High Overhead Cabinets

Hinged doors are available in solid steel (HD) or steel-framed plexiglas (HDP).



Sliding Doors for 29" High Overhead Cabinets

Sliding doors are available in solid steel (SD) or steel-framed plexiglas (SDP).

Additional Shelves

For 29" high cabinets only. Shelves are 13 1/2" deep.

PART NO.	USE WITH CABINET WIDTH
OHC-S23	22 3/16"
OHC-S28	28 1/4"
OHC-S30	30"
OHC-S34	33 3/4"
OHC-S36	36"
OHC-S40	40 1/4"
OHC-S42	42"
OHC-S47	47"
OHC-S48	48"
OHC-S56	56 1/2"

How to order an overhead cabinet

1. **Select overhead cabinet** based on your choice of dimensions. To order an overhead cabinet without doors, use the base part number as it appears in the charts to the left.

2.  **Select optional door type.**

for 16" high overhead cabinets
RD = retractable door

for 29" high overhead cabinets

HD = hinged doors

HDP* = hinged doors with steel-framed plexiglas

SD** = sliding doors

SDP** = sliding doors with steel-framed plexiglas

** plexiglas doors available for cabinets 28" and wider only*

*** sliding doors available for cabinets 40" and wider only*

3.  **Select lock type.**

RG = individual

KA = keyed-alike

MA = master

All cabinets lock at bottom.

4. ☐ **Select paint color.** For color chart, see back cover.

EXAMPLE: to order an OHC2316 overhead cabinet with a retractable door, an individual lock and Bright Blue paint, the part number would be **OHC2316-RDRGBB**.

Overhead cabinets are 15" deep and are available in two heights (16" and 29") and a variety of widths to suit individual storage needs.

Overhead cabinets feature shelves adjustable at 1 1/2" increments. All cabinets with doors offer locks to protect stored materials.

Retractable doors are available for 16" high cabinets. Sliding or hinged metal doors (both with and without a plexiglas window) are available for 29" high cabinets.

Overhead Cabinet Mounting Components

Lista overhead cabinets can be mounted to a wall for stability and permanence. Mount either directly to the wall with customer-supplied hardware, or by using a Wall Mounting Kit.

Overhead cabinets can also be easily mounted atop a stationary riser shelf for convenient support without having to mount the unit to the wall. Stationary riser shelves are available either with or without a back panel, and can be situated above any counter top.



Wall Mounting Kits

Brackets for mounting overhead cabinets to wall. Starter kit is required for first cabinet in row. One adder kit is required for each additional cabinet used. Starter kit includes brackets and end filler strips; adder kit includes brackets only. Color to match housing.

16" High Cabinet Wall Mounting Kits

STARTER PART NO.	ADDER PART NO.	USE WITH CAB. WIDTH
OHC-WB2316	OHC-WB23A	22 3/16"
OHC-WB2816	OHC-WB28A	28 1/4"
OHC-WB3016	OHC-WB30A	30"
OHC-WB3416	OHC-WB34A	33 3/4"
OHC-WB3616	OHC-WB36A	36"
OHC-WB4016	OHC-WB40A	40 1/4"
OHC-WB4216	OHC-WB42A	42"
OHC-WB4716	OHC-WB47A	47"
OHC-WB4816	OHC-WB48A	48"
OHC-WB5616	OHC-WB56A	56 1/2"

29" High Cabinet Wall Mounting Kits

STARTER PART NO.	ADDER PART NO.	USE WITH CAB. WIDTH
OHC-WB2329	OHC-WB23A	22 3/16"
OHC-WB2829	OHC-WB28A	28 1/4"
OHC-WB3029	OHC-WB30A	30"
OHC-WB3429	OHC-WB34A	33 3/4"
OHC-WB3629	OHC-WB36A	36"
OHC-WB4029	OHC-WB40A	40 1/4"
OHC-WB4229	OHC-WB42A	42"
OHC-WB4729	OHC-WB47A	47"
OHC-WB4829	OHC-WB48A	48"
OHC-WB5629	OHC-WB56A	56 1/2"



Stationary Riser Shelves – 15" deep

Shelf is 13 1/2" high overall (12" clearance). Other heights available. (Optional pegboard closed back rear panel is shown above.) Specify paint color(s) from chart on back cover.

Open Riser Shelves

Open back, no shelf backstop

PART NO.	TOP LENGTH
SRS48-15D	48"
SRS60-15D	60"
SRS72-15D	72"
SRS84-15D	84"
SRS96-15D	96"

Open back, with shelf backstop

PART NO.	TOP LENGTH
SRS48-1-15D	48"
SRS60-1-15D	60"
SRS72-1-15D	72"
SRS84-1-15D	84"
SRS96-1-15D	96"

Riser Shelves with Full Panel

Solid closed back, with shelf backstop

PART NO.	TOP LENGTH
SRS48-2-15D	48"
SRS60-2-15D	60"
SRS72-2-15D	72"
SRS84-2-15D	84"
SRS96-2-15D	96"

Pegboard closed back, with shelf backstop (shown above)

PART NO.	TOP LENGTH
SRS48-2P-15D	48"
SRS60-2P-15D	60"
SRS72-2P-15D	72"
SRS84-2P-15D	84"
SRS96-2P-15D	96"

Louvered closed back, with shelf backstop

PART NO.	TOP LENGTH
SRS48-2L-15D	48"
SRS60-2L-15D	60"
SRS72-2L-15D	72"
SRS84-2L-15D	84"
SRS96-2L-15D	96"



Butcher Block Counter Tops

Tops are 1 3/4" thick butcher block hardwood.

PART NO.	FOR USE WITH
28 1/2" deep	
NW2BCT	2 NW cabinets
NW3BCT	3 NW cabinets
NW4BCT	4 NW cabinets
MP2BCT	2 MP cabinets
MP3BCT	3 MP cabinets
MP4BCT	4 MP cabinets
MP5BCT	5 MP cabinets
SC2BCT*	2 SC cabinets
SC3BCT	3 SC cabinets
SC4BCT**	4 SC cabinets
22 1/2" deep	
CL2BCT	2 CL cabinets
ST2BCT	2 ST cabinets
ST3BCT	3 ST cabinets
HS2BCT	2 HS cabinets

*can also be used for 1 DW cabinet

**can also be used for 2 DW cabinets

Plastic Laminate Counter Tops

Tops are 1 9/16" thick standard dove gray laminate over wood core.

PART NO.	FOR USE WITH
28 1/2" deep	
NW2PCT	2 NW cabinets
NW3PCT	3 NW cabinets
NW4PCT	4 NW cabinets
MP2PCT	2 MP cabinets
MP3PCT	3 MP cabinets
MP4PCT	4 MP cabinets
SC2PCT*	2 SC cabinets
SC3PCT	3 SC cabinets
SC4PCT**	4 SC cabinets
22 1/2" deep	
CL2PCT	2 CL cabinets
ST2PCT	2 ST cabinets
ST3PCT	3 ST cabinets
HS2PCT	2 HS cabinets

*can also be used for 1 DW cabinet

**can also be used for 2 DW cabinets

Phenolic Resin Counter Tops

Top is a high-pressure laminate designed for laboratory worksurfaces. Resistant to chemicals, stains or discoloration. Top is 1" thick phenolic resin, available in black.

PART NO.	FOR USE WITH
28 1/2" deep	
NW2RCT	2 NW cabinets
NW3RCT	3 NW cabinets
NW4RCT	4 NW cabinets
MP2RCT	2 MP cabinets
MP3RCT	3 MP cabinets
MP4RCT	4 MP cabinets
SC2RCT*	2 SC cabinets
SC3RCT	3 SC cabinets
22 1/2" deep	
ST2RCT	2 ST cabinets
ST3RCT	3 ST cabinets
HS2RCT	2 HS cabinets

*can also be used for 1 DW cabinet

Stainless Steel Counter Tops

Top is constructed of durable, heavy gauge stainless steel, fitted over top and sides of wood core, 1 13/16" thick.

PART NO.	FOR USE WITH
28 1/2" deep	
NW1LSSCT	1 NW cabinet
NW2LSSCT	2 NW cabinets
NW3LSSCT	3 NW cabinets
MP1LSSCT	1 MP cabinet
MP2LSSCT	2 MP cabinets
MP3LSSCT	3 MP cabinets
SC1LSSCT	1 SC cabinet
SC2LSSCT*	2 SC cabinets
SC3LSSCT	3 SC cabinets
SC4LSSCT**	4 SC cabinets
MW1LSSCT	1 MW cabinet
MW2LSSCT	2 MW cabinets
DW1LSSCT	1 DW cabinet
22 1/2" deep	
CL1LSSCT	1 CL cabinet
CL2LSSCT	2 CL cabinets
ST1LSSCT	1 ST cabinet
ST2LSSCT	2 ST cabinets
HS1LSSCT	1 HS cabinet
HS2LSSCT	2 HS cabinets

*can also be used for 1 DW cabinet

**can also be used for 2 DW cabinets

Counter Top Maximum Lengths*

TOP	MAXIMUM LENGTH
Butcher block	144"
Plastic laminate	120"
Phenolic resin	144"
Stainless steel	114 1/2"

*counter tops can be arranged end-to-end for longer spans

Cabinet Housing Widths

HOUSING	WIDTH
NW	16 7/8"
MP	22 3/16"
SC	28 1/4"
MW	47"
DW	56 1/2"
CL	22 3/16"
ST	28 1/4"
HS	40 1/4"

Lista counter tops provide a durable and attractive work surface for rows of cabinets.

Counter tops are flush to the cabinets side-to-side and front-to-back. Tops are supplied with lag bolts and can be ordered for individual cabinets or as a continuous top for cabinet rows.

See chart to the left for length limitations for cabinet rows.

To order a counter top for a row of cabinets with a variety of different widths, add the total width of all cabinet housings in the row (see chart to left). To order, please contact your Lista representative.

For cabinet tops for single cabinets, see page 67.



Computer Cabinets

Lista's versatile, feature-packed computer cabinet is designed to provide maximum protection from metal shards, dust and other workplace debris. The computer cabinet is ideal for PC's, terminals, and computer peripherals on the shop floor and in a variety of industrial and repair environments.



Aircraft mechanics in Northwest Airlines' Avionics Maintenance Department access computers above a plane being repaired at one of its Minneapolis hangars.



A mobile computer cabinet is paired with a mobile industrial workbench in Toyota Racing Development's machine shop.




A technician accesses a Lista computer cabinet which houses a diagnostic computer. The computer cabinet's mobility allows it to be relocated within the department as needed.

Computer Cabinet Features and Options

Lista's computer cabinet is packed with powerful features.

- Air intake fan with guard and fine filter (replaceable from the outside) – creates positive pressure, eliminates dust and possible damage to electrical components
- Large keyboard tray with hinged front gate allows space for mouse
- Monitor door has clear plexiglas window for visibility and protection
- Retractable door option for convenient access to touch screen monitors
- Monitor and lower door locks are keyed alike
- Lower sections provide secure storage for CPU and printer – printer tray extends for ease of access
- Surge suppressor protects equipment and hardware using advanced circuitry, eliminates dangers caused by surges, spikes and EMI/RFI noise
- 6 1/2" wide rear access panel for ease of connection and routing of cables
- Several base options available
- Optional fan for lower section of cabinet
- Optional exterior folding shelf for additional storage



FRONT

MODEL CWS1350 SHOWN
WITH OPTIONAL MOBILE BASE



BACK

Easy-Order Computer Cabinet Combination



Easy-Order computer cabinet comes with:

- Hinged upper section door with plexiglas window (opening for monitor is 24" wide x 19 1/2" high x 24" deep)
- Double hinged lower section doors
- Keyboard tray with hinged front gate
- Printer tray
- Bottom shelf
- Back access panel
- Cord channel/outlet strip
- Upper fan

Other options and accessories to augment cabinets must be ordered from the charts to the right.

28 1/4" wide x 57 1/8" high x 29 1/2" deep

PART NO.

CWS1350- ■ ■ □

How to order an Easy-Order Computer Cabinet

1. Select Easy-Order Computer Cabinet combination.

2. ■ Select base type.

NB = none
FT = fork truck
PT = pallet truck
2FB = 2" frame base
4FB = 4" frame base
6FB = 6" frame base
4B = 4" mobile base
6B = 6" mobile base

For base descriptions, see SC cabinet bases on page 39.

3. ■ Select lock type.

RG = individual
KA = keyed-alike
MA = master

For additional lock options, see page 62.

4. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order a CWS1350 cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **CWS1350-FTRGBB**.



Retractable Door

Door slides out and back for access to monitor. Provides convenient access to touch screens. Reduces opening height by 2 1/2".

PART NO.

RD525/SC-P

Electrical and Fan Options

PART NO.	DESCRIPTION
FAN-CWS	second fan for lower section
CWS-OUT/36U	second outlet strip and bracket



Folding Shelves

Shelf can be mounted on either the left or right side of cabinet. 50 lb. maximum capacity. Shelf is 15" wide x 28 1/2" deep.

PART NO.	MOUNTS TO
FS-36DX15-L	left side
FS-36DX15-R	right side

Mobile Handles

Handles are mounted to either the side or front of cabinet. Cabinets are pre-drilled and handles are mounted in the field. Hardware included. For descriptions, see page 66.

PART NO.	DESCRIPTION
HSG-HNDL/36	side push metal handle
MHAN	front push plastic handles (pair)

Sink Cabinets

Sink cabinet includes a cabinet housing, flush door or double flush doors, a bottom shelf, and cut-outs for sink and plumbing. **Does not include counter top or sink basin.**



Sink Cabinets – Flush Door

PART NO.	HOUSING	HEIGHT*
28 1/4" wide x 28 1/2" deep		
SC750SINK- ■ ■ □	SC	33 1/2"
SC900SINK- ■ ■ □	SC	39 3/8"
28 1/4" wide x 22 1/2" deep		
ST750SINK- ■ ■ □	ST	33 1/2"
ST900SINK- ■ ■ □	ST	39 3/8"

*does not include height of counter top or base



Sink Cabinets – Double Flush Door

PART NO.	HOUSING	HEIGHT*
47" wide x 28 1/2" deep		
MW750SINK- ■ ■ □	MW	33 1/2"
MW900SINK- ■ ■ □	MW	39 3/8"
56 1/2" wide x 28 1/2" deep		
DW750SINK- ■ ■ □	DW	33 1/2"
DW900SINK- ■ ■ □	DW	39 3/8"
40 1/4" wide x 22 1/2" deep		
HS750SINK- ■ ■ □	HS	33 1/2"
HS900SINK- ■ ■ □	HS	39 3/8"

*does not include height of counter top or base

How to order an Easy-Order Sink Cabinet

1. Select a cabinet from the charts to the left.
2. ■ Select base type.
 FT = fork truck
 PT = pallet truck
 2FB = 2" frame
3. ■ Select lock type.
 RG = individual
 KA = keyed-alike
 MA = master
 For additional lock options, see page 62.
4. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order an MW750SINK sink cabinet with a fork truck base, an individual lock and Bright Blue paint, the part number would be **MW750SINK-FTRGBB**.

Lista file drawer cabinets

make ideal companions to any

Lista workspace.



File Drawer Cabinet

File drawer cabinet housing is 16 7/8" (428mm) wide x 28 1/2" (725mm) deep. Drawers are full extension with 165 lb. (75kg) maximum load capacity. For letter-sized files only.

DRAWER HT.		
11" (300N-FFH)		
11" (300N-FFH)		
PART NO.	DRWS.	HT.
NW0600-0201N- ■ ■ □	2	27 1/2"

DRAWER HT.		
11" (300N-FFH)		
11" (300N-FFH)		
11" (300N-FFH)		
PART NO.	DRWS.	HT.
NW0900-0301N- ■ ■ □	3	39 3/8"

DRAWER HT.		
11" (300N-FFH)		
11" (300N-FFH)		
11" (300N-FFH)		
11" (300N-FFH)		
PART NO.	DRWS.	HT.
NW1225-0401N- ■ ■ □	4	52 3/16"

How to order an Easy-Order File Drawer Cabinet

1. Select file drawer cabinet combination.
2. ■ Select base type.
 NB = none
 2FB = 2" frame base
 4FB = 4" frame base
3. ■ Select lock type.
 NL = none
 RG = individual
 KA = keyed-alike
 MA = master
 For additional lock options, see page 62.
4. □ Select paint color. For color chart, see back cover.

EXAMPLE: to order an NW0900-0301N file cabinet with a 2" frame base, an individual lock and Bright Blue paint, the part number would be **NW0900-0301N-2FBRGBB**.

Control Stations

The secure, durable and flexible Lista Control Station is ideal for meeting the needs of a wide array of manufacturing floor applications:

- Quality station or foreman's workstation on the manufacturing floor
- Gauging station on an automotive assembly line
- Line supervisor's station in an assembly plant
- Shipping dock

This unique combination of a workbench, bookshelf and cabinet offers a private, protected, lockable workspace with organized storage and ready access to manuals and tools. The work area features a pegboard and one or two bookshelves. The Control Station is available in two heights – 91 1/2" or 99 3/8" tall.

The Control Station is available in all Lista paint colors (see back cover); the tambour door is available in dove gray only.



The Control Station features a slide-down tambour door that can be locked at the desktop or at the base of the station.




MODEL CS2200/5



The Control Station's work area offers protection from dust and dirt for your expensive computer equipment, instruments and gauges. The Station's pegboard and bookshelves let you keep manuals and tools close at hand. The worksurface height at the butcher block top is 35 1/4".




The Control Station's storage cabinets can be outfitted with modular drawers in a variety of sizes. Drawers can be configured for compartmentalized storage of tools and parts, or to hold hanging files.



Easy-Order Control Station Combinations


The Control Station is available in 3 Easy-Order configurations. These 3 models are designed to accommodate the broadest range of Control Station sizes and features.



Basic Control Station 60 1/4" wide x 29 3/4" deep

Equipped as shown with lockable tambour door, bookshelf, pegboard, fluorescent light and 1 3/4" thick butcher block counter top. A variety of optional stationary and mobile cabinets can be placed under the counter top; see the cabinet section of this catalog to select the cabinet size that best fits your needs.


PART NO.	HEIGHT	NO. OF BKSHV.	PEGBOARD HEIGHT
CS2000	91 1/2"	1	18"
CS2200	99 3/8"	2	15"
Without tambour door			
CS2000-ND	78 3/4"	1	18"
CS2200-ND	86 5/8"	2	15"



Control Station – Configurable 60 1/4" wide x 29 3/4" deep

Equipped as shown with lockable tambour door, bookshelf, pegboard, fluorescent light, 1 3/4" thick butcher block counter top and a 750 height framework for SC Standard Width drawers. To select drawers for the framework, see page 40.

PART NO.	HEIGHT	NO. OF BKSHV.	PEGBOARD HEIGHT
CS2000/1	91 1/2"	1	18"
CS2200/1	99 3/8"	2	15"
Without tambour door			
CS2000/1-ND	78 3/4"	1	18"
CS2200/1-ND	86 5/8"	2	15"



Control Station – Pre-configured 60 1/4" wide x 29 3/4" deep

Equipped as shown with lockable tambour door, bookshelf, pegboard, fluorescent light, 1 3/4" thick butcher block counter top and a 750 height Standard Width framework, containing 1 each of the following height drawers:

- 75F (2")
- 100F (3")
- 125F (4")
- 150F (5")
- 300F-FFH (11") drawer with a letter-size file folder hanger (see photo to left).

PART NO.	HEIGHT	NO. OF BKSHV.	PEGBOARD HEIGHT
CS2000/5	91 1/2"	1	18"
CS2200/5	99 3/8"	2	15"
Without tambour door			
CS2000/5-ND	78 3/4"	1	18"
CS2200/5-ND	86 5/8"	2	15"

Mezzanines and Stacked Cabinets

Lista Storage Wall® Systems (see pages 72-85) and stacked cabinets serve as ideal mezzanine supports. Our technical support and design team can help you determine the option that best suits your space and needs.

Stacked cabinets

With their all-steel construction, Lista cabinets can be stacked to help you maximize your floor space. You can rapidly re-arrange storage layouts to suit your changing needs.



To add a second level of storage space without adding an additional floor to their maintenance area, Gulf States Paper Corp. utilizes a mezzanine system. The system is home to 49 sets of stacked cabinets.

When Osram Sylvania needed to relocate a 3,300 square foot stockroom into a 1,500 square foot space, a mezzanine was the answer. The company combined new Lista cabinet housings and drawers with existing Lista cabinets to create this space- and money-saving solution.





Storage Walls Systems and stacked cabinets lend themselves to a variety of mezzanine configurations that take advantage of all available height. Examples pictured here are (clockwise from top) installations at a utility maintenance department, an aircraft repair facility and an automotive manufacturing plant.



Lista Drawer Accessories



Lista Drawer Accessories

How to Order Custom Drawer Partitions and Dividers	118
Partitions	119
Dividers	119
Plastic Boxes	120
Conductive Plastic Boxes	120
Grooved Trays	120
Conductive Grooved Trays	120
Other Accessories	121-122
Milling Cutter Holders	121
Corrugated Steel Supports	121
Holding Pins	121
Slotted Tool Supports	121
Arbor Holders	121
Allen Key Holders	121
Molded Collet Holders	121
File Drawer Inserts	122
Plastic Angular Supports	122
Drawer Liners	122
Sliding Accessory Tray	122
Foam Drawer Liners	122

Lista drawer partitioning accessories provide complete protection and systematic organization for whatever you need to store – from tools to electronic components to small parts.

Customized compartments

The partitioning slots on the sidewalls of all Lista drawers are $2\frac{1}{32}$ " apart, both front to back and side to side, providing for more possible partitioning configurations than any other drawer in the industry. Anything you need to store has its specific compartment, is well protected and easily retrievable.

Solving difficult problems

Our experienced technical support and design team is pleased to review your inventory and assist you in solving any difficult storage problem, free of charge.

How to Order **Custom** Drawer Partitions and Dividers

These are the basic steps required for ordering custom drawer partitions and dividers from Lista.

EASY-ORDER DRAWER INTERIOR SETS:

Preconfigured drawer interior sets for many popular drawer layouts are available for all sizes of Lista drawers:

NW Width	page 17
MP Width	page 21
SC Width	pages 26-27
MW Width	page 31
DW Width	page 35
CL Width	page 47
ST Width	page 51
HS Width	page 55

For tool holders, tool trays for drawers, drawer frames and other CNC and machine tool accessories, please see pages 90-91.

The Lista drawer subdivision system

Lista drawers are subdivided using 2 basic accessories: partitions, which divide the drawer into rows, and dividers, which define compartments within those rows.


The part designations for ordering partitions or dividers have 3 components:

1. **A letter or letters prefix indicating the part.** "P" is for slotted drawer partitions, "LP" is for plain drawer partitions, and "D" is for aluminum drawer dividers (for descriptions, see page 119).
2. **A number indicating the drawer model (height) number**, and therefore the height of the partition or divider.
3. **A number indicating the length of the partition or divider** in slots/units.

Drawer slot/unit dimensions are as follows:

NW Width	19 units W x 36 units D
MP Width	27 units W x 36 units D
Standard Width	36 units W x 36 units D
Mid-Width	64 units W x 36 units D
Double Width	78 units W x 36 units D
CL Width	27 units W x 27 units D
ST Width	36 units W x 27 units D
HS Width	54 units W x 27 units D

The examples to the right use an HS Width shallow depth cabinet drawer (40 1/4" wide) which has 54 slots/units side to side and 27 slots/units front to back.



Slotted and Plain Drawer Partitions


Partitions can divide a drawer into either horizontal or vertical rows.

The length of the partitions used in a drawer is determined by the number of slots/units in the drawer, front to back or side to side.




Aluminum Drawer Dividers

To further divide drawers into smaller compartments, order aluminum drawer dividers. To divide each of the 3 sections in the previous examples into 3 smaller sections, you would order 2 drawer dividers for each large section or a total of 6. **To subdivide drawers using dividers, you must specify slotted drawer partitions.**




EXAMPLE A: if you want to divide a model HS100F drawer into 3 sections each, running front to back, order 2 slotted drawer partitions **P100-27**.

P = slotted drawer partition
100 = drawer height model number
27 = units front to back




EXAMPLE A: if you have divided the drawer into 3 equal sections running front to back, each section is 18 slots/units wide ($54 \div 3 = 18$). So order 6 **D100-18** dividers.

D = drawer divider
100 = drawer height model number
18 = units wide



EXAMPLE B: if you want to divide the same drawer into 3 sections running side to side, order 2 slotted partitions **P100-54**.

P = slotted drawer partition
100 = drawer height model number
54 = units side to side




EXAMPLE B: if you have divided the drawer into 3 equal rows running side to side, each section is 9 slots/units wide ($27 \div 3 = 9$). So order 6 **D100-9** dividers.

D = drawer divider
100 = drawer height model number
9 = units wide

Partitions and Dividers

Slotted Drawer Partitions


These slotted steel sheet partitions are the basic drawer dividers. They divide drawers into small or large compartments by length and/or width. Partition ends slide easily into drawer sidewall slots and can be bolted to the perforated drawer bottom. Partitions are slotted at $2\frac{1}{32}$ " intervals to match the drawer sidewalls and should be ordered to match particular drawer heights, widths and depths (see chart). Color: gray.



FOR USE WITH DRAWER HEIGHT						
	75	100/125	150/175	200/225	250	300/350/400
PARTITION HEIGHT						
	2"	3"	5"	7"	8 15/16"	10 15/16"
LENGTH IN UNITS/INCHES	PARTITION PART NUMBER					
27 / 18"	P75-27	P100-27	P150-27	P200-27	P250-27	P300-27
30 / 20"	P75-30	P100-30	P150-30	P200-30	-	-
36 / 24"	P75-36	P100-36	P150-36	P200-36	P250-36	P300-36
54 / 36 1/8"	P75-54	P100-54	P150-54	P200-54	P250-54	P300-54
64 / 42 13/16"	P75-64	P100-64	P150-64	P200-64	P250-64	P300-64
78 / 52 3/16"	P75-78	P100-78	P150-78	P200-78	P250-78	P300-78

Plain Drawer Partitions


For use when drawers will not be subdivided using dividers. These non-slotted steel sheet partitions divide drawers into larger compartments either by length or width. Bottom strips can be bolted to the perforated drawer bottom for additional stability, and the ends slide into slots in drawer sidewalls or slotted drawer partitions. Plain partitions should be ordered to match drawer sidewall height. Color: gray.



FOR USE WITH DRAWER HEIGHT						
	75	100/125	150/175	200/225	250	300/350/400
PARTITION HEIGHT						
	2"	3"	5"	7"	8 15/16"	10 15/16"
LENGTH IN UNITS/INCHES	PARTITION PART NUMBER					
19 / 12 1/2"	LP75-19	LP100-19	LP150-19	LP200-19	LP250-19	LP300-19
24 / 16"	LP75-24	LP100-24	LP150-24	LP200-24	-	-
27 / 18"	LP75-27	LP100-27	LP150-27	LP200-27	LP250-27	LP300-27
30 / 20"	LP75-30	LP100-30	LP150-30	LP200-30	-	-
36 / 24"	LP75-36	LP100-36	LP150-36	LP200-36	LP250-36	LP300-36
54 / 36 1/8"	LP75-54	LP100-54	LP150-54	LP200-54	LP250-54	LP300-54
64 / 42 13/16"	LP75-64	LP100-64	LP150-64	LP200-64	LP250-64	LP300-64
78 / 52 3/16"	LP75-78	LP100-78	LP150-78	LP200-78	LP250-78	LP300-78

Drawer Slot Snap-On Label Holders

Clip-on label holders (not included, see to right) can be attached to these durable red plastic holders, which fit all slotted partitions or slotted drawer walls for labeling adjacent drawer contents. Angled for easier reading.



PART NO.	WIDTH	HEIGHT
SLH-1	1 3/16" (30mm)	5/8" (16mm)
SLH-2	2" (50mm)	5/8" (16mm)

Aluminum Drawer Dividers

Dividers subdivide drawers into smaller compartments for specialized storage. Aluminum dividers come in a variety of lengths and slip into slots in drawer sidewalls and/or slotted drawer partitions. Top edges are rounded and smooth for safety. Full-width angled top can accommodate most text and bar-code labels. Dividers can be fastened to drawer bottom for greater stability (fasteners included). Dividers should be ordered to match drawer sidewall height.



FOR USE WITH DRAWER HEIGHT						
	75	100/125	150/175	200/225	250	300/350/400
DIVIDER HEIGHT						
	2"	3"	5"	7"	8 15/16"	10 15/16"
LENGTH IN UNITS/INCHES*	DIVIDER PART NUMBER					
3 / 1 7/8"	D75-3	D100-3	-	-	-	-
4 / 2 1/2"	D75-4	D100-4	-	-	-	-
5 / 3 1/16"	D75-5	D100-5	-	-	-	-
6 / 3 7/8"	D75-6	D100-6	D150-6	D200-6	-	-
7 / 4 1/2"	D75-7	D100-7	D150-7	D200-7	-	-
8 / 5 3/16"	D75-8	D100-8	D150-8	D200-8	-	-
9 / 5 7/8"	D75-9	D100-9	D150-9	D200-9	D250-9	D300-9
10 / 6 9/16"	D75-10	D100-10	D150-10	D200-10	D250-10	D300-10
12 / 7 7/8"	D75-12	D100-12	D150-12	D200-12	D250-12	D300-12
15 / 9 7/8"	D75-15	D100-15	D150-15	D200-15	D250-15	D300-15
18 / 11 7/8"	D75-18	D100-18	D150-18	D200-18	D250-18	D300-18

*usable space is 3/8" less

Clip-on Label Holder

Black plastic label holders easily clip onto Lista aluminum drawer dividers, plastic boxes and tray dividers. When labeled using Lista Script software, DLH-1 holders use 18.787 labels; DLH-2 holders use 18.786 labels; DLH-3 holders use 18.785 labels (see page 120 to order label sheets).



PART NO.	FOR USE WITH
DLH-1	plastic box dividers PB-24D, PB-24ASD slotted grooved tray dividers STD-2, STD-3, STD-4 conductive slotted grooved tray dividers STD-3AS, STD-4AS grooved tray divider 2GTD drawer slot snap-on label holder SLH-1
DLH-2	drawer slot snap-on label holder SLH-2
DLH-3	all aluminum drawer dividers



Plastic Boxes

Plastic Boxes

Made of high impact polystyrene (HIPS) red plastic, these boxes are for storing small parts. Boxes slip in and out of drawers or plastic box rails for easy loading and dispensing and have label holder slots. Boxes should be ordered to match particular drawer height.



PART NO.	FOR DRAWER NUMBER/HT.	L X W X H	MAX. BOXES PER DRAWER/HOUSING STYLE						
			NW	MP/ST	SC	MW	DW	CL	HS
PB-1*		3" x 3" x 1"	36	48	64	112	136	36	72
PB-2		3" x 3" x 1"	36	48	64	112	136	36	72
PB-3		3" x 6" x 1"	16	24	32	56	68	18	36
PB-4		6" x 6" x 1"	8	12	16	28	32	9	18
PB-5	75	3" x 3" x 2"	36	48	64	112	136	36	72
PB-6	75	3" x 6" x 2"	16	24	32	56	68	18	36
PB-7	75	6" x 6" x 2"	8	12	16	28	32	9	18
PB-8	100	3" x 6" x 3"	16	24	32	56	68	18	36
PB-9	100	6" x 6" x 3"	8	12	16	28	32	9	18
PB-24	75	2" x 4" x 2"	36	54	72	126	156	24	81
PB-8D	divider for PB-8								
PB-24D	divider for PB-24								

*PB-1 box has a fixed center divider that makes 2 compartments – 3" x 1 1/2"

Conductive Plastic Boxes



Made of conductive black high impact polystyrene (HIPS) for storing electrostatically sensitive components or devices. Boxes slip in and out for easy loading and dispensing and have label holder slots. Order to match drawer height.



PART NO.	FOR DRAWER NUMBER/HT.	L X W X H	MAX. BOXES PER DRAWER/HOUSING STYLE						
			NW	MP/ST	SC	MW	DW	CL	HS
PB-1AS		3" x 3" x 1"	36	48	64	112	136	36	72
PB-2AS		3" x 3" x 1"	36	48	64	112	136	36	72
PB-3AS		3" x 6" x 1"	16	24	32	56	68	18	36
PB-4AS		6" x 6" x 1"	8	12	16	28	32	9	18
PB-5AS	75	3" x 3" x 2"	36	48	64	112	136	36	72
PB-6AS	75	3" x 6" x 2"	16	24	32	56	68	18	36
PB-7AS	75	6" x 6" x 2"	8	12	16	28	32	9	18
PB-8AS	100	3" x 6" x 3"	16	24	32	56	68	18	36
PB-9AS	100	6" x 6" x 3"	8	12	16	28	32	9	18
PB-24AS	75	2" x 4" x 2"	36	54	72	126	156	24	81
PB-8ASD	divider for PB-8AS								
PB-24ASD	divider for PB-24AS								

Angled Label Holders for Plastic Boxes



Fits into slot in plastic boxes. Transparent label protectors included.

PART NO.	FOR USE WITH
X280*	plastic boxes (red)
X280-AS	conductive plastic boxes (black)

*not for use with PB-24 box

Grooved Tray Divider

1 1/8" wide x 1" high galvanized steel divider fits into slots in grooved tray to separate and label contents.




PART NO.

2GTD

Grooved Trays

Grooved Trays

These high impact red ABS plastic trays are for individual storage of side sensitive tools such as taps and reamers. Tools are held in place by wedge-shaped grooves which prevent side-to-side movement in the drawer. In 2 parts, each part with end tongues to fit slotted partitions or drawer sidewall. Each 2-part tray is 9 units (153mm) wide x 97mm deep. Sectioned off with D-9 drawer dividers. Larger trays in the set are slotted for clip-on label holders (not included, see page 119). Grooved tray dividers (see to left) not included.



PART NO.	FOR MAXIMUM TOOL DIAMETER	NO. OF GROOVES
PGT-19	5/16" (8mm)	11
PGT-29	9/16" (14mm)	8
PGT-39	3/4" (20mm)	6

Slotted Grooved Trays

Trays are for storage of drills, gauges, mills, etc. Made of durable high impact polystyrene (HIPS) red plastic with end tongues so units snap together to form a continuous tray. Slotted at 9/16" increments, plastic dividers subdivide individual grooves into smaller compartments. Each 6" x 6" tray can have 2, 3, or 4 grooves. Clip-on label holders not included (see page 119).



PART NO.	FOR MAXIMUM TOOL DIAMETER	NO. OF GROOVES	SLOTTED TRAY DIVIDERS	AVERAGE QTY. REQUIRED PER SLOTTED TRAY
			PART NO.	
SGT-4	1 1/4" (33mm)	4	STD-4	5 dividers
SGT-3	1 3/4" (45mm)	3	STD-3	4 dividers
SGT-2	2 3/4" (70mm)	2	STD-2	3 dividers

Conductive Slotted Grooved Trays



Trays are for storage of electrostatically sensitive components and MOS semiconductor devices. Made of conductive black high impact polystyrene (HIPS). Each groove is slotted at 9/16" intervals with end tongues so units snap together to form a continuous tray. Clip-on label holders (see page 119) not included.



PART NO.	FOR MAXIMUM TOOL DIAMETER	NO. OF GROOVES	SLOTTED TRAY DIVIDERS	AVERAGE QTY. REQUIRED PER SLOTTED TRAY
			PART NO.	
SGT-4AS	1 1/4" (33mm)	4	STD-4AS	5 dividers
SGT-3AS	1 3/4" (45mm)	3	STD-3AS	4 dividers

Paper Label Sheets

Perforated sheets of label paper allow printing of labels with Lista Script software that fit perfectly into the wide variety of Lista label-holding tabs and covers. One package of 18.784 drawer handle labels is included with each Lista cabinet.

PART NO.	LABEL SIZE	FOR USE WITH	SHEETS/PKG.	LABELS/SHEET
18.784	210mm x 22mm	all hinged drawer handle covers	5 sheets (A4 size)	30
18.785	47mm x 18mm	DLH-3 label holders	2 sheets (A4 size)	52
18.786	47mm x 12mm	X280 and X280-AS label holders	2 sheets (A4 size)	76
		DLH-2 label holders		
18.787	27mm x 12mm	DLH-1 label holders	2 sheets (A4 size)	133
18.932	52.5mm x 18mm	self-adhesive label holders	2 sheets (A4 size)	52



Milling Cutter Holders

Tools with center holes are put over these holders for non-slip stability in the drawer. Red high-impact plastic holders can be fastened together to any required height and are bolted to perforated drawer bottom. Nuts are included.

PART NO.	FOR ARBOR-HOLE SIZE
CH-1	1/2" (12mm)
CH-2	5/8" (15.5mm)
CH-3	7/8" (21.5mm)
CH-4	1" (25mm)
CH-8	1 1/16" (26.5mm)
CH-5	1 1/4" (31mm)
CH-6	1 1/2" (37.5mm)
CH-9	1 9/16" (39.5mm)
CH-7	2" (49.5mm)



Corrugated Steel Supports

For holding arbors, punches, drifts, etc., with 17 recesses. Held with plain partition. Pressed steel sheet, electrophoretically deposited, stoved enamel. Finished in gray.

PART NO.	LENGTH
X1152	18"



Holding Pins

Galvanized steel rods with screw bottoms are bolted to perforated drawer bottom for positioning and holding irregularly shaped tools. Nuts included.

PART NO.	DIAMETER	HEIGHT
HP-1	1/4" (6mm)	1" (26mm)
HP-2	1/4" (6mm)	2" (52mm)
HP-3	1/4" (6mm)	3" (77mm)



Slotted Tool Supports

These 1/16" thick, 24" long aluminum slotted carriers are perfect for storing wrenches, etc. Bottom strip is bolted to perforated drawer bottom. Fasteners included. Ordered individually.

PART NO.	HEIGHT	SLOT OPENING
X214	1 1/16" (26.5mm)	1/4" (7mm)
X36	1 1/16" (26.5mm)	3/16" (5mm)



Arbor Holders

For horizontally storing tools larger than standard grooved trays. Supports are bolted in pairs to perforated drawer bottom. Elongated slots for fastening bolts allow precise positioning for particular tool diameter. Made of durable high impact red plastic. Fasteners included. Comes in pairs.

PART NO.	SIZE
AH	1" W x 3" D x 2" H
	25mm W x 75mm D x 50mm H



Metric Allen Key Holders

Red high impact plastic trays for sets of allen wrenches 1.5mm to 10mm.

PART NO.	SIZE
AKH	6" wide x 6" deep x 1" high



Molded Collet Holders

For the storage of standard collets in drawers. Trays sit over partition slots on the sides of the drawer, so the full usable width and depth of the drawer may be used. Each collet holder is 12" wide x 9 1/2" deep x 2" high.

PART NO.	HOLDS
CH-25MM/R8-72	(72) R8 collets/ 25mm straight tools
CH-32MM/C5-42	(42) C5 collets/ 32mm straight tools



Collet Holders Per Drawer

DRAWER SIZE	MAX. HOLDERS
NW	2
MP	2
SC	4
MW	6
DW	10
ST	2
HS	3



File Drawer Inserts

Fits into a 300 height drawer and converts it into a useable file drawer for either letter- or legal-sized files.

PART NO.	USE WITH	NO. PER DRAW.	ORIENTA.
FFH19	NW*	1	side-to-side
FFH27	MP	1	side-to-side
	ST	1	front-to-back
	HS	2	front-to-back
FFH36	MP	1	front-to-back
	SC	1	front-to-back
	MW	3	front-to-back
	DW	3	front-to-back


*all NW300N-FFH and NW325N-FFH drawers come with side supports for front-to-back file storage



Plastic Angular Supports

Pairs of supports hold files and small tools. Twelve segments, red only.

PART NO.	SIZE
X1153	3 1/8" W x 17 1/2" D x 1/2" H 80mm W x 445mm D x 12mm H



Drawer Liners

- Non-slip polyester mesh liner protects items from shifting or sliding. Protects drawer bottom from scratches and dents. Liner is non-toxic, washable and treated to inhibit mold and mildew.
- Plastic liners are 1/16" thick, clear only.

PART NO.	FOR USE WITH DRAWER
Mesh liner	
NWMDL	NW
MPMDL	MP, ST
SCMDL	SC
MWMDL	MW
DWMDL	DW
CLMDL	CL
HSMDL	HS
Plastic liner	
NWPDL	NW
MPPDL	MP, ST
SCPDL	SC
MWPDL	MW
DWPDL	DW
HSPDL	HS



Sliding Accessory Tray

Tray fits into any 100 height or higher NW or MP Width drawer and can slide forward or back to allow access to the rest of the drawer contents. For use with 1" high plastic boxes (PB-1, PB-2, PB-3 and PB-4). Plastic boxes must be ordered separately – see page 120.

PART NO.	FOR USE WITH
AT19	NW width drawers
AT27	MP width drawers



Foam Drawer Liners

Shadowed foam drawer insert liners protect, identify and control valuable inventory. Using a 2-layer insert system, the upper blue foam liner cushions tools and components in perfectly-shaped cut-outs, while the bottom yellow rigid foam liner makes it easy to spot when a tool is missing from the drawer.

Foam drawer liner kits consist of the following:

- (5) sheets of 1/2" thick royal blue cross linked oil-resistant Tool Control Foam (polyethylene base, standard density 2#) with self-adhesive back
- (1) sheet of 1" thick royal blue cross linked oil-resistant Tool Control Foam (polyethylene base, standard density 2#) with self-adhesive back
- (6) sheets of 1/8" thick yellow high-density cross linked Tool Control Foam (polyethylene base, standard density 2#)
- (6) vellum sheets for tracing your tools
- (1) Exacto® knife for cutting blue foam
- (1) 18" ruler for measuring
- (1) instruction booklet


PART NO.	DIMEN.	USE WITH DR.
FDL-18X24/LOK	18" x 24"	MP, ST
FDL-24X24/LOK	24" x 24"	SC
FDL-36X18/LOK	36" x 18"	HS

Foam Drawer Liner Sets for Other Lista Drawer Sizes

Foam liner sets may be ordered individually to fit all Lista drawer dimensions. Each set includes:

- (1) sheet of 1/2" or 1" thick royal blue cross linked oil-resistant foam with self-adhesive back
- (1) sheet of 1/8" thick yellow high-density cross linked foam
- (1) instruction booklet

PART NO.	DIMEN.	THICK.	USE W/DRAW.
FDL-MP-1/2IN	18" x 24"	1/2"	MP
FDL-SC-1/2IN	24" x 24"	1/2"	SC
FDL-MW-1/2IN	42 13/16" x 24"	1/2"	MW
FDL-DW-1/2IN	52 3/16" x 24"	1/2"	DW
FDL-ST-1/2IN	24" x 18"	1/2"	ST
FDL-HS-1/2IN	36 1/8" x 18"	1/2"	HS
FDL-MP-1IN	18" x 24"	1"	MP
FDL-SC-1IN	24" x 24"	1"	SC
FDL-MW-1IN	42 13/16" x 24"	1"	MW
FDL-DW-1IN	52 3/16" x 24"	1"	DW
FDL-ST-1IN	24" x 18"	1"	ST
FDL-HS-1IN	36 1/8" x 18"	1"	HS



Other Options

- Foam liners can be custom made to your exact specifications, including designing, cutting and labeling the inserts for your specific tool storage requirements.
- Technical grade foam inserts are available for medical, crime lab or archival storage/ museum applications. This foam does not off-gas, and can be sterilized.
- Contact your Lista representative for details.

Accessories			
Computer cabinet	110		
Mobile	66		
Tool transporters	93		
Allen key holders	121		
Aluminum drawer dividers	119		
Arbor holders	121		
B220 tool transporters	94		
B240 tool transporters	95		
Butcher block top	67, 107		
Cabinet counter tops	107		
Cabinet tops	67		
Casters	66		
CL width shallow depth cabinets			
Bases	59		
Cabinet tops	67		
Doors	61		
Drawers, shelves, roll-out trays	60		
Easy-Order combinations	44-45		
Easy-Order drawer interior sets	47		
Easy-Order mobile combinations	46		
Housings	58		
Lock and keying options	59		
Clip-on label holders	119		
CNC			
Bench Stand	97		
Cabinets	96-97		
Machine tool cabinets	96-99		
Tool holder frames	91-92		
Tool holders	90		
Tool trays	91		
Workbenches	97		
Colors	41, 61, back cover		
Combinations cabinets	63		
Computer cabinets	110		
Accessories	110		
Conductive plastic boxes	120		
Conductive slotted grooved trays	120		
Control Stations	113		
Corrugated steel supports	121		
Counter tops	107		
Doors			
Full depth cabinet	41		
Shallow depth cabinet	61		
Storage Wall	84-85		
Drawer accessories	119-122		
Allen key holders	121		
Aluminum drawer dividers	119		
Arbor holders	121		
Clip-on label holders	119		
Conductive plastic boxes	120		
Conductive slotted grooved trays	120		
Corrugated steel supports	121		
Drawer liners	122		
Drawer partition label holders	119		
File drawer inserts	122		
Foam drawer liners	122		
Grooved trays	120		
Holding pins	121		
How to order	118		
Milling cutter holders	121		
Molded collet holders	121		
Paper label sheets	120		
Plain drawer partitions	119		
Plastic angular supports	122		
Plastic boxes	120		
Sliding accessory trays	122		
Slotted drawer partitions	119		
Slotted grooved trays	120		
Slotted tool supports	121		
Drawer liners			
Mesh	122		
Plastic	122		
Drawer partition label holders	119		
Drawer/retaining options	63		
DW (double width) cabinets			
Bases	39		
Cabinet tops	67		
Doors	41		
Drawers, shelves, roll-out trays	40		
Easy-Order combinations	32-33		
Easy-Order drawer interior sets	35		
Easy-Order mobile combinations	34		
Housings	38		
Lock and keying options	39		
Easy-Order			
Computer cabinets	110		
Machine tool cabinets	96-99		
Tool crib cabinets	100-101		
Tool transporters	94		
B220 tool transporters	94		
B240 tool transporters	95		
File drawer			
Cabinets	111		
Inserts	122		
Foam drawer liners	122		
Folding shelves	66		
Fork truck bases	39, 59		
Frame bases	39, 59		
Full depth cabinets			
Bases	39		
Doors	41		
Drawers, shelves, roll-out trays	40		
Housings	38		
How to order custom	37		
How to order Easy-Order	13		
Lock and keying options	39		
Grooved trays	120		
Handles, mobile	66		
Hanging Shelf Cabinet	66		
Hasp lock	62		
Hinged door shelf cabinets	69		
Hinged lock bar	62		
Holding pins	121		
How to order			
Custom drawer partitions and dividers	118		
Custom full depth cabinets	37		
Custom shallow depth cabinets	57		
Easy-Order full depth cabinets	13		
Easy-Order shallow depth cabs	43		
Storage Wall systems	77		
HS shallow depth cabinets			
Bases	59		
Cabinet tops	67		
Doors	61		
Drawers, shelves, roll-out trays	60		
Easy-Order combinations	52-53		
Easy-Order drawer interior sets	55		
Easy-Order mobile combinations	54		
Housings	58		
Lock and keying options	59		
Individual Drawer Latch (IDL)	63, 82		
Keyless keypad lock	62		
Label holders, shelf	79, 81		
Label sheets	120		
Ladders, Storage Wall	83		
Lock-In-Lock-Out (LILO)	63, 82		
Locks			
Cabinet	62		
Storage Wall	82		
Machine Tool Cabinets	96-99		
Mezzanines	114-115		
Milling cutter holders	121		
Mobile accessories	66		
Mobile bases	39, 59		
Molded collet holders	121		
MP width cabinets			
Bases	39		
Cabinet tops	67		
Doors	41		
Drawers, shelves, roll-out trays	40		
Easy-Order combinations	18-19		
Easy-Order drawer interior sets	21		
Easy-Order mobile combinations	20		
Housings	38		
Lock and keying options	39		
MW (mid-width) cabinets			
Bases	39		
Cabinet tops	67		
Doors	41		
Drawers, shelves, roll-out trays	40		
Easy-Order combinations	28-29		
Easy-Order drawer interior sets	31		
Easy-Order mobile combinations	30		
Housings	38		
Lock and keying options	39		
NW (narrow width) cabinets			
Bases	39		
Cabinet tops	67		
Doors	41		
Drawers, shelves, roll-out trays	40		
Easy-Order combinations	14-15		
Easy-Order drawer interior sets	17		
Easy-Order mobile combinations	16		
File drawer cabinets	111		
Housings	38		
Lock and keying options	39		
Overhead cabinets	104-106		
Housings	105		
Shelves	105		
Stationary riser shelves	106		
Wall mounting kits	106		
Pallet bases	39, 59		
Paper label sheets	120		
Phenolic resin top	67, 107		
Plain drawer partitions	119		
Plastic angular supports	122		
Plastic boxes	120		
Plastic laminate top	67, 107		
Retainer top	67		
SC (standard width) cabinets			
Bases	39		
Cabinet tops	67		
Doors	41		
Drawers, shelves, roll-out trays	40		
Easy-Order combinations	22-24		
Easy-Order drawer interior sets	26-27		
Easy-Order mobile combinations	25		
Housings	38		
Lock and keying options	39		
Shallow depth cabinets			
Bases	59		
Doors	61		
Drawers, shelves, roll-out trays	60		
Housings	58		
How to order custom	57		
How to order Easy-Order	43		
Lock and keying options	59		
Shelf cabinets	69		
Sink cabinets	111		
Sliding accessory trays	122		
Sliding door shelf cabinets	69		
Slotted drawer partitions	119		
Slotted grooved trays	120		
Slotted tool supports	121		
ST shallow depth cabinets			
Bases	59		
Cabinet tops	67		
Doors	61		
Drawers, shelves, roll-out trays	60		
Easy-Order combinations	48-49		
Easy-Order drawer interior sets	51		
Easy-Order mobile combinations	50		
Housings	58		
Lock and keying options	59		
Stainless steel cabinet cover	67		
Stainless steel counter top	107		
Stationary riser shelves	106		
Storage Wall systems			
Bookcases and counter tops	83		
Doors	84-85		
Full depth frames and panels	78		
Full depth roll-out trays	79		
Full depth shelves and accessories	79		
How to order	77		
Ladders	83		
Locking systems	82		
Shallow depth frames and panels	80		
Shallow depth roll-out trays	81		
Shallow depth shelves and accessories	81		
Toolboxes	64-65		
Tool crib cabinets	100-101		
Tool holders, CNC	90		
Tool transporters	92		
Accessories	93		
Easy-Order B220	94		
Easy-Order B240	95		
Tops	67		
Wet clean bases	39, 59		
Workbenches, CNC	97		

Lista Colors



CODE COLOR

BE Beige



CODE COLOR

BB* Bright Blue



CODE COLOR

BK* Black



CODE COLOR

CB Classic Blue




CODE COLOR

GR Dark Gray



CODE COLOR

GG Green



CODE COLOR

LG* Light Gray




CODE COLOR

NR Red



CODE COLOR

SN Sand



CODE COLOR

FW White

** Available with ESD properties. To specify ESD paint, add prefix "ESD" to paint part number. For ESD paint specifications, contact Lista Customer Service.*

Color differences exist between color samples and actual finishes. Please contact your Lista representative for accurate color matching. Custom colors are available and will be quoted on request.



Lista International headquarters and manufacturing facility in Holliston, MA, USA.

For information about Lista's comprehensive line of workbenches, workstations, accessory systems, trolleys and flow racks, ask for our General Workbench and Workspace Furniture Catalog.



Represented by

LISTA
making workspace work®

Lista International Corporation
106 Lowland Street
Holliston, MA 01746-2094
USA

Telephone: (508) 429-1350

Toll-Free: (800) 722-3020

Fax: (508) 626-0353

Internet: www.listaintl.com

E-mail: sales@listaintl.com

ISO 9001 Certified

Product specifications are subject to change without notice and are those in effect at time of shipment.

© 2008 Lista International Corporation Printed in U.S.A.
06-08 125M

Lista®, Making Workspace Work®, Align®, Arlink®, Definite Positioning System®, PrevenTip® and Storage Wall® are registered trademarks of Lista International Corporation.