



LEAD-FREE P/N	DIM "M"	DIM "A"	P.C.B. Thk.
88983-001LF	2.80	11.30	1.6mm
88983-002LF	3.80	12.70	2.4mm
88983-003LF	2.20	10.70	1.6mm



NOTE:

- 1) For p.c. board layout see customer
- 2) PACKAGING SPEC: SEE GS-14-920

1.27u Min. Au.
Positions 1&2
Plating on contact area

rev	ecn no	dr	date
H	LS06-0022	LGO	06/03/06
J	LS08-0057	LGO	2008/02/18
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	☒	tolerance std ISO 406 ISO 1101	projection 	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	Hendrickse	97/11/12	ANGULAR		0.X	±0.1	size
Eng	-	-			0.XX	±0.1	A3
Chr	P.Schalk	92/04/24	0.XX' ±2"	LINEAR	0.XXX	±0.1	Scale
Appr	D.Andrews	92/04/24	Product family		METRAL		5:1
					Spec ref -		ECN LS08-0057
							Rev.
							J
							88983
							CUSTOMER sheet 1 of 1



RA HDR CONT

50ohm MINI COAX

catalog no

dwg no

88983