



### Features:

- ✓ Designed for RG6 Cable
- ✓ Quick three step installation process: Strip, Comb and Push-on.
- ✓ No Crimp tool required

### Materials:

Connector Body: Gold plated brass  
 Ferrule: Gold plated annealed copper  
 Insulator: Delrin

### Ratings:

Impedance: 75 ohms  
 Frequency: 0 to 500 MHz  
 VSWR: 1.5 max  
 Insulation Resistance: 5000 Megohms min.  
 Contact Resistance: 3 Milliohms max.  
 Voltage: \*500Vrms  
 Temperature: -40 to 65 C  
 Durability: 500 matings  
 Cable Retention: 40lbs. min.

*\*Hands free testing* in controlled voltage environment; *For CE compliance*: not intended for hand held use at voltages above 33Vrms/70 Vdc

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060  
 For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)