

PLETRONICS 10.7 MHz MONOLITHIC CRYSTAL FILTER SERIES[®]

[Package Outlines](#)

Part# (Click to Order)	Channel Spacing	# of poles	Passband		Stopband				Ripple	Loss	Terminating Impedance	Package Code
			dB	kHz	dB	kHz	dB	kHz	dB	dB	Ω //pF//pF	
P10M8A	12.5 kHz	2	3	±3.75	18	±15.0			0.5	2.0	1600//4	A-3
P10M8B		4	3	±3.75	40	±12.5			1.0	2.5	1600//2.5//16	A-3X2
P10M8C		6	3	±3.75	45	±8.75	65	±12.5	2.0	3.5	1600//4	C-1
P10M8D		8	3	±3.75	60	±8.75	90	±12.5	2.0	4.0	1600//4	D-1
P10M8E		10	3	±3.75	75	±8.75	90	±10.5	2.0	5.0	1600//4	E-1
P10M12A	20 kHz	2	3	±6.0	20	±25.0			0.5	1.5	2500//2.5	A-3
P10M12B		4	3	±6.0	40	±20.0			1.0	2.0	2200//1.5//8	A-3X2
P10M12C		6	3	±6.0	50	±14.0	65	±20.0	2.0	3.0	3000//1.5	C-1
P10M12D		8	3	±6.0	65	±14.0	90	±20.0	2.0	3.5	3000//1.5	D-1
P10M15A	25 kHz	2	3	±7.5	18	±25.0			0.5	1.5	3000//2	A-3
P10M15B		4	3	±7.5	40	±25.0			1.0	2.0	3000//2//5.5	A-3X2
P10M15C		6	6	±7.5	45	±17.5	65	±25.0	2.0	2.5	3000//2	C-1
P10M15D		8	6	±7.5	60	±15.0	80	±20.0	2.0	3.5	3000//2	D-1
P10M15E		10	6	±7.5	75	±15.0	90	±17.5	2.0	4.0	3000//2	E-1
P10M30A	50 kHz	2	3	±15.0	18	±50.0			0.5	1.5	5000//0	A-3
P10M30B		4	3	±15.0	40	±50.0			1.0	2.0	5500//-1//0	A-3X2
P10M30C		6	6	±15.0	60	±45.0			2.0	2.5	5500//-1	C-1
P10M30D		8	6	±15.0	60	±30.0	80	±40.0	2.0	3.5	5500//-1	D-1
P10N15A	25 kHz	2	3	±7.5	18	±25.0			0.5	1.5	3000//2	A-4

[P10N15B](#)

4

3

 ± 7.5

40

 ± 25.0

1.0

2.0

3000//2//5.5

A-4X2

HOW TO REACH US:

Pletronics, Inc.
19013-36th Avenue West, Suite H
Lynnwood, WA 98036 USA

(425) 776-1880
FAX: (425) 776-2760
email: ple-sales@pletronics.com

-
- ◆ [Home](#)
 - ◆ [Products](#)
 - ◆ [Contact Info](#)
 - ◆ [Company Info](#)
 - ◆ [Distributors](#)
 - ◆ [Representatives](#)
 - ◆ [Browser Settings](#)

Last modified 11/11/99
All specifications subject to change without notice.
Specification sheets and images, copyright 2001 Pletronics, Inc.