



REV	DOCUMENT	CHANGED BY	CHECK
2	0038444	KVS 09APR08	ASD



4 AIRSEARCH MFG. CO. HAS TESTED MICRO SWITCH LISTING IISM2454 AND DETERMINED IT HAS SUCCESSFULLY PASSED 10,000 OPERATIONS AT 30 VDC, 5.0 AMPS RES. AND 3 AMPS IND. AT 75° F ± 10° F AND 375° F ± 10° F
-25° F
REFERENCE AIRSEARCH MFG. CO. FILE: E: RRR: 0076: 0903 - 69

REPLACES

CHARACTERISTICS	ELECTRICAL DATA	DESIGN UNITS: INCH	DRAWN	VK	15 FEB 08	Honeywell			
OPERATING FORCE - - - - 3 - 5 OZ	CONTACT ARRANGEMENT S P D T	TOLERANCES UNLESS NOTED:	CHECK	RJ	15 FEB 08				
RELEASE FORCE - - - - - 1 OZ MIN	30 VOLTS DC RATING	NO PLACE X ±	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
	SEA LEVEL	ONE PLACE .X ±							
DIFFERENTIAL TRAVEL - - .0015 - .0040	INDUCTIVE 3 AMP	TWO PLACE .XX ±	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	REV
OVERTRAVEL - - - - - .005 MIN	RESISTIVE 5 AMP	THREE PLACE .XXX ±				B	I	11SM2454	2
		FOUR PLACE .XXXX ±	RASTER			SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1
		ANGLES ±							
		THIRD ANGLE PROJECTION 							