

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191930171

Status:

Active

Description:

VersaKrimp™ Ring Tongue Terminal for 8 AWG Wire

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Mil-Spec

Product Name

Type

Ring and Spade Terminals

19193

Type I Noninsulated; Class 2

AS20659-108, MS20659-108

VersaKrimp™

Ring

Physical

Barrel Type

Insulation

Material - Plating Mating

Packaging Type

Plating min: Mating (µin)

Plating min: Mating (µm)

Plating min: Termination (µin)

Plating min: Termination (µm)

Stud Size

Termination Interface: Style

Wire Size AWG

Wire Size mm²

Closed - Brazed

None

Tin

Bag

100

2.5

100

2.5

5/16" (M8)

Crimp or Compression

8

0.60 - 10.5

Electrical

CSA

UL

LR18689

E32244

Material Info

Old Part Number

D-351-56

Reference - Drawing Numbers

Sales Drawing

SD-19193-017




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19193Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Putt Pump Dieless Head System	0192860065
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640074400
Die Set (large) for the HHLS Hydraulic Crimper	0192900001
Hand Crimp Tool	0640013900
Manual Putt Pump Hydraulic System, Die set required	0192860117

Manual tool for 0192940008
Crimping non-
insulated 8AWG thru
4/0 Terminals

This document was generated on 02/03/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION