

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	CPFIUG881-CUST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	----------------	-----------	----	------------------	-----------

Description: 36434 BNC twist-on plug RG58
Part No: CPFIUG881
Application: For RG58 Cable
Crimp Tool: N/A
Impedance: 50 Ohms
Frequency Range: 0-4 GHz
Material: Body Zinc Nickel plated
Contact Brass Gold plated
Insulator Teflon
Coupling nut Zinc Nickel plated
RoHS Compliance: Yes
Technical Detail: Refer to Emerson Document P/N 27-0000



DRAWING NO.

CPFIUG881-CUST

REVISIONS

01	OFFICAL RELEASE					2009.09.09
	08-17-09	J	T	T		08:56:08 +0800

REF 1/4-28UNEF

9.5
(.375)HEX Ø (5.4
(.211))19.2
(.756)36
(1.416)REF Ø 14.5
(.571)

DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
		JEAN.JIN	08-17-09
DECIMALS	mm	CHECKED BY	DATE
X	± 0.5	TERRY.W	08-17-09
X.X	± 0.2	APPROVED BY	DATE
X.XX	± 0.1	THOMAS	08-17-09
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

		Connectivity Solutions	
TITLE		36434 BNC TWIST-ON PLUG RG58	
SHEET	DRAWING NO.	SIZE	
1 OF 1	CPFIUG881-CUST	A	

CUSTOMER COPY

5

4

3

2

1