

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT 2011

BY TE CONNECTIVITY.

ALL RIGHTS RESERVED.









LOC
DWDIST
—

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECR-11-023831	23NOV11	AW	WK

NOTES:

- MATERIAL:
HOUSING: LCP, UL94 V-0, BLACK COLOR.
ACTUATOR: LCP, UL94 V-0, NATURAL COLOR.
CONTACTS: PHOSPHOR BRONZE.
PEGS: PHOSPHOR BRONZE.
- FINISH:
CONTACTS: GOLD FLASH PLATED ON CONTACT AREA AND SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED $1.27\mu\text{m}$ [$50\mu''$] MIN. NICKEL.
PEGS: GOLD FLASH PLATED OVER $1.27\mu\text{m}$ [$50\mu''$] MIN. NICKEL
- REFLOW SOLDER CAPABLE TO 260°C PER TEC-109-201, CONDITION B.
- SUBSTANCE RESTRICTIONS FOR LOW HALOGEN (BY WEIGHT):
 - BROMINE (Br) ≤ 900 PPM (0.09%)
 - CHLORINE (Cl) ≤ 900 PPM (0.09%)
 - TOTAL CONCENTRATION OF CHLORINE (Cl) + BROMINE (Br) ≤ 1500 PPM (0.15%)



21.60	22.25	21.00	21.65	20.40	22.80	71	7-2041390-1
15.60	16.25	15.00	15.65	14.40	16.80	51	5-2041390-1
13.80	14.45	13.20	13.85	12.60	15.00	45	4-2041390-5
12.00	12.65	11.40	12.05	10.80	13.20	39	3-2041390-9
F	E	D	C	B	A	NO. OF CONTACTS	PART NUMBER
DIMENSIONS							

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 15JUN2011		TE Connectivity							
		CHK S. CHIEN 15JUN2011									
		APVD W. KODAMA 15JUN2011									
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		0 PLC ± —		FPC CONNECTOR, 0.3 PITCH, ZIF, BOTTOM CONTACT							
		1 PLC ± 0.3									
		2 PLC ± 0.2									
		3 PLC ± 0.15									
		4 PLC ± —									
ANGLES ± —		PRODUCT SPEC 108-57877									
		APPLICATION SPEC —									
MATERIAL		FINISH		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
SEE NOTE		SEE NOTE		WEIGHT —		A3		00779		C-2041390	
CUSTOMER DRAWING				SCALE —		SHEET 1 OF 2		REV C			

4

3

2

1

LOC	DIST	REVISIONS				
DW	—	P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1		

NOTES:

1. MATERIAL:
BOX: FIBREBOARD, CORRUGATED, DOUBLE WALL.
COVER TAPE: PET, TRANSPARENT.
CARRIER TAPE: POLYSTYRENES, TRANSPARENT.
REEL: HIPS, BLUE COLOR.
BAG: POLYETHYLENES, TRANSPARENT.
2. EACH BAG SHALL BE INCLUDED DESICCANT.
3. PEELING STRENGTH: 0.1 ~ 1.3 N (10 ~ 130 GRAMS).
4. PEELING SPEED: 300 mm/min.

D

D

C






C

B

B

A

A



27000	6	4500	4.56	9.56	71
45000	10	4500	4.41	9.41	51
45000	10	4500	3.96	8.96	45
45000	10	4500	3.42	8.42	39
PCS /BOX	REELS /BOX	PCS /TAPE	N/W (Kg)	G/W (Kg)	NO. OF CONTACTS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 15JUN2011	 TE Connectivity		
		CHK S. CHIEN 15JUN2011			
		APVD W. KODAMA 15JUN2011	NAME		
DIMENSIONS: MM		PRODUCT SPEC	FPC CONNECTOR, 0.3 PITCH, ZIF, BOTTOM CONTACT		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC			
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C=2041390
			CUSTOMER DRAWING		RESTRICTED TO
			SCALE	SHEET 2 OF 2	REV C