

Customer Information Sheet

DRAWING No.: M20-890XX05

SHEET 2 OF 2


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION




ALL DIMENSIONS IN mm



SPECIFICATION:

MATERIAL:
MOULDING - NYLON 6T UL94V-0, BLACK
CONTACT - BRASS
FINISH:
CONTACT - GOLD
ELECTRICAL:
CURRENT RATING - 3.0A
CONTACT RESISTANCE - 20 MILLIOHMS MAX
INSULATION RESISTANCE - 5,000 MEGOHMS MIN
DIELECTRIC STRENGTH - 500V AC/MINUTE
ENVIRONMENTAL:
TEMPERATURE RANGE - -40°C TO $+105^{\circ}\text{C}$
FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C001XX (LATEST ISSUE)

ORDER CODE:
M20-890XX05
No. OF WAYS
03 TO 36



RECOMMENDED PAD LAYOUT

JAE	2	15.04.03	7405
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>[Signature]</i>			
CHECKED: <i>[Signature]</i>			
DRAWN: J. EVANS			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN INC U.S.A. TEL: (812) 285 0055 FAX: (812) 285 0056	HARWIN PLC U.K. TEL: 023 9237 0451 FAX: 023 9231 4590	HARWIN PTE SINGAPORE TEL: 65 7794909 FAX: 65 7793868
--	--	---

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION

TOLERANCES

X. - $\pm 1\text{mm}$
X.X - $\pm 0.25\text{mm}$
X.XX - $\pm 0.10\text{mm}$
X.XXX - $\pm 0.01\text{mm}$
ANGLES - $\pm 5^{\circ}$
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:

2.54mm PITCH SIL HORIZONTAL
SMT PIN HEADER ASSEMBLY

DRAWING NUMBER:

M20-890XX05

SHT
2
OF
2