


EPIC® Rectangular Connectors

MC Series Plugs & Receptacles




3 CONTACT HIGH VOLTAGE MODULES




Rated Voltage:
1000V

Rated Current:
50A




Plug




Plug	Receptacle
10399800	10399900

Contacts Sold Separately

Receptacle



MACHINE CONTACTS: DIAMETER 3.6 MM



Bags of 100				
mm²	AWG	Silver		Stripping Length (mm)
		Pin	Socket	
1.5	16	1121070C	1121570C	10
2.5	14	1121060C	1121560C	10
4.0	12	1121000C	1121500C	10
6.0	10	1121010C	1121510C	10
10	8	1121020C	1121520C	10

Part number= 1 contact

TOOLS




Locator
11147210



Crimp Dies
1.5 - 2.5: 11147110
4.0 - 10: 11147120



Crimp Tool
11147000



Removal Tool
11171100