


SPECIFICATIONS:

Rating: DC30V 1A ;

Contact resistance: 100m Ω (Max.) ;

Insulation resistance: DC500V 100M Ω (Min.) ;

Withstand voltage: AC 1000V for 1 minute ;

Operating force: 700 $\pm$ 150g ;

Operating Temp.: -25 $^{\circ}$ C ~ +65 $^{\circ}$ C

Life cycle: 20,000 cycles ;

Total Travel: 1.5 $\pm$ 0.3 mm .

MATERIAL:

Frame:Nylon66,UL rated:94V-2 Min. ;


Cap:POM ;

Terminal:Brass,Silver or Tin plated .

Function:

ON(P-6)-OFF-ON (P-1)-OFF

Cap Color: Black



P.C.B. LAYOUT

RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 3-22-12

Rev. 2

Unit: mm

Checked By: *G. Gold*

2 | Added Operating Temp. 11-13-12.

Title:

PUSH BUTTON SWITCH

CW P/N:

GPTS203312B