


Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: .5A/125VAC
- Electrical Life: 5,000 cycles
- Insulation resistance: 500VDC @ 100M Ω min.
- Dielectric strength: 500VAC for one minute
- Contact resistance: 50m Ω max.

Mechanical Specifications:

- Circuit: 2P SPST On-(Off)

Materials:

- Terminals: silver plated brass
- Spring: piano wire
- Stopper, knob: ABS
- Contacts: tin plated brass
- Body: plastic
- Bushing: nickel plated brass
- Nut: nickel plated steel
- Washer: uni-chromium plated steel

Note:

- RoHS Compliant

Mouser Stock No.	Button Color
104-0014	Green
104-0015	Red
104-0016	Black

Pushbutton Switches
104-0014, 104-0015, 104-0016

Mountain Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[104-0016](#) [104-0014](#)