



Long Barrel Copper Lug

T&B Catalog Number:

LCN6-12

78378603272

Status:

Active

Description:

Copper Two-Hole Lug - Straight Long Barrel - max 35KV, 6 Str. Wire, 1/2 Bolt Size, Tin Plated, Blue

Features

Made of high-conductivity seamless copper tubing.
Tin plated for corrosion resistance.

Specifically chamfered barrel for ease of installation.

Color-coded for matching die identification.

UL Listed for AWG conductor when installed with Blackburn, Burndy, T&B or Andersons Tools.

Complies with Subpart 111.60-17 of Federal Register's Coast Guard Electrical Engineering Rules and Regulations.

General

Material	Copper
Finish	Tin Plated
Wire Size	6 Str.
Number of Studs	2
Stud Size	1/2
Bolt Hole Spacing	1 3/4
Tongue Angle	Straight
Barrel Length	Long
Barrel Shape	Standard
Die Color	Blue

Dimension Information

A (inches)	25/32
B (inches)	3
C (inches)	1/2
L (inches)	4 5/32
T (inches)	3/32
W (inches)	7/8

Specifications

Voltage Rating	35KV
----------------	------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	16.2 lbs. per 100

Notes

For use with copper conductor: AWG, stranded, flexible cable, welding cable and portable cord. Specially designed for industrial and building applications.

Certifications

RoHS Compliance Yes

Certifications

File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com