

# Product Specifications



219584-2 | C6 PR4 UTP PVC WHITE SOLID RiB305m

**Copper Twisted Pair Cable, Category 6, 4-pair, unshielded, white**

## Body Features

Jacket Material	PVC
Cable Configuration	UTP
Jacket Color	White
Conductor Material	Copper
Insulation Material	PE

## Configuration Features

Number of Pairs	4
Number of Conductors	8

## Dimensions

Overall Outside Diameter	5.700 mm   0.224 in
Conductor Diameter	.485 – .546 mm
Length	305.000 m   1000.656 ft
Wire Diameter	5.495 mm   0.216 in
Wire Size (CMA)	.205 mm <sup>2</sup>   24 AWG

## Industry Standards

Flammability Rating	PVC
---------------------	-----

## Packaging Features

Packaging Method	Reel-in-a-Box
Packaging Quantity	1000

## Product Availability

Region	EMEA
--------	------

## Product Type Features

Performance Category	Category 6
Cable Style	Simplex
Cable Type	Twisted Pair
Product Classification	Cable - ISO/IEC Category
Product Type	Cable
Shielded	No
Wire/Cable Type	Twisted Pair

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant