




FEATURES:

- Ideal for providing jumper wires between small components.

MATERIALS:

Conn: 1st End - Minipincer® Test Clip

Material: Beryllium copper contact.

Finish: Gold plated.

Insulation: Nylon

Wire: 20 AWG, 41 x 36 t.c. PVC insulated, 2.2 (.087) O.D.

Marking: "POMONA 5419-XX-"

Conn: 2nd End – Same as first

RATINGS:

Operating Temperature: +80°C. (+176°F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 300 WVDC Max.

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 5419-XX-*

XX – Cable Lengths, Standard Lengths: 8" (203), 12" (305), 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1524).

*= Color, -0 Black, -2 Red

Ordering Example: 5419-60-2 Indicates 60" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA