


REV. 0
DCO 17200

COIL: @ 25°C	
RESISTANCE	10,000 OHMS ±10%
NOMINAL VOLTAGE	40.0 VDC
MUST OPERATE	2.0 mADC
MUST RELEASE	

CUSTOMER DATA SHEET



TERMINAL VIEW

ENVIRONMENT:	
VIBRATION	10 CPS TO 2000 CPS @ 15 g's
SHOCK	50 g's 11 ± 1 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

CONTACT RATING:	LOW LEVEL - 2A
	@ 28 VDC RESISTIVE - 5A @ 115 VAC
	RESISTIVE 100,000 OPERATIONS

NOTES: OPERATE TIME 15 MS MAX.
RELEASE TIME 10 MS MAX.
CONTACT BOUNCE 2 MS MAX.

DR. BSH 8/15/01 CK. TLG 8-15-01

CUST. CII STD
CUST. NO. REV.

"SF" RELAY

CII Technologies
advanced control electronic solutions

SF5101Y00

NOT the LATEST REVISION