

Path: [Home](#) > [Rack Index](#) > SOHO Knockdown - Desk Rack Cabinets (RCSC Series)



(click to enlarge)



Assembly  
Instructions

### ***Features:***

- Perfect for SOHO (Small Office, Home Office) applications for servers, storage & networking...
- Supplied unassembled (four cabinet pieces & four rails), requires only a phillips screwdriver to assemble...
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included) - see assembly instructions...
- Shipped in a flat pack container for handling ease & protection (see photo below)...
- Heavy duty, 16-gauge steel, 19" rack mount cabinet...
- 12U version is 25" high (fits under most desks)...
- Expandable in the future - easily stacks and/or gangs to other units (see accessories below). Requires baying kit (**RCSCBAY**) to lock cabinets together...
- Panel rails are infinitely adjustable (front to back), square hole punched for cage-nuts to full EIA hole centers (5/8 - 5/8 - 1/2 inch spacing)...
- Includes two pairs of rails (for rear support of heavier equipment), a starter pack of (50) 10-32 cagenuts & matching 1421ABK black screws...
- Overall width of 24" provides ample space for most cabling requirements...
- Generous cable-entry "punch-outs" with gasket strip material included...
- Optional doors (perforated to meet server manufacturers air flow requirements), fans and casters available...
- Front & back lip is .75" so usable depth is reduced by 1.5"
- Recommended maximum weight - 1,500 pounds...
- Rugged textured black powder paint finish.

### **24" Deep Models** (Maximum Mounting Depth = 23")

Part Number	Color		Drawing File Size		.zip File Size	Panel Height		Overall Height No Casters (Inches)
						Inches	Units	
<b>RCSC1902124BK1</b>	Black		84K		98K	<b>21.00</b>	12	25
<b>RCSC1904224BK1</b>	Black		102K		128K	<b>42.00</b>	24	46

### **31" Deep Models** (Maximum Mounting Depth = 30.0")

Part Number	Color		Drawing File Size		.zip File Size	Panel Height		Overall Height No Casters (Inches)
						Inches	Units	
<b>RCSC1902131BK1</b>	Black		86K		99K	<b>21.00</b>	12	25
<b>RCSC1904231BK1</b>	Black		97K		115K	<b>42.00</b>	24	46

**36" Deep Models**

\* (Maximum Mounting Depth = 30.0")


Part Number	Color		Drawing File Size		.zip File Size	Panel Height		Overall Height No Casters (Inches)
						Inches	Units	
<b>RCSC1902136BK1</b>	Black		87K		98K	<b>21.00</b>	12	25
<b>RCSC1904236BK1</b>	Black		99K		117K	<b>42.00</b>	24	46

\* 36" deep models have extended cable space in the back


---




PART No. RCSC1904231




L.S. VIEW




FRONT VIEW




BOTTOM VIEW



TOP VIEW



R.S. VIEW



REAR VIEW

